

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027765

Luminaire Tested: S125DIP-B375D1090UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027765
REPORT IS A COMBINATION OF REPORTS P1001851 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D1090UB30-4F0-XX-W2A-F4
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5171.5 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027765

CATALOG NUMBER: S125DIP-B375D1090UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1027765

CATALOG NUMBER: S125DIP-B375D1090UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37
1	93	89	85	82	83	80	76	74	62	60	58	47	45	44	32	31	31
2	85	77	72	67	75	70	65	60	55	51	48	41	39	37	28	27	26
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22
4	70	60	52	47	63	54	48	42	43	38	34	32	29	27	22	20	19
5	65	53	46	40	58	48	41	36	38	33	30	29	25	23	20	18	16
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	24	20	18	17	14	13
8	51	39	31	26	45	35	29	24	28	23	20	21	18	16	15	13	11
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10
10	44	32	25	21	39	29	23	19	24	19	16	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3643	3643	3643
5°	3643	3559	3565
10°	3613	3477	3466
15°	3566	3380	3349
20°	3501	3266	3215
25°	3433	3143	3071
30°	3350	3014	2920
35°	3261	2879	2751
40°	3169	2737	2600
45°	3070	2598	2439
50°	2961	2441	2253
55°	2853	2267	2081
60°	2724	2084	1882
65°	2570	1872	1675
70°	2414	1629	1437
75°	2149	1341	1161
80°	1832	1002	854
85°	1412	593	470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3070 cd/sqm

TEST NUMBER: P1027765

CATALOG NUMBER: S125DIP-B375D1090UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	1.0
10°-20°	151.6	2.9
20°-30°	223.8	4.3
30°-40°	261.1	5.0
40°-50°	262.2	5.1
50°-60°	230.2	4.5
60°-70°	171.4	3.3
70°-80°	97.9	1.9
80°-90°	30.2	0.6
90°-100°	369.2	7.1
100°-110°	766.8	14.8
110°-120°	716.2	13.8
120°-130°	579.6	11.2
130°-140°	465.6	9.0
140°-150°	351.5	6.8
150°-160°	247.5	4.8
160°-170°	145.9	2.8
170°-180°	47.4	0.9
0°-30°	429.0	8.3
0°-40°	690.0	13.3
0°-60°	1182.4	22.9
0°-90°	1482.0	28.7
90°-120°	1852.2	35.8
90°-150°	3248.8	62.8
90°-180°	3690.0	71.4
0°-180°	5171.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	569	569	569	569	569	
5°	568	567	562	566	566	54
15°	541	540	535	537	537	153
25°	491	489	483	484	483	226
35°	424	422	416	414	410	265
45°	347	346	340	335	333	268
55°	264	263	257	253	250	236
65°	179	178	173	169	167	177
75°	95	94	92	90	89	101
85°	25	25	25	25	24	27
90°	1	9	16	21	23	4
95°	33	96	876	397	232	34
105°	112	156	717	1411	1310	118
115°	200	241	575	1240	1459	197
125°	277	324	552	986	1150	246
135°	324	390	548	827	955	252
145°	378	432	550	684	753	237
155°	431	464	536	605	632	198
165°	470	483	514	545	554	133
175°	489	489	493	499	497	46
180°	490	490	490	490	490	

TEST NUMBER: P1027765

CATALOG NUMBER: S125DIP-B375D1090UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	568.6	568.6	568.6	568.6	568.6
2.5°	570.4	569.1	564.6	569.1	568.6
5°	567.7	566.8	562.3	566.4	565.9
7.5°	563.7	562.8	557.8	561.9	561.4
10°	557.8	556.9	552.0	555.6	555.1
12.5°	550.6	548.8	544.3	547.0	547.0
15°	541.2	539.8	534.9	537.1	537.1
17.5°	531.3	529.0	524.1	526.8	524.5
20°	518.2	517.3	511.5	514.6	512.4
22.5°	505.2	503.4	498.0	499.8	498.4
25°	491.3	489.0	483.2	484.1	482.7
27.5°	475.1	473.7	467.9	468.3	467.0
30°	459.3	458.0	451.2	450.3	449.0
32.5°	442.2	440.0	434.1	432.3	429.6
35°	424.2	422.4	416.1	413.9	410.3
37.5°	405.8	403.5	397.7	394.5	392.3
40°	386.9	384.6	378.3	374.3	372.9
42.5°	366.6	364.8	358.5	354.9	352.7
45°	347.3	345.5	340.1	334.7	333.3
47.5°	326.2	326.6	319.9	314.5	311.3
50°	305.9	304.6	299.2	293.3	290.2
52.5°	285.2	284.3	278.5	273.5	269.9
55°	264.5	263.2	256.9	252.8	249.7
57.5°	242.5	242.0	236.6	231.2	229.9
60°	221.8	220.0	215.0	210.5	207.4
62.5°	200.2	198.8	194.8	189.8	187.6
65°	178.6	177.7	172.7	168.7	166.9
67.5°	157.5	155.7	152.1	148.5	147.6
70°	137.7	135.4	131.4	128.7	126.9
72.5°	116.1	114.7	112.5	109.3	107.5
75°	94.9	94.0	91.8	90.4	88.6
77.5°	75.1	74.7	73.3	72.4	71.1
80°	56.7	56.7	55.8	55.3	54.4
82.5°	40.5	39.6	39.6	38.7	38.7
85°	24.7	25.2	25.2	24.7	23.8
87.5°	12.1	12.1	11.7	11.7	10.8
90°	1.0	8.9	15.8	20.8	22.7
92.5°	14.8	81.0	394.4	105.2	73.1
95°	32.6	96.4	875.7	397.3	232.3
97.5°	50.4	104.3	945.9	717.5	509.0
100°	69.2	119.6	892.5	1014.0	770.9
102.5°	89.9	136.9	798.6	1265.1	1063.5
105°	111.7	156.2	716.6	1410.8	1309.6
107.5°	132.4	176.4	655.3	1451.8	1457.8
110°	155.2	197.6	614.8	1412.8	1525.0

TEST NUMBER: P1027765

CATALOG NUMBER: S125DIP-B375D1090UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	177.9	219.0	591.0	1331.3	1517.1
115°	199.6	240.6	575.2	1239.9	1458.8
117.5°	219.4	262.9	566.3	1156.9	1370.8
120°	239.2	284.2	560.4	1087.2	1285.8
122.5°	259.9	305.0	555.5	1031.4	1210.7
125°	276.7	324.2	551.5	986.4	1149.5
127.5°	290.6	343.0	549.5	947.8	1093.1
130°	303.4	360.8	547.5	908.8	1048.6
132.5°	313.3	376.5	547.5	866.8	1004.2
135°	324.2	389.9	547.5	826.8	954.7
137.5°	338.0	402.2	548.5	784.8	903.4
140°	349.9	412.6	549.5	746.2	849.0
142.5°	363.7	422.6	550.5	713.1	798.6
145°	377.6	432.4	549.5	684.4	753.1
147.5°	392.4	441.3	547.5	659.7	712.6
150°	405.2	449.2	544.6	639.5	680.0
152.5°	419.1	457.1	540.6	622.2	654.3
155°	430.9	463.6	535.7	605.3	631.6
157.5°	441.8	470.0	530.7	589.6	610.8
160°	452.7	475.0	525.8	573.8	590.0
162.5°	461.6	479.8	519.9	559.4	571.3
165°	470.5	483.3	513.9	545.0	553.5
167.5°	476.4	485.3	508.0	531.8	536.7
170°	482.3	487.8	503.1	518.9	521.8
172.5°	486.3	488.7	497.1	508.5	508.0
175°	489.2	489.2	493.2	499.1	497.1
177.5°	491.2	489.2	490.2	493.2	490.2
180°	490.2	490.2	490.2	490.2	490.2

(END OF REPORT)