

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028023

Luminaire Tested: S125DIP-B610D1270UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028023
REPORT IS A COMBINATION OF REPORTS P1002187 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D1270UB27-4F0-XX-W2A-F4
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6767.8 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028023

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1028023

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	34	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	35	30	28	26
4	72	61	54	48	65	56	49	44	45	40	37	36	32	30	27	25	23
5	66	54	47	41	59	50	43	38	41	35	31	32	28	26	24	22	20
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17
7	56	44	36	31	51	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6075	6075	6075
5°	6075	5934	5946
10°	6025	5799	5780
15°	5947	5636	5585
20°	5839	5447	5362
25°	5725	5241	5122
30°	5586	5027	4870
35°	5438	4802	4587
40°	5285	4564	4335
45°	5119	4332	4068
50°	4937	4070	3757
55°	4757	3781	3470
60°	4542	3475	3137
65°	4285	3122	2793
70°	4025	2716	2396
75°	3584	2235	1937
80°	3054	1670	1425
85°	2361	988	786

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5119 cd/sqm

TEST NUMBER: P1028023

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.5	1.3
10°-20°	252.7	3.7
20°-30°	373.1	5.5
30°-40°	435.3	6.4
40°-50°	437.2	6.5
50°-60°	383.8	5.7
60°-70°	285.9	4.2
70°-80°	163.3	2.4
80°-90°	49.4	0.7
90°-100°	430.0	6.4
100°-110°	893.1	13.2
110°-120°	834.2	12.3
120°-130°	675.0	10.0
130°-140°	542.4	8.0
140°-150°	409.4	6.0
150°-160°	288.2	4.3
160°-170°	169.9	2.5
170°-180°	55.2	0.8
0°-30°	715.3	10.6
0°-40°	1150.7	17.0
0°-60°	1971.7	29.1
0°-90°	2470.3	36.5
90°-120°	2157.3	31.9
90°-150°	3784.1	55.9
90°-180°	4298.0	63.5
0°-180°	6767.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	948	948	948	948	948	
5°	947	945	938	944	944	90
15°	902	900	892	896	896	254
25°	819	815	806	807	805	377
35°	707	704	694	690	684	443
45°	579	576	567	558	556	446
55°	441	439	428	422	416	394
65°	298	296	288	281	278	295
75°	158	157	153	151	148	169
85°	41	42	42	41	40	45
90°	1	10	18	24	26	5
95°	38	112	1020	463	270	40
105°	130	182	835	1643	1525	137
115°	232	280	670	1444	1699	229
125°	322	378	642	1149	1339	286
135°	378	454	638	963	1112	293
145°	440	504	640	797	877	276
155°	502	540	624	705	736	231
165°	548	563	599	635	645	154
175°	570	570	574	581	579	54
180°	571	571	571	571	571	

TEST NUMBER: P1028023

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	948.2	948.2	948.2	948.2	948.2
2.5°	951.2	949.0	941.5	949.0	948.2
5°	946.7	945.2	937.7	944.5	943.7
7.5°	940.0	938.5	930.2	937.0	936.2
10°	930.2	928.7	920.5	926.5	925.7
12.5°	918.2	915.2	907.7	912.2	912.2
15°	902.5	900.2	892.0	895.7	895.7
17.5°	886.0	882.2	874.0	878.5	874.7
20°	864.2	862.7	853.0	858.2	854.5
22.5°	842.5	839.5	830.4	833.4	831.2
25°	819.2	815.4	805.7	807.2	804.9
27.5°	792.2	789.9	780.2	780.9	778.7
30°	765.9	763.7	752.4	750.9	748.7
32.5°	737.4	733.7	723.9	720.9	716.4
35°	707.4	704.4	693.9	690.2	684.2
37.5°	676.7	672.9	663.2	657.9	654.2
40°	645.2	641.4	630.9	624.1	621.9
42.5°	611.4	608.4	597.9	591.9	588.1
45°	579.1	576.1	567.1	558.1	555.9
47.5°	543.9	544.6	533.4	524.4	519.1
50°	510.1	507.9	498.9	489.1	483.9
52.5°	475.6	474.1	464.4	456.1	450.1
55°	441.1	438.9	428.4	421.6	416.3
57.5°	404.3	403.6	394.6	385.6	383.3
60°	369.8	366.8	358.6	351.1	345.8
62.5°	333.8	331.6	324.8	316.6	312.8
65°	297.8	296.3	288.1	281.3	278.3
67.5°	262.6	259.6	253.6	247.6	246.1
70°	229.6	225.8	219.1	214.6	211.6
72.5°	193.5	191.3	187.5	182.3	179.3
75°	158.3	156.8	153.0	150.8	147.8
77.5°	125.3	124.5	122.3	120.8	118.5
80°	94.5	94.5	93.0	92.3	90.8
82.5°	67.5	66.0	66.0	64.5	64.5
85°	41.3	42.0	42.0	41.3	39.8
87.5°	20.3	20.3	19.5	19.5	18.0
90°	1.2	10.4	18.4	24.2	26.5
92.5°	17.3	94.4	459.3	122.6	85.2
95°	38.0	112.2	1020.0	462.8	270.5
97.5°	58.7	121.4	1101.7	835.8	592.9
100°	80.6	139.3	1039.5	1181.2	897.9
102.5°	104.8	159.4	930.2	1473.5	1238.7
105°	130.1	181.9	834.6	1643.4	1525.3
107.5°	154.3	205.5	763.2	1691.1	1698.0
110°	180.7	230.2	716.0	1645.6	1776.3

TEST NUMBER: P1028023

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	207.2	255.0	688.4	1550.6	1767.1
115°	232.5	280.3	670.0	1444.2	1699.2
117.5°	255.6	306.2	659.6	1347.5	1596.7
120°	278.6	331.0	652.7	1266.4	1497.7
122.5°	302.8	355.2	647.0	1201.3	1410.2
125°	322.3	377.6	642.4	1148.9	1338.8
127.5°	338.5	399.4	640.1	1104.0	1273.2
130°	353.4	420.2	637.8	1058.5	1221.4
132.5°	364.9	438.6	637.8	1009.6	1169.6
135°	377.6	454.2	637.8	963.0	1112.1
137.5°	393.7	468.6	638.9	914.0	1052.2
140°	407.5	480.6	640.1	869.2	988.9
142.5°	423.6	492.1	641.2	830.6	930.2
145°	439.8	503.6	640.1	797.2	877.2
147.5°	457.0	514.0	637.8	768.4	830.0
150°	472.0	523.2	634.3	744.8	792.0
152.5°	488.1	532.4	629.7	724.7	762.1
155°	501.9	540.0	623.9	705.1	735.6
157.5°	514.6	547.4	618.2	686.7	711.4
160°	527.2	553.2	612.4	668.2	687.3
162.5°	537.6	558.9	605.5	651.6	665.4
165°	548.0	563.0	598.6	634.9	644.7
167.5°	554.9	565.2	591.7	619.3	625.1
170°	561.8	568.1	586.0	604.4	607.8
172.5°	566.4	569.2	579.1	592.3	591.7
175°	569.8	569.8	574.4	581.4	579.1
177.5°	572.1	569.8	571.0	574.4	571.0
180°	571.0	571.0	571.0	571.0	571.0

(END OF REPORT)