

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027792

Luminaire Tested: S125DIP-B375D1090UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027792
REPORT IS A COMBINATION OF REPORTS P1001878 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D1090UB50-4F0-XX-W2A-F4
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4972.2 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027792

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1027792

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37
1	93	89	85	82	83	80	76	74	62	60	58	47	45	44	32	31	31
2	85	77	72	67	75	70	65	60	55	51	48	41	39	37	28	27	26
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22
4	70	60	52	47	63	54	48	42	43	38	34	32	29	27	22	20	19
5	65	53	46	40	58	48	41	36	38	33	30	29	25	23	20	18	16
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	24	20	18	17	14	13
8	51	39	31	26	45	35	29	24	28	23	20	21	18	16	15	13	11
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10
10	44	32	25	21	39	29	23	19	24	19	16	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3503	3503	3503
5°	3503	3422	3428
10°	3474	3343	3333
15°	3428	3249	3221
20°	3367	3141	3091
25°	3300	3022	2953
30°	3221	2898	2808
35°	3136	2769	2645
40°	3047	2632	2500
45°	2952	2498	2346
50°	2847	2346	2166
55°	2743	2180	2001
60°	2619	2004	1809
65°	2471	1800	1611
70°	2321	1566	1382
75°	2067	1289	1117
80°	1761	962	821
85°	1361	569	452

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2952 cd/sqm

TEST NUMBER: P1027792

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	1.0
10°-20°	145.7	2.9
20°-30°	215.1	4.3
30°-40°	251.0	5.0
40°-50°	252.1	5.1
50°-60°	221.3	4.5
60°-70°	164.8	3.3
70°-80°	94.1	1.9
80°-90°	29.1	0.6
90°-100°	354.9	7.1
100°-110°	737.2	14.8
110°-120°	688.6	13.8
120°-130°	557.2	11.2
130°-140°	447.7	9.0
140°-150°	337.9	6.8
150°-160°	237.9	4.8
160°-170°	140.2	2.8
170°-180°	45.6	0.9
0°-30°	412.5	8.3
0°-40°	663.5	13.3
0°-60°	1136.8	22.9
0°-90°	1424.9	28.7
90°-120°	1780.8	35.8
90°-150°	3123.6	62.8
90°-180°	3547.0	71.3
0°-180°	4972.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	547	547	547	547	547	
5°	546	545	541	545	544	52
15°	520	519	514	516	516	147
25°	472	470	464	465	464	217
35°	408	406	400	398	394	255
45°	334	332	327	322	320	257
55°	254	253	247	243	240	227
65°	172	171	166	162	160	170
75°	91	90	88	87	85	97
85°	24	24	24	24	23	26
90°	1	9	15	20	22	4
95°	31	93	842	382	223	33
105°	107	150	689	1356	1259	113
115°	192	231	553	1192	1403	189
125°	266	312	530	948	1105	236
135°	312	375	526	795	918	242
145°	363	416	528	658	724	228
155°	414	446	515	582	607	191
165°	452	465	494	524	532	127
175°	470	470	474	480	478	45
180°	471	471	471	471	471	

TEST NUMBER: P1027792

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	546.7	546.7	546.7	546.7	546.7
2.5°	548.5	547.2	542.8	547.2	546.7
5°	545.9	545.0	540.7	544.6	544.1
7.5°	542.0	541.1	536.3	540.2	539.8
10°	536.3	535.5	530.7	534.2	533.8
12.5°	529.4	527.7	523.4	526.0	526.0
15°	520.3	519.0	514.3	516.5	516.5
17.5°	510.8	508.7	503.9	506.5	504.3
20°	498.3	497.4	491.8	494.8	492.7
22.5°	485.7	484.0	478.8	480.6	479.3
25°	472.3	470.2	464.5	465.4	464.1
27.5°	456.8	455.5	449.8	450.3	449.0
30°	441.6	440.3	433.8	433.0	431.7
32.5°	425.2	423.0	417.4	415.7	413.1
35°	407.9	406.2	400.1	397.9	394.5
37.5°	390.1	388.0	382.4	379.3	377.2
40°	372.0	369.8	363.8	359.9	358.6
42.5°	352.5	350.8	344.7	341.3	339.1
45°	333.9	332.2	327.0	321.8	320.5
47.5°	313.6	314.0	307.5	302.3	299.3
50°	294.1	292.8	287.6	282.0	279.0
52.5°	274.2	273.4	267.7	263.0	259.5
55°	254.3	253.0	247.0	243.1	240.1
57.5°	233.1	232.7	227.5	222.3	221.0
60°	213.2	211.5	206.8	202.4	199.4
62.5°	192.5	191.2	187.3	182.5	180.4
65°	171.7	170.9	166.1	162.2	160.5
67.5°	151.4	149.7	146.2	142.7	141.9
70°	132.4	130.2	126.3	123.7	122.0
72.5°	111.6	110.3	108.1	105.1	103.4
75°	91.3	90.4	88.2	86.9	85.2
77.5°	72.2	71.8	70.5	69.6	68.3
80°	54.5	54.5	53.6	53.2	52.3
82.5°	38.9	38.1	38.1	37.2	37.2
85°	23.8	24.2	24.2	23.8	22.9
87.5°	11.7	11.7	11.2	11.2	10.4
90°	1.0	8.6	15.2	20.0	21.9
92.5°	14.3	77.9	379.2	101.2	70.3
95°	31.4	92.6	841.9	382.0	223.3
97.5°	48.5	100.2	909.4	689.9	489.4
100°	66.5	115.0	858.1	975.0	741.2
102.5°	86.5	131.6	767.8	1216.4	1022.5
105°	107.4	150.1	688.9	1356.5	1259.1
107.5°	127.3	169.6	630.0	1395.9	1401.6
110°	149.2	190.0	591.1	1358.4	1466.2

TEST NUMBER: P1027792

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	171.0	210.5	568.3	1280.0	1458.6
115°	192.0	231.4	553.0	1192.1	1402.6
117.5°	211.0	252.8	544.5	1112.2	1318.0
120°	230.0	273.2	538.8	1045.3	1236.3
122.5°	249.9	293.2	534.0	991.6	1164.1
125°	266.1	311.6	530.2	948.4	1105.1
127.5°	279.4	329.8	528.3	911.3	1051.0
130°	291.7	346.8	526.4	873.8	1008.2
132.5°	301.2	362.0	526.4	833.4	965.5
135°	311.7	374.8	526.4	794.9	917.9
137.5°	325.0	386.8	527.4	754.5	868.5
140°	336.4	396.8	528.3	717.4	816.3
142.5°	349.7	406.2	529.3	685.6	767.8
145°	363.0	415.8	528.3	658.0	724.1
147.5°	377.3	424.3	526.4	634.3	685.1
150°	389.6	431.9	523.6	614.8	653.8
152.5°	402.9	439.5	519.8	598.2	629.1
155°	414.3	445.6	515.0	582.0	607.2
157.5°	424.8	451.8	510.3	566.8	587.3
160°	435.2	456.6	505.5	551.6	567.3
162.5°	443.8	461.4	499.8	537.8	549.2
165°	452.3	464.6	494.1	524.0	532.1
167.5°	458.0	466.6	488.4	511.2	516.0
170°	463.7	469.0	483.7	498.8	501.7
172.5°	467.5	469.9	478.0	488.9	488.4
175°	470.4	470.4	474.2	479.9	478.0
177.5°	472.3	470.4	471.3	474.2	471.3
180°	471.3	471.3	471.3	471.3	471.3

(END OF REPORT)