

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027809

Luminaire Tested: S125DIP-B375D1270UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027809
REPORT IS A COMBINATION OF REPORTS P1001910 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D1270UB30-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5647.0 lumens
Efficiency: N/A
Efficacy: 117.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027809

CATALOG NUMBER: S125DIP-B375D1270UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1027809

CATALOG NUMBER: S125DIP-B375D1270UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34
1	92	88	84	81	82	79	76	73	61	59	57	45	44	43	30	29	29
2	84	77	71	66	75	69	64	60	54	50	47	40	37	36	27	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18
5	64	53	45	39	57	48	41	36	37	33	29	28	25	22	19	17	15
6	59	47	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13
7	54	43	35	30	48	38	32	27	30	25	22	23	19	17	16	14	12
8	50	39	31	26	45	35	28	24	27	23	19	21	17	15	14	12	11
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	10
10	44	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3643	3643	3643
5°	3643	3559	3565
10°	3613	3477	3466
15°	3566	3380	3349
20°	3501	3266	3215
25°	3433	3143	3071
30°	3350	3014	2920
35°	3261	2879	2751
40°	3169	2737	2600
45°	3070	2598	2439
50°	2961	2441	2253
55°	2853	2267	2081
60°	2724	2084	1882
65°	2570	1872	1675
70°	2414	1629	1437
75°	2149	1341	1161
80°	1832	1002	854
85°	1412	593	470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3070 cd/sqm

TEST NUMBER: P1027809

CATALOG NUMBER: S125DIP-B375D1270UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	1.0
10°-20°	151.6	2.7
20°-30°	223.8	4.0
30°-40°	261.1	4.6
40°-50°	262.2	4.6
50°-60°	230.2	4.1
60°-70°	171.4	3.0
70°-80°	97.9	1.7
80°-90°	30.6	0.5
90°-100°	99.2	1.8
100°-110°	294.8	5.2
110°-120°	499.9	8.9
120°-130°	658.2	11.7
130°-140°	737.5	13.1
140°-150°	722.9	12.8
150°-160°	607.2	10.8
160°-170°	403.6	7.1
170°-180°	141.3	2.5
0°-30°	429.0	7.6
0°-40°	690.0	12.2
0°-60°	1182.4	20.9
0°-90°	1482.3	26.2
90°-120°	894.0	15.8
90°-150°	3012.5	53.3
90°-180°	4165.0	73.8
0°-180°	5647.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	569	569	569	569	569	
5°	568	567	562	566	566	54
15°	541	540	535	537	537	153
25°	491	489	483	484	483	226
35°	424	422	416	414	410	265
45°	347	346	340	335	333	268
55°	264	263	257	253	250	236
65°	179	178	173	169	167	177
75°	95	94	92	90	89	101
85°	25	25	25	25	24	27
90°	1	10	19	24	28	7
95°	76	78	89	98	100	79
105°	265	271	278	284	288	282
115°	500	505	508	506	505	495
125°	730	737	739	736	735	654
135°	950	957	958	958	953	732
145°	1151	1156	1159	1159	1156	719
155°	1317	1317	1318	1323	1317	607
165°	1432	1430	1431	1435	1428	404
175°	1489	1484	1484	1491	1483	141
180°	1492	1492	1492	1492	1492	

TEST NUMBER: P1027809

CATALOG NUMBER: S125DIP-B375D1270UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	568.6	568.6	568.6	568.6	568.6
2.5°	570.4	569.1	564.6	569.1	568.6
5°	567.7	566.8	562.3	566.4	565.9
7.5°	563.7	562.8	557.8	561.9	561.4
10°	557.8	556.9	552.0	555.6	555.1
12.5°	550.6	548.8	544.3	547.0	547.0
15°	541.2	539.8	534.9	537.1	537.1
17.5°	531.3	529.0	524.1	526.8	524.5
20°	518.2	517.3	511.5	514.6	512.4
22.5°	505.2	503.4	498.0	499.8	498.4
25°	491.3	489.0	483.2	484.1	482.7
27.5°	475.1	473.7	467.9	468.3	467.0
30°	459.3	458.0	451.2	450.3	449.0
32.5°	442.2	440.0	434.1	432.3	429.6
35°	424.2	422.4	416.1	413.9	410.3
37.5°	405.8	403.5	397.7	394.5	392.3
40°	386.9	384.6	378.3	374.3	372.9
42.5°	366.6	364.8	358.5	354.9	352.7
45°	347.3	345.5	340.1	334.7	333.3
47.5°	326.2	326.6	319.9	314.5	311.3
50°	305.9	304.6	299.2	293.3	290.2
52.5°	285.2	284.3	278.5	273.5	269.9
55°	264.5	263.2	256.9	252.8	249.7
57.5°	242.5	242.0	236.6	231.2	229.9
60°	221.8	220.0	215.0	210.5	207.4
62.5°	200.2	198.8	194.8	189.8	187.6
65°	178.6	177.7	172.7	168.7	166.9
67.5°	157.5	155.7	152.1	148.5	147.6
70°	137.7	135.4	131.4	128.7	126.9
72.5°	116.1	114.7	112.5	109.3	107.5
75°	94.9	94.0	91.8	90.4	88.6
77.5°	75.1	74.7	73.3	72.4	71.1
80°	56.7	56.7	55.8	55.3	54.4
82.5°	40.5	39.6	39.6	38.7	38.7
85°	24.7	25.2	25.2	24.7	23.8
87.5°	12.1	12.1	11.7	11.7	10.8
90°	1.2	10.5	18.6	24.4	27.9
92.5°	34.8	40.6	51.1	59.2	61.5
95°	75.5	77.8	89.4	97.5	99.9
97.5°	116.1	117.3	133.5	140.5	141.7
100°	162.6	162.6	177.7	188.1	190.4
102.5°	212.5	218.3	224.1	235.7	239.2
105°	264.8	270.6	277.5	284.5	288.0
107.5°	321.7	327.5	333.3	336.8	336.8
110°	380.9	386.7	390.2	393.7	392.5

TEST NUMBER: P1027809

CATALOG NUMBER: S125DIP-B375D1270UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	441.3	443.6	448.2	449.4	447.1
115°	500.5	505.1	507.5	506.3	505.1
117.5°	560.9	562.1	564.4	565.5	560.9
120°	616.6	622.4	623.6	623.6	619.0
122.5°	677.0	678.2	681.7	680.5	677.0
125°	730.4	737.4	738.6	736.2	735.1
127.5°	789.7	793.1	794.3	793.1	790.8
130°	841.9	847.7	850.0	848.9	846.6
132.5°	894.2	904.6	903.5	902.3	898.8
135°	949.9	956.9	958.0	958.0	953.4
137.5°	1002.2	1009.1	1011.5	1012.6	1006.8
140°	1052.1	1057.9	1061.4	1063.7	1057.9
142.5°	1102.0	1106.7	1111.3	1112.5	1106.7
145°	1150.8	1155.5	1158.9	1158.9	1155.5
147.5°	1196.1	1199.6	1201.9	1205.4	1196.1
150°	1241.4	1240.2	1244.9	1244.9	1242.6
152.5°	1278.6	1280.9	1282.0	1285.5	1280.9
155°	1316.9	1316.9	1318.0	1322.7	1316.9
157.5°	1351.7	1349.4	1350.5	1355.2	1347.1
160°	1381.9	1378.4	1379.6	1384.2	1378.4
162.5°	1408.6	1406.3	1406.3	1412.1	1405.1
165°	1431.8	1429.5	1430.7	1435.3	1428.4
167.5°	1452.7	1448.1	1448.1	1455.1	1448.1
170°	1469.0	1464.4	1464.4	1471.3	1463.2
172.5°	1480.6	1476.0	1476.0	1482.9	1476.0
175°	1488.7	1484.1	1484.1	1491.1	1482.9
177.5°	1494.5	1489.9	1488.7	1495.7	1487.6
180°	1492.2	1492.2	1492.2	1492.2	1492.2

(END OF REPORT)