

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028041

Luminaire Tested: S125DIP-B610D1270UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028041
REPORT IS A COMBINATION OF REPORTS P1002220 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D1270UB35-4F0-XX-W2A-F4
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6855.9 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028041

CATALOG NUMBER: S125DIP-B610D1270UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1028041

CATALOG NUMBER: S125DIP-B610D1270UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	44	44	36
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37	37	37	31
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	34	32	31	31	31	26
3	79	69	62	56	71	63	57	52	51	47	43	40	37	35	30	28	26	26	26	22
4	72	61	54	48	65	56	49	44	45	40	37	36	32	30	27	25	23	23	23	19
5	66	54	47	41	59	50	43	38	41	35	31	32	28	26	24	22	20	20	20	16
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17	17	17	14
7	56	44	36	31	51	40	33	28	33	28	24	26	22	20	20	17	15	15	15	13
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14	14	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	12	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	11	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6154	6154	6154
5°	6154	6012	6023
10°	6104	5873	5855
15°	6024	5708	5657
20°	5915	5517	5431
25°	5799	5309	5188
30°	5659	5092	4933
35°	5509	4864	4646
40°	5353	4624	4392
45°	5186	4389	4121
50°	5001	4123	3805
55°	4819	3829	3515
60°	4601	3520	3178
65°	4341	3162	2829
70°	4076	2751	2427
75°	3630	2265	1962
80°	3093	1691	1443
85°	2390	1002	796

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5186 cd/sqm

TEST NUMBER: P1028041

CATALOG NUMBER: S125DIP-B610D1270UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	1.3
10°-20°	256.0	3.7
20°-30°	378.0	5.5
30°-40°	441.0	6.4
40°-50°	442.9	6.5
50°-60°	388.8	5.7
60°-70°	289.6	4.2
70°-80°	165.4	2.4
80°-90°	50.1	0.7
90°-100°	435.6	6.4
100°-110°	904.8	13.2
110°-120°	845.1	12.3
120°-130°	683.8	10.0
130°-140°	549.4	8.0
140°-150°	414.7	6.0
150°-160°	292.0	4.3
160°-170°	172.1	2.5
170°-180°	56.0	0.8
0°-30°	724.6	10.6
0°-40°	1165.6	17.0
0°-60°	1997.3	29.1
0°-90°	2502.3	36.5
90°-120°	2185.5	31.9
90°-150°	3833.5	55.9
90°-180°	4354.0	63.5
0°-180°	6855.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	960	960	960	960	960	
5°	959	958	950	957	956	91
15°	914	912	904	907	907	258
25°	830	826	816	818	815	382
35°	717	714	703	699	693	448
45°	587	584	574	565	563	452
55°	447	444	434	427	422	399
65°	302	300	292	285	282	299
75°	160	159	155	153	150	171
85°	42	43	43	42	40	46
90°	1	10	19	24	27	6
95°	38	114	1033	469	274	40
105°	132	184	846	1665	1545	139
115°	236	284	679	1463	1721	232
125°	326	382	651	1164	1356	290
135°	382	460	646	976	1127	297
145°	446	510	648	808	889	279
155°	508	547	632	714	745	234
165°	555	570	606	643	653	156
175°	577	577	582	589	587	55
180°	578	578	578	578	578	

TEST NUMBER: P1028041

CATALOG NUMBER: S125DIP-B610D1270UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	960.5	960.5	960.5	960.5	960.5
2.5°	963.6	961.3	953.7	961.3	960.5
5°	959.0	957.5	949.9	956.7	956.0
7.5°	952.2	950.6	942.3	949.1	948.4
10°	942.3	940.8	932.4	938.5	937.7
12.5°	930.1	927.1	919.5	924.0	924.0
15°	914.2	911.9	903.5	907.3	907.3
17.5°	897.4	893.6	885.3	889.8	886.1
20°	875.4	873.9	864.0	869.3	865.5
22.5°	853.4	850.3	841.2	844.3	842.0
25°	829.8	826.0	816.1	817.7	815.4
27.5°	802.5	800.2	790.3	791.1	788.8
30°	775.9	773.6	762.2	760.7	758.4
32.5°	747.0	743.2	733.3	730.3	725.7
35°	716.6	713.6	702.9	699.1	693.0
37.5°	685.4	681.6	671.8	666.4	662.6
40°	653.5	649.7	639.1	632.2	630.0
42.5°	619.3	616.3	605.6	599.6	595.8
45°	586.6	583.6	574.5	565.4	563.1
47.5°	550.9	551.7	540.3	531.2	525.9
50°	516.7	514.5	505.3	495.5	490.1
52.5°	481.8	480.3	470.4	462.0	455.9
55°	446.8	444.5	433.9	427.1	421.7
57.5°	409.6	408.8	399.7	390.6	388.3
60°	374.6	371.6	363.2	355.6	350.3
62.5°	338.2	335.9	329.0	320.7	316.9
65°	301.7	300.2	291.8	285.0	281.9
67.5°	266.0	262.9	256.8	250.8	249.2
70°	232.5	228.7	221.9	217.3	214.3
72.5°	196.1	193.8	190.0	184.7	181.6
75°	160.3	158.8	155.0	152.7	149.7
77.5°	126.9	126.1	123.9	122.3	120.1
80°	95.7	95.7	94.2	93.5	91.9
82.5°	68.4	66.9	66.9	65.4	65.4
85°	41.8	42.6	42.6	41.8	40.3
87.5°	20.5	20.5	19.8	19.8	18.2
90°	1.2	10.5	18.7	24.5	26.8
92.5°	17.5	95.6	465.3	124.2	86.3
95°	38.5	113.7	1033.3	468.8	274.1
97.5°	59.5	123.0	1116.1	846.7	600.6
100°	81.6	141.1	1053.1	1196.6	909.7
102.5°	106.1	161.5	942.3	1492.8	1254.9
105°	131.8	184.2	845.5	1664.8	1545.2
107.5°	156.3	208.2	773.2	1713.2	1720.2
110°	183.1	233.2	725.4	1667.2	1799.5

TEST NUMBER: P1028041

CATALOG NUMBER: S125DIP-B610D1270UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	209.9	258.3	697.4	1570.9	1790.2
115°	235.6	284.0	678.7	1463.0	1721.3
117.5°	258.9	310.2	668.2	1365.0	1617.6
120°	282.2	335.3	661.2	1282.8	1517.3
122.5°	306.7	359.8	655.4	1217.0	1428.6
125°	326.5	382.5	650.8	1163.9	1356.3
127.5°	342.9	404.6	648.4	1118.4	1289.8
130°	358.0	425.6	646.1	1072.3	1237.4
132.5°	369.7	444.4	646.1	1022.8	1184.9
135°	382.5	460.0	646.1	975.6	1126.6
137.5°	398.8	474.6	647.3	926.0	1065.9
140°	412.8	486.9	648.4	880.5	1001.8
142.5°	429.2	498.6	649.6	841.4	942.3
145°	445.5	510.2	648.4	807.6	888.7
147.5°	463.0	520.8	646.1	778.4	840.8
150°	478.2	530.0	642.6	754.6	802.4
152.5°	494.5	539.4	637.9	734.2	772.0
155°	508.5	547.0	632.1	714.3	745.2
157.5°	521.3	554.6	626.3	695.6	720.7
160°	534.1	560.4	620.4	677.0	696.2
162.5°	544.6	566.2	613.4	660.1	674.1
165°	555.1	570.3	606.4	643.2	653.1
167.5°	562.1	572.6	599.4	627.4	633.3
170°	569.1	575.6	593.6	612.2	615.8
172.5°	573.8	576.7	586.6	600.0	599.4
175°	577.3	577.3	581.9	588.9	586.6
177.5°	579.6	577.3	578.4	581.9	578.4
180°	578.4	578.4	578.4	578.4	578.4

(END OF REPORT)