

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027836

Luminaire Tested: S125DIP-B375D1270UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027836
REPORT IS A COMBINATION OF REPORTS P1001937 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D1270UB50-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5430.0 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027836

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1027836

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34
1	92	88	84	81	82	79	76	73	61	59	57	45	44	43	30	29	29
2	84	77	71	66	75	69	64	60	54	50	47	40	37	36	27	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18
5	64	53	45	39	57	48	41	36	37	33	29	28	25	22	19	17	15
6	59	47	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13
7	54	43	35	30	48	38	32	27	30	25	22	23	19	17	16	14	12
8	50	39	31	26	45	35	28	24	27	23	19	21	17	15	14	12	11
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	10
10	44	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3503	3503	3503
5°	3503	3422	3428
10°	3474	3343	3333
15°	3428	3249	3221
20°	3367	3141	3091
25°	3300	3022	2953
30°	3221	2898	2808
35°	3136	2769	2645
40°	3047	2632	2500
45°	2952	2498	2346
50°	2847	2346	2166
55°	2743	2180	2001
60°	2619	2004	1809
65°	2471	1800	1611
70°	2321	1566	1382
75°	2067	1289	1117
80°	1761	962	821
85°	1361	569	452

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2952 cd/sqm

TEST NUMBER: P1027836

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	1.0
10°-20°	145.7	2.7
20°-30°	215.1	4.0
30°-40°	251.0	4.6
40°-50°	252.1	4.6
50°-60°	221.3	4.1
60°-70°	164.8	3.0
70°-80°	94.1	1.7
80°-90°	29.4	0.5
90°-100°	95.4	1.8
100°-110°	283.5	5.2
110°-120°	480.8	8.9
120°-130°	632.9	11.7
130°-140°	709.2	13.1
140°-150°	695.1	12.8
150°-160°	583.9	10.8
160°-170°	388.1	7.1
170°-180°	135.8	2.5
0°-30°	412.5	7.6
0°-40°	663.5	12.2
0°-60°	1136.8	20.9
0°-90°	1425.2	26.2
90°-120°	859.7	15.8
90°-150°	2896.9	53.4
90°-180°	4005.0	73.8
0°-180°	5430.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	547	547	547	547	547	
5°	546	545	541	545	544	52
15°	520	519	514	516	516	147
25°	472	470	464	465	464	217
35°	408	406	400	398	394	255
45°	334	332	327	322	320	257
55°	254	253	247	243	240	227
65°	172	171	166	162	160	170
75°	91	90	88	87	85	97
85°	24	24	24	24	23	26
90°	1	10	18	24	27	6
95°	73	75	86	94	96	76
105°	255	260	267	274	277	271
115°	481	486	488	487	486	476
125°	702	709	710	708	707	629
135°	913	920	921	921	917	704
145°	1107	1111	1114	1114	1111	692
155°	1266	1266	1267	1272	1266	583
165°	1377	1375	1376	1380	1374	388
175°	1432	1427	1427	1434	1426	136
180°	1435	1435	1435	1435	1435	

TEST NUMBER: P1027836

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	546.7	546.7	546.7	546.7	546.7
2.5°	548.5	547.2	542.8	547.2	546.7
5°	545.9	545.0	540.7	544.6	544.1
7.5°	542.0	541.1	536.3	540.2	539.8
10°	536.3	535.5	530.7	534.2	533.8
12.5°	529.4	527.7	523.4	526.0	526.0
15°	520.3	519.0	514.3	516.5	516.5
17.5°	510.8	508.7	503.9	506.5	504.3
20°	498.3	497.4	491.8	494.8	492.7
22.5°	485.7	484.0	478.8	480.6	479.3
25°	472.3	470.2	464.5	465.4	464.1
27.5°	456.8	455.5	449.8	450.3	449.0
30°	441.6	440.3	433.8	433.0	431.7
32.5°	425.2	423.0	417.4	415.7	413.1
35°	407.9	406.2	400.1	397.9	394.5
37.5°	390.1	388.0	382.4	379.3	377.2
40°	372.0	369.8	363.8	359.9	358.6
42.5°	352.5	350.8	344.7	341.3	339.1
45°	333.9	332.2	327.0	321.8	320.5
47.5°	313.6	314.0	307.5	302.3	299.3
50°	294.1	292.8	287.6	282.0	279.0
52.5°	274.2	273.4	267.7	263.0	259.5
55°	254.3	253.0	247.0	243.1	240.1
57.5°	233.1	232.7	227.5	222.3	221.0
60°	213.2	211.5	206.8	202.4	199.4
62.5°	192.5	191.2	187.3	182.5	180.4
65°	171.7	170.9	166.1	162.2	160.5
67.5°	151.4	149.7	146.2	142.7	141.9
70°	132.4	130.2	126.3	123.7	122.0
72.5°	111.6	110.3	108.1	105.1	103.4
75°	91.3	90.4	88.2	86.9	85.2
77.5°	72.2	71.8	70.5	69.6	68.3
80°	54.5	54.5	53.6	53.2	52.3
82.5°	38.9	38.1	38.1	37.2	37.2
85°	23.8	24.2	24.2	23.8	22.9
87.5°	11.7	11.7	11.2	11.2	10.4
90°	1.1	10.1	17.9	23.5	26.8
92.5°	33.5	39.1	49.1	57.0	59.2
95°	72.6	74.8	86.0	93.8	96.0
97.5°	111.7	112.8	128.4	135.1	136.2
100°	156.3	156.3	170.9	180.9	183.1
102.5°	204.4	209.9	215.5	226.7	230.0
105°	254.6	260.2	266.9	273.6	276.9
107.5°	309.3	314.9	320.5	323.8	323.8
110°	366.3	371.9	375.2	378.6	377.4

TEST NUMBER: P1027836

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	424.3	426.6	431.0	432.2	429.9
115°	481.3	485.8	488.0	486.9	485.8
117.5°	539.4	540.5	542.7	543.8	539.4
120°	593.0	598.5	599.7	599.7	595.2
122.5°	651.0	652.1	655.5	654.4	651.0
125°	702.4	709.1	710.2	708.0	706.9
127.5°	759.3	762.7	763.8	762.7	760.5
130°	809.6	815.2	817.4	816.3	814.1
132.5°	859.8	869.9	868.8	867.7	864.3
135°	913.4	920.1	921.3	921.3	916.8
137.5°	963.7	970.4	972.6	973.7	968.2
140°	1011.7	1017.3	1020.6	1022.9	1017.3
142.5°	1059.7	1064.2	1068.7	1069.8	1064.2
145°	1106.6	1111.1	1114.4	1114.4	1111.1
147.5°	1150.2	1153.5	1155.8	1159.1	1150.2
150°	1193.7	1192.6	1197.1	1197.1	1194.8
152.5°	1229.5	1231.7	1232.8	1236.2	1231.7
155°	1266.3	1266.3	1267.4	1271.9	1266.3
157.5°	1299.8	1297.6	1298.7	1303.2	1295.3
160°	1328.8	1325.5	1326.6	1331.1	1325.5
162.5°	1354.5	1352.3	1352.3	1357.9	1351.2
165°	1376.9	1374.6	1375.7	1380.2	1373.5
167.5°	1397.0	1392.5	1392.5	1399.2	1392.5
170°	1412.6	1408.1	1408.1	1414.8	1407.0
172.5°	1423.8	1419.3	1419.3	1426.0	1419.3
175°	1431.6	1427.1	1427.1	1433.8	1426.0
177.5°	1437.2	1432.7	1431.6	1438.3	1430.5
180°	1434.9	1434.9	1434.9	1434.9	1434.9

(END OF REPORT)