

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028076

Luminaire Tested: S125DIP-B610D375UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028076
REPORT IS A COMBINATION OF REPORTS P1002270 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D375UB30-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3765.0 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028076

CATALOG NUMBER: S125DIP-B610D375UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028076

CATALOG NUMBER: S125DIP-B610D375UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	101	97	93	89	95	91	88	85	81	78	76	71	69	68	63	61	60
2	92	85	78	73	87	80	74	69	71	67	63	63	59	56	55	53	50
3	84	74	67	61	79	70	63	58	63	57	53	55	51	48	49	46	43
4	77	66	58	51	72	62	55	49	56	50	45	49	45	41	44	40	37
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	36	32	28
7	60	48	40	34	57	45	38	33	41	35	30	37	31	28	33	28	25
8	56	43	35	30	53	41	34	29	37	31	27	34	28	25	30	26	23
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6127	6127	6127
5°	6127	5985	5997
10°	6076	5848	5829
15°	5997	5684	5632
20°	5889	5493	5407
25°	5773	5285	5165
30°	5634	5069	4911
35°	5484	4843	4626
40°	5330	4603	4372
45°	5163	4370	4103
50°	4980	4105	3789
55°	4798	3813	3500
60°	4581	3504	3165
65°	4322	3148	2817
70°	4058	2738	2417
75°	3614	2254	1953
80°	3080	1684	1436
85°	2378	997	792

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5163 cd/sqm

TEST NUMBER: P1028076

CATALOG NUMBER: S125DIP-B610D375UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.2	2.4
10°-20°	254.9	6.8
20°-30°	376.3	10.0
30°-40°	439.0	11.7
40°-50°	440.9	11.7
50°-60°	387.1	10.3
60°-70°	288.3	7.7
70°-80°	164.6	4.4
80°-90°	48.3	1.3
90°-100°	30.4	0.8
100°-110°	90.3	2.4
110°-120°	153.1	4.1
120°-130°	201.5	5.4
130°-140°	225.8	6.0
140°-150°	221.4	5.9
150°-160°	185.9	4.9
160°-170°	123.6	3.3
170°-180°	43.3	1.1
0°-30°	721.4	19.2
0°-40°	1160.5	30.8
0°-60°	1988.5	52.8
0°-90°	2489.7	66.1
90°-120°	273.8	7.3
90°-150°	922.5	24.5
90°-180°	1275.0	33.9
0°-180°	3765.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	956	956	956	956	956	
5°	955	953	946	952	952	91
15°	910	908	900	903	903	257
25°	826	822	812	814	812	380
35°	713	710	700	696	690	446
45°	584	581	572	563	561	450
55°	445	443	432	425	420	397
65°	300	299	290	284	281	298
75°	160	158	154	152	149	170
85°	42	42	42	42	40	46
90°	0	3	6	8	8	4
95°	23	24	27	30	31	24
105°	81	83	85	87	88	86
115°	153	155	155	155	155	152
125°	224	226	226	225	225	200
135°	291	293	293	293	292	224
145°	352	354	355	355	354	220
155°	403	403	404	405	403	186
165°	438	438	438	440	437	124
175°	456	454	454	457	454	43
180°	457	457	457	457	457	

TEST NUMBER: P1028076

CATALOG NUMBER: S125DIP-B610D375UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	956.3	956.3	956.3	956.3	956.3
2.5°	959.3	957.1	949.5	957.1	956.3
5°	954.8	953.3	945.7	952.5	951.8
7.5°	948.0	946.5	938.1	944.9	944.2
10°	938.1	936.6	928.3	934.4	933.6
12.5°	926.0	923.0	915.4	920.0	920.0
15°	910.1	907.9	899.6	903.3	903.3
17.5°	893.5	889.7	881.4	885.9	882.2
20°	871.6	870.0	860.2	865.5	861.7
22.5°	849.6	846.6	837.5	840.5	838.3
25°	826.2	822.4	812.5	814.1	811.8
27.5°	798.9	796.7	786.8	787.6	785.3
30°	772.5	770.2	758.8	757.3	755.0
32.5°	743.7	739.9	730.1	727.1	722.5
35°	713.4	710.4	699.8	696.0	690.0
37.5°	682.4	678.6	668.8	663.5	659.7
40°	650.6	646.9	636.3	629.5	627.2
42.5°	616.6	613.6	603.0	596.9	593.1
45°	584.1	581.0	572.0	562.9	560.6
47.5°	548.5	549.3	537.9	528.8	523.5
50°	514.5	512.2	503.1	493.3	488.0
52.5°	479.7	478.1	468.3	460.0	453.9
55°	444.9	442.6	432.0	425.2	419.9
57.5°	407.8	407.0	398.0	388.9	386.6
60°	373.0	370.0	361.6	354.1	348.8
62.5°	336.7	334.4	327.6	319.3	315.5
65°	300.4	298.8	290.5	283.7	280.7
67.5°	264.8	261.8	255.7	249.7	248.2
70°	231.5	227.7	220.9	216.4	213.4
72.5°	195.2	192.9	189.1	183.8	180.8
75°	159.6	158.1	154.3	152.1	149.0
77.5°	126.3	125.6	123.3	121.8	119.5
80°	95.3	95.3	93.8	93.1	91.5
82.5°	68.1	66.6	66.6	65.1	65.1
85°	41.6	42.4	42.4	41.6	40.1
87.5°	20.4	20.4	19.7	19.7	18.2
90°	0.4	3.2	5.7	7.5	8.5
92.5°	10.7	12.4	15.6	18.1	18.8
95°	23.1	23.8	27.4	29.9	30.6
97.5°	35.6	35.9	40.9	43.0	43.4
100°	49.8	49.8	54.4	57.6	58.3
102.5°	65.1	66.9	68.6	72.2	73.3
105°	81.1	82.9	85.0	87.1	88.2
107.5°	98.5	100.3	102.1	103.1	103.1
110°	116.6	118.4	119.5	120.5	120.2

TEST NUMBER: P1028076

CATALOG NUMBER: S125DIP-B610D375UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.1	135.8	137.3	137.6	136.9
115°	153.3	154.7	155.4	155.0	154.7
117.5°	171.8	172.1	172.8	173.2	171.8
120°	188.8	190.6	191.0	191.0	189.5
122.5°	207.3	207.7	208.7	208.4	207.3
125°	223.7	225.8	226.2	225.4	225.1
127.5°	241.8	242.9	243.2	242.9	242.2
130°	257.8	259.6	260.3	259.9	259.2
132.5°	273.8	277.0	276.7	276.3	275.2
135°	290.9	293.0	293.4	293.4	291.9
137.5°	306.9	309.0	309.7	310.1	308.3
140°	322.2	323.9	325.0	325.7	323.9
142.5°	337.5	338.9	340.3	340.7	338.9
145°	352.4	353.8	354.9	354.9	353.8
147.5°	366.3	367.3	368.0	369.1	366.3
150°	380.1	379.8	381.2	381.2	380.5
152.5°	391.5	392.2	392.6	393.6	392.2
155°	403.2	403.2	403.6	405.0	403.2
157.5°	413.9	413.2	413.6	415.0	412.5
160°	423.2	422.1	422.4	423.9	422.1
162.5°	431.3	430.6	430.6	432.4	430.3
165°	438.5	437.7	438.1	439.5	437.4
167.5°	444.9	443.4	443.4	445.6	443.4
170°	449.8	448.4	448.4	450.5	448.1
172.5°	453.4	452.0	452.0	454.1	452.0
175°	455.9	454.5	454.5	456.6	454.1
177.5°	457.7	456.2	455.9	458.0	455.5
180°	456.9	456.9	456.9	456.9	456.9

(END OF REPORT)