

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028077

Luminaire Tested: S125DIP-B610D375UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028077
REPORT IS A COMBINATION OF REPORTS P1002271 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D375UB30-4F0-XX-W2A-F4
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3816.7 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028077

CATALOG NUMBER: S125DIP-B610D375UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1028077

CATALOG NUMBER: S125DIP-B610D375UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65		
1	101	97	93	89	95	91	88	84	80	78	75	71	69	67	62	60	59	55		
2	92	84	78	73	86	80	74	69	71	66	62	62	59	56	54	52	50	46		
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42	39		
4	77	66	58	51	72	62	55	49	55	49	45	49	44	41	43	39	36	33		
5	71	59	50	44	66	55	48	42	50	43	39	44	39	35	39	35	32	29		
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25		
7	60	48	39	34	57	45	38	32	41	34	30	36	31	27	32	28	25	22		
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	30	25	22	20		
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18		
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6127	6127	6127
5°	6127	5985	5997
10°	6076	5848	5829
15°	5997	5684	5632
20°	5889	5493	5407
25°	5773	5285	5165
30°	5634	5069	4911
35°	5484	4843	4626
40°	5330	4603	4372
45°	5163	4370	4103
50°	4980	4105	3789
55°	4798	3813	3500
60°	4581	3504	3165
65°	4322	3148	2817
70°	4058	2738	2417
75°	3614	2254	1953
80°	3080	1684	1436
85°	2378	997	792

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5163 cd/sqm

TEST NUMBER: P1028077

CATALOG NUMBER: S125DIP-B610D375UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.2	2.4
10°-20°	254.9	6.7
20°-30°	376.3	9.9
30°-40°	439.0	11.5
40°-50°	440.9	11.6
50°-60°	387.1	10.1
60°-70°	288.3	7.6
70°-80°	164.6	4.3
80°-90°	48.3	1.3
90°-100°	132.8	3.5
100°-110°	275.8	7.2
110°-120°	257.6	6.7
120°-130°	208.4	5.5
130°-140°	167.5	4.4
140°-150°	126.4	3.3
150°-160°	89.0	2.3
160°-170°	52.5	1.4
170°-180°	17.1	0.4
0°-30°	721.4	18.9
0°-40°	1160.5	30.4
0°-60°	1988.5	52.1
0°-90°	2489.7	65.2
90°-120°	666.2	17.5
90°-150°	1168.5	30.6
90°-180°	1327.0	34.8
0°-180°	3816.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	956	956	956	956	956	
5°	955	953	946	952	952	91
15°	910	908	900	903	903	257
25°	826	822	812	814	812	380
35°	713	710	700	696	690	446
45°	584	581	572	563	561	450
55°	445	443	432	425	420	397
65°	300	299	290	284	281	298
75°	160	158	154	152	149	170
85°	42	42	42	42	40	46
90°	0	3	6	7	8	4
95°	12	35	315	143	84	12
105°	40	56	258	507	471	42
115°	72	87	207	446	525	71
125°	100	117	198	355	413	88
135°	117	140	197	297	343	90
145°	136	156	198	246	271	85
155°	155	167	193	218	227	71
165°	169	174	185	196	199	48
175°	176	176	177	180	179	17
180°	176	176	176	176	176	

TEST NUMBER: P1028077

CATALOG NUMBER: S125DIP-B610D375UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	956.3	956.3	956.3	956.3	956.3
2.5°	959.3	957.1	949.5	957.1	956.3
5°	954.8	953.3	945.7	952.5	951.8
7.5°	948.0	946.5	938.1	944.9	944.2
10°	938.1	936.6	928.3	934.4	933.6
12.5°	926.0	923.0	915.4	920.0	920.0
15°	910.1	907.9	899.6	903.3	903.3
17.5°	893.5	889.7	881.4	885.9	882.2
20°	871.6	870.0	860.2	865.5	861.7
22.5°	849.6	846.6	837.5	840.5	838.3
25°	826.2	822.4	812.5	814.1	811.8
27.5°	798.9	796.7	786.8	787.6	785.3
30°	772.5	770.2	758.8	757.3	755.0
32.5°	743.7	739.9	730.1	727.1	722.5
35°	713.4	710.4	699.8	696.0	690.0
37.5°	682.4	678.6	668.8	663.5	659.7
40°	650.6	646.9	636.3	629.5	627.2
42.5°	616.6	613.6	603.0	596.9	593.1
45°	584.1	581.0	572.0	562.9	560.6
47.5°	548.5	549.3	537.9	528.8	523.5
50°	514.5	512.2	503.1	493.3	488.0
52.5°	479.7	478.1	468.3	460.0	453.9
55°	444.9	442.6	432.0	425.2	419.9
57.5°	407.8	407.0	398.0	388.9	386.6
60°	373.0	370.0	361.6	354.1	348.8
62.5°	336.7	334.4	327.6	319.3	315.5
65°	300.4	298.8	290.5	283.7	280.7
67.5°	264.8	261.8	255.7	249.7	248.2
70°	231.5	227.7	220.9	216.4	213.4
72.5°	195.2	192.9	189.1	183.8	180.8
75°	159.6	158.1	154.3	152.1	149.0
77.5°	126.3	125.6	123.3	121.8	119.5
80°	95.3	95.3	93.8	93.1	91.5
82.5°	68.1	66.6	66.6	65.1	65.1
85°	41.6	42.4	42.4	41.6	40.1
87.5°	20.4	20.4	19.7	19.7	18.2
90°	0.4	3.2	5.7	7.4	8.2
92.5°	5.3	29.2	141.8	37.8	26.3
95°	11.7	34.7	314.9	142.9	83.5
97.5°	18.1	37.5	340.2	258.0	183.1
100°	24.9	43.0	321.0	364.7	277.3
102.5°	32.3	49.2	287.2	455.0	382.5
105°	40.2	56.2	257.7	507.4	471.0
107.5°	47.6	63.4	235.7	522.2	524.3
110°	55.8	71.1	221.1	508.2	548.5



TEST NUMBER: P1028077

CATALOG NUMBER: S125DIP-B610D375UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	64.0	78.8	212.6	478.8	545.7
115°	71.8	86.6	206.9	446.0	524.7
117.5°	78.9	94.6	203.7	416.1	493.0
120°	86.0	102.2	201.6	391.0	462.5
122.5°	93.5	109.6	199.8	370.9	435.5
125°	99.5	116.6	198.4	354.8	413.4
127.5°	104.5	123.4	197.6	340.9	393.2
130°	109.1	129.8	196.9	326.8	377.2
132.5°	112.7	135.4	196.9	311.8	361.2
135°	116.6	140.2	196.9	297.4	343.4
137.5°	121.6	144.7	197.3	282.2	324.9
140°	125.8	148.4	197.6	268.4	305.4
142.5°	130.8	152.0	198.0	256.5	287.2
145°	135.8	155.5	197.6	246.2	270.9
147.5°	141.1	158.8	196.9	237.2	256.3
150°	145.7	161.6	195.9	230.0	244.6
152.5°	150.7	164.4	194.4	223.8	235.3
155°	155.0	166.7	192.7	217.8	227.1
157.5°	158.9	169.0	190.9	212.0	219.7
160°	162.8	170.8	189.1	206.4	212.2
162.5°	166.0	172.6	187.0	201.2	205.5
165°	169.2	173.9	184.8	196.0	199.1
167.5°	171.3	174.5	182.7	191.2	193.0
170°	173.5	175.4	180.9	186.6	187.7
172.5°	174.9	175.8	178.8	182.9	182.7
175°	176.0	176.0	177.4	179.5	178.8
177.5°	176.7	176.0	176.3	177.4	176.3
180°	176.3	176.3	176.3	176.3	176.3

(END OF REPORT)