

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027853

Luminaire Tested: S125DIP-B375D375UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027853
REPORT IS A COMBINATION OF REPORTS P1001969 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D375UB30-4F0-XX-W2A-F
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2954.0 lumens
Efficiency: N/A
Efficacy: 132.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027853

CATALOG NUMBER: S125DIP-B375D375UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1027853

CATALOG NUMBER: S125DIP-B375D375UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	50
1	98	93	89	86	90	86	83	80	73	71	68	61	59	58	50	48	47	47	47	42
2	89	82	75	70	82	75	70	66	64	60	57	53	51	48	44	42	40	40	40	35
3	81	72	64	58	75	66	60	55	56	52	48	47	44	41	39	36	34	34	34	30
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	35	32	29	29	29	26
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	25	25	22
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	22	22	19
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20	20	20	17
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18	18	18	15
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	16	16	14
10	47	35	27	23	43	32	26	22	28	23	19	24	20	17	20	17	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3643	3643	3643
5°	3643	3559	3565
10°	3613	3477	3466
15°	3566	3380	3349
20°	3501	3266	3215
25°	3433	3143	3071
30°	3350	3014	2920
35°	3261	2879	2751
40°	3169	2737	2600
45°	3070	2598	2439
50°	2961	2441	2253
55°	2853	2267	2081
60°	2724	2084	1882
65°	2570	1872	1675
70°	2414	1629	1437
75°	2149	1341	1161
80°	1832	1002	854
85°	1412	593	470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3070 cd/sqm

TEST NUMBER: P1027853

CATALOG NUMBER: S125DIP-B375D375UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	1.8
10°-20°	151.6	5.1
20°-30°	223.8	7.6
30°-40°	261.1	8.8
40°-50°	262.2	8.9
50°-60°	230.2	7.8
60°-70°	171.4	5.8
70°-80°	97.9	3.3
80°-90°	29.0	1.0
90°-100°	16.3	0.6
100°-110°	108.2	3.7
110°-120°	194.9	6.6
120°-130°	250.2	8.5
130°-140°	269.1	9.1
140°-150°	252.6	8.5
150°-160°	204.3	6.9
160°-170°	132.1	4.5
170°-180°	45.6	1.5
0°-30°	429.0	14.5
0°-40°	690.0	23.4
0°-60°	1182.4	40.0
0°-90°	1480.7	50.1
90°-120°	319.5	10.8
90°-150°	1091.3	36.9
90°-180°	1473.0	49.9
0°-180°	2954.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	569	569	569	569	569	
5°	568	567	562	566	566	54
15°	541	540	535	537	537	153
25°	491	489	483	484	483	226
35°	424	422	416	414	410	265
45°	347	346	340	335	333	268
55°	264	263	257	253	250	236
65°	179	178	173	169	167	177
75°	95	94	92	90	89	101
85°	25	25	25	25	24	27
90°	0	3	6	8	8	3
95°	20	19	6	8	8	25
105°	104	106	106	106	106	111
115°	196	198	198	197	195	195
125°	279	282	282	280	279	249
135°	348	350	350	349	347	268
145°	404	404	404	405	402	252
155°	444	442	443	444	441	205
165°	469	467	467	469	466	132
175°	480	478	478	481	478	46
180°	480	480	480	480	480	

TEST NUMBER: P1027853

CATALOG NUMBER: S125DIP-B375D375UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	568.6	568.6	568.6	568.6	568.6
2.5°	570.4	569.1	564.6	569.1	568.6
5°	567.7	566.8	562.3	566.4	565.9
7.5°	563.7	562.8	557.8	561.9	561.4
10°	557.8	556.9	552.0	555.6	555.1
12.5°	550.6	548.8	544.3	547.0	547.0
15°	541.2	539.8	534.9	537.1	537.1
17.5°	531.3	529.0	524.1	526.8	524.5
20°	518.2	517.3	511.5	514.6	512.4
22.5°	505.2	503.4	498.0	499.8	498.4
25°	491.3	489.0	483.2	484.1	482.7
27.5°	475.1	473.7	467.9	468.3	467.0
30°	459.3	458.0	451.2	450.3	449.0
32.5°	442.2	440.0	434.1	432.3	429.6
35°	424.2	422.4	416.1	413.9	410.3
37.5°	405.8	403.5	397.7	394.5	392.3
40°	386.9	384.6	378.3	374.3	372.9
42.5°	366.6	364.8	358.5	354.9	352.7
45°	347.3	345.5	340.1	334.7	333.3
47.5°	326.2	326.6	319.9	314.5	311.3
50°	305.9	304.6	299.2	293.3	290.2
52.5°	285.2	284.3	278.5	273.5	269.9
55°	264.5	263.2	256.9	252.8	249.7
57.5°	242.5	242.0	236.6	231.2	229.9
60°	221.8	220.0	215.0	210.5	207.4
62.5°	200.2	198.8	194.8	189.8	187.6
65°	178.6	177.7	172.7	168.7	166.9
67.5°	157.5	155.7	152.1	148.5	147.6
70°	137.7	135.4	131.4	128.7	126.9
72.5°	116.1	114.7	112.5	109.3	107.5
75°	94.9	94.0	91.8	90.4	88.6
77.5°	75.1	74.7	73.3	72.4	71.1
80°	56.7	56.7	55.8	55.3	54.4
82.5°	40.5	39.6	39.6	38.7	38.7
85°	24.7	25.2	25.2	24.7	23.8
87.5°	12.1	12.1	11.7	11.7	10.8
90°	0.4	3.2	5.7	7.5	8.5
92.5°	6.8	3.6	5.7	7.5	7.8
95°	20.3	19.2	5.7	7.5	7.5
97.5°	38.0	40.2	6.4	7.1	7.5
100°	59.4	60.4	61.9	8.9	7.5
102.5°	81.1	82.5	83.2	83.9	54.0
105°	104.5	105.9	105.9	105.9	105.6
107.5°	128.7	128.7	129.4	129.8	128.3
110°	152.2	152.2	152.9	151.8	152.2

TEST NUMBER: P1027853

CATALOG NUMBER: S125DIP-B375D375UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.2	175.3	175.6	174.2	173.5
115°	196.3	198.0	198.4	197.0	194.8
117.5°	219.4	219.4	220.8	218.7	217.9
120°	240.7	240.3	241.4	240.7	238.9
122.5°	259.5	261.3	261.7	261.0	258.8
125°	279.1	281.6	281.6	280.2	279.1
127.5°	297.9	299.7	299.4	298.7	295.8
130°	315.0	316.8	317.1	316.1	314.3
132.5°	332.1	334.2	333.1	333.1	331.4
135°	348.1	350.2	349.5	348.8	346.6
137.5°	363.0	365.1	364.4	364.4	362.6
140°	377.6	378.3	377.9	378.6	376.5
142.5°	390.7	391.1	391.8	391.8	389.7
145°	403.5	404.2	404.2	404.6	402.5
147.5°	414.9	414.9	415.3	415.6	413.1
150°	425.6	424.9	425.6	426.3	423.4
152.5°	435.9	434.1	434.8	435.5	433.0
155°	444.4	442.3	443.0	444.1	441.2
157.5°	451.2	450.1	450.1	451.2	448.3
160°	458.3	456.2	456.5	457.9	455.1
162.5°	464.0	461.8	462.2	464.3	461.1
165°	469.0	466.8	467.2	469.3	466.5
167.5°	472.9	470.7	471.1	473.6	470.4
170°	476.1	473.6	473.9	476.8	473.6
172.5°	478.2	475.7	476.4	478.9	475.7
175°	479.6	477.5	477.8	480.7	477.5
177.5°	480.7	478.6	478.9	481.4	478.6
180°	479.6	479.6	479.6	479.6	479.6

(END OF REPORT)