

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027855

Luminaire Tested: S125DIP-B375D375UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027855
REPORT IS A COMBINATION OF REPORTS P1001971 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D375UB30-4F0-XX-W2A-F4
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2807.7 lumens
Efficiency: N/A
Efficacy: 125.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027855

CATALOG NUMBER: S125DIP-B375D375UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1027855

CATALOG NUMBER: S125DIP-B375D375UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	86	91	87	84	81	74	72	70	63	61	59	52	51	49
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	42
3	82	72	65	59	75	67	60	55	57	52	48	49	45	42	40	38	35
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	27
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23
7	58	46	38	32	54	43	36	31	37	32	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3643	3643	3643
5°	3643	3559	3565
10°	3613	3477	3466
15°	3566	3380	3349
20°	3501	3266	3215
25°	3433	3143	3071
30°	3350	3014	2920
35°	3261	2879	2751
40°	3169	2737	2600
45°	3070	2598	2439
50°	2961	2441	2253
55°	2853	2267	2081
60°	2724	2084	1882
65°	2570	1872	1675
70°	2414	1629	1437
75°	2149	1341	1161
80°	1832	1002	854
85°	1412	593	470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3070 cd/sqm

TEST NUMBER: P1027855

CATALOG NUMBER: S125DIP-B375D375UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	1.9
10°-20°	151.6	5.4
20°-30°	223.8	8.0
30°-40°	261.1	9.3
40°-50°	262.2	9.3
50°-60°	230.2	8.2
60°-70°	171.4	6.1
70°-80°	97.9	3.5
80°-90°	29.0	1.0
90°-100°	132.8	4.7
100°-110°	275.8	9.8
110°-120°	257.6	9.2
120°-130°	208.4	7.4
130°-140°	167.5	6.0
140°-150°	126.4	4.5
150°-160°	89.0	3.2
160°-170°	52.5	1.9
170°-180°	17.1	0.6
0°-30°	429.0	15.3
0°-40°	690.0	24.6
0°-60°	1182.4	42.1
0°-90°	1480.7	52.7
90°-120°	666.2	23.7
90°-150°	1168.5	41.6
90°-180°	1327.0	47.3
0°-180°	2807.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	569	569	569	569	569	
5°	568	567	562	566	566	54
15°	541	540	535	537	537	153
25°	491	489	483	484	483	226
35°	424	422	416	414	410	265
45°	347	346	340	335	333	268
55°	264	263	257	253	250	236
65°	179	178	173	169	167	177
75°	95	94	92	90	89	101
85°	25	25	25	25	24	27
90°	0	3	6	7	8	2
95°	12	35	315	143	84	12
105°	40	56	258	507	471	42
115°	72	87	207	446	525	71
125°	100	117	198	355	413	88
135°	117	140	197	297	343	90
145°	136	156	198	246	271	85
155°	155	167	193	218	227	71
165°	169	174	185	196	199	48
175°	176	176	177	180	179	17
180°	176	176	176	176	176	

TEST NUMBER: P1027855

CATALOG NUMBER: S125DIP-B375D375UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	568.6	568.6	568.6	568.6	568.6
2.5°	570.4	569.1	564.6	569.1	568.6
5°	567.7	566.8	562.3	566.4	565.9
7.5°	563.7	562.8	557.8	561.9	561.4
10°	557.8	556.9	552.0	555.6	555.1
12.5°	550.6	548.8	544.3	547.0	547.0
15°	541.2	539.8	534.9	537.1	537.1
17.5°	531.3	529.0	524.1	526.8	524.5
20°	518.2	517.3	511.5	514.6	512.4
22.5°	505.2	503.4	498.0	499.8	498.4
25°	491.3	489.0	483.2	484.1	482.7
27.5°	475.1	473.7	467.9	468.3	467.0
30°	459.3	458.0	451.2	450.3	449.0
32.5°	442.2	440.0	434.1	432.3	429.6
35°	424.2	422.4	416.1	413.9	410.3
37.5°	405.8	403.5	397.7	394.5	392.3
40°	386.9	384.6	378.3	374.3	372.9
42.5°	366.6	364.8	358.5	354.9	352.7
45°	347.3	345.5	340.1	334.7	333.3
47.5°	326.2	326.6	319.9	314.5	311.3
50°	305.9	304.6	299.2	293.3	290.2
52.5°	285.2	284.3	278.5	273.5	269.9
55°	264.5	263.2	256.9	252.8	249.7
57.5°	242.5	242.0	236.6	231.2	229.9
60°	221.8	220.0	215.0	210.5	207.4
62.5°	200.2	198.8	194.8	189.8	187.6
65°	178.6	177.7	172.7	168.7	166.9
67.5°	157.5	155.7	152.1	148.5	147.6
70°	137.7	135.4	131.4	128.7	126.9
72.5°	116.1	114.7	112.5	109.3	107.5
75°	94.9	94.0	91.8	90.4	88.6
77.5°	75.1	74.7	73.3	72.4	71.1
80°	56.7	56.7	55.8	55.3	54.4
82.5°	40.5	39.6	39.6	38.7	38.7
85°	24.7	25.2	25.2	24.7	23.8
87.5°	12.1	12.1	11.7	11.7	10.8
90°	0.4	3.2	5.7	7.4	8.2
92.5°	5.3	29.2	141.8	37.8	26.3
95°	11.7	34.7	314.9	142.9	83.5
97.5°	18.1	37.5	340.2	258.0	183.1
100°	24.9	43.0	321.0	364.7	277.3
102.5°	32.3	49.2	287.2	455.0	382.5
105°	40.2	56.2	257.7	507.4	471.0
107.5°	47.6	63.4	235.7	522.2	524.3
110°	55.8	71.1	221.1	508.2	548.5

TEST NUMBER: P1027855

CATALOG NUMBER: S125DIP-B375D375UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	64.0	78.8	212.6	478.8	545.7
115°	71.8	86.6	206.9	446.0	524.7
117.5°	78.9	94.6	203.7	416.1	493.0
120°	86.0	102.2	201.6	391.0	462.5
122.5°	93.5	109.6	199.8	370.9	435.5
125°	99.5	116.6	198.4	354.8	413.4
127.5°	104.5	123.4	197.6	340.9	393.2
130°	109.1	129.8	196.9	326.8	377.2
132.5°	112.7	135.4	196.9	311.8	361.2
135°	116.6	140.2	196.9	297.4	343.4
137.5°	121.6	144.7	197.3	282.2	324.9
140°	125.8	148.4	197.6	268.4	305.4
142.5°	130.8	152.0	198.0	256.5	287.2
145°	135.8	155.5	197.6	246.2	270.9
147.5°	141.1	158.8	196.9	237.2	256.3
150°	145.7	161.6	195.9	230.0	244.6
152.5°	150.7	164.4	194.4	223.8	235.3
155°	155.0	166.7	192.7	217.8	227.1
157.5°	158.9	169.0	190.9	212.0	219.7
160°	162.8	170.8	189.1	206.4	212.2
162.5°	166.0	172.6	187.0	201.2	205.5
165°	169.2	173.9	184.8	196.0	199.1
167.5°	171.3	174.5	182.7	191.2	193.0
170°	173.5	175.4	180.9	186.6	187.7
172.5°	174.9	175.8	178.8	182.9	182.7
175°	176.0	176.0	177.4	179.5	178.8
177.5°	176.7	176.0	176.3	177.4	176.3
180°	176.3	176.3	176.3	176.3	176.3

(END OF REPORT)