

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028095

Luminaire Tested: S125DIP-B610D375UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028095
REPORT IS A COMBINATION OF REPORTS P1002289 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D375UB40-4F0-XX-W2A-F4
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3795.7 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028095

CATALOG NUMBER: S125DIP-B610D375UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1028095

CATALOG NUMBER: S125DIP-B610D375UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65		
1	101	97	93	89	95	91	88	84	80	78	75	71	69	67	62	60	59	55		
2	92	84	78	73	86	80	74	69	71	66	62	62	59	56	54	52	50	46		
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42	39		
4	77	66	58	51	72	62	55	49	55	49	45	49	44	41	43	39	36	33		
5	71	59	50	44	66	55	48	42	50	43	39	44	39	35	39	35	32	29		
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25		
7	60	48	39	34	57	45	38	32	41	34	30	36	31	27	32	28	25	22		
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	30	25	22	20		
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18		
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6093	6093	6093
5°	6093	5951	5963
10°	6043	5815	5796
15°	5963	5652	5601
20°	5856	5462	5377
25°	5741	5256	5136
30°	5602	5041	4883
35°	5453	4816	4600
40°	5300	4577	4348
45°	5134	4345	4080
50°	4952	4082	3767
55°	4771	3791	3480
60°	4556	3485	3146
65°	4298	3131	2801
70°	4035	2724	2403
75°	3593	2243	1943
80°	3063	1675	1429
85°	2367	990	788

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5134 cd/sqm

TEST NUMBER: P1028095

CATALOG NUMBER: S125DIP-B610D375UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.7	2.4
10°-20°	253.5	6.7
20°-30°	374.2	9.9
30°-40°	436.6	11.5
40°-50°	438.5	11.6
50°-60°	384.9	10.1
60°-70°	286.7	7.6
70°-80°	163.7	4.3
80°-90°	48.0	1.3
90°-100°	132.1	3.5
100°-110°	274.3	7.2
110°-120°	256.2	6.8
120°-130°	207.3	5.5
130°-140°	166.6	4.4
140°-150°	125.7	3.3
150°-160°	88.5	2.3
160°-170°	52.2	1.4
170°-180°	17.0	0.4
0°-30°	717.4	18.9
0°-40°	1154.0	30.4
0°-60°	1977.3	52.1
0°-90°	2475.7	65.2
90°-120°	662.6	17.5
90°-150°	1162.3	30.6
90°-180°	1320.0	34.8
0°-180°	3795.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	951	951	951	951	951	
5°	949	948	940	947	946	90
15°	905	903	894	898	898	255
25°	822	818	808	810	807	378
35°	709	706	696	692	686	444
45°	581	578	569	560	558	447
55°	442	440	430	423	418	395
65°	299	297	289	282	279	296
75°	159	157	154	151	148	169
85°	41	42	42	41	40	45
90°	0	3	6	7	8	4
95°	12	34	313	142	83	12
105°	40	56	256	505	468	42
115°	71	86	206	444	522	70
125°	99	116	197	353	411	88
135°	116	140	196	296	342	90
145°	135	155	197	245	269	85
155°	154	166	192	217	226	71
165°	168	173	184	195	198	47
175°	175	175	176	179	178	17
180°	175	175	175	175	175	

TEST NUMBER: P1028095

CATALOG NUMBER: S125DIP-B610D375UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	950.9	950.9	950.9	950.9	950.9
2.5°	953.9	951.7	944.1	951.7	950.9
5°	949.4	947.9	940.4	947.2	946.4
7.5°	942.6	941.1	932.9	939.6	938.9
10°	932.9	931.4	923.1	929.1	928.3
12.5°	920.8	917.8	910.3	914.8	914.8
15°	905.0	902.8	894.5	898.3	898.3
17.5°	888.5	884.7	876.4	881.0	877.2
20°	866.7	865.2	855.4	860.6	856.9
22.5°	844.8	841.8	832.8	835.8	833.6
25°	821.5	817.8	808.0	809.5	807.2
27.5°	794.4	792.2	782.4	783.2	780.9
30°	768.1	765.8	754.6	753.1	750.8
32.5°	739.5	735.8	726.0	723.0	718.5
35°	709.4	706.4	695.9	692.1	686.1
37.5°	678.6	674.8	665.0	659.8	656.0
40°	647.0	643.2	632.7	625.9	623.7
42.5°	613.1	610.1	599.6	593.6	589.8
45°	580.8	577.8	568.7	559.7	557.5
47.5°	545.4	546.2	534.9	525.9	520.6
50°	511.6	509.3	500.3	490.5	485.2
52.5°	477.0	475.5	465.7	457.4	451.4
55°	442.4	440.1	429.6	422.8	417.5
57.5°	405.5	404.7	395.7	386.7	384.4
60°	370.9	367.9	359.6	352.1	346.8
62.5°	334.8	332.5	325.7	317.5	313.7
65°	298.7	297.2	288.9	282.1	279.1
67.5°	263.3	260.3	254.3	248.3	246.8
70°	230.2	226.4	219.7	215.2	212.2
72.5°	194.1	191.8	188.1	182.8	179.8
75°	158.7	157.2	153.5	151.2	148.2
77.5°	125.6	124.9	122.6	121.1	118.9
80°	94.8	94.8	93.3	92.5	91.0
82.5°	67.7	66.2	66.2	64.7	64.7
85°	41.4	42.1	42.1	41.4	39.9
87.5°	20.3	20.3	19.6	19.6	18.1
90°	0.4	3.2	5.7	7.4	8.1
92.5°	5.3	29.0	141.1	37.6	26.2
95°	11.7	34.4	313.3	142.2	83.1
97.5°	18.0	37.3	338.4	256.7	182.1
100°	24.8	42.8	319.3	362.8	275.8
102.5°	32.2	49.0	285.7	452.6	380.5
105°	40.0	55.8	256.4	504.8	468.5
107.5°	47.4	63.1	234.4	519.4	521.6
110°	55.5	70.7	219.9	505.4	545.6



TEST NUMBER: P1028095

CATALOG NUMBER: S125DIP-B610D375UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	63.6	78.3	211.5	476.3	542.8
115°	71.4	86.1	205.8	443.6	521.9
117.5°	78.5	94.0	202.6	413.9	490.4
120°	85.6	101.6	200.5	389.0	460.0
122.5°	93.0	109.1	198.7	369.0	433.2
125°	99.0	116.0	197.3	352.9	411.2
127.5°	104.0	122.7	196.6	339.1	391.1
130°	108.6	129.1	195.9	325.1	375.2
132.5°	112.1	134.7	195.9	310.1	359.3
135°	116.0	139.5	195.9	295.8	341.6
137.5°	120.9	144.0	196.2	280.8	323.2
140°	125.2	147.6	196.6	267.0	303.7
142.5°	130.1	151.1	197.0	255.1	285.7
145°	135.1	154.7	196.6	244.8	269.4
147.5°	140.4	157.9	195.9	236.0	254.9
150°	145.0	160.7	194.8	228.8	243.3
152.5°	149.9	163.6	193.4	222.6	234.1
155°	154.2	165.9	191.6	216.6	225.9
157.5°	158.1	168.1	189.9	210.9	218.5
160°	161.9	169.9	188.1	205.2	211.1
162.5°	165.1	171.6	186.0	200.1	204.4
165°	168.3	172.9	183.9	195.0	198.0
167.5°	170.4	173.6	181.7	190.2	192.0
170°	172.6	174.5	180.0	185.6	186.7
172.5°	174.0	174.8	177.9	181.9	181.7
175°	175.0	175.0	176.4	178.6	177.9
177.5°	175.7	175.0	175.4	176.4	175.4
180°	175.4	175.4	175.4	175.4	175.4

(END OF REPORT)