

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028111

Luminaire Tested: S125DIP-B610D610UB27-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028111
REPORT IS A COMBINATION OF REPORTS P1002305 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D610UB27-4F0-XX-W2A-F
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4818.0 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028111

CATALOG NUMBER: S125DIP-B610D610UB27-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1028111

CATALOG NUMBER: S125DIP-B610D610UB27-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48
2	89	82	76	70	82	76	70	66	64	60	57	54	51	49	44	42	41
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	35
4	74	64	56	50	68	59	52	47	50	45	41	43	38	35	35	32	30
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	32	28	26
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23
7	58	46	38	32	54	43	36	30	37	31	27	31	27	24	26	23	20
8	54	42	34	28	50	39	32	27	34	28	24	29	24	21	24	21	18
9	50	38	30	25	46	36	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6075	6075	6075
5°	6075	5934	5946
10°	6025	5799	5780
15°	5947	5636	5585
20°	5839	5447	5362
25°	5725	5241	5122
30°	5586	5027	4870
35°	5438	4802	4587
40°	5285	4564	4335
45°	5119	4332	4068
50°	4937	4070	3757
55°	4757	3781	3470
60°	4542	3475	3137
65°	4285	3122	2793
70°	4025	2716	2396
75°	3584	2235	1937
80°	3054	1670	1425
85°	2361	988	786

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5119 cd/sqm

TEST NUMBER: P1028111

CATALOG NUMBER: S125DIP-B610D610UB27-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.5	1.9
10°-20°	252.7	5.2
20°-30°	373.1	7.7
30°-40°	435.3	9.0
40°-50°	437.2	9.1
50°-60°	383.8	8.0
60°-70°	285.9	5.9
70°-80°	163.3	3.4
80°-90°	48.3	1.0
90°-100°	26.0	0.5
100°-110°	172.6	3.6
110°-120°	310.8	6.4
120°-130°	398.9	8.3
130°-140°	429.0	8.9
140°-150°	402.7	8.4
150°-160°	325.7	6.8
160°-170°	210.6	4.4
170°-180°	72.6	1.5
0°-30°	715.3	14.8
0°-40°	1150.7	23.9
0°-60°	1971.7	40.9
0°-90°	2469.1	51.2
90°-120°	509.3	10.6
90°-150°	1739.8	36.1
90°-180°	2349.0	48.8
0°-180°	4818.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	948	948	948	948	948	
5°	947	945	938	944	944	90
15°	902	900	892	896	896	254
25°	819	815	806	807	805	377
35°	707	704	694	690	684	443
45°	579	576	567	558	556	446
55°	441	439	428	422	416	394
65°	298	296	288	281	278	295
75°	158	157	153	151	148	169
85°	41	42	42	41	40	45
90°	1	5	9	12	14	4
95°	32	31	9	12	12	40
105°	167	169	169	169	168	177
115°	313	316	316	314	311	310
125°	445	449	449	447	445	397
135°	555	558	557	556	553	428
145°	643	644	644	645	642	402
155°	708	705	706	708	703	326
165°	748	744	745	748	744	211
175°	765	761	762	766	761	73
180°	765	765	765	765	765	

TEST NUMBER: P1028111

CATALOG NUMBER: S125DIP-B610D610UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	948.2	948.2	948.2	948.2	948.2
2.5°	951.2	949.0	941.5	949.0	948.2
5°	946.7	945.2	937.7	944.5	943.7
7.5°	940.0	938.5	930.2	937.0	936.2
10°	930.2	928.7	920.5	926.5	925.7
12.5°	918.2	915.2	907.7	912.2	912.2
15°	902.5	900.2	892.0	895.7	895.7
17.5°	886.0	882.2	874.0	878.5	874.7
20°	864.2	862.7	853.0	858.2	854.5
22.5°	842.5	839.5	830.4	833.4	831.2
25°	819.2	815.4	805.7	807.2	804.9
27.5°	792.2	789.9	780.2	780.9	778.7
30°	765.9	763.7	752.4	750.9	748.7
32.5°	737.4	733.7	723.9	720.9	716.4
35°	707.4	704.4	693.9	690.2	684.2
37.5°	676.7	672.9	663.2	657.9	654.2
40°	645.2	641.4	630.9	624.1	621.9
42.5°	611.4	608.4	597.9	591.9	588.1
45°	579.1	576.1	567.1	558.1	555.9
47.5°	543.9	544.6	533.4	524.4	519.1
50°	510.1	507.9	498.9	489.1	483.9
52.5°	475.6	474.1	464.4	456.1	450.1
55°	441.1	438.9	428.4	421.6	416.3
57.5°	404.3	403.6	394.6	385.6	383.3
60°	369.8	366.8	358.6	351.1	345.8
62.5°	333.8	331.6	324.8	316.6	312.8
65°	297.8	296.3	288.1	281.3	278.3
67.5°	262.6	259.6	253.6	247.6	246.1
70°	229.6	225.8	219.1	214.6	211.6
72.5°	193.5	191.3	187.5	182.3	179.3
75°	158.3	156.8	153.0	150.8	147.8
77.5°	125.3	124.5	122.3	120.8	118.5
80°	94.5	94.5	93.0	92.3	90.8
82.5°	67.5	66.0	66.0	64.5	64.5
85°	41.3	42.0	42.0	41.3	39.8
87.5°	20.3	20.3	19.5	19.5	18.0
90°	0.6	5.1	9.1	11.9	13.6
92.5°	10.8	5.7	9.1	11.9	12.5
95°	32.3	30.6	9.1	11.9	11.9
97.5°	60.7	64.1	10.2	11.3	11.9
100°	94.7	96.4	98.6	14.2	11.9
102.5°	129.2	131.5	132.6	133.8	86.2
105°	166.6	168.9	168.9	168.9	168.3
107.5°	205.2	205.2	206.3	206.9	204.6
110°	242.6	242.6	243.7	242.0	242.6

TEST NUMBER: P1028111

CATALOG NUMBER: S125DIP-B610D610UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	277.7	279.4	280.0	277.7	276.6
115°	312.9	315.7	316.3	314.0	310.6
117.5°	349.7	349.7	352.0	348.6	347.5
120°	383.7	383.2	384.9	383.7	380.9
122.5°	413.8	416.6	417.2	416.1	412.7
125°	445.0	448.9	448.9	446.7	445.0
127.5°	475.0	477.8	477.3	476.1	471.6
130°	502.2	505.0	505.6	503.9	501.1
132.5°	529.4	532.8	531.1	531.1	528.3
135°	554.9	558.3	557.2	556.1	552.7
137.5°	578.7	582.1	581.0	581.0	578.2
140°	602.0	603.1	602.5	603.7	600.3
142.5°	622.9	623.5	624.6	624.6	621.2
145°	643.4	644.5	644.5	645.1	641.7
147.5°	661.5	661.5	662.1	662.6	658.7
150°	678.5	677.4	678.5	679.6	675.1
152.5°	694.9	692.1	693.2	694.4	690.4
155°	708.5	705.1	706.3	708.0	703.4
157.5°	719.3	717.6	717.6	719.3	714.8
160°	730.6	727.2	727.8	730.1	725.5
162.5°	739.7	736.3	736.9	740.3	735.2
165°	747.7	744.3	744.8	748.2	743.7
167.5°	753.9	750.5	751.1	755.0	749.9
170°	759.0	755.0	755.6	760.1	755.0
172.5°	762.4	758.4	759.6	763.5	758.4
175°	764.7	761.3	761.8	766.4	761.3
177.5°	766.4	763.0	763.5	767.5	763.0
180°	764.7	764.7	764.7	764.7	764.7

(END OF REPORT)