

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027917

Luminaire Tested: S125DIP-B375D610UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027917
REPORT IS A COMBINATION OF REPORTS P1002048 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D610UB40-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3512.0 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027917

CATALOG NUMBER: S125DIP-B375D610UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1027917

CATALOG NUMBER: S125DIP-B375D610UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	88	84	87	84	80	77	69	67	65	55	54	52	43	42	41
2	87	80	74	69	79	73	68	64	60	57	53	49	46	44	38	36	34
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22
6	61	50	41	36	56	46	38	33	38	33	29	31	27	24	24	22	19
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15
9	49	37	29	24	45	34	27	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3624	3624	3624
5°	3624	3540	3546
10°	3594	3458	3447
15°	3547	3361	3331
20°	3482	3249	3198
25°	3414	3126	3055
30°	3331	2998	2904
35°	3243	2864	2736
40°	3152	2722	2586
45°	3053	2585	2426
50°	2945	2427	2241
55°	2838	2255	2070
60°	2709	2073	1872
65°	2555	1862	1666
70°	2400	1620	1429
75°	2137	1334	1155
80°	1823	996	849
85°	1407	590	468

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3053 cd/sqm

TEST NUMBER: P1027917

CATALOG NUMBER: S125DIP-B375D610UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.4	1.5
10°-20°	150.7	4.3
20°-30°	222.5	6.3
30°-40°	259.6	7.4
40°-50°	260.8	7.4
50°-60°	228.9	6.5
60°-70°	170.5	4.9
70°-80°	97.4	2.8
80°-90°	29.3	0.8
90°-100°	48.6	1.4
100°-110°	144.3	4.1
110°-120°	244.8	7.0
120°-130°	322.2	9.2
130°-140°	361.1	10.3
140°-150°	353.9	10.1
150°-160°	297.3	8.5
160°-170°	197.6	5.6
170°-180°	69.2	2.0
0°-30°	426.7	12.1
0°-40°	686.3	19.5
0°-60°	1176.0	33.5
0°-90°	1473.1	41.9
90°-120°	437.7	12.5
90°-150°	1474.8	42.0
90°-180°	2039.0	58.1
0°-180°	3512.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	566	566	566	566	566	
5°	565	564	559	563	563	54
15°	538	537	532	534	534	152
25°	489	486	480	481	480	225
35°	422	420	414	412	408	264
45°	345	344	338	333	332	266
55°	263	262	256	252	248	235
65°	178	177	172	168	166	176
75°	94	94	91	90	88	100
85°	25	25	25	25	24	27
90°	1	5	9	12	14	4
95°	37	38	44	48	49	39
105°	130	132	136	139	141	138
115°	245	247	248	248	247	242
125°	358	361	362	360	360	320
135°	465	468	469	469	467	358
145°	563	566	567	567	566	352
155°	645	645	645	648	645	297
165°	701	700	700	703	699	198
175°	729	727	727	730	726	69
180°	730	730	730	730	730	

TEST NUMBER: P1027917

CATALOG NUMBER: S125DIP-B375D610UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	565.6	565.6	565.6	565.6	565.6
2.5°	567.3	566.0	561.5	566.0	565.6
5°	564.7	563.8	559.3	563.3	562.9
7.5°	560.6	559.7	554.8	558.8	558.4
10°	554.8	553.9	549.0	552.6	552.1
12.5°	547.7	545.9	541.4	544.1	544.1
15°	538.3	536.9	532.0	534.2	534.2
17.5°	528.4	526.2	521.3	523.9	521.7
20°	515.4	514.5	508.7	511.9	509.6
22.5°	502.5	500.7	495.3	497.1	495.8
25°	488.6	486.4	480.5	481.4	480.1
27.5°	472.5	471.1	465.3	465.8	464.4
30°	456.8	455.5	448.8	447.9	446.5
32.5°	439.8	437.6	431.8	430.0	427.3
35°	421.9	420.1	413.9	411.6	408.1
37.5°	403.6	401.3	395.5	392.4	390.2
40°	384.8	382.6	376.3	372.3	370.9
42.5°	364.7	362.9	356.6	353.0	350.8
45°	345.4	343.6	338.3	332.9	331.5
47.5°	324.4	324.8	318.1	312.8	309.6
50°	304.3	302.9	297.5	291.7	288.6
52.5°	283.7	282.8	277.0	272.0	268.5
55°	263.1	261.7	255.5	251.5	248.3
57.5°	241.2	240.7	235.3	230.0	228.6
60°	220.6	218.8	213.9	209.4	206.3
62.5°	199.1	197.8	193.7	188.8	186.6
65°	177.6	176.7	171.8	167.8	166.0
67.5°	156.6	154.8	151.2	147.7	146.8
70°	136.9	134.7	130.7	128.0	126.2
72.5°	115.4	114.1	111.9	108.7	106.9
75°	94.4	93.5	91.3	89.9	88.1
77.5°	74.7	74.3	72.9	72.0	70.7
80°	56.4	56.4	55.5	55.0	54.1
82.5°	40.3	39.4	39.4	38.5	38.5
85°	24.6	25.1	25.1	24.6	23.7
87.5°	12.1	12.1	11.6	11.6	10.7
90°	0.6	5.1	9.1	11.9	13.6
92.5°	17.1	19.9	25.0	29.0	30.1
95°	37.0	38.1	43.8	47.8	48.9
97.5°	56.9	57.4	65.4	68.8	69.4
100°	79.6	79.6	87.0	92.1	93.2
102.5°	104.0	106.9	109.7	115.4	117.1
105°	129.6	132.5	135.9	139.3	141.0
107.5°	157.5	160.3	163.2	164.9	164.9
110°	186.5	189.3	191.0	192.7	192.2

TEST NUMBER: P1027917

CATALOG NUMBER: S125DIP-B375D610UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	216.0	217.2	219.4	220.0	218.9
115°	245.0	247.3	248.4	247.9	247.3
117.5°	274.6	275.2	276.3	276.9	274.6
120°	301.9	304.7	305.3	305.3	303.0
122.5°	331.4	332.0	333.7	333.1	331.4
125°	357.6	361.0	361.6	360.4	359.9
127.5°	386.6	388.3	388.9	388.3	387.2
130°	412.2	415.0	416.1	415.6	414.4
132.5°	437.8	442.9	442.3	441.7	440.0
135°	465.0	468.5	469.0	469.0	466.7
137.5°	490.6	494.0	495.2	495.7	492.9
140°	515.1	517.9	519.6	520.8	517.9
142.5°	539.5	541.8	544.1	544.6	541.8
145°	563.4	565.7	567.4	567.4	565.7
147.5°	585.6	587.3	588.4	590.1	585.6
150°	607.7	607.2	609.4	609.4	608.3
152.5°	625.9	627.1	627.6	629.3	627.1
155°	644.7	644.7	645.3	647.5	644.7
157.5°	661.7	660.6	661.2	663.5	659.5
160°	676.5	674.8	675.4	677.7	674.8
162.5°	689.6	688.5	688.5	691.3	687.9
165°	701.0	699.8	700.4	702.7	699.3
167.5°	711.2	708.9	708.9	712.3	708.9
170°	719.2	716.9	716.9	720.3	716.3
172.5°	724.8	722.6	722.6	726.0	722.6
175°	728.8	726.6	726.6	730.0	726.0
177.5°	731.7	729.4	728.8	732.2	728.3
180°	730.5	730.5	730.5	730.5	730.5

(END OF REPORT)