

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028208

Luminaire Tested: S125DIP-B850D1090UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028208
REPORT IS A COMBINATION OF REPORTS P1002450 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D1090UB30-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6982.0 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028208

CATALOG NUMBER: S125DIP-B850D1090UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028208

CATALOG NUMBER: S125DIP-B850D1090UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	39
3	81	71	64	58	74	66	60	55	56	51	47	47	43	40	38	36	33
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	25	22
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	30	25	46	35	28	24	30	25	21	26	22	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8456	8456	8456
5°	8456	8259	8275
10°	8386	8070	8045
15°	8276	7843	7774
20°	8127	7581	7462
25°	7968	7295	7128
30°	7774	6996	6777
35°	7569	6683	6384
40°	7356	6353	6034
45°	7126	6030	5662
50°	6872	5665	5229
55°	6621	5262	4831
60°	6322	4837	4367
65°	5964	4345	3888
70°	5601	3780	3334
75°	4988	3112	2696
80°	4253	2325	1983
85°	3282	1376	1092

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7126 cd/sqm

TEST NUMBER: P1028208

CATALOG NUMBER: S125DIP-B850D1090UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.5	1.8
10°-20°	351.8	5.0
20°-30°	519.3	7.4
30°-40°	605.9	8.7
40°-50°	608.5	8.7
50°-60°	534.2	7.7
60°-70°	397.9	5.7
70°-80°	227.2	3.3
80°-90°	67.6	1.0
90°-100°	84.5	1.2
100°-110°	250.9	3.6
110°-120°	425.6	6.1
120°-130°	560.2	8.0
130°-140°	627.8	9.0
140°-150°	615.3	8.8
150°-160°	516.9	7.4
160°-170°	343.6	4.9
170°-180°	120.2	1.7
0°-30°	995.6	14.3
0°-40°	1601.5	22.9
0°-60°	2744.3	39.3
0°-90°	3437.0	49.2
90°-120°	761.0	10.9
90°-150°	2564.3	36.7
90°-180°	3545.0	50.8
0°-180°	6982.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1320	1320	1320	1320	1320	
5°	1318	1316	1305	1314	1314	125
15°	1256	1253	1241	1247	1247	354
25°	1140	1135	1121	1124	1120	525
35°	985	980	966	961	952	616
45°	806	802	789	777	774	621
55°	614	611	596	587	580	548
65°	414	412	401	392	387	411
75°	220	218	213	210	206	235
85°	57	58	58	57	55	63
90°	1	9	16	21	24	8
95°	64	66	76	83	85	67
105°	225	230	236	242	245	240
115°	426	430	432	431	430	421
125°	622	628	629	627	626	557
135°	809	814	816	816	812	623
145°	980	984	986	986	984	612
155°	1121	1121	1122	1126	1121	516
165°	1219	1217	1218	1222	1216	344
175°	1267	1263	1263	1269	1262	120
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1028208

CATALOG NUMBER: S125DIP-B850D1090UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.8	1319.8	1319.8	1319.8	1319.8
2.5°	1323.9	1320.8	1310.4	1320.8	1319.8
5°	1317.7	1315.6	1305.1	1314.5	1313.5
7.5°	1308.3	1306.2	1294.7	1304.1	1303.1
10°	1294.7	1292.6	1281.1	1289.5	1288.4
12.5°	1278.0	1273.8	1263.4	1269.6	1269.6
15°	1256.1	1252.9	1241.4	1246.7	1246.7
17.5°	1233.1	1227.9	1216.4	1222.7	1217.4
20°	1202.8	1200.7	1187.2	1194.5	1189.2
22.5°	1172.5	1168.4	1155.8	1160.0	1156.9
25°	1140.2	1134.9	1121.4	1123.5	1120.3
27.5°	1102.6	1099.4	1085.9	1086.9	1083.8
30°	1066.0	1062.9	1047.2	1045.2	1042.0
32.5°	1026.4	1021.1	1007.6	1003.4	997.1
35°	984.6	980.4	965.8	960.6	952.2
37.5°	941.8	936.6	923.0	915.7	910.5
40°	897.9	892.7	878.1	868.7	865.6
42.5°	851.0	846.8	832.2	823.8	818.6
45°	806.1	801.9	789.3	776.8	773.7
47.5°	757.0	758.0	742.4	729.8	722.5
50°	710.0	706.9	694.3	680.8	673.5
52.5°	662.0	659.9	646.3	634.8	626.5
55°	613.9	610.8	596.2	586.8	579.5
57.5°	562.8	561.7	549.2	536.7	533.5
60°	514.7	510.6	499.1	488.6	481.3
62.5°	464.6	461.5	452.1	440.6	435.4
65°	414.5	412.4	400.9	391.5	387.4
67.5°	365.4	361.3	352.9	344.6	342.5
70°	319.5	314.3	304.9	298.6	294.4
72.5°	269.4	266.2	261.0	253.7	249.5
75°	220.3	218.2	213.0	209.9	205.7
77.5°	174.4	173.3	170.2	168.1	165.0
80°	131.6	131.6	129.5	128.4	126.3
82.5°	94.0	91.9	91.9	89.8	89.8
85°	57.4	58.5	58.5	57.4	55.3
87.5°	28.2	28.2	27.1	27.1	25.1
90°	1.0	8.9	15.8	20.8	23.7
92.5°	29.7	34.6	43.5	50.4	52.4
95°	64.3	66.2	76.1	83.0	85.0
97.5°	98.8	99.8	113.7	119.6	120.6
100°	138.4	138.4	151.2	160.1	162.1
102.5°	180.9	185.8	190.8	200.7	203.6
105°	225.4	230.3	236.2	242.2	245.1
107.5°	273.8	278.8	283.7	286.7	286.7
110°	324.2	329.2	332.1	335.1	334.1

TEST NUMBER: P1028208

CATALOG NUMBER: S125DIP-B850D1090UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.6	377.6	381.6	382.5	380.6
115°	426.0	430.0	432.0	431.0	430.0
117.5°	477.4	478.4	480.4	481.4	477.4
120°	524.9	529.8	530.8	530.8	526.9
122.5°	576.3	577.3	580.2	579.3	576.3
125°	621.8	627.7	628.7	626.7	625.7
127.5°	672.2	675.1	676.1	675.1	673.2
130°	716.6	721.6	723.6	722.6	720.6
132.5°	761.1	770.0	769.0	768.1	765.1
135°	808.6	814.5	815.5	815.5	811.5
137.5°	853.1	859.0	861.0	862.0	857.0
140°	895.6	900.5	903.5	905.4	900.5
142.5°	938.1	942.0	946.0	947.0	942.0
145°	979.6	983.5	986.5	986.5	983.5
147.5°	1018.1	1021.1	1023.1	1026.0	1018.1
150°	1056.7	1055.7	1059.7	1059.7	1057.7
152.5°	1088.3	1090.3	1091.3	1094.2	1090.3
155°	1120.9	1120.9	1121.9	1125.9	1120.9
157.5°	1150.6	1148.6	1149.6	1153.6	1146.6
160°	1176.3	1173.3	1174.3	1178.3	1173.3
162.5°	1199.0	1197.1	1197.1	1202.0	1196.1
165°	1218.8	1216.8	1217.8	1221.8	1215.8
167.5°	1236.6	1232.6	1232.6	1238.6	1232.6
170°	1250.4	1246.5	1246.5	1252.4	1245.5
172.5°	1260.3	1256.4	1256.4	1262.3	1256.4
175°	1267.2	1263.3	1263.3	1269.2	1262.3
177.5°	1272.2	1268.2	1267.2	1273.2	1266.2
180°	1270.2	1270.2	1270.2	1270.2	1270.2

(END OF REPORT)