

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028217

Luminaire Tested: S125DIP-B850D1090UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028217
REPORT IS A COMBINATION OF REPORTS P1002459 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D1090UB35-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7012.0 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028217

CATALOG NUMBER: S125DIP-B850D1090UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028217

CATALOG NUMBER: S125DIP-B850D1090UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	39
3	81	71	64	58	74	66	60	55	56	51	47	47	43	40	38	36	33
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	25	22
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	30	25	46	35	28	24	30	25	21	26	22	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8493	8493	8493
5°	8493	8295	8311
10°	8423	8105	8080
15°	8313	7878	7807
20°	8163	7614	7494
25°	8002	7327	7160
30°	7809	7027	6807
35°	7602	6713	6412
40°	7388	6380	6060
45°	7157	6057	5687
50°	6902	5690	5252
55°	6650	5285	4852
60°	6350	4858	4386
65°	5990	4364	3905
70°	5625	3796	3349
75°	5011	3125	2708
80°	4269	2334	1992
85°	3299	1380	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7157 cd/sqm

TEST NUMBER: P1028217

CATALOG NUMBER: S125DIP-B850D1090UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	1.8
10°-20°	353.3	5.0
20°-30°	521.6	7.4
30°-40°	608.6	8.7
40°-50°	611.2	8.7
50°-60°	536.5	7.7
60°-70°	399.6	5.7
70°-80°	228.2	3.3
80°-90°	67.9	1.0
90°-100°	84.8	1.2
100°-110°	252.0	3.6
110°-120°	427.4	6.1
120°-130°	562.6	8.0
130°-140°	630.4	9.0
140°-150°	617.9	8.8
150°-160°	519.1	7.4
160°-170°	345.0	4.9
170°-180°	120.7	1.7
0°-30°	1000.0	14.3
0°-40°	1608.5	22.9
0°-60°	2756.3	39.3
0°-90°	3452.0	49.2
90°-120°	764.2	10.9
90°-150°	2575.2	36.7
90°-180°	3560.0	50.8
0°-180°	7012.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1323	1321	1311	1320	1319	126
15°	1262	1258	1247	1252	1252	356
25°	1145	1140	1126	1128	1125	527
35°	989	985	970	965	956	619
45°	810	805	793	780	777	624
55°	617	614	599	589	582	550
65°	416	414	403	393	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	63
90°	1	9	16	21	24	8
95°	64	66	76	83	85	67
105°	226	231	237	243	246	241
115°	428	432	434	433	432	423
125°	624	630	631	629	628	559
135°	812	818	819	819	815	626
145°	984	988	991	991	988	615
155°	1126	1126	1127	1131	1126	519
165°	1224	1222	1223	1227	1221	345
175°	1273	1269	1269	1275	1268	121
180°	1276	1276	1276	1276	1276	

TEST NUMBER: P1028217

CATALOG NUMBER: S125DIP-B850D1090UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1325.5	1325.5	1325.5	1325.5	1325.5
2.5°	1329.7	1326.6	1316.1	1326.6	1325.5
5°	1323.4	1321.3	1310.8	1320.3	1319.2
7.5°	1314.0	1311.9	1300.4	1309.8	1308.7
10°	1300.4	1298.3	1286.7	1295.1	1294.1
12.5°	1283.6	1279.4	1268.9	1275.2	1275.2
15°	1261.6	1258.4	1246.9	1252.1	1252.1
17.5°	1238.5	1233.2	1221.7	1228.0	1222.7
20°	1208.1	1206.0	1192.3	1199.7	1194.4
22.5°	1177.7	1173.5	1160.9	1165.1	1161.9
25°	1145.1	1139.9	1126.3	1128.4	1125.2
27.5°	1107.4	1104.2	1090.6	1091.7	1088.5
30°	1070.7	1067.5	1051.8	1049.7	1046.6
32.5°	1030.8	1025.6	1012.0	1007.8	1001.5
35°	988.9	984.7	970.0	964.8	956.4
37.5°	945.9	940.7	927.0	919.7	914.4
40°	901.9	896.6	881.9	872.5	869.3
42.5°	854.7	850.5	835.8	827.4	822.2
45°	809.6	805.4	792.8	780.2	777.1
47.5°	760.3	761.3	745.6	733.0	725.7
50°	713.1	709.9	697.4	683.7	676.4
52.5°	664.9	662.8	649.1	637.6	629.2
55°	616.6	613.5	598.8	589.4	582.0
57.5°	565.2	564.2	551.6	539.0	535.9
60°	517.0	512.8	501.3	490.8	483.4
62.5°	466.7	463.5	454.1	442.5	437.3
65°	416.3	414.2	402.7	393.3	389.1
67.5°	367.0	362.8	354.5	346.1	344.0
70°	320.9	315.6	306.2	299.9	295.7
72.5°	270.6	267.4	262.2	254.8	250.6
75°	221.3	219.2	213.9	210.8	206.6
77.5°	175.1	174.1	170.9	168.8	165.7
80°	132.1	132.1	130.0	129.0	126.9
82.5°	94.4	92.3	92.3	90.2	90.2
85°	57.7	58.7	58.7	57.7	55.6
87.5°	28.3	28.3	27.3	27.3	25.2
90°	1.0	8.9	15.9	20.8	23.8
92.5°	29.8	34.7	43.7	50.6	52.6
95°	64.5	66.5	76.4	83.4	85.4
97.5°	99.3	100.3	114.2	120.1	121.1
100°	139.0	139.0	151.9	160.8	162.8
102.5°	181.7	186.6	191.6	201.5	204.5
105°	226.3	231.3	237.2	243.2	246.2
107.5°	275.0	279.9	284.9	287.9	287.9
110°	325.6	330.6	333.5	336.5	335.5



TEST NUMBER: P1028217

CATALOG NUMBER: S125DIP-B850D1090UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	377.2	379.2	383.2	384.2	382.2
115°	427.8	431.8	433.8	432.8	431.8
117.5°	479.5	480.4	482.4	483.4	479.5
120°	527.1	532.1	533.1	533.1	529.1
122.5°	578.7	579.7	582.7	581.7	578.7
125°	624.4	630.3	631.3	629.3	628.4
127.5°	675.0	678.0	679.0	678.0	676.0
130°	719.7	724.6	726.6	725.6	723.7
132.5°	764.3	773.3	772.3	771.3	768.3
135°	812.0	818.0	818.9	818.9	815.0
137.5°	856.7	862.6	864.6	865.6	860.6
140°	899.4	904.3	907.3	909.3	904.3
142.5°	942.0	946.0	950.0	951.0	946.0
145°	983.7	987.7	990.7	990.7	987.7
147.5°	1022.4	1025.4	1027.4	1030.4	1022.4
150°	1061.2	1060.2	1064.1	1064.1	1062.1
152.5°	1092.9	1094.9	1095.9	1098.9	1094.9
155°	1125.7	1125.7	1126.7	1130.6	1125.7
157.5°	1155.5	1153.5	1154.5	1158.4	1151.5
160°	1181.3	1178.3	1179.3	1183.3	1178.3
162.5°	1204.1	1202.1	1202.1	1207.1	1201.1
165°	1224.0	1222.0	1223.0	1226.9	1221.0
167.5°	1241.8	1237.8	1237.8	1243.8	1237.8
170°	1255.7	1251.7	1251.7	1257.7	1250.8
172.5°	1265.6	1261.7	1261.7	1267.6	1261.7
175°	1272.6	1268.6	1268.6	1274.6	1267.6
177.5°	1277.6	1273.6	1272.6	1278.5	1271.6
180°	1275.6	1275.6	1275.6	1275.6	1275.6

(END OF REPORT)