

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028218

Luminaire Tested: S125DIP-B850D1090UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028218
REPORT IS A COMBINATION OF REPORTS P1002460 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D1090UB35-4F0-XX-W2A-F4
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7157.6 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028218

CATALOG NUMBER: S125DIP-B850D1090UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1028218

CATALOG NUMBER: S125DIP-B850D1090UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	97	93	89	86	89	86	82	79	72	70	67	60	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	39
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	25
6	62	50	42	36	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16
10	47	35	27	22	43	32	26	21	28	22	19	24	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8493	8493	8493
5°	8493	8295	8311
10°	8423	8105	8080
15°	8313	7878	7807
20°	8163	7614	7494
25°	8002	7327	7160
30°	7809	7027	6807
35°	7602	6713	6412
40°	7388	6380	6060
45°	7157	6057	5687
50°	6902	5690	5252
55°	6650	5285	4852
60°	6350	4858	4386
65°	5990	4364	3905
70°	5625	3796	3349
75°	5011	3125	2708
80°	4269	2334	1992
85°	3299	1380	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7157 cd/sqm

TEST NUMBER: P1028218

CATALOG NUMBER: S125DIP-B850D1090UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	1.7
10°-20°	353.3	4.9
20°-30°	521.6	7.3
30°-40°	608.6	8.5
40°-50°	611.2	8.5
50°-60°	536.5	7.5
60°-70°	399.6	5.6
70°-80°	228.2	3.2
80°-90°	67.9	0.9
90°-100°	370.8	5.2
100°-110°	770.1	10.8
110°-120°	719.3	10.0
120°-130°	582.1	8.1
130°-140°	467.7	6.5
140°-150°	353.0	4.9
150°-160°	248.5	3.5
160°-170°	146.5	2.0
170°-180°	47.6	0.7
0°-30°	1000.0	14.0
0°-40°	1608.5	22.5
0°-60°	2756.3	38.5
0°-90°	3452.0	48.2
90°-120°	1860.2	26.0
90°-150°	3263.0	45.6
90°-180°	3706.0	51.8
0°-180°	7157.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1323	1321	1311	1320	1319	126
15°	1262	1258	1247	1252	1252	356
25°	1145	1140	1126	1128	1125	527
35°	989	985	970	965	956	619
45°	810	805	793	780	777	624
55°	617	614	599	589	582	550
65°	416	414	403	393	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	63
90°	1	9	16	21	23	6
95°	33	97	880	399	233	34
105°	112	157	720	1417	1315	118
115°	200	242	578	1245	1465	197
125°	278	326	554	991	1154	247
135°	326	392	550	830	959	253
145°	379	434	552	687	756	238
155°	433	466	538	608	634	199
165°	472	485	516	547	556	133
175°	491	491	495	501	499	47
180°	492	492	492	492	492	

TEST NUMBER: P1028218

CATALOG NUMBER: S125DIP-B850D1090UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1325.5	1325.5	1325.5	1325.5	1325.5
2.5°	1329.7	1326.6	1316.1	1326.6	1325.5
5°	1323.4	1321.3	1310.8	1320.3	1319.2
7.5°	1314.0	1311.9	1300.4	1309.8	1308.7
10°	1300.4	1298.3	1286.7	1295.1	1294.1
12.5°	1283.6	1279.4	1268.9	1275.2	1275.2
15°	1261.6	1258.4	1246.9	1252.1	1252.1
17.5°	1238.5	1233.2	1221.7	1228.0	1222.7
20°	1208.1	1206.0	1192.3	1199.7	1194.4
22.5°	1177.7	1173.5	1160.9	1165.1	1161.9
25°	1145.1	1139.9	1126.3	1128.4	1125.2
27.5°	1107.4	1104.2	1090.6	1091.7	1088.5
30°	1070.7	1067.5	1051.8	1049.7	1046.6
32.5°	1030.8	1025.6	1012.0	1007.8	1001.5
35°	988.9	984.7	970.0	964.8	956.4
37.5°	945.9	940.7	927.0	919.7	914.4
40°	901.9	896.6	881.9	872.5	869.3
42.5°	854.7	850.5	835.8	827.4	822.2
45°	809.6	805.4	792.8	780.2	777.1
47.5°	760.3	761.3	745.6	733.0	725.7
50°	713.1	709.9	697.4	683.7	676.4
52.5°	664.9	662.8	649.1	637.6	629.2
55°	616.6	613.5	598.8	589.4	582.0
57.5°	565.2	564.2	551.6	539.0	535.9
60°	517.0	512.8	501.3	490.8	483.4
62.5°	466.7	463.5	454.1	442.5	437.3
65°	416.3	414.2	402.7	393.3	389.1
67.5°	367.0	362.8	354.5	346.1	344.0
70°	320.9	315.6	306.2	299.9	295.7
72.5°	270.6	267.4	262.2	254.8	250.6
75°	221.3	219.2	213.9	210.8	206.6
77.5°	175.1	174.1	170.9	168.8	165.7
80°	132.1	132.1	130.0	129.0	126.9
82.5°	94.4	92.3	92.3	90.2	90.2
85°	57.7	58.7	58.7	57.7	55.6
87.5°	28.3	28.3	27.3	27.3	25.2
90°	1.0	8.9	15.9	20.8	22.8
92.5°	14.9	81.4	396.1	105.7	73.5
95°	32.8	96.8	879.5	399.0	233.3
97.5°	50.6	104.7	950.0	720.7	511.2
100°	69.5	120.1	896.4	1018.4	774.3
102.5°	90.3	137.5	802.1	1270.6	1068.1
105°	112.2	156.8	719.7	1417.0	1315.3
107.5°	133.0	177.2	658.1	1458.2	1464.2
110°	155.8	198.5	617.4	1419.0	1531.6

TEST NUMBER: P1028218

CATALOG NUMBER: S125DIP-B850D1090UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	178.7	219.9	593.6	1337.1	1523.7
115°	200.5	241.7	577.7	1245.3	1465.1
117.5°	220.4	264.0	568.8	1161.9	1376.8
120°	240.2	285.4	562.8	1091.9	1291.4
122.5°	261.1	306.2	557.9	1035.8	1216.0
125°	277.9	325.6	553.9	990.6	1154.4
127.5°	291.8	344.4	551.9	952.0	1097.9
130°	304.7	362.3	549.9	912.8	1053.2
132.5°	314.7	378.2	549.9	870.6	1008.5
135°	325.6	391.6	549.9	830.4	958.9
137.5°	339.5	404.0	550.9	788.2	907.3
140°	351.4	414.4	551.9	749.4	852.7
142.5°	365.3	424.4	552.9	716.2	802.1
145°	379.2	434.3	551.9	687.4	756.4
147.5°	394.1	443.2	549.9	662.6	715.7
150°	407.0	451.2	546.9	642.2	682.9
152.5°	420.9	459.1	543.0	624.8	657.1
155°	432.8	465.6	538.0	608.0	634.3
157.5°	443.7	472.0	533.0	592.1	613.5
160°	454.6	477.0	528.1	576.2	592.6
162.5°	463.6	482.0	522.1	561.8	573.7
165°	472.5	485.4	516.2	547.4	555.9
167.5°	478.5	487.4	510.2	534.0	539.0
170°	484.4	489.9	505.3	521.1	524.1
172.5°	488.4	490.9	499.3	510.7	510.2
175°	491.4	491.4	495.3	501.3	499.3
177.5°	493.3	491.4	492.4	495.3	492.4
180°	492.4	492.4	492.4	492.4	492.4

(END OF REPORT)