

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027986

Luminaire Tested: S125DIP-B610D1090UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027986
REPORT IS A COMBINATION OF REPORTS P1002150 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D1090UB30-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6036.0 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027986

CATALOG NUMBER: S125DIP-B610D1090UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1027986

CATALOG NUMBER: S125DIP-B610D1090UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48
1	96	91	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34
3	79	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17
8	53	40	33	27	48	37	30	26	31	26	22	25	22	19	20	17	15
9	49	37	29	24	45	34	27	23	29	23	20	23	20	17	19	16	14
10	46	34	27	22	42	31	25	20	26	21	18	22	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6127	6127	6127
5°	6127	5985	5997
10°	6076	5848	5829
15°	5997	5684	5632
20°	5889	5493	5407
25°	5773	5285	5165
30°	5634	5069	4911
35°	5484	4843	4626
40°	5330	4603	4372
45°	5163	4370	4103
50°	4980	4105	3789
55°	4798	3813	3500
60°	4581	3504	3165
65°	4322	3148	2817
70°	4058	2738	2417
75°	3614	2254	1953
80°	3080	1684	1436
85°	2378	997	792

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5163 cd/sqm

TEST NUMBER: P1027986

CATALOG NUMBER: S125DIP-B610D1090UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.2	1.5
10°-20°	254.9	4.2
20°-30°	376.3	6.2
30°-40°	439.0	7.3
40°-50°	440.9	7.3
50°-60°	387.1	6.4
60°-70°	288.3	4.8
70°-80°	164.6	2.7
80°-90°	49.5	0.8
90°-100°	84.5	1.4
100°-110°	250.9	4.2
110°-120°	425.6	7.1
120°-130°	560.2	9.3
130°-140°	627.8	10.4
140°-150°	615.3	10.2
150°-160°	516.9	8.6
160°-170°	343.6	5.7
170°-180°	120.2	2.0
0°-30°	721.4	12.0
0°-40°	1160.5	19.2
0°-60°	1988.5	32.9
0°-90°	2491.0	41.3
90°-120°	761.0	12.6
90°-150°	2564.3	42.5
90°-180°	3545.0	58.7
0°-180°	6036.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	956	956	956	956	956	
5°	955	953	946	952	952	91
15°	910	908	900	903	903	257
25°	826	822	812	814	812	380
35°	713	710	700	696	690	446
45°	584	581	572	563	561	450
55°	445	443	432	425	420	397
65°	300	299	290	284	281	298
75°	160	158	154	152	149	170
85°	42	42	42	42	40	46
90°	1	9	16	21	24	7
95°	64	66	76	83	85	67
105°	225	230	236	242	245	240
115°	426	430	432	431	430	421
125°	622	628	629	627	626	557
135°	809	814	816	816	812	623
145°	980	984	986	986	984	612
155°	1121	1121	1122	1126	1121	516
165°	1219	1217	1218	1222	1216	344
175°	1267	1263	1263	1269	1262	120
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1027986

CATALOG NUMBER: S125DIP-B610D1090UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	956.3	956.3	956.3	956.3	956.3
2.5°	959.3	957.1	949.5	957.1	956.3
5°	954.8	953.3	945.7	952.5	951.8
7.5°	948.0	946.5	938.1	944.9	944.2
10°	938.1	936.6	928.3	934.4	933.6
12.5°	926.0	923.0	915.4	920.0	920.0
15°	910.1	907.9	899.6	903.3	903.3
17.5°	893.5	889.7	881.4	885.9	882.2
20°	871.6	870.0	860.2	865.5	861.7
22.5°	849.6	846.6	837.5	840.5	838.3
25°	826.2	822.4	812.5	814.1	811.8
27.5°	798.9	796.7	786.8	787.6	785.3
30°	772.5	770.2	758.8	757.3	755.0
32.5°	743.7	739.9	730.1	727.1	722.5
35°	713.4	710.4	699.8	696.0	690.0
37.5°	682.4	678.6	668.8	663.5	659.7
40°	650.6	646.9	636.3	629.5	627.2
42.5°	616.6	613.6	603.0	596.9	593.1
45°	584.1	581.0	572.0	562.9	560.6
47.5°	548.5	549.3	537.9	528.8	523.5
50°	514.5	512.2	503.1	493.3	488.0
52.5°	479.7	478.1	468.3	460.0	453.9
55°	444.9	442.6	432.0	425.2	419.9
57.5°	407.8	407.0	398.0	388.9	386.6
60°	373.0	370.0	361.6	354.1	348.8
62.5°	336.7	334.4	327.6	319.3	315.5
65°	300.4	298.8	290.5	283.7	280.7
67.5°	264.8	261.8	255.7	249.7	248.2
70°	231.5	227.7	220.9	216.4	213.4
72.5°	195.2	192.9	189.1	183.8	180.8
75°	159.6	158.1	154.3	152.1	149.0
77.5°	126.3	125.6	123.3	121.8	119.5
80°	95.3	95.3	93.8	93.1	91.5
82.5°	68.1	66.6	66.6	65.1	65.1
85°	41.6	42.4	42.4	41.6	40.1
87.5°	20.4	20.4	19.7	19.7	18.2
90°	1.0	8.9	15.8	20.8	23.7
92.5°	29.7	34.6	43.5	50.4	52.4
95°	64.3	66.2	76.1	83.0	85.0
97.5°	98.8	99.8	113.7	119.6	120.6
100°	138.4	138.4	151.2	160.1	162.1
102.5°	180.9	185.8	190.8	200.7	203.6
105°	225.4	230.3	236.2	242.2	245.1
107.5°	273.8	278.8	283.7	286.7	286.7
110°	324.2	329.2	332.1	335.1	334.1

TEST NUMBER: P1027986

CATALOG NUMBER: S125DIP-B610D1090UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.6	377.6	381.6	382.5	380.6
115°	426.0	430.0	432.0	431.0	430.0
117.5°	477.4	478.4	480.4	481.4	477.4
120°	524.9	529.8	530.8	530.8	526.9
122.5°	576.3	577.3	580.2	579.3	576.3
125°	621.8	627.7	628.7	626.7	625.7
127.5°	672.2	675.1	676.1	675.1	673.2
130°	716.6	721.6	723.6	722.6	720.6
132.5°	761.1	770.0	769.0	768.1	765.1
135°	808.6	814.5	815.5	815.5	811.5
137.5°	853.1	859.0	861.0	862.0	857.0
140°	895.6	900.5	903.5	905.4	900.5
142.5°	938.1	942.0	946.0	947.0	942.0
145°	979.6	983.5	986.5	986.5	983.5
147.5°	1018.1	1021.1	1023.1	1026.0	1018.1
150°	1056.7	1055.7	1059.7	1059.7	1057.7
152.5°	1088.3	1090.3	1091.3	1094.2	1090.3
155°	1120.9	1120.9	1121.9	1125.9	1120.9
157.5°	1150.6	1148.6	1149.6	1153.6	1146.6
160°	1176.3	1173.3	1174.3	1178.3	1173.3
162.5°	1199.0	1197.1	1197.1	1202.0	1196.1
165°	1218.8	1216.8	1217.8	1221.8	1215.8
167.5°	1236.6	1232.6	1232.6	1238.6	1232.6
170°	1250.4	1246.5	1246.5	1252.4	1245.5
172.5°	1260.3	1256.4	1256.4	1262.3	1256.4
175°	1267.2	1263.3	1263.3	1269.2	1262.3
177.5°	1272.2	1268.2	1267.2	1273.2	1266.2
180°	1270.2	1270.2	1270.2	1270.2	1270.2

(END OF REPORT)