

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028279

Luminaire Tested: S125DIP-B850D1270UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028279
REPORT IS A COMBINATION OF REPORTS P1002536 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D1270UB50-4F0-XX-W2A-F
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7933.0 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028279

CATALOG NUMBER: S125DIP-B850D1270UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1028279

CATALOG NUMBER: S125DIP-B850D1270UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	48	48	42
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41	41	41	35
2	87	80	74	69	79	73	68	63	60	57	53	48	46	44	38	36	34	34	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	29	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	25	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	22	22	18
6	61	49	41	36	56	45	38	33	38	33	29	31	27	24	24	21	19	19	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	17	17	14
8	53	40	33	28	48	37	30	26	31	26	22	26	22	19	20	17	15	15	15	13
9	49	37	29	24	45	34	27	23	29	23	20	24	20	17	19	16	14	14	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	13	13	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8131	8131	8131
5°	8131	7942	7957
10°	8064	7760	7735
15°	7958	7542	7475
20°	7815	7289	7175
25°	7662	7014	6855
30°	7476	6727	6517
35°	7278	6427	6138
40°	7073	6109	5802
45°	6852	5799	5445
50°	6608	5448	5028
55°	6367	5060	4645
60°	6080	4651	4199
65°	5735	4178	3738
70°	5385	3635	3206
75°	4796	2992	2593
80°	4088	2235	1907
85°	3156	1321	1051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6852 cd/sqm

TEST NUMBER: P1028279

CATALOG NUMBER: S125DIP-B850D1270UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.7	1.5
10°-20°	338.2	4.3
20°-30°	499.4	6.3
30°-40°	582.6	7.3
40°-50°	585.2	7.4
50°-60°	513.6	6.5
60°-70°	382.6	4.8
70°-80°	218.5	2.8
80°-90°	65.3	0.8
90°-100°	51.2	0.6
100°-110°	340.0	4.3
110°-120°	612.3	7.7
120°-130°	785.9	9.9
130°-140°	845.3	10.7
140°-150°	793.3	10.0
150°-160°	641.7	8.1
160°-170°	415.0	5.2
170°-180°	143.1	1.8
0°-30°	957.4	12.1
0°-40°	1540.0	19.4
0°-60°	2638.8	33.3
0°-90°	3305.2	41.7
90°-120°	1003.5	12.6
90°-150°	3428.0	43.2
90°-180°	4628.0	58.3
0°-180°	7933.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1267	1265	1255	1264	1263	120
15°	1208	1205	1194	1199	1199	341
25°	1096	1091	1078	1080	1077	504
35°	947	943	929	924	916	592
45°	775	771	759	747	744	597
55°	590	587	573	564	557	527
65°	399	397	386	376	372	395
75°	212	210	205	202	198	226
85°	55	56	56	55	53	60
90°	1	10	18	24	27	7
95°	64	60	18	24	24	78
105°	328	333	333	333	332	348
115°	616	622	623	619	612	611
125°	877	884	884	880	877	783
135°	1093	1100	1098	1096	1089	843
145°	1268	1270	1270	1271	1264	793
155°	1396	1389	1392	1395	1386	643
165°	1473	1466	1468	1474	1465	416
175°	1506	1500	1501	1510	1500	143
180°	1506	1506	1506	1506	1506	

TEST NUMBER: P1028279

CATALOG NUMBER: S125DIP-B850D1270UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1269.0	1269.0	1269.0	1269.0	1269.0
2.5°	1273.1	1270.0	1260.0	1270.0	1269.0
5°	1267.0	1265.0	1255.0	1264.0	1263.0
7.5°	1258.0	1256.0	1244.9	1254.0	1253.0
10°	1244.9	1242.9	1231.9	1239.9	1238.9
12.5°	1228.9	1224.9	1214.8	1220.8	1220.8
15°	1207.8	1204.8	1193.7	1198.8	1198.8
17.5°	1185.7	1180.7	1169.6	1175.7	1170.6
20°	1156.6	1154.6	1141.5	1148.6	1143.5
22.5°	1127.5	1123.5	1111.4	1115.4	1112.4
25°	1096.4	1091.3	1078.3	1080.3	1077.3
27.5°	1060.2	1057.2	1044.1	1045.2	1042.1
30°	1025.1	1022.1	1007.0	1005.0	1002.0
32.5°	986.9	981.9	968.8	964.8	958.8
35°	946.8	942.7	928.7	923.7	915.6
37.5°	905.6	900.6	887.5	880.5	875.5
40°	863.4	858.4	844.4	835.3	832.3
42.5°	818.2	814.2	800.2	792.1	787.1
45°	775.1	771.1	759.0	747.0	744.0
47.5°	727.9	728.9	713.8	701.8	694.8
50°	682.7	679.7	667.7	654.6	647.6
52.5°	636.5	634.5	621.5	610.4	602.4
55°	590.3	587.3	573.3	564.2	557.2
57.5°	541.1	540.1	528.1	516.0	513.0
60°	495.0	490.9	479.9	469.9	462.8
62.5°	446.8	443.8	434.7	423.7	418.7
65°	398.6	396.6	385.5	376.5	372.5
67.5°	351.4	347.4	339.3	331.3	329.3
70°	307.2	302.2	293.2	287.1	283.1
72.5°	259.0	256.0	251.0	244.0	240.0
75°	211.8	209.8	204.8	201.8	197.8
77.5°	167.7	166.7	163.6	161.6	158.6
80°	126.5	126.5	124.5	123.5	121.5
82.5°	90.4	88.4	88.4	86.3	86.3
85°	55.2	56.2	56.2	55.2	53.2
87.5°	27.1	27.1	26.1	26.1	24.1
90°	1.1	10.1	17.9	23.5	26.8
92.5°	21.2	11.2	17.9	23.5	24.6
95°	63.7	60.3	17.9	23.5	23.5
97.5°	119.5	126.2	20.1	22.3	23.5
100°	186.5	189.9	194.3	27.9	23.5
102.5°	254.6	259.1	261.3	263.6	169.8
105°	328.3	332.8	332.8	332.8	331.7
107.5°	404.3	404.3	406.5	407.6	403.2
110°	478.0	478.0	480.2	476.9	478.0

TEST NUMBER: P1028279

CATALOG NUMBER: S125DIP-B850D1270UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	547.2	550.6	551.7	547.2	545.0
115°	616.5	622.0	623.2	618.7	612.0
117.5°	689.1	689.1	693.5	686.8	684.6
120°	756.1	754.9	758.3	756.1	750.5
122.5°	815.3	820.8	822.0	819.7	813.0
125°	876.7	884.5	884.5	880.0	876.7
127.5°	935.9	941.4	940.3	938.1	929.2
130°	989.5	995.1	996.2	992.8	987.2
132.5°	1043.1	1049.8	1046.4	1046.4	1040.8
135°	1093.3	1100.0	1097.8	1095.6	1088.9
137.5°	1140.2	1146.9	1144.7	1144.7	1139.1
140°	1186.0	1188.3	1187.1	1189.4	1182.7
142.5°	1227.3	1228.5	1230.7	1230.7	1224.0
145°	1267.5	1269.8	1269.8	1270.9	1264.2
147.5°	1303.3	1303.3	1304.4	1305.5	1297.7
150°	1336.8	1334.6	1336.8	1339.0	1330.1
152.5°	1369.2	1363.6	1365.8	1368.1	1360.2
155°	1396.0	1389.3	1391.5	1394.9	1385.9
157.5°	1417.2	1413.8	1413.8	1417.2	1408.3
160°	1439.5	1432.8	1433.9	1438.4	1429.5
162.5°	1457.4	1450.7	1451.8	1458.5	1448.5
165°	1473.0	1466.3	1467.5	1474.2	1465.2
167.5°	1485.3	1478.6	1479.7	1487.6	1477.5
170°	1495.4	1487.6	1488.7	1497.6	1487.6
172.5°	1502.1	1494.3	1496.5	1504.3	1494.3
175°	1506.5	1499.8	1501.0	1509.9	1499.8
177.5°	1509.9	1503.2	1504.3	1512.1	1503.2
180°	1506.5	1506.5	1506.5	1506.5	1506.5

(END OF REPORT)