

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028344

Luminaire Tested: S125DIP-B850D610UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028344
REPORT IS A COMBINATION OF REPORTS P1002631 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D610UB30-4F0-XX-W2A-F4
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5570.4 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028344

CATALOG NUMBER: S125DIP-B850D610UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1028344

CATALOG NUMBER: S125DIP-B850D610UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	100	96	92	88	94	90	86	83	79	76	74	68	67	65	59	58	56
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	50	47
3	83	74	66	60	78	69	62	57	61	56	51	53	49	46	46	43	40
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	38	35
5	70	58	50	44	65	55	47	42	48	42	38	43	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	38	33	38	34	30	34	30	27
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8456	8456	8456
5°	8456	8259	8275
10°	8386	8070	8045
15°	8276	7843	7774
20°	8127	7581	7462
25°	7968	7295	7128
30°	7774	6996	6777
35°	7569	6683	6384
40°	7356	6353	6034
45°	7126	6030	5662
50°	6872	5665	5229
55°	6621	5262	4831
60°	6322	4837	4367
65°	5964	4345	3888
70°	5601	3780	3334
75°	4988	3112	2696
80°	4253	2325	1983
85°	3282	1376	1092

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7126 cd/sqm

TEST NUMBER: P1028344

CATALOG NUMBER: S125DIP-B850D610UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.5	2.2
10°-20°	351.8	6.3
20°-30°	519.3	9.3
30°-40°	605.9	10.9
40°-50°	608.5	10.9
50°-60°	534.2	9.6
60°-70°	397.9	7.1
70°-80°	227.2	4.1
80°-90°	66.7	1.2
90°-100°	213.5	3.8
100°-110°	443.6	8.0
110°-120°	414.3	7.4
120°-130°	335.2	6.0
130°-140°	269.3	4.8
140°-150°	203.3	3.6
150°-160°	143.1	2.6
160°-170°	84.4	1.5
170°-180°	27.4	0.5
0°-30°	995.6	17.9
0°-40°	1601.5	28.8
0°-60°	2744.3	49.3
0°-90°	3436.1	61.7
90°-120°	1071.4	19.2
90°-150°	1879.3	33.7
90°-180°	2134.0	38.3
0°-180°	5570.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1320	1320	1320	1320	1320	
5°	1318	1316	1305	1314	1314	125
15°	1256	1253	1241	1247	1247	354
25°	1140	1135	1121	1124	1120	525
35°	985	980	966	961	952	616
45°	806	802	789	777	774	621
55°	614	611	596	587	580	548
65°	414	412	401	392	387	411
75°	220	218	213	210	206	235
85°	57	58	58	57	55	63
90°	1	5	9	12	13	5
95°	19	56	506	230	134	20
105°	65	90	414	816	758	68
115°	116	139	333	717	844	114
125°	160	188	319	571	665	142
135°	188	226	317	478	552	146
145°	218	250	318	396	436	137
155°	249	268	310	350	365	115
165°	272	280	297	315	320	77
175°	283	283	285	289	288	27
180°	284	284	284	284	284	

TEST NUMBER: P1028344

CATALOG NUMBER: S125DIP-B850D610UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.8	1319.8	1319.8	1319.8	1319.8
2.5°	1323.9	1320.8	1310.4	1320.8	1319.8
5°	1317.7	1315.6	1305.1	1314.5	1313.5
7.5°	1308.3	1306.2	1294.7	1304.1	1303.1
10°	1294.7	1292.6	1281.1	1289.5	1288.4
12.5°	1278.0	1273.8	1263.4	1269.6	1269.6
15°	1256.1	1252.9	1241.4	1246.7	1246.7
17.5°	1233.1	1227.9	1216.4	1222.7	1217.4
20°	1202.8	1200.7	1187.2	1194.5	1189.2
22.5°	1172.5	1168.4	1155.8	1160.0	1156.9
25°	1140.2	1134.9	1121.4	1123.5	1120.3
27.5°	1102.6	1099.4	1085.9	1086.9	1083.8
30°	1066.0	1062.9	1047.2	1045.2	1042.0
32.5°	1026.4	1021.1	1007.6	1003.4	997.1
35°	984.6	980.4	965.8	960.6	952.2
37.5°	941.8	936.6	923.0	915.7	910.5
40°	897.9	892.7	878.1	868.7	865.6
42.5°	851.0	846.8	832.2	823.8	818.6
45°	806.1	801.9	789.3	776.8	773.7
47.5°	757.0	758.0	742.4	729.8	722.5
50°	710.0	706.9	694.3	680.8	673.5
52.5°	662.0	659.9	646.3	634.8	626.5
55°	613.9	610.8	596.2	586.8	579.5
57.5°	562.8	561.7	549.2	536.7	533.5
60°	514.7	510.6	499.1	488.6	481.3
62.5°	464.6	461.5	452.1	440.6	435.4
65°	414.5	412.4	400.9	391.5	387.4
67.5°	365.4	361.3	352.9	344.6	342.5
70°	319.5	314.3	304.9	298.6	294.4
72.5°	269.4	266.2	261.0	253.7	249.5
75°	220.3	218.2	213.0	209.9	205.7
77.5°	174.4	173.3	170.2	168.1	165.0
80°	131.6	131.6	129.5	128.4	126.3
82.5°	94.0	91.9	91.9	89.8	89.8
85°	57.4	58.5	58.5	57.4	55.3
87.5°	28.2	28.2	27.1	27.1	25.1
90°	0.6	5.2	9.1	12.0	13.1
92.5°	8.6	46.9	228.1	60.9	42.3
95°	18.9	55.8	506.5	229.8	134.4
97.5°	29.2	60.3	547.1	415.1	294.4
100°	40.0	69.2	516.3	586.6	445.9
102.5°	52.0	79.2	461.9	731.8	615.2
105°	64.6	90.3	414.5	816.2	757.5
107.5°	76.6	102.1	379.0	839.8	843.3
110°	89.8	114.4	355.6	817.3	882.1

TEST NUMBER: P1028344

CATALOG NUMBER: S125DIP-B850D610UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	102.9	126.6	341.9	770.1	877.6
115°	115.5	139.2	332.7	717.2	843.8
117.5°	126.9	152.0	327.6	669.2	793.0
120°	138.4	164.4	324.2	628.8	743.8
122.5°	150.4	176.4	321.3	596.6	700.3
125°	160.1	187.6	319.0	570.6	664.9
127.5°	168.1	198.4	317.9	548.2	632.3
130°	175.5	208.6	316.7	525.7	606.6
132.5°	181.2	217.8	316.7	501.4	580.9
135°	187.5	225.6	316.7	478.2	552.3
137.5°	195.5	232.7	317.3	453.9	522.5
140°	202.4	238.7	317.9	431.6	491.1
142.5°	210.4	244.4	318.4	412.5	461.9
145°	218.4	250.1	317.9	395.9	435.6
147.5°	227.0	255.3	316.7	381.6	412.2
150°	234.4	259.8	315.0	369.9	393.3
152.5°	242.4	264.4	312.7	359.9	378.5
155°	249.3	268.1	309.9	350.2	365.3
157.5°	255.6	271.8	307.0	341.0	353.3
160°	261.8	274.7	304.1	331.9	341.3
162.5°	267.0	277.6	300.7	323.6	330.4
165°	272.1	279.6	297.3	315.3	320.2
167.5°	275.6	280.8	293.9	307.5	310.4
170°	279.0	282.2	291.0	300.2	301.9
172.5°	281.3	282.7	287.6	294.2	293.9
175°	283.0	283.0	285.3	288.7	287.6
177.5°	284.1	283.0	283.6	285.3	283.6
180°	283.6	283.6	283.6	283.6	283.6

(END OF REPORT)