

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028112

Luminaire Tested: S125DIP-B610D610UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028112
REPORT IS A COMBINATION OF REPORTS P1002306 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D610UB27-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4502.0 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028112

CATALOG NUMBER: S125DIP-B610D610UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028112

CATALOG NUMBER: S125DIP-B610D610UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	94	90	87	92	88	84	81	75	73	71	64	62	60	53	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43
3	82	72	65	59	76	67	61	56	58	53	49	50	46	43	42	39	37
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	31
5	69	57	49	43	64	53	46	41	46	40	36	40	35	32	33	30	27
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21
8	55	42	34	29	51	39	32	27	35	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	24	20	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6075	6075	6075
5°	6075	5934	5946
10°	6025	5799	5780
15°	5947	5636	5585
20°	5839	5447	5362
25°	5725	5241	5122
30°	5586	5027	4870
35°	5438	4802	4587
40°	5285	4564	4335
45°	5119	4332	4068
50°	4937	4070	3757
55°	4757	3781	3470
60°	4542	3475	3137
65°	4285	3122	2793
70°	4025	2716	2396
75°	3584	2235	1937
80°	3054	1670	1425
85°	2361	988	786

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5119 cd/sqm

TEST NUMBER: P1028112

CATALOG NUMBER: S125DIP-B610D610UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.5	2.0
10°-20°	252.7	5.6
20°-30°	373.1	8.3
30°-40°	435.3	9.7
40°-50°	437.2	9.7
50°-60°	383.8	8.5
60°-70°	285.9	6.4
70°-80°	163.3	3.6
80°-90°	48.3	1.1
90°-100°	48.4	1.1
100°-110°	143.9	3.2
110°-120°	244.0	5.4
120°-130°	321.3	7.1
130°-140°	360.0	8.0
140°-150°	352.9	7.8
150°-160°	296.4	6.6
160°-170°	197.0	4.4
170°-180°	69.0	1.5
0°-30°	715.3	15.9
0°-40°	1150.7	25.6
0°-60°	1971.7	43.8
0°-90°	2469.1	54.8
90°-120°	436.4	9.7
90°-150°	1470.5	32.7
90°-180°	2033.0	45.2
0°-180°	4502.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	948	948	948	948	948	
5°	947	945	938	944	944	90
15°	902	900	892	896	896	254
25°	819	815	806	807	805	377
35°	707	704	694	690	684	443
45°	579	576	567	558	556	446
55°	441	439	428	422	416	394
65°	298	296	288	281	278	295
75°	158	157	153	151	148	169
85°	41	42	42	41	40	45
90°	1	5	9	12	14	5
95°	37	38	44	48	49	39
105°	129	132	136	139	141	138
115°	244	247	248	247	247	242
125°	356	360	360	359	359	319
135°	464	467	468	468	465	357
145°	562	564	566	566	564	351
155°	643	643	643	646	643	296
165°	699	698	698	701	697	197
175°	727	724	724	728	724	69
180°	728	728	728	728	728	

TEST NUMBER: P1028112

CATALOG NUMBER: S125DIP-B610D610UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	948.2	948.2	948.2	948.2	948.2
2.5°	951.2	949.0	941.5	949.0	948.2
5°	946.7	945.2	937.7	944.5	943.7
7.5°	940.0	938.5	930.2	937.0	936.2
10°	930.2	928.7	920.5	926.5	925.7
12.5°	918.2	915.2	907.7	912.2	912.2
15°	902.5	900.2	892.0	895.7	895.7
17.5°	886.0	882.2	874.0	878.5	874.7
20°	864.2	862.7	853.0	858.2	854.5
22.5°	842.5	839.5	830.4	833.4	831.2
25°	819.2	815.4	805.7	807.2	804.9
27.5°	792.2	789.9	780.2	780.9	778.7
30°	765.9	763.7	752.4	750.9	748.7
32.5°	737.4	733.7	723.9	720.9	716.4
35°	707.4	704.4	693.9	690.2	684.2
37.5°	676.7	672.9	663.2	657.9	654.2
40°	645.2	641.4	630.9	624.1	621.9
42.5°	611.4	608.4	597.9	591.9	588.1
45°	579.1	576.1	567.1	558.1	555.9
47.5°	543.9	544.6	533.4	524.4	519.1
50°	510.1	507.9	498.9	489.1	483.9
52.5°	475.6	474.1	464.4	456.1	450.1
55°	441.1	438.9	428.4	421.6	416.3
57.5°	404.3	403.6	394.6	385.6	383.3
60°	369.8	366.8	358.6	351.1	345.8
62.5°	333.8	331.6	324.8	316.6	312.8
65°	297.8	296.3	288.1	281.3	278.3
67.5°	262.6	259.6	253.6	247.6	246.1
70°	229.6	225.8	219.1	214.6	211.6
72.5°	193.5	191.3	187.5	182.3	179.3
75°	158.3	156.8	153.0	150.8	147.8
77.5°	125.3	124.5	122.3	120.8	118.5
80°	94.5	94.5	93.0	92.3	90.8
82.5°	67.5	66.0	66.0	64.5	64.5
85°	41.3	42.0	42.0	41.3	39.8
87.5°	20.3	20.3	19.5	19.5	18.0
90°	0.6	5.1	9.1	11.9	13.6
92.5°	17.0	19.8	24.9	28.9	30.0
95°	36.8	38.0	43.6	47.6	48.7
97.5°	56.7	57.3	65.2	68.6	69.2
100°	79.4	79.4	86.7	91.8	93.0
102.5°	103.7	106.6	109.4	115.1	116.8
105°	129.2	132.1	135.5	138.9	140.6
107.5°	157.0	159.8	162.7	164.4	164.4
110°	185.9	188.8	190.5	192.2	191.6



TEST NUMBER: P1028112

CATALOG NUMBER: S125DIP-B610D610UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	215.4	216.5	218.8	219.4	218.2
115°	244.3	246.6	247.7	247.1	246.6
117.5°	273.8	274.3	275.5	276.0	273.8
120°	301.0	303.8	304.4	304.4	302.1
122.5°	330.5	331.0	332.7	332.2	330.5
125°	356.5	359.9	360.5	359.4	358.8
127.5°	385.4	387.1	387.7	387.1	386.0
130°	411.0	413.8	414.9	414.4	413.2
132.5°	436.5	441.6	441.0	440.4	438.7
135°	463.7	467.1	467.6	467.6	465.4
137.5°	489.2	492.6	493.7	494.3	491.4
140°	513.6	516.4	518.1	519.2	516.4
142.5°	537.9	540.2	542.5	543.0	540.2
145°	561.7	564.0	565.7	565.7	564.0
147.5°	583.8	585.5	586.7	588.4	583.8
150°	605.9	605.4	607.6	607.6	606.5
152.5°	624.1	625.2	625.8	627.5	625.2
155°	642.8	642.8	643.4	645.6	642.8
157.5°	659.8	658.7	659.2	661.5	657.5
160°	674.5	672.8	673.4	675.7	672.8
162.5°	687.6	686.4	686.4	689.3	685.9
165°	698.9	697.8	698.3	700.6	697.2
167.5°	709.1	706.8	706.8	710.2	706.8
170°	717.0	714.8	714.8	718.2	714.2
172.5°	722.7	720.5	720.5	723.9	720.5
175°	726.7	724.4	724.4	727.8	723.9
177.5°	729.5	727.3	726.7	730.1	726.1
180°	728.4	728.4	728.4	728.4	728.4

(END OF REPORT)