

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028398

Luminaire Tested: S125DIP-B850D850UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028398
REPORT IS A COMBINATION OF REPORTS P1002700 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D850UB35-4F0-XX-W2A-F4
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6314.9 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028398

CATALOG NUMBER: S125DIP-B850D850UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1028398

CATALOG NUMBER: S125DIP-B850D850UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43
3	82	72	65	59	76	67	61	56	58	53	49	50	46	43	42	39	36
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31
5	69	57	49	43	64	53	46	41	46	40	36	40	35	32	33	30	27
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8493	8493	8493
5°	8493	8295	8311
10°	8423	8105	8080
15°	8313	7878	7807
20°	8163	7614	7494
25°	8002	7327	7160
30°	7809	7027	6807
35°	7602	6713	6412
40°	7388	6380	6060
45°	7157	6057	5687
50°	6902	5690	5252
55°	6650	5285	4852
60°	6350	4858	4386
65°	5990	4364	3905
70°	5625	3796	3349
75°	5011	3125	2708
80°	4269	2334	1992
85°	3299	1380	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7157 cd/sqm

TEST NUMBER: P1028398

CATALOG NUMBER: S125DIP-B850D850UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	2.0
10°-20°	353.3	5.6
20°-30°	521.6	8.3
30°-40°	608.6	9.6
40°-50°	611.2	9.7
50°-60°	536.5	8.5
60°-70°	399.6	6.3
70°-80°	228.2	3.6
80°-90°	67.4	1.1
90°-100°	286.5	4.5
100°-110°	595.1	9.4
110°-120°	555.8	8.8
120°-130°	449.8	7.1
130°-140°	361.4	5.7
140°-150°	272.8	4.3
150°-160°	192.1	3.0
160°-170°	113.2	1.8
170°-180°	36.8	0.6
0°-30°	1000.0	15.8
0°-40°	1608.5	25.5
0°-60°	2756.3	43.6
0°-90°	3451.5	54.7
90°-120°	1437.4	22.8
90°-150°	2521.3	39.9
90°-180°	2863.0	45.3
0°-180°	6314.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1323	1321	1311	1320	1319	126
15°	1262	1258	1247	1252	1252	356
25°	1145	1140	1126	1128	1125	527
35°	989	985	970	965	956	619
45°	810	805	793	780	777	624
55°	617	614	599	589	582	550
65°	416	414	403	393	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	63
90°	1	7	12	16	18	6
95°	25	75	680	308	180	26
105°	87	121	556	1095	1016	91
115°	155	187	446	962	1132	153
125°	215	252	428	766	892	191
135°	252	302	425	642	741	195
145°	293	336	426	531	584	184
155°	334	360	416	470	490	154
165°	365	375	399	423	430	103
175°	380	380	383	387	386	36
180°	380	380	380	380	380	

TEST NUMBER: P1028398

CATALOG NUMBER: S125DIP-B850D850UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1325.5	1325.5	1325.5	1325.5	1325.5
2.5°	1329.7	1326.6	1316.1	1326.6	1325.5
5°	1323.4	1321.3	1310.8	1320.3	1319.2
7.5°	1314.0	1311.9	1300.4	1309.8	1308.7
10°	1300.4	1298.3	1286.7	1295.1	1294.1
12.5°	1283.6	1279.4	1268.9	1275.2	1275.2
15°	1261.6	1258.4	1246.9	1252.1	1252.1
17.5°	1238.5	1233.2	1221.7	1228.0	1222.7
20°	1208.1	1206.0	1192.3	1199.7	1194.4
22.5°	1177.7	1173.5	1160.9	1165.1	1161.9
25°	1145.1	1139.9	1126.3	1128.4	1125.2
27.5°	1107.4	1104.2	1090.6	1091.7	1088.5
30°	1070.7	1067.5	1051.8	1049.7	1046.6
32.5°	1030.8	1025.6	1012.0	1007.8	1001.5
35°	988.9	984.7	970.0	964.8	956.4
37.5°	945.9	940.7	927.0	919.7	914.4
40°	901.9	896.6	881.9	872.5	869.3
42.5°	854.7	850.5	835.8	827.4	822.2
45°	809.6	805.4	792.8	780.2	777.1
47.5°	760.3	761.3	745.6	733.0	725.7
50°	713.1	709.9	697.4	683.7	676.4
52.5°	664.9	662.8	649.1	637.6	629.2
55°	616.6	613.5	598.8	589.4	582.0
57.5°	565.2	564.2	551.6	539.0	535.9
60°	517.0	512.8	501.3	490.8	483.4
62.5°	466.7	463.5	454.1	442.5	437.3
65°	416.3	414.2	402.7	393.3	389.1
67.5°	367.0	362.8	354.5	346.1	344.0
70°	320.9	315.6	306.2	299.9	295.7
72.5°	270.6	267.4	262.2	254.8	250.6
75°	221.3	219.2	213.9	210.8	206.6
77.5°	175.1	174.1	170.9	168.8	165.7
80°	132.1	132.1	130.0	129.0	126.9
82.5°	94.4	92.3	92.3	90.2	90.2
85°	57.7	58.7	58.7	57.7	55.6
87.5°	28.3	28.3	27.3	27.3	25.2
90°	0.8	6.9	12.3	16.1	17.6
92.5°	11.5	62.9	306.0	81.7	56.8
95°	25.3	74.8	679.6	308.4	180.2
97.5°	39.1	80.9	734.0	556.8	395.0
100°	53.7	92.8	692.6	787.0	598.3
102.5°	69.8	106.2	619.8	981.8	825.3
105°	86.7	121.2	556.1	1094.9	1016.3
107.5°	102.8	136.9	508.5	1126.8	1131.4
110°	120.4	153.4	477.1	1096.5	1183.5

TEST NUMBER: P1028398

CATALOG NUMBER: S125DIP-B850D850UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	138.1	169.9	458.7	1033.2	1177.4
115°	154.9	186.8	446.4	962.2	1132.1
117.5°	170.3	204.0	439.5	897.8	1063.9
120°	185.6	220.5	434.9	843.8	997.9
122.5°	201.7	236.6	431.1	800.3	939.6
125°	214.8	251.6	428.0	765.5	892.0
127.5°	225.5	266.2	426.5	735.6	848.3
130°	235.5	280.0	424.9	705.2	813.8
132.5°	243.1	292.2	424.9	672.7	779.3
135°	251.6	302.5	424.9	641.6	740.9
137.5°	262.3	312.2	425.7	609.0	701.1
140°	271.5	320.2	426.5	579.1	658.9
142.5°	282.3	327.9	427.2	553.4	619.8
145°	293.0	335.5	426.5	531.2	584.5
147.5°	304.5	342.4	424.9	512.0	553.0
150°	314.5	348.6	422.6	496.3	527.7
152.5°	325.2	354.8	419.6	482.8	507.8
155°	334.4	359.8	415.7	469.8	490.1
157.5°	342.9	364.7	411.9	457.6	474.0
160°	351.3	368.6	408.1	445.2	457.9
162.5°	358.2	372.4	403.5	434.1	443.3
165°	365.1	375.1	398.8	423.0	429.5
167.5°	369.7	376.6	394.2	412.6	416.5
170°	374.3	378.5	390.4	402.7	405.0
172.5°	377.4	379.3	385.8	394.6	394.2
175°	379.7	379.7	382.7	387.3	385.8
177.5°	381.2	379.7	380.4	382.7	380.4
180°	380.4	380.4	380.4	380.4	380.4

(END OF REPORT)