

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028417

Luminaire Tested: S125RDIP-B1090D1090UB27-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028417
REPORT IS A COMBINATION OF REPORTS P1004922 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D1090UB27-4F0-XX-W2A-F
Description: Define 5 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8225.0 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028417

CATALOG NUMBER: S125RDIP-B1090D1090UB27-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1028417

CATALOG NUMBER: S125RDIP-B1090D1090UB27-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	51
1	98	94	90	87	91	87	84	81	74	71	69	62	60	58	50	49	48	48	48	43
2	90	82	76	71	82	76	71	67	65	61	58	54	52	49	45	43	41	41	41	36
3	82	72	65	59	75	67	61	56	57	53	49	48	45	42	40	37	35	35	35	31
4	75	64	56	50	69	60	53	48	51	46	42	43	39	36	36	33	30	30	30	27
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	32	29	27	27	27	23
6	63	52	43	38	58	48	41	36	41	36	32	35	31	27	29	26	24	24	24	21
7	59	47	39	33	54	43	36	31	38	32	28	32	28	24	27	23	21	21	21	18
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	19	19	17
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	17	17	15
10	47	35	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11287	11287	11287
5°	11288	11005	11023
10°	11178	10728	10633
15°	11019	10340	10121
20°	10824	9873	9584
25°	10599	9417	9008
30°	10325	8915	8403
35°	10044	8406	7760
40°	9777	7883	7133
45°	9456	7319	6475
50°	9130	6720	5806
55°	8753	6129	5113
60°	8367	5454	4394
65°	7907	4700	3619
70°	7369	3827	2848
75°	6627	2877	2075
80°	5591	1864	1399
85°	4185	1002	788

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9456 cd/sqm

TEST NUMBER: P1028417

CATALOG NUMBER: S125RDIP-B1090D1090UB27-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.8	2.0
10°-20°	463.3	5.6
20°-30°	671.8	8.2
30°-40°	765.4	9.3
40°-50°	746.0	9.1
50°-60°	627.8	7.6
60°-70°	440.0	5.3
70°-80°	225.6	2.7
80°-90°	58.2	0.7
90°-100°	44.9	0.5
100°-110°	298.4	3.6
110°-120°	537.3	6.5
120°-130°	689.7	8.4
130°-140°	741.8	9.0
140°-150°	696.2	8.5
150°-160°	563.1	6.8
160°-170°	364.2	4.4
170°-180°	125.6	1.5
0°-30°	1300.9	15.8
0°-40°	2066.3	25.1
0°-60°	3440.2	41.8
0°-90°	4164.0	50.6
90°-120°	880.5	10.7
90°-150°	3008.1	36.6
90°-180°	4061.0	49.4
0°-180°	8225.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1762	1762	1762	1762	1762	
5°	1759	1754	1739	1752	1750	167
15°	1672	1664	1636	1635	1623	472
25°	1517	1497	1448	1430	1416	698
35°	1307	1275	1215	1176	1158	818
45°	1070	1031	958	905	885	825
55°	812	769	694	635	613	726
65°	550	504	434	380	361	544
75°	293	253	197	168	158	309
85°	73	49	43	41	40	80
90°	1	9	16	21	24	7
95°	56	53	16	21	21	68
105°	288	292	292	292	291	305
115°	541	546	547	543	537	536
125°	769	776	776	772	769	687
135°	959	965	963	961	956	740
145°	1112	1114	1114	1115	1109	696
155°	1225	1219	1221	1224	1216	564
165°	1293	1287	1288	1294	1286	365
175°	1322	1316	1317	1325	1316	126
180°	1322	1322	1322	1322	1322	

TEST NUMBER: P1028417

CATALOG NUMBER: S125RDIP-B1090D1090UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1761.6	1761.6	1761.6	1761.6	1761.6
2.5°	1765.6	1761.6	1748.3	1761.6	1760.3
5°	1758.9	1753.6	1739.0	1752.3	1749.6
7.5°	1745.6	1740.3	1723.0	1733.6	1731.0
10°	1725.7	1721.7	1703.0	1707.0	1703.0
12.5°	1703.0	1697.7	1671.1	1673.8	1667.1
15°	1672.4	1664.5	1636.5	1635.2	1623.2
17.5°	1640.5	1628.5	1595.3	1588.6	1579.3
20°	1601.9	1588.6	1546.0	1539.4	1527.4
22.5°	1559.3	1546.0	1500.8	1486.2	1476.9
25°	1516.8	1496.8	1447.6	1430.3	1415.7
27.5°	1468.9	1444.9	1393.0	1370.4	1355.8
30°	1415.7	1390.4	1334.5	1303.9	1291.9
32.5°	1363.8	1333.2	1276.0	1241.4	1225.4
35°	1306.6	1274.6	1214.7	1176.2	1157.5
37.5°	1252.0	1213.4	1152.2	1107.0	1088.4
40°	1193.5	1153.5	1089.7	1039.1	1023.2
42.5°	1132.3	1091.0	1024.5	976.6	951.3
45°	1069.7	1031.1	958.0	904.7	884.8
47.5°	1004.5	964.6	891.4	836.9	814.3
50°	943.3	899.4	823.6	767.7	747.7
52.5°	876.8	831.6	761.0	699.8	679.9
55°	811.6	769.0	694.5	634.6	613.4
57.5°	745.1	699.8	628.0	569.5	550.8
60°	681.2	634.6	562.8	504.3	484.3
62.5°	613.4	569.5	496.3	443.1	423.1
65°	549.5	504.3	433.7	380.5	360.6
67.5°	485.6	440.4	372.5	322.0	306.0
70°	420.4	375.2	308.7	267.4	251.5
72.5°	356.6	312.7	251.5	214.2	204.9
75°	292.7	252.8	196.9	167.6	158.3
77.5°	227.5	195.6	149.0	126.4	118.4
80°	173.0	141.0	103.8	91.8	89.1
82.5°	119.7	91.8	69.2	65.2	63.9
85°	73.2	49.2	42.6	41.2	39.9
87.5°	30.6	21.3	20.0	20.0	18.6
90°	1.0	8.8	15.7	20.6	23.5
92.5°	18.6	9.8	15.7	20.6	21.6
95°	55.9	52.9	15.7	20.6	20.6
97.5°	104.9	110.7	17.6	19.6	20.6
100°	163.7	166.6	170.5	24.5	20.6
102.5°	223.4	227.4	229.3	231.3	149.0
105°	288.1	292.0	292.0	292.0	291.1
107.5°	354.8	354.8	356.7	357.7	353.8
110°	419.4	419.4	421.4	418.5	419.4

TEST NUMBER: P1028417

CATALOG NUMBER: S125RDIP-B1090D1090UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	480.2	483.1	484.1	480.2	478.2
115°	541.0	545.9	546.8	542.9	537.0
117.5°	604.7	604.7	608.6	602.7	600.8
120°	663.5	662.5	665.4	663.5	658.6
122.5°	715.4	720.3	721.3	719.3	713.5
125°	769.3	776.2	776.2	772.3	769.3
127.5°	821.3	826.2	825.2	823.2	815.4
130°	868.3	873.2	874.2	871.2	866.3
132.5°	915.3	921.2	918.3	918.3	913.4
135°	959.4	965.3	963.4	961.4	955.5
137.5°	1000.6	1006.5	1004.5	1004.5	999.6
140°	1040.8	1042.7	1041.8	1043.7	1037.8
142.5°	1077.0	1078.0	1080.0	1080.0	1074.1
145°	1112.3	1114.3	1114.3	1115.3	1109.4
147.5°	1143.7	1143.7	1144.7	1145.6	1138.8
150°	1173.1	1171.1	1173.1	1175.0	1167.2
152.5°	1201.5	1196.6	1198.6	1200.5	1193.7
155°	1225.0	1219.1	1221.1	1224.0	1216.2
157.5°	1243.6	1240.7	1240.7	1243.6	1235.8
160°	1263.2	1257.4	1258.3	1262.3	1254.4
162.5°	1278.9	1273.0	1274.0	1279.9	1271.1
165°	1292.6	1286.8	1287.7	1293.6	1285.8
167.5°	1303.4	1297.5	1298.5	1305.4	1296.6
170°	1312.2	1305.4	1306.4	1314.2	1305.4
172.5°	1318.1	1311.3	1313.2	1320.1	1311.3
175°	1322.0	1316.2	1317.1	1325.0	1316.2
177.5°	1325.0	1319.1	1320.1	1326.9	1319.1
180°	1322.0	1322.0	1322.0	1322.0	1322.0

(END OF REPORT)