

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028424

Luminaire Tested: S125RDIP-B1090D1090UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028424
REPORT IS A COMBINATION OF REPORTS P1004939 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D1090UB30-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7745.0 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028424

CATALOG NUMBER: S125RDIP-B1090D1090UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028424

CATALOG NUMBER: S125RDIP-B1090D1090UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	87	92	88	85	82	76	73	71	64	62	61	53	52	51
2	90	83	77	72	84	77	72	67	66	63	59	57	54	51	47	45	43
3	83	73	66	60	76	68	62	57	59	54	50	50	47	43	42	39	37
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32
5	69	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28
6	64	52	44	38	59	49	41	36	42	37	32	37	32	29	31	28	25
7	59	47	39	34	55	44	37	32	39	33	29	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	21	18
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11384	11384	11384
5°	11385	11100	11118
10°	11275	10821	10726
15°	11115	10429	10209
20°	10918	9958	9667
25°	10691	9498	9086
30°	10414	8992	8476
35°	10131	8479	7827
40°	9862	7951	7194
45°	9538	7382	6531
50°	9210	6778	5856
55°	8829	6182	5157
60°	8439	5502	4432
65°	7976	4741	3650
70°	7434	3859	2872
75°	6684	2902	2093
80°	5639	1880	1411
85°	4220	1009	796

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9538 cd/sqm

TEST NUMBER: P1028424

CATALOG NUMBER: S125RDIP-B1090D1090UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.2	2.2
10°-20°	467.3	6.0
20°-30°	677.6	8.7
30°-40°	772.0	10.0
40°-50°	752.5	9.7
50°-60°	633.3	8.2
60°-70°	443.8	5.7
70°-80°	227.5	2.9
80°-90°	58.7	0.8
90°-100°	84.5	1.1
100°-110°	250.9	3.2
110°-120°	425.6	5.5
120°-130°	560.2	7.2
130°-140°	627.8	8.1
140°-150°	615.3	7.9
150°-160°	516.9	6.7
160°-170°	343.6	4.4
170°-180°	120.2	1.6
0°-30°	1312.2	16.9
0°-40°	2084.2	26.9
0°-60°	3470.0	44.8
0°-90°	4200.0	54.2
90°-120°	761.0	9.8
90°-150°	2564.3	33.1
90°-180°	3545.0	45.8
0°-180°	7745.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1774	1769	1754	1767	1765	168
15°	1687	1679	1651	1649	1637	476
25°	1530	1510	1460	1443	1428	704
35°	1318	1286	1225	1186	1168	825
45°	1079	1040	966	913	892	832
55°	819	776	700	640	619	732
65°	554	509	438	384	364	549
75°	295	255	199	169	160	312
85°	74	50	43	42	40	81
90°	1	9	16	21	24	9
95°	64	66	76	83	85	67
105°	225	230	236	242	245	240
115°	426	430	432	431	430	421
125°	622	628	629	627	626	557
135°	809	814	816	816	812	623
145°	980	984	986	986	984	612
155°	1121	1121	1122	1126	1121	516
165°	1219	1217	1218	1222	1216	344
175°	1267	1263	1263	1269	1262	120
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1028424

CATALOG NUMBER: S125RDIP-B1090D1090UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1776.8	1776.8	1776.8	1776.8	1776.8
2.5°	1780.8	1776.8	1763.4	1776.8	1775.5
5°	1774.1	1768.8	1754.0	1767.4	1764.7
7.5°	1760.7	1755.4	1737.9	1748.6	1746.0
10°	1740.6	1736.6	1717.8	1721.8	1717.8
12.5°	1717.8	1712.4	1685.6	1688.3	1681.5
15°	1686.9	1678.9	1650.7	1649.3	1637.3
17.5°	1654.7	1642.6	1609.1	1602.4	1593.0
20°	1615.8	1602.4	1559.4	1552.7	1540.6
22.5°	1572.8	1559.4	1513.8	1499.0	1489.6
25°	1529.9	1509.8	1460.1	1442.7	1427.9
27.5°	1481.6	1457.4	1405.1	1382.3	1367.5
30°	1427.9	1402.4	1346.0	1315.2	1303.1
32.5°	1375.6	1344.7	1287.0	1252.1	1236.0
35°	1317.9	1285.6	1225.3	1186.3	1167.5
37.5°	1262.8	1223.9	1162.2	1116.6	1097.8
40°	1203.8	1163.5	1099.1	1048.1	1032.0
42.5°	1142.1	1100.4	1033.3	985.0	959.5
45°	1079.0	1040.1	966.2	912.6	892.4
47.5°	1013.2	973.0	899.1	844.1	821.3
50°	951.5	907.2	830.7	774.3	754.2
52.5°	884.4	838.8	767.6	705.9	685.8
55°	818.6	775.7	700.5	640.1	618.7
57.5°	751.5	705.9	633.4	574.4	555.6
60°	687.1	640.1	567.7	508.6	488.5
62.5°	618.7	574.4	500.6	446.9	426.8
65°	554.3	508.6	437.5	383.8	363.7
67.5°	489.8	444.2	375.8	324.8	308.7
70°	424.1	378.4	311.3	269.7	253.6
72.5°	359.7	315.4	253.6	216.1	206.7
75°	295.2	255.0	198.6	169.1	159.7
77.5°	229.5	197.3	150.3	127.5	119.4
80°	174.5	142.3	104.7	92.6	89.9
82.5°	120.8	92.6	69.8	65.8	64.4
85°	73.8	49.7	42.9	41.6	40.3
87.5°	30.9	21.5	20.1	20.1	18.8
90°	1.0	8.9	15.8	20.8	23.7
92.5°	29.7	34.6	43.5	50.4	52.4
95°	64.3	66.2	76.1	83.0	85.0
97.5°	98.8	99.8	113.7	119.6	120.6
100°	138.4	138.4	151.2	160.1	162.1
102.5°	180.9	185.8	190.8	200.7	203.6
105°	225.4	230.3	236.2	242.2	245.1
107.5°	273.8	278.8	283.7	286.7	286.7
110°	324.2	329.2	332.1	335.1	334.1

TEST NUMBER: P1028424

CATALOG NUMBER: S125RDIP-B1090D1090UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.6	377.6	381.6	382.5	380.6
115°	426.0	430.0	432.0	431.0	430.0
117.5°	477.4	478.4	480.4	481.4	477.4
120°	524.9	529.8	530.8	530.8	526.9
122.5°	576.3	577.3	580.2	579.3	576.3
125°	621.8	627.7	628.7	626.7	625.7
127.5°	672.2	675.1	676.1	675.1	673.2
130°	716.6	721.6	723.6	722.6	720.6
132.5°	761.1	770.0	769.0	768.1	765.1
135°	808.6	814.5	815.5	815.5	811.5
137.5°	853.1	859.0	861.0	862.0	857.0
140°	895.6	900.5	903.5	905.4	900.5
142.5°	938.1	942.0	946.0	947.0	942.0
145°	979.6	983.5	986.5	986.5	983.5
147.5°	1018.1	1021.1	1023.1	1026.0	1018.1
150°	1056.7	1055.7	1059.7	1059.7	1057.7
152.5°	1088.3	1090.3	1091.3	1094.2	1090.3
155°	1120.9	1120.9	1121.9	1125.9	1120.9
157.5°	1150.6	1148.6	1149.6	1153.6	1146.6
160°	1176.3	1173.3	1174.3	1178.3	1173.3
162.5°	1199.0	1197.1	1197.1	1202.0	1196.1
165°	1218.8	1216.8	1217.8	1221.8	1215.8
167.5°	1236.6	1232.6	1232.6	1238.6	1232.6
170°	1250.4	1246.5	1246.5	1252.4	1245.5
172.5°	1260.3	1256.4	1256.4	1262.3	1256.4
175°	1267.2	1263.3	1263.3	1269.2	1262.3
177.5°	1272.2	1268.2	1267.2	1273.2	1266.2
180°	1270.2	1270.2	1270.2	1270.2	1270.2

(END OF REPORT)