

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028463

Luminaire Tested: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028463
REPORT IS A COMBINATION OF REPORTS P1004988 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1
Description: Define 5 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8353.0 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	57	57	57	57	57	57
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49	49	49	43
2	90	83	77	72	83	77	72	67	65	61	58	55	52	50	45	43	42	42	42	37
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36	36	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	33	31	31	31	28
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	27	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	24	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21	21	21	19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	19	19	17
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	23	20	17	17	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10412	10412	10412	10412
5°	10403	11734	10403	9019
10°	10344	13186	10309	7797
15°	10232	13951	10162	6788
20°	10096	15060	10006	6136
25°	9919	17046	9808	5569
30°	9740	18119	9594	5163
35°	9507	14901	9374	4785
40°	9093	10119	9017	4445
45°	8551	7274	8539	4111
50°	7993	5594	8032	3801
55°	7367	4549	7352	3504
60°	6784	3728	6752	3111
65°	6105	3106	6143	2504
70°	5543	2493	5520	2085
75°	4682	1889	4682	1713
80°	3794	1152	3752	1152
85°	2670	606	2596	685

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 14820 cd/sqm

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.8	1.9
10°-20°	456.8	5.5
20°-30°	724.4	8.7
30°-40°	875.3	10.5
40°-50°	779.3	9.3
50°-60°	597.6	7.2
60°-70°	388.1	4.6
70°-80°	188.4	2.3
80°-90°	46.6	0.6
90°-100°	98.7	1.2
100°-110°	293.1	3.5
110°-120°	497.1	6.0
120°-130°	654.4	7.8
130°-140°	733.3	8.8
140°-150°	718.7	8.6
150°-160°	603.7	7.2
160°-170°	401.3	4.8
170°-180°	140.4	1.7
0°-30°	1337.0	16.0
0°-40°	2212.3	26.5
0°-60°	3589.2	43.0
0°-90°	4212.3	50.4
90°-120°	888.8	10.6
90°-150°	2995.2	35.9
90°-180°	4141.0	49.6
0°-180°	8353.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1625	1625	1625	1625	1625	
5°	1621	1862	1621	1432	1621	154
15°	1553	2237	1542	1089	1553	438
25°	1420	2679	1404	875	1420	654
35°	1237	2223	1219	714	1237	770
45°	967	994	966	562	967	746
55°	683	546	682	420	683	612
65°	424	310	427	250	424	424
75°	207	144	207	131	207	222
85°	47	31	45	35	47	53
90°	1	28	1	28	1	8
95°	75	99	75	99	75	78
105°	263	286	263	286	263	281
115°	498	502	498	502	498	492
125°	726	731	726	731	726	651
135°	944	948	944	948	944	728
145°	1144	1149	1144	1149	1144	715
155°	1309	1309	1309	1309	1309	603
165°	1424	1420	1424	1420	1424	402
175°	1480	1474	1480	1474	1480	141
180°	1484	1484	1484	1484	1484	

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1626.3	1639.7	1643.7	1654.3	1666.3	1669.0	1675.7	1685.0	1690.4	1689.0	1689.0
5°	1621.0	1643.7	1659.7	1678.4	1701.0	1710.4	1718.4	1738.4	1754.4	1763.7	1779.7
7.5°	1611.6	1645.0	1671.7	1699.7	1734.4	1750.4	1767.7	1795.8	1825.1	1843.8	1861.1
10°	1597.0	1639.7	1677.0	1718.4	1765.1	1789.1	1810.4	1853.1	1889.1	1913.2	1953.2
12.5°	1575.6	1629.0	1681.0	1735.7	1794.4	1819.8	1849.1	1895.8	1946.5	1981.2	2014.6
15°	1552.9	1617.0	1673.0	1738.4	1809.1	1847.8	1885.1	1934.5	1979.9	2018.6	2057.2
17.5°	1526.3	1594.3	1663.7	1738.4	1818.4	1857.1	1889.1	1947.8	1995.9	2034.6	2069.3
20°	1494.2	1570.3	1649.0	1731.7	1813.1	1849.1	1879.8	1943.8	1986.5	2027.9	2077.3
22.5°	1459.6	1542.3	1626.3	1707.7	1787.7	1826.4	1862.5	1918.5	1965.2	2021.2	2085.3
25°	1419.5	1510.2	1595.6	1677.0	1753.1	1789.1	1821.1	1882.5	1947.8	2018.6	2090.6
27.5°	1379.5	1467.6	1550.3	1625.0	1707.7	1741.1	1773.1	1850.5	1927.8	2002.5	2101.3
30°	1335.5	1424.9	1496.9	1566.3	1646.3	1681.0	1721.0	1809.1	1897.1	1998.5	2118.6
32.5°	1286.1	1367.5	1434.2	1506.2	1578.3	1621.0	1671.7	1767.7	1869.1	1990.5	2144.0
35°	1236.7	1302.1	1363.5	1431.5	1518.3	1563.6	1613.0	1714.4	1841.1	1986.5	2165.3
37.5°	1174.0	1236.7	1284.8	1354.2	1443.5	1496.9	1546.3	1663.7	1807.8	1977.2	2164.0
40°	1110.0	1163.4	1208.7	1280.8	1378.2	1427.5	1480.9	1609.0	1773.1	1950.5	2132.0
42.5°	1040.6	1086.0	1135.4	1204.7	1299.5	1347.5	1408.9	1558.3	1725.0	1913.2	2049.2
45°	967.3	1011.3	1052.6	1124.7	1219.4	1271.4	1338.1	1491.6	1666.3	1834.4	1915.8
47.5°	895.2	933.9	977.9	1040.6	1136.7	1194.1	1262.1	1426.2	1587.6	1729.0	1735.7
50°	825.8	856.5	893.9	957.9	1058.0	1112.7	1183.4	1336.8	1494.2	1591.6	1526.3
52.5°	753.8	781.8	820.5	876.5	969.9	1034.0	1095.3	1248.8	1380.8	1446.2	1326.1
55°	683.1	707.1	747.1	809.8	891.2	940.6	1003.3	1146.0	1262.1	1263.4	1132.7
57.5°	613.7	635.1	668.4	724.4	800.5	857.9	915.2	1039.3	1118.0	1095.3	949.9
60°	552.3	565.7	596.4	651.1	721.8	763.1	824.5	928.6	980.6	939.2	783.1
62.5°	488.3	501.6	525.7	569.7	636.4	680.4	719.1	804.5	840.5	777.8	649.7
65°	424.3	440.3	457.6	492.3	555.0	584.4	619.0	681.7	716.4	643.1	532.3
67.5°	368.2	376.2	393.6	429.6	473.6	500.3	524.3	567.0	573.7	515.0	424.3
70°	316.2	318.9	334.9	356.2	389.6	405.6	425.6	450.9	450.9	402.9	330.9
72.5°	257.5	261.5	273.5	296.2	316.2	324.2	330.9	346.9	344.2	300.2	250.8
75°	206.8	209.5	218.8	229.5	237.5	252.2	257.5	254.8	253.5	216.1	188.1
77.5°	160.1	161.4	168.1	177.4	178.8	184.1	180.1	180.1	168.1	146.8	132.1
80°	117.4	118.7	121.4	124.1	124.1	124.1	124.1	117.4	109.4	96.1	92.1
82.5°	78.7	78.7	80.0	82.7	81.4	78.7	76.0	69.4	64.0	60.0	57.4
85°	46.7	46.7	48.0	46.7	41.4	40.0	37.4	36.0	34.7	33.4	33.4
87.5°	22.7	21.3	18.7	16.0	16.0	16.0	16.0	16.0	16.0	14.7	14.7
90°	1.2	3.2	5.3	7.3	9.4	10.4	11.3	13.1	14.9	16.7	18.5
92.5°	34.6	35.9	37.2	38.5	39.8	40.4	41.6	43.9	46.2	48.5	50.8
95°	75.0	75.5	76.1	76.6	77.1	77.4	78.7	81.2	83.8	86.3	88.9
97.5°	115.5	115.7	116.0	116.2	116.5	116.6	118.4	122.0	125.6	129.2	132.8
100°	161.6	161.6	161.6	161.6	161.6	161.6	163.3	166.6	170.0	173.3	176.7
102.5°	211.3	212.6	213.9	215.2	216.5	217.1	217.7	219.0	220.3	221.5	222.8
105°	263.2	264.5	265.8	267.1	268.4	269.0	269.8	271.3	272.8	274.4	275.9
107.5°	319.8	321.1	322.4	323.7	325.0	325.6	326.2	327.5	328.8	330.1	331.4
110°	378.7	380.0	381.3	382.6	383.9	384.5	384.9	385.6	386.4	387.1	387.9

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	438.7	439.2	439.7	440.2	440.7	441.0	441.5	442.6	443.6	444.7	445.7
115°	497.6	498.6	499.6	500.7	501.7	502.2	502.5	503.0	503.5	504.0	504.5
117.5°	557.7	557.9	558.2	558.4	558.7	558.8	559.1	559.6	560.1	560.6	561.1
120°	613.1	614.4	615.7	617.0	618.3	618.9	619.0	619.3	619.5	619.8	620.0
122.5°	673.1	673.4	673.6	673.9	674.2	674.3	674.7	675.4	676.2	676.9	677.7
125°	726.2	727.8	729.3	730.9	732.4	733.2	733.3	733.6	733.8	734.1	734.3
127.5°	785.1	785.9	786.7	787.4	788.2	788.6	788.7	789.0	789.2	789.5	789.7
130°	837.1	838.4	839.6	840.9	842.2	842.8	843.1	843.6	844.1	844.6	845.1
132.5°	889.0	891.3	893.6	895.9	898.2	899.4	899.3	899.0	898.8	898.5	898.3
135°	944.4	946.0	947.5	949.1	950.6	951.4	951.5	951.8	952.0	952.3	952.5
137.5°	996.4	997.9	999.5	1001.0	1002.5	1003.3	1003.6	1004.1	1004.6	1005.1	1005.6
140°	1046.0	1047.3	1048.6	1049.9	1051.2	1051.8	1052.2	1053.0	1053.7	1054.5	1055.3
142.5°	1095.7	1096.7	1097.7	1098.8	1099.8	1100.3	1100.8	1101.8	1102.9	1103.9	1104.9
145°	1144.2	1145.2	1146.2	1147.3	1148.3	1148.8	1149.2	1150.0	1150.7	1151.5	1152.3
147.5°	1189.2	1190.0	1190.8	1191.5	1192.3	1192.7	1193.0	1193.5	1194.0	1194.5	1195.0
150°	1234.2	1234.0	1233.7	1233.5	1233.2	1233.1	1233.6	1234.6	1235.7	1236.7	1237.7
152.5°	1271.2	1271.7	1272.2	1272.7	1273.2	1273.5	1273.6	1273.9	1274.2	1274.4	1274.7
155°	1309.3	1309.3	1309.3	1309.3	1309.3	1309.3	1309.4	1309.7	1309.8	1310.2	1310.4
157.5°	1343.9	1343.4	1342.9	1342.4	1341.9	1341.6	1341.7	1342.0	1342.3	1342.5	1342.8
160°	1373.9	1373.1	1372.4	1371.6	1370.9	1370.5	1370.6	1370.9	1371.1	1371.4	1371.6
162.5°	1400.5	1400.0	1399.5	1399.0	1398.5	1398.2	1398.2	1398.2	1398.2	1398.2	1398.2
165°	1423.6	1423.1	1422.6	1422.1	1421.6	1421.3	1421.4	1421.7	1421.9	1422.2	1422.4
167.5°	1444.4	1443.4	1442.4	1441.3	1440.3	1439.8	1439.8	1439.8	1439.8	1439.8	1439.8
170°	1460.5	1459.5	1458.5	1457.4	1456.4	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9
172.5°	1472.1	1471.1	1470.1	1469.0	1468.0	1467.5	1467.5	1467.5	1467.5	1467.5	1467.5
175°	1480.2	1479.2	1478.1	1477.1	1476.0	1475.5	1475.5	1475.5	1475.5	1475.5	1475.5
177.5°	1485.9	1484.9	1483.9	1482.8	1481.8	1481.3	1481.2	1480.9	1480.7	1480.4	1480.2
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1695.7	1705.0	1713.0	1709.0	1725.0	1723.7	1726.4	1731.7	1733.0	1730.4	1725.0
5°	1787.7	1801.1	1823.8	1835.8	1833.1	1843.8	1849.1	1857.1	1865.1	1862.5	1862.5
7.5°	1890.5	1909.2	1931.8	1962.5	1966.5	1975.9	1991.9	1991.9	2001.2	1997.2	1995.9
10°	1979.9	2002.5	2038.6	2062.6	2073.3	2078.6	2094.6	2099.9	2110.6	2111.9	2111.9
12.5°	2053.2	2093.3	2117.3	2141.3	2146.6	2154.6	2166.6	2174.7	2178.7	2178.7	2174.7
15°	2091.9	2124.0	2152.0	2177.3	2192.0	2198.7	2210.7	2220.0	2225.3	2237.4	2240.0
17.5°	2107.9	2146.6	2192.0	2228.0	2253.4	2260.0	2284.1	2292.1	2302.7	2308.1	2314.7
20°	2130.6	2186.7	2241.4	2285.4	2309.4	2326.7	2352.1	2389.4	2400.1	2400.1	2396.1
22.5°	2150.6	2222.7	2297.4	2368.1	2388.1	2422.8	2469.5	2509.5	2525.5	2532.2	2526.9
25°	2174.7	2273.4	2370.8	2458.8	2513.5	2538.9	2601.6	2649.6	2668.3	2679.0	2681.6
27.5°	2216.0	2340.1	2464.2	2576.2	2632.3	2661.6	2727.0	2768.3	2791.0	2800.4	2793.7
30°	2262.7	2414.8	2558.9	2658.9	2696.3	2732.3	2775.0	2791.0	2785.7	2785.7	2805.7
32.5°	2310.7	2468.2	2596.2	2661.6	2675.0	2669.6	2652.3	2604.2	2576.2	2576.2	2593.6
35°	2337.4	2473.5	2538.9	2517.5	2465.5	2434.8	2340.1	2286.7	2226.7	2222.7	2242.7
37.5°	2322.7	2381.4	2354.8	2214.7	2144.0	2085.3	1937.2	1878.5	1834.4	1773.1	1867.8
40°	2220.0	2200.0	2061.2	1859.8	1781.1	1698.4	1581.0	1522.3	1460.9	1451.5	1474.2
42.5°	2046.6	1927.8	1725.0	1530.3	1450.2	1391.5	1302.1	1244.8	1206.1	1190.1	1216.7
45°	1830.4	1643.7	1440.9	1286.1	1198.1	1167.4	1086.0	1035.3	1005.9	993.9	1012.6
47.5°	1566.3	1378.2	1186.1	1055.3	1003.3	972.6	917.9	873.9	848.5	840.5	848.5
50°	1330.1	1136.7	975.3	891.2	844.5	819.2	773.8	745.8	725.8	720.4	733.8
52.5°	1126.0	949.9	827.2	752.5	721.8	700.4	668.4	644.4	632.4	627.0	636.4
55°	943.2	800.5	701.8	637.7	615.0	601.7	573.7	560.3	547.0	545.7	555.0
57.5°	781.8	683.1	592.4	547.0	540.3	520.3	496.3	484.3	477.6	476.3	480.3
60°	651.1	563.0	508.3	468.3	458.9	442.9	429.6	421.6	413.6	410.9	413.6
62.5°	541.7	472.3	428.3	401.6	388.2	384.2	369.6	360.2	358.9	358.9	361.6
65°	446.9	388.2	360.2	338.9	329.5	325.5	314.9	308.2	309.5	309.5	310.9
67.5°	364.2	321.5	296.2	285.5	277.5	276.2	265.5	262.8	260.2	260.2	262.8
70°	289.5	262.8	244.1	238.8	237.5	228.1	224.1	222.8	218.8	220.1	220.1
72.5°	226.8	209.5	198.8	190.8	192.1	186.8	181.4	181.4	178.8	182.8	182.8
75°	168.1	160.1	152.1	149.4	152.1	149.4	145.4	144.1	145.4	144.1	144.1
77.5°	124.1	120.1	117.4	116.1	116.1	110.7	108.1	110.7	105.4	108.1	108.1
80°	86.7	81.4	80.0	77.4	78.7	74.7	76.0	73.4	73.4	73.4	73.4
82.5°	54.7	53.4	53.4	53.4	52.0	52.0	52.0	52.0	52.0	52.0	50.7
85°	33.4	32.0	32.0	32.0	30.7	30.7	30.7	30.7	30.7	30.7	30.7
87.5°	13.3	14.7	14.7	16.0	14.7	13.3	13.3	13.3	14.7	14.7	13.3
90°	19.8	21.0	22.3	23.6	24.2	24.6	25.4	26.1	26.9	27.7	26.9
92.5°	52.6	54.4	56.2	58.0	58.9	59.2	59.7	60.2	60.7	61.2	60.7
95°	90.7	92.5	94.3	96.1	97.0	97.3	97.8	98.3	98.8	99.3	98.8
97.5°	134.3	135.9	137.4	138.9	139.7	139.8	140.1	140.4	140.6	140.9	140.6
100°	179.0	181.3	183.6	185.9	187.0	187.3	187.8	188.3	188.9	189.4	188.9
102.5°	225.4	228.0	230.5	233.1	234.4	234.8	235.5	236.3	237.0	237.8	237.0
105°	277.5	279.0	280.6	282.1	282.9	283.3	284.0	284.8	285.5	286.3	285.5
107.5°	332.2	332.9	333.7	334.4	334.8	334.8	334.8	334.8	334.8	334.8	334.8
110°	388.7	389.5	390.2	391.0	391.4	391.3	391.0	390.7	390.5	390.2	390.5

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	445.9	446.2	446.4	446.7	446.8	446.5	446.0	445.5	445.0	444.5	445.0
115°	504.3	504.0	503.8	503.5	503.4	503.3	503.0	502.7	502.5	502.2	502.5
117.5°	561.4	561.6	561.9	562.2	562.3	561.8	560.8	559.7	558.7	557.7	558.7
120°	620.0	620.0	620.0	620.0	620.0	619.5	618.5	617.4	616.4	615.4	616.4
122.5°	677.5	677.2	677.0	676.7	676.6	676.2	675.4	674.7	673.9	673.1	673.9
125°	733.8	733.3	732.8	732.3	732.0	731.9	731.6	731.3	731.1	730.8	731.1
127.5°	789.5	789.2	789.0	788.7	788.6	788.3	787.8	787.3	786.8	786.3	786.8
130°	844.9	844.6	844.4	844.1	844.0	843.7	843.2	842.7	842.2	841.7	842.2
132.5°	898.0	897.8	897.5	897.2	897.1	896.7	895.9	895.2	894.4	893.6	894.4
135°	952.5	952.5	952.5	952.5	952.5	952.0	951.0	949.9	948.9	947.9	948.9
137.5°	1005.9	1006.1	1006.4	1006.7	1006.8	1006.2	1004.9	1003.6	1002.3	1001.0	1002.3
140°	1055.8	1056.3	1056.8	1057.3	1057.6	1057.0	1055.7	1054.4	1053.1	1051.8	1053.1
142.5°	1105.2	1105.4	1105.7	1106.0	1106.1	1105.5	1104.2	1102.9	1101.6	1100.3	1101.6
145°	1152.3	1152.3	1152.3	1152.3	1152.3	1151.9	1151.1	1150.4	1149.6	1148.8	1149.6
147.5°	1195.8	1196.5	1197.3	1198.0	1198.4	1197.4	1195.3	1193.3	1191.2	1189.2	1191.2
150°	1237.7	1237.7	1237.7	1237.7	1237.7	1237.4	1236.9	1236.4	1235.9	1235.4	1235.9
152.5°	1275.5	1276.2	1277.0	1277.7	1278.1	1277.6	1276.6	1275.5	1274.5	1273.5	1274.5
155°	1311.4	1312.5	1313.5	1314.6	1315.1	1314.5	1313.2	1311.9	1310.6	1309.3	1310.6
157.5°	1343.8	1344.8	1345.9	1346.9	1347.4	1346.5	1344.7	1342.9	1341.1	1339.3	1341.1
160°	1372.6	1373.7	1374.7	1375.8	1376.3	1375.7	1374.4	1373.1	1371.8	1370.5	1371.8
162.5°	1399.5	1400.8	1402.1	1403.4	1404.0	1403.2	1401.7	1400.1	1398.6	1397.0	1398.6
165°	1423.4	1424.5	1425.5	1426.6	1427.1	1426.3	1424.8	1423.2	1421.7	1420.1	1421.7
167.5°	1441.3	1442.9	1444.4	1445.9	1446.7	1445.9	1444.4	1442.9	1441.3	1439.8	1441.3
170°	1457.4	1459.0	1460.5	1462.0	1462.8	1461.9	1460.1	1458.4	1456.6	1454.8	1456.6
172.5°	1469.0	1470.6	1472.1	1473.6	1474.4	1473.6	1472.1	1470.6	1469.0	1467.5	1469.0
175°	1477.1	1478.6	1480.2	1481.7	1482.5	1481.6	1479.8	1478.0	1476.2	1474.4	1476.2
177.5°	1481.7	1483.3	1484.8	1486.3	1487.1	1486.2	1484.4	1482.6	1480.8	1479.0	1480.8
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1731.7	1722.4	1726.4	1722.4	1718.4	1714.4	1705.0	1691.7	1681.0	1673.0	1671.7
5°	1865.1	1853.1	1845.1	1841.1	1833.1	1822.4	1805.1	1785.1	1761.1	1751.7	1733.0
7.5°	1987.9	1983.9	1965.2	1962.5	1957.2	1937.2	1907.8	1881.1	1850.5	1825.1	1801.1
10°	2103.9	2094.6	2081.3	2062.6	2059.9	2034.6	2006.5	1969.2	1929.2	1905.2	1862.5
12.5°	2176.0	2165.3	2150.6	2138.6	2132.0	2115.9	2077.3	2039.9	2003.9	1959.9	1922.5
15°	2228.0	2214.7	2188.0	2178.7	2170.6	2149.3	2121.3	2082.6	2034.6	2003.9	1950.5
17.5°	2298.7	2282.7	2256.0	2238.7	2224.0	2190.7	2150.6	2098.6	2053.2	2018.6	1970.5
20°	2380.1	2356.1	2321.4	2298.7	2277.4	2238.7	2182.7	2121.3	2055.9	2013.2	1963.9
22.5°	2514.9	2469.5	2414.8	2382.8	2353.4	2286.7	2220.0	2144.0	2070.6	2006.5	1946.5
25°	2645.6	2600.2	2532.2	2488.2	2442.8	2365.4	2277.4	2172.0	2078.6	2003.9	1925.2
27.5°	2767.0	2720.3	2657.6	2604.2	2560.2	2444.1	2328.1	2209.3	2090.6	1987.9	1907.8
30°	2795.0	2775.0	2727.0	2680.3	2640.3	2533.5	2398.8	2248.0	2105.3	1973.2	1883.8
32.5°	2625.6	2675.0	2687.0	2680.3	2654.9	2578.9	2454.8	2296.1	2126.6	1966.5	1843.8
35°	2273.4	2362.8	2454.8	2504.2	2528.2	2538.9	2465.5	2320.1	2141.3	1955.9	1817.1
37.5°	1885.1	1971.9	2117.3	2190.7	2272.0	2378.8	2408.1	2314.7	2134.6	1947.8	1774.4
40°	1548.9	1659.7	1779.7	1846.5	1917.2	2109.3	2254.7	2244.0	2113.3	1918.5	1741.1
42.5°	1260.8	1330.1	1435.5	1508.9	1595.6	1810.4	2005.2	2101.3	2049.2	1882.5	1698.4
45°	1051.3	1104.7	1179.4	1254.1	1307.5	1502.2	1733.0	1890.5	1939.8	1818.4	1633.0
47.5°	885.9	925.9	991.3	1038.0	1095.3	1248.8	1448.9	1670.3	1774.4	1727.7	1563.6
50°	759.1	791.1	843.2	872.5	923.2	1055.3	1207.4	1439.5	1597.0	1602.3	1471.6
52.5°	648.4	680.4	724.4	749.8	780.5	869.9	1023.3	1219.4	1400.8	1467.6	1366.2
55°	564.3	583.0	619.0	639.1	667.1	753.8	851.2	1017.9	1207.4	1316.8	1252.8
57.5°	487.0	507.0	529.7	545.7	565.7	635.1	723.1	848.5	1036.6	1155.4	1134.0
60°	424.3	436.3	457.6	469.6	488.3	533.7	595.0	720.4	869.9	981.9	993.9
62.5°	365.6	376.2	390.9	401.6	413.6	449.6	495.0	584.4	715.1	836.5	852.5
65°	314.9	324.2	332.2	341.5	350.9	373.6	412.2	481.6	583.0	696.4	731.1
67.5°	269.5	272.2	284.2	285.5	290.8	308.2	336.2	392.2	465.6	556.3	601.7
70°	225.5	230.8	233.5	237.5	242.8	254.8	277.5	306.9	361.6	434.9	477.6
72.5°	182.8	184.1	188.1	190.8	196.1	205.5	216.1	238.8	273.5	326.9	365.6
75°	145.4	146.8	149.4	150.8	154.8	157.4	162.8	178.8	202.8	234.8	262.8
77.5°	109.4	112.1	114.7	114.7	116.1	118.7	121.4	126.7	138.8	160.1	184.1
80°	74.7	76.0	76.0	77.4	76.0	80.0	84.1	90.7	96.1	102.7	114.7
82.5°	52.0	52.0	52.0	53.4	53.4	54.7	54.7	56.0	57.4	61.4	66.7
85°	32.0	32.0	33.4	30.7	32.0	33.4	33.4	32.0	33.4	34.7	36.0
87.5°	13.3	13.3	14.7	14.7	14.7	14.7	13.3	14.7	13.3	14.7	14.7
90°	26.1	25.4	24.6	24.2	23.6	22.3	21.0	19.8	18.5	16.7	14.9
92.5°	60.2	59.7	59.2	58.9	58.0	56.2	54.4	52.6	50.8	48.5	46.2
95°	98.3	97.8	97.3	97.0	96.1	94.3	92.5	90.7	88.9	86.3	83.8
97.5°	140.4	140.1	139.8	139.7	138.9	137.4	135.9	134.3	132.8	129.2	125.6
100°	188.3	187.8	187.3	187.0	185.9	183.6	181.3	179.0	176.7	173.3	170.0
102.5°	236.3	235.5	234.8	234.4	233.1	230.5	228.0	225.4	222.8	221.5	220.3
105°	284.8	284.0	283.3	282.9	282.1	280.6	279.0	277.5	275.9	274.4	272.8
107.5°	334.8	334.8	334.8	334.8	334.4	333.7	332.9	332.2	331.4	330.1	328.8
110°	390.7	391.0	391.3	391.4	391.0	390.2	389.5	388.7	387.9	387.1	386.4

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	445.5	446.0	446.5	446.8	446.7	446.4	446.2	445.9	445.7	444.7	443.6
115°	502.7	503.0	503.3	503.4	503.5	503.8	504.0	504.3	504.5	504.0	503.5
117.5°	559.7	560.8	561.8	562.3	562.2	561.9	561.6	561.4	561.1	560.6	560.1
120°	617.4	618.5	619.5	620.0	620.0	620.0	620.0	620.0	620.0	619.8	619.5
122.5°	674.7	675.4	676.2	676.6	676.7	677.0	677.2	677.5	677.7	676.9	676.2
125°	731.3	731.6	731.9	732.0	732.3	732.8	733.3	733.8	734.3	734.1	733.8
127.5°	787.3	787.8	788.3	788.6	788.7	789.0	789.2	789.5	789.7	789.5	789.2
130°	842.7	843.2	843.7	844.0	844.1	844.4	844.6	844.9	845.1	844.6	844.1
132.5°	895.2	895.9	896.7	897.1	897.2	897.5	897.8	898.0	898.3	898.5	898.8
135°	949.9	951.0	952.0	952.5	952.5	952.5	952.5	952.5	952.5	952.3	952.0
137.5°	1003.6	1004.9	1006.2	1006.8	1006.7	1006.4	1006.1	1005.9	1005.6	1005.1	1004.6
140°	1054.4	1055.7	1057.0	1057.6	1057.3	1056.8	1056.3	1055.8	1055.3	1054.5	1053.7
142.5°	1102.9	1104.2	1105.5	1106.1	1106.0	1105.7	1105.4	1105.2	1104.9	1103.9	1102.9
145°	1150.4	1151.1	1151.9	1152.3	1152.3	1152.3	1152.3	1152.3	1152.3	1151.5	1150.7
147.5°	1193.3	1195.3	1197.4	1198.4	1198.0	1197.3	1196.5	1195.8	1195.0	1194.5	1194.0
150°	1236.4	1236.9	1237.4	1237.7	1237.7	1237.7	1237.7	1237.7	1237.7	1236.7	1235.7
152.5°	1275.5	1276.6	1277.6	1278.1	1277.7	1277.0	1276.2	1275.5	1274.7	1274.4	1274.2
155°	1311.9	1313.2	1314.5	1315.1	1314.6	1313.5	1312.5	1311.4	1310.4	1310.2	1309.9
157.5°	1342.9	1344.7	1346.5	1347.4	1346.9	1345.9	1344.8	1343.8	1342.8	1342.5	1342.3
160°	1373.1	1374.4	1375.7	1376.3	1375.8	1374.7	1373.7	1372.6	1371.6	1371.4	1371.1
162.5°	1400.1	1401.7	1403.2	1404.0	1403.4	1402.1	1400.8	1399.5	1398.2	1398.2	1398.2
165°	1423.2	1424.8	1426.3	1427.1	1426.6	1425.5	1424.5	1423.4	1422.4	1422.2	1421.9
167.5°	1442.9	1444.4	1445.9	1446.7	1445.9	1444.4	1442.9	1441.3	1439.8	1439.8	1439.8
170°	1458.4	1460.1	1461.9	1462.8	1462.0	1460.5	1459.0	1457.4	1455.9	1455.9	1455.9
172.5°	1470.6	1472.1	1473.6	1474.4	1473.6	1472.1	1470.6	1469.0	1467.5	1467.5	1467.5
175°	1478.0	1479.8	1481.6	1482.5	1481.7	1480.2	1478.6	1477.1	1475.5	1475.5	1475.5
177.5°	1482.6	1484.4	1486.2	1487.1	1486.3	1484.8	1483.3	1481.7	1480.2	1480.4	1480.7
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1667.7	1659.7	1654.3	1653.0	1645.0	1638.3	1630.3	1629.0	1625.0	1614.3	1607.6
5°	1719.7	1701.0	1697.0	1685.0	1665.0	1650.3	1631.7	1621.0	1609.0	1589.0	1573.0
7.5°	1773.1	1747.7	1729.0	1711.7	1683.7	1657.0	1630.3	1609.0	1587.6	1558.3	1534.3
10°	1825.1	1786.4	1763.7	1738.4	1699.7	1659.7	1622.3	1591.6	1556.9	1522.3	1487.6
12.5°	1873.1	1823.8	1790.4	1754.4	1706.4	1657.0	1609.0	1566.3	1530.3	1483.6	1444.9
15°	1902.5	1847.8	1814.4	1779.7	1707.7	1653.0	1597.0	1542.3	1494.2	1444.9	1408.9
17.5°	1919.8	1858.5	1821.1	1789.1	1715.7	1641.0	1569.0	1510.2	1458.2	1399.5	1351.5
20°	1911.8	1851.8	1817.1	1786.4	1701.0	1626.3	1548.9	1480.9	1415.5	1355.5	1304.8
22.5°	1894.5	1831.8	1793.1	1765.1	1689.0	1601.0	1515.6	1442.2	1374.2	1314.1	1256.8
25°	1857.1	1795.8	1762.4	1727.7	1653.0	1569.0	1482.2	1403.5	1331.5	1267.4	1203.4
27.5°	1823.8	1749.1	1714.4	1683.7	1605.0	1530.3	1444.9	1358.2	1284.8	1218.1	1154.0
30°	1785.1	1701.0	1663.7	1622.3	1551.6	1480.9	1395.5	1315.5	1239.4	1168.7	1107.3
32.5°	1743.7	1646.3	1603.6	1556.9	1484.9	1418.2	1346.1	1267.4	1191.4	1122.0	1058.0
35°	1690.4	1586.3	1536.9	1492.9	1418.2	1351.5	1284.8	1219.4	1143.4	1070.0	1008.6
37.5°	1639.7	1524.9	1472.9	1422.2	1343.5	1279.4	1224.7	1163.4	1090.0	1019.3	960.6
40°	1582.3	1450.2	1396.8	1350.2	1268.8	1198.1	1148.7	1100.7	1036.6	968.6	904.5
42.5°	1530.3	1380.8	1324.8	1276.8	1191.4	1124.7	1078.0	1038.0	981.9	919.2	853.9
45°	1458.2	1306.1	1248.8	1198.1	1111.3	1048.6	1000.6	965.9	921.9	863.2	804.5
47.5°	1391.5	1234.1	1171.4	1110.0	1031.3	967.3	923.2	896.5	867.2	815.2	755.1
50°	1310.1	1151.4	1087.3	1036.6	947.2	892.5	848.5	829.8	803.2	753.8	705.8
52.5°	1222.1	1071.3	1011.3	949.9	867.2	813.8	775.1	753.8	732.4	696.4	651.1
55°	1119.3	981.9	925.9	871.2	788.5	739.1	704.4	681.7	669.7	636.4	603.0
57.5°	1020.6	891.2	839.2	788.5	716.4	660.4	637.7	617.7	600.4	576.3	548.3
60°	920.6	803.2	747.1	701.8	639.1	588.4	569.7	549.7	536.3	517.6	497.6
62.5°	805.8	705.8	663.1	620.4	567.0	527.0	505.6	489.6	472.3	460.3	442.9
65°	684.4	613.7	572.3	540.3	489.6	453.6	437.6	426.9	412.2	400.2	386.9
67.5°	571.0	515.0	497.6	462.9	424.3	392.2	380.2	366.9	354.9	348.2	336.2
70°	461.6	421.6	404.2	394.9	352.2	330.9	320.2	314.9	300.2	293.5	285.5
72.5°	357.5	342.9	330.9	318.9	290.8	277.5	265.5	260.2	249.5	244.1	241.5
75°	264.2	254.8	248.2	246.8	234.8	221.5	209.5	206.8	198.8	193.5	190.8
77.5°	185.4	182.8	181.4	182.8	174.8	166.8	164.1	161.4	152.1	150.8	150.8
80°	121.4	128.1	128.1	126.7	124.1	122.7	118.7	116.1	110.7	109.4	110.7
82.5°	74.7	78.7	80.0	82.7	81.4	80.0	77.4	76.0	77.4	74.7	76.0
85°	37.4	40.0	45.4	45.4	46.7	46.7	46.7	45.4	42.7	44.0	42.7
87.5°	14.7	16.0	16.0	16.0	14.7	18.7	20.0	20.0	20.0	17.3	17.3
90°	13.1	11.3	10.4	9.4	7.3	5.3	3.2	1.2	3.2	5.3	7.3
92.5°	43.9	41.6	40.4	39.8	38.5	37.2	35.9	34.6	35.9	37.2	38.5
95°	81.2	78.7	77.4	77.1	76.6	76.1	75.5	75.0	75.5	76.1	76.6
97.5°	122.0	118.4	116.6	116.5	116.2	116.0	115.7	115.5	115.7	116.0	116.2
100°	166.6	163.3	161.6	161.6	161.6	161.6	161.6	161.6	161.6	161.6	161.6
102.5°	219.0	217.7	217.1	216.5	215.2	213.9	212.6	211.3	212.6	213.9	215.2
105°	271.3	269.8	269.0	268.4	267.1	265.8	264.5	263.2	264.5	265.8	267.1
107.5°	327.5	326.2	325.6	325.0	323.7	322.4	321.1	319.8	321.1	322.4	323.7
110°	385.6	384.9	384.5	383.9	382.6	381.3	380.0	378.7	380.0	381.3	382.6

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	442.6	441.5	441.0	440.7	440.2	439.7	439.2	438.7	439.2	439.7	440.2
115°	503.0	502.5	502.2	501.7	500.7	499.6	498.6	497.6	498.6	499.6	500.7
117.5°	559.6	559.1	558.8	558.7	558.4	558.2	557.9	557.7	557.9	558.2	558.4
120°	619.3	619.0	618.9	618.3	617.0	615.7	614.4	613.1	614.4	615.7	617.0
122.5°	675.4	674.7	674.3	674.2	673.9	673.6	673.4	673.1	673.4	673.6	673.9
125°	733.6	733.3	733.2	732.4	730.9	729.3	727.8	726.2	727.8	729.3	730.9
127.5°	789.0	788.7	788.6	788.2	787.4	786.7	785.9	785.1	785.9	786.7	787.4
130°	843.6	843.1	842.8	842.2	840.9	839.6	838.4	837.1	838.4	839.6	840.9
132.5°	899.0	899.3	899.4	898.2	895.9	893.6	891.3	889.0	891.3	893.6	895.9
135°	951.8	951.5	951.4	950.6	949.1	947.5	946.0	944.4	946.0	947.5	949.1
137.5°	1004.1	1003.6	1003.3	1002.5	1001.0	999.5	997.9	996.4	997.9	999.5	1001.0
140°	1053.0	1052.2	1051.8	1051.2	1049.9	1048.6	1047.3	1046.0	1047.3	1048.6	1049.9
142.5°	1101.8	1100.8	1100.3	1099.8	1098.8	1097.7	1096.7	1095.7	1096.7	1097.7	1098.8
145°	1150.0	1149.2	1148.8	1148.3	1147.3	1146.2	1145.2	1144.2	1145.2	1146.2	1147.3
147.5°	1193.5	1193.0	1192.7	1192.3	1191.5	1190.8	1190.0	1189.2	1190.0	1190.8	1191.5
150°	1234.6	1233.6	1233.1	1233.2	1233.5	1233.7	1234.0	1234.2	1234.0	1233.7	1233.5
152.5°	1273.9	1273.6	1273.5	1273.2	1272.7	1272.2	1271.7	1271.2	1271.7	1272.2	1272.7
155°	1309.7	1309.4	1309.3	1309.3	1309.3	1309.3	1309.3	1309.3	1309.3	1309.3	1309.3
157.5°	1342.0	1341.7	1341.6	1341.9	1342.4	1342.9	1343.4	1343.9	1343.4	1342.9	1342.4
160°	1370.9	1370.6	1370.5	1370.9	1371.6	1372.4	1373.1	1373.9	1373.1	1372.4	1371.6
162.5°	1398.2	1398.2	1398.2	1398.5	1399.0	1399.5	1400.0	1400.5	1400.0	1399.5	1399.0
165°	1421.7	1421.4	1421.3	1421.6	1422.1	1422.6	1423.1	1423.6	1423.1	1422.6	1422.1
167.5°	1439.8	1439.8	1439.8	1440.3	1441.3	1442.4	1443.4	1444.4	1443.4	1442.4	1441.3
170°	1455.9	1455.9	1455.9	1456.4	1457.4	1458.5	1459.5	1460.5	1459.5	1458.5	1457.4
172.5°	1467.5	1467.5	1467.5	1468.0	1469.0	1470.1	1471.1	1472.1	1471.1	1470.1	1469.0
175°	1475.5	1475.5	1475.5	1476.0	1477.1	1478.1	1479.2	1480.2	1479.2	1478.1	1477.1
177.5°	1480.9	1481.2	1481.3	1481.8	1482.8	1483.9	1484.9	1485.9	1484.9	1483.9	1482.8
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1603.6	1598.3	1594.3	1590.3	1573.0	1554.3	1551.6	1547.6	1539.6	1548.9	1544.9
5°	1562.3	1550.3	1543.6	1526.3	1504.9	1488.9	1475.6	1459.6	1452.9	1447.5	1446.2
7.5°	1511.6	1500.9	1488.9	1471.6	1444.9	1418.2	1398.2	1382.2	1368.8	1362.2	1362.2
10°	1462.2	1448.9	1432.9	1403.5	1378.2	1344.8	1323.5	1307.5	1288.8	1278.1	1268.8
12.5°	1411.5	1396.8	1382.2	1344.8	1315.5	1280.8	1250.1	1230.1	1220.7	1208.7	1192.7
15°	1360.8	1338.1	1323.5	1286.1	1248.8	1214.1	1194.1	1172.7	1151.4	1139.4	1134.0
17.5°	1307.5	1291.4	1267.4	1227.4	1186.1	1155.4	1126.0	1106.0	1080.7	1068.6	1056.6
20°	1259.4	1235.4	1211.4	1171.4	1131.4	1090.0	1060.6	1036.6	1020.6	1011.3	1000.6
22.5°	1202.1	1179.4	1159.4	1116.7	1072.6	1034.0	1001.9	987.3	971.3	956.6	945.9
25°	1152.7	1130.0	1110.0	1063.3	1015.3	979.3	955.2	936.6	919.2	912.6	901.9
27.5°	1100.7	1079.3	1052.6	1005.9	963.3	932.6	907.2	889.9	876.5	863.2	855.2
30°	1051.3	1027.3	1003.3	952.6	917.9	887.2	863.2	841.8	831.2	824.5	811.2
32.5°	1003.3	972.6	952.6	905.9	872.5	843.2	823.2	804.5	791.1	779.1	768.5
35°	951.2	917.9	897.9	859.2	824.5	795.1	777.8	764.5	748.5	737.8	732.4
37.5°	901.9	873.9	853.9	813.8	779.1	755.1	736.4	719.1	712.4	697.8	695.1
40°	848.5	824.5	805.8	767.1	735.1	716.4	696.4	680.4	668.4	661.7	652.4
42.5°	800.5	780.5	760.5	724.4	693.8	671.1	656.4	641.7	631.0	620.4	613.7
45°	756.5	735.1	716.4	681.7	651.1	631.0	616.4	599.0	596.4	581.7	575.0
47.5°	709.8	691.1	675.1	639.1	611.0	591.0	573.7	561.7	549.7	544.3	535.0
50°	664.4	645.7	627.0	595.0	569.7	549.7	532.3	519.0	512.3	504.3	496.3
52.5°	615.0	600.4	585.7	552.3	527.0	509.6	495.0	477.6	471.0	464.3	458.9
55°	573.7	552.3	536.3	508.3	485.6	466.9	450.9	437.6	430.9	425.6	418.9
57.5°	517.6	504.3	491.0	465.6	444.3	425.6	409.6	398.9	390.9	386.9	388.2
60°	469.6	454.9	446.9	420.3	398.9	384.2	369.6	358.9	350.9	346.9	345.5
62.5°	418.9	408.2	393.6	374.9	353.5	340.2	329.5	321.5	308.2	306.9	302.9
65°	369.6	361.6	348.2	330.9	313.5	301.5	289.5	278.8	273.5	266.8	262.8
67.5°	321.5	313.5	301.5	286.8	274.8	262.8	252.2	241.5	232.1	226.8	224.1
70°	274.8	268.2	260.2	242.8	228.1	218.8	210.8	204.1	194.8	192.1	190.8
72.5°	229.5	222.8	218.8	204.1	190.8	182.8	174.8	168.1	164.1	162.8	158.8
75°	188.1	181.4	176.1	162.8	154.8	149.4	141.4	138.8	134.7	133.4	132.1
77.5°	146.8	140.1	138.8	129.4	120.1	117.4	114.7	109.4	109.4	109.4	106.7
80°	105.4	104.1	102.7	93.4	89.4	86.7	85.4	81.4	78.7	76.0	74.7
82.5°	70.7	69.4	68.0	64.0	60.0	58.7	57.4	54.7	54.7	56.0	53.4
85°	42.7	40.0	38.7	37.4	34.7	34.7	36.0	34.7	34.7	34.7	33.4
87.5°	16.0	16.0	16.0	16.0	17.3	14.7	16.0	16.0	14.7	14.7	13.3
90°	9.4	10.4	11.3	13.1	14.9	16.7	18.5	19.8	21.0	22.3	23.6
92.5°	39.8	40.4	41.6	43.9	46.2	48.5	50.8	52.6	54.4	56.2	58.0
95°	77.1	77.4	78.7	81.2	83.8	86.3	88.9	90.7	92.5	94.3	96.1
97.5°	116.5	116.6	118.4	122.0	125.6	129.2	132.8	134.3	135.9	137.4	138.9
100°	161.6	161.6	163.3	166.6	170.0	173.3	176.7	179.0	181.3	183.6	185.9
102.5°	216.5	217.1	217.7	219.0	220.3	221.5	222.8	225.4	228.0	230.5	233.1
105°	268.4	269.0	269.8	271.3	272.8	274.4	275.9	277.5	279.0	280.6	282.1
107.5°	325.0	325.6	326.2	327.5	328.8	330.1	331.4	332.2	332.9	333.7	334.4
110°	383.9	384.5	384.9	385.6	386.4	387.1	387.9	388.7	389.5	390.2	391.0

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	440.7	441.0	441.5	442.6	443.6	444.7	445.7	445.9	446.2	446.4	446.7
115°	501.7	502.2	502.5	503.0	503.5	504.0	504.5	504.3	504.0	503.8	503.5
117.5°	558.7	558.8	559.1	559.6	560.1	560.6	561.1	561.4	561.6	561.9	562.2
120°	618.3	618.9	619.0	619.3	619.5	619.8	620.0	620.0	620.0	620.0	620.0
122.5°	674.2	674.3	674.7	675.4	676.2	676.9	677.7	677.5	677.2	677.0	676.7
125°	732.4	733.2	733.3	733.6	733.8	734.1	734.3	733.8	733.3	732.8	732.3
127.5°	788.2	788.6	788.7	789.0	789.2	789.5	789.7	789.5	789.2	789.0	788.7
130°	842.2	842.8	843.1	843.6	844.1	844.6	845.1	844.9	844.6	844.4	844.1
132.5°	898.2	899.4	899.3	899.0	898.8	898.5	898.3	898.0	897.8	897.5	897.2
135°	950.6	951.4	951.5	951.8	952.0	952.3	952.5	952.5	952.5	952.5	952.5
137.5°	1002.5	1003.3	1003.6	1004.1	1004.6	1005.1	1005.6	1005.9	1006.1	1006.4	1006.7
140°	1051.2	1051.8	1052.2	1053.0	1053.7	1054.5	1055.3	1055.8	1056.3	1056.8	1057.3
142.5°	1099.8	1100.3	1100.8	1101.8	1102.9	1103.9	1104.9	1105.2	1105.4	1105.7	1106.0
145°	1148.3	1148.8	1149.2	1150.0	1150.7	1151.5	1152.3	1152.3	1152.3	1152.3	1152.3
147.5°	1192.3	1192.7	1193.0	1193.5	1194.0	1194.5	1195.0	1195.8	1196.5	1197.3	1198.0
150°	1233.2	1233.1	1233.6	1234.6	1235.7	1236.7	1237.7	1237.7	1237.7	1237.7	1237.7
152.5°	1273.2	1273.5	1273.6	1273.9	1274.2	1274.4	1274.7	1275.5	1276.2	1277.0	1277.7
155°	1309.3	1309.3	1309.4	1309.7	1309.9	1310.2	1310.4	1311.4	1312.5	1313.5	1314.6
157.5°	1341.9	1341.6	1341.7	1342.0	1342.3	1342.5	1342.8	1343.8	1344.8	1345.9	1346.9
160°	1370.9	1370.5	1370.6	1370.9	1371.1	1371.4	1371.6	1372.6	1373.7	1374.7	1375.8
162.5°	1398.5	1398.2	1398.2	1398.2	1398.2	1398.2	1398.2	1399.5	1400.8	1402.1	1403.4
165°	1421.6	1421.3	1421.4	1421.7	1421.9	1422.2	1422.4	1423.4	1424.5	1425.5	1426.6
167.5°	1440.3	1439.8	1439.8	1439.8	1439.8	1439.8	1439.8	1441.3	1442.9	1444.4	1445.9
170°	1456.4	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1457.4	1459.0	1460.5	1462.0
172.5°	1468.0	1467.5	1467.5	1467.5	1467.5	1467.5	1467.5	1469.0	1470.6	1472.1	1473.6
175°	1476.0	1475.5	1475.5	1475.5	1475.5	1475.5	1475.5	1477.1	1478.6	1480.2	1481.7
177.5°	1481.8	1481.3	1481.2	1480.9	1480.7	1480.4	1480.2	1481.7	1483.3	1484.8	1486.3
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1538.3	1540.9	1534.3	1531.6	1526.3	1532.9	1534.3	1532.9	1544.9	1539.6	1542.3
5°	1448.9	1443.5	1439.5	1430.2	1430.2	1431.5	1435.5	1428.9	1432.9	1442.2	1440.9
7.5°	1350.2	1347.5	1348.8	1338.1	1330.1	1332.8	1330.1	1342.1	1348.8	1346.1	1351.5
10°	1260.8	1266.1	1254.1	1248.8	1243.4	1248.8	1247.4	1250.1	1258.1	1263.4	1272.8
12.5°	1188.7	1187.4	1180.7	1175.4	1166.0	1168.7	1176.7	1174.0	1175.4	1187.4	1186.1
15°	1120.7	1112.7	1107.3	1095.3	1098.0	1088.7	1096.7	1106.0	1110.0	1120.7	1127.3
17.5°	1052.6	1051.3	1044.6	1043.3	1028.6	1024.6	1032.6	1035.3	1039.3	1044.6	1054.0
20°	995.3	993.9	984.6	981.9	969.9	977.9	975.3	980.6	983.3	993.9	997.9
22.5°	943.2	936.6	933.9	929.9	925.9	924.6	929.9	928.6	937.9	941.9	943.2
25°	895.2	889.9	888.5	881.9	879.2	875.2	879.2	883.2	893.9	897.9	903.2
27.5°	851.2	847.2	844.5	839.2	835.2	835.2	837.8	843.2	847.2	849.8	852.5
30°	811.2	808.5	800.5	797.8	793.8	793.8	793.8	796.5	803.2	811.2	815.2
32.5°	769.8	764.5	759.1	759.1	755.1	755.1	756.5	759.1	765.8	767.1	773.8
35°	729.8	724.4	720.4	717.8	719.1	713.8	716.4	720.4	728.4	731.1	735.1
37.5°	691.1	689.8	681.7	677.7	680.4	680.4	679.1	681.7	687.1	692.4	695.1
40°	648.4	645.7	645.7	641.7	643.1	637.7	641.7	644.4	647.1	652.4	656.4
42.5°	611.0	608.4	603.0	604.4	600.4	600.4	603.0	604.4	608.4	615.0	617.7
45°	571.0	571.0	568.3	564.3	565.7	561.7	564.3	565.7	571.0	577.7	575.0
47.5°	532.3	531.0	531.0	525.7	528.3	524.3	528.3	529.7	532.3	536.3	535.0
50°	495.0	491.0	492.3	491.0	489.6	489.6	492.3	492.3	495.0	495.0	499.0
52.5°	456.3	456.3	453.6	454.9	457.6	454.9	458.9	454.9	457.6	458.9	461.6
55°	421.6	418.9	420.3	418.9	424.3	420.3	424.3	421.6	424.3	422.9	425.6
57.5°	384.2	380.2	381.6	380.2	384.2	382.9	386.9	382.9	384.2	385.6	389.6
60°	341.5	341.5	341.5	338.9	342.9	342.9	341.5	341.5	346.9	349.5	348.2
62.5°	301.5	300.2	296.2	294.8	296.2	293.5	298.8	297.5	300.2	302.9	305.5
65°	257.5	254.8	253.5	250.8	250.8	249.5	250.8	256.2	257.5	258.8	265.5
67.5°	221.5	220.1	218.8	214.8	214.8	217.5	217.5	217.5	225.5	221.5	226.8
70°	189.4	186.8	184.1	182.8	182.8	184.1	185.4	186.8	185.4	190.8	192.1
72.5°	158.8	160.1	157.4	157.4	157.4	156.1	156.1	158.8	160.1	158.8	160.1
75°	132.1	132.1	130.7	132.1	132.1	130.7	130.7	133.4	133.4	132.1	136.1
77.5°	106.7	105.4	102.7	100.1	101.4	100.1	101.4	100.1	104.1	108.1	105.4
80°	74.7	73.4	73.4	73.4	74.7	73.4	76.0	73.4	74.7	74.7	76.0
82.5°	53.4	54.7	54.7	53.4	54.7	53.4	54.7	54.7	54.7	53.4	54.7
85°	34.7	34.7	34.7	34.7	33.4	34.7	34.7	34.7	36.0	34.7	36.0
87.5°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7	16.0	14.7	16.0
90°	24.2	24.6	25.4	26.1	26.9	27.7	26.9	26.1	25.4	24.6	24.2
92.5°	58.9	59.2	59.7	60.2	60.7	61.2	60.7	60.2	59.7	59.2	58.9
95°	97.0	97.3	97.8	98.3	98.8	99.3	98.8	98.3	97.8	97.3	97.0
97.5°	139.7	139.8	140.1	140.4	140.6	140.9	140.6	140.4	140.1	139.8	139.7
100°	187.0	187.3	187.8	188.3	188.9	189.4	188.9	188.3	187.8	187.3	187.0
102.5°	234.4	234.8	235.5	236.3	237.0	237.8	237.0	236.3	235.5	234.8	234.4
105°	282.9	283.3	284.0	284.8	285.5	286.3	285.5	284.8	284.0	283.3	282.9
107.5°	334.8	334.8	334.8	334.8	334.8	334.8	334.8	334.8	334.8	334.8	334.8
110°	391.4	391.3	391.0	390.7	390.5	390.2	390.5	390.7	391.0	391.3	391.4

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	446.8	446.5	446.0	445.5	445.0	444.5	445.0	445.5	446.0	446.5	446.8
115°	503.4	503.3	503.0	502.7	502.5	502.2	502.5	502.7	503.0	503.3	503.4
117.5°	562.3	561.8	560.8	559.7	558.7	557.7	558.7	559.7	560.8	561.8	562.3
120°	620.0	619.5	618.5	617.4	616.4	615.4	616.4	617.4	618.5	619.5	620.0
122.5°	676.6	676.2	675.4	674.7	673.9	673.1	673.9	674.7	675.4	676.2	676.6
125°	732.0	731.9	731.6	731.3	731.1	730.8	731.1	731.3	731.6	731.9	732.0
127.5°	788.6	788.3	787.8	787.3	786.8	786.3	786.8	787.3	787.8	788.3	788.6
130°	844.0	843.7	843.2	842.7	842.2	841.7	842.2	842.7	843.2	843.7	844.0
132.5°	897.1	896.7	895.9	895.2	894.4	893.6	894.4	895.2	895.9	896.7	897.1
135°	952.5	952.0	951.0	949.9	948.9	947.9	948.9	949.9	951.0	952.0	952.5
137.5°	1006.8	1006.2	1004.9	1003.6	1002.3	1001.0	1002.3	1003.6	1004.9	1006.2	1006.8
140°	1057.6	1057.0	1055.7	1054.4	1053.1	1051.8	1053.1	1054.4	1055.7	1057.0	1057.6
142.5°	1106.1	1105.5	1104.2	1102.9	1101.6	1100.3	1101.6	1102.9	1104.2	1105.5	1106.1
145°	1152.3	1151.9	1151.1	1150.4	1149.6	1148.8	1149.6	1150.4	1151.1	1151.9	1152.3
147.5°	1198.4	1197.4	1195.3	1193.3	1191.2	1189.2	1191.2	1193.3	1195.3	1197.4	1198.4
150°	1237.7	1237.4	1236.9	1236.4	1235.9	1235.4	1235.9	1236.4	1236.9	1237.4	1237.7
152.5°	1278.1	1277.6	1276.6	1275.5	1274.5	1273.5	1274.5	1275.5	1276.6	1277.6	1278.1
155°	1315.1	1314.5	1313.2	1311.9	1310.6	1309.3	1310.6	1311.9	1313.2	1314.5	1315.1
157.5°	1347.4	1346.5	1344.7	1342.9	1341.1	1339.3	1341.1	1342.9	1344.7	1346.5	1347.4
160°	1376.3	1375.7	1374.4	1373.1	1371.8	1370.5	1371.8	1373.1	1374.4	1375.7	1376.3
162.5°	1404.0	1403.2	1401.7	1400.1	1398.6	1397.0	1398.6	1400.1	1401.7	1403.2	1404.0
165°	1427.1	1426.3	1424.8	1423.2	1421.7	1420.1	1421.7	1423.2	1424.8	1426.3	1427.1
167.5°	1446.7	1445.9	1444.4	1442.9	1441.3	1439.8	1441.3	1442.9	1444.4	1445.9	1446.7
170°	1462.8	1461.9	1460.1	1458.4	1456.6	1454.8	1456.6	1458.4	1460.1	1461.9	1462.8
172.5°	1474.4	1473.6	1472.1	1470.6	1469.0	1467.5	1469.0	1470.6	1472.1	1473.6	1474.4
175°	1482.5	1481.6	1479.8	1478.0	1476.2	1474.4	1476.2	1478.0	1479.8	1481.6	1482.5
177.5°	1487.1	1486.2	1484.4	1482.6	1480.8	1479.0	1480.8	1482.6	1484.4	1486.2	1487.1
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1536.9	1543.6	1538.3	1534.3	1544.9	1550.3	1550.3	1559.6	1569.0	1577.0	1578.3
5°	1442.2	1452.9	1455.5	1454.2	1470.2	1478.2	1495.6	1504.9	1518.3	1527.6	1538.3
7.5°	1355.5	1370.2	1371.5	1374.2	1398.2	1411.5	1426.2	1450.2	1468.9	1482.2	1494.2
10°	1268.8	1278.1	1287.4	1299.5	1323.5	1346.1	1367.5	1392.8	1416.9	1430.2	1447.5
12.5°	1203.4	1210.1	1220.7	1228.7	1254.1	1274.1	1302.1	1336.8	1371.5	1382.2	1403.5
15°	1135.4	1139.4	1160.7	1168.7	1190.1	1223.4	1240.8	1274.1	1311.5	1331.5	1355.5
17.5°	1056.6	1080.7	1094.0	1103.3	1130.0	1156.7	1184.7	1219.4	1267.4	1286.1	1303.5
20°	1000.6	1017.9	1032.6	1044.6	1068.6	1108.7	1134.0	1162.0	1207.4	1228.7	1254.1
22.5°	951.2	965.9	979.3	992.6	1008.6	1044.6	1074.0	1112.7	1158.0	1178.0	1207.4
25°	904.5	919.2	927.2	943.2	964.6	989.9	1024.6	1059.3	1104.7	1127.3	1155.4
27.5°	859.2	873.9	888.5	901.9	916.6	940.6	964.6	1008.6	1055.3	1082.0	1106.0
30°	820.5	827.2	840.5	855.2	869.9	892.5	920.6	951.2	1004.6	1028.6	1058.0
32.5°	777.8	789.8	799.2	809.8	828.5	847.2	872.5	911.2	953.9	976.6	1008.6
35°	737.8	748.5	755.1	773.8	785.8	805.8	831.2	865.9	901.9	927.2	955.2
37.5°	699.1	709.8	717.8	728.4	744.5	761.8	788.5	813.8	856.5	877.9	909.9
40°	659.1	668.4	677.7	689.8	704.4	725.8	741.8	773.8	808.5	832.5	856.5
42.5°	620.4	625.7	636.4	649.7	664.4	683.1	705.8	731.1	765.8	787.1	808.5
45°	579.0	588.4	600.4	609.7	623.0	641.7	661.7	684.4	719.1	740.4	763.1
47.5°	540.3	547.0	555.0	569.7	587.0	600.4	621.7	643.1	675.1	695.1	716.4
50°	500.3	507.0	519.0	528.3	541.7	559.0	579.0	601.7	632.4	645.7	667.1
52.5°	462.9	465.6	477.6	487.0	500.3	520.3	536.3	556.3	585.7	600.4	621.7
55°	425.6	428.3	434.9	444.3	458.9	475.0	492.3	515.0	540.3	553.7	573.7
57.5°	386.9	389.6	396.2	402.9	417.6	432.3	452.3	471.0	496.3	508.3	527.0
60°	348.2	348.2	354.9	364.2	374.9	388.2	405.6	428.3	446.9	461.6	475.0
62.5°	306.9	310.9	314.9	321.5	333.5	349.5	364.2	380.2	402.9	413.6	425.6
65°	265.5	269.5	277.5	284.2	293.5	304.2	322.9	336.2	353.5	365.6	376.2
67.5°	229.5	233.5	238.8	246.8	253.5	265.5	278.8	292.2	310.9	318.9	326.9
70°	192.1	196.1	200.1	210.8	217.5	226.8	236.1	249.5	265.5	270.8	277.5
72.5°	162.8	164.1	169.4	172.1	181.4	189.4	200.1	208.1	220.1	226.8	232.1
75°	137.4	137.4	138.8	141.4	146.8	152.1	160.1	168.1	178.8	182.8	189.4
77.5°	108.1	112.1	110.7	113.4	116.1	118.7	125.4	130.7	141.4	144.1	146.8
80°	77.4	78.7	82.7	86.7	86.7	90.7	94.7	96.1	102.7	106.7	106.7
82.5°	56.0	57.4	56.0	57.4	58.7	60.0	64.0	69.4	69.4	70.7	73.4
85°	34.7	34.7	36.0	37.4	37.4	36.0	38.7	37.4	38.7	41.4	41.4
87.5°	17.3	16.0	16.0	16.0	16.0	16.0	17.3	16.0	17.3	17.3	17.3
90°	23.6	22.3	21.0	19.8	18.5	16.7	14.9	13.1	11.3	10.4	9.4
92.5°	58.0	56.2	54.4	52.6	50.8	48.5	46.2	43.9	41.6	40.4	39.8
95°	96.1	94.3	92.5	90.7	88.9	86.3	83.8	81.2	78.7	77.4	77.1
97.5°	138.9	137.4	135.9	134.3	132.8	129.2	125.6	122.0	118.4	116.6	116.5
100°	185.9	183.6	181.3	179.0	176.7	173.3	170.0	166.6	163.3	161.6	161.6
102.5°	233.1	230.5	228.0	225.4	222.8	221.5	220.3	219.0	217.7	217.1	216.5
105°	282.1	280.6	279.0	277.5	275.9	274.4	272.8	271.3	269.8	269.0	268.4
107.5°	334.4	333.7	332.9	332.2	331.4	330.1	328.8	327.5	326.2	325.6	325.0
110°	391.0	390.2	389.5	388.7	387.9	387.1	386.4	385.6	384.9	384.5	383.9

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	446.7	446.4	446.2	445.9	445.7	444.7	443.6	442.6	441.5	441.0	440.7
115°	503.5	503.8	504.0	504.3	504.5	504.0	503.5	503.0	502.5	502.2	501.7
117.5°	562.2	561.9	561.6	561.4	561.1	560.6	560.1	559.6	559.1	558.8	558.7
120°	620.0	620.0	620.0	620.0	620.0	619.8	619.5	619.3	619.0	618.9	618.3
122.5°	676.7	677.0	677.2	677.5	677.7	676.9	676.2	675.4	674.7	674.3	674.2
125°	732.3	732.8	733.3	733.8	734.3	734.1	733.8	733.6	733.3	733.2	732.4
127.5°	788.7	789.0	789.2	789.5	789.7	789.5	789.2	789.0	788.7	788.6	788.2
130°	844.1	844.4	844.6	844.9	845.1	844.6	844.1	843.6	843.1	842.8	842.2
132.5°	897.2	897.5	897.8	898.0	898.3	898.5	898.8	899.0	899.3	899.4	898.2
135°	952.5	952.5	952.5	952.5	952.5	952.3	952.0	951.8	951.5	951.4	950.6
137.5°	1006.7	1006.4	1006.1	1005.9	1005.6	1005.1	1004.6	1004.1	1003.6	1003.3	1002.5
140°	1057.3	1056.8	1056.3	1055.8	1055.3	1054.5	1053.7	1053.0	1052.2	1051.8	1051.2
142.5°	1106.0	1105.7	1105.4	1105.2	1104.9	1103.9	1102.9	1101.8	1100.8	1100.3	1099.8
145°	1152.3	1152.3	1152.3	1152.3	1152.3	1151.5	1150.7	1150.0	1149.2	1148.8	1148.3
147.5°	1198.0	1197.3	1196.5	1195.8	1195.0	1194.5	1194.0	1193.5	1193.0	1192.7	1192.3
150°	1237.7	1237.7	1237.7	1237.7	1237.7	1236.7	1235.7	1234.6	1233.6	1233.1	1233.2
152.5°	1277.7	1277.0	1276.2	1275.5	1274.7	1274.4	1274.2	1273.9	1273.6	1273.5	1273.2
155°	1314.6	1313.5	1312.5	1311.4	1310.4	1310.2	1309.9	1309.7	1309.4	1309.3	1309.3
157.5°	1346.9	1345.9	1344.8	1343.8	1342.8	1342.5	1342.3	1342.0	1341.7	1341.6	1341.9
160°	1375.8	1374.7	1373.7	1372.6	1371.6	1371.4	1371.1	1370.9	1370.6	1370.5	1370.9
162.5°	1403.4	1402.1	1400.8	1399.5	1398.2	1398.2	1398.2	1398.2	1398.2	1398.2	1398.5
165°	1426.6	1425.5	1424.5	1423.4	1422.4	1422.2	1421.9	1421.7	1421.4	1421.3	1421.6
167.5°	1445.9	1444.4	1442.9	1441.3	1439.8	1439.8	1439.8	1439.8	1439.8	1439.8	1440.3
170°	1462.0	1460.5	1459.0	1457.4	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1456.4
172.5°	1473.6	1472.1	1470.6	1469.0	1467.5	1467.5	1467.5	1467.5	1467.5	1467.5	1468.0
175°	1481.7	1480.2	1478.6	1477.1	1475.5	1475.5	1475.5	1475.5	1475.5	1475.5	1476.0
177.5°	1486.3	1484.8	1483.3	1481.7	1480.2	1480.4	1480.7	1480.9	1481.2	1481.3	1481.8
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1625.0	1625.0	1625.0	1625.0
2.5°	1587.6	1599.6	1611.6	1626.3
5°	1555.6	1577.0	1599.6	1621.0
7.5°	1520.9	1551.6	1581.0	1611.6
10°	1482.2	1520.9	1554.3	1597.0
12.5°	1439.5	1480.9	1527.6	1575.6
15°	1396.8	1448.9	1498.2	1552.9
17.5°	1356.8	1406.2	1460.9	1526.3
20°	1308.8	1363.5	1424.9	1494.2
22.5°	1258.1	1318.1	1384.8	1459.6
25°	1215.4	1276.8	1340.8	1419.5
27.5°	1168.7	1232.7	1295.5	1379.5
30°	1115.3	1184.7	1248.8	1335.5
32.5°	1064.6	1134.0	1204.7	1286.1
35°	1015.3	1083.3	1154.0	1236.7
37.5°	968.6	1030.0	1099.3	1174.0
40°	924.6	980.6	1042.0	1110.0
42.5°	868.5	933.9	991.3	1040.6
45°	820.5	873.9	927.2	967.3
47.5°	764.5	817.8	863.2	895.2
50°	717.8	760.5	797.8	825.8
52.5°	661.7	701.8	732.4	753.8
55°	607.0	641.7	668.4	683.1
57.5°	557.7	580.4	600.4	613.7
60°	503.0	520.3	537.7	552.3
62.5°	444.3	462.9	472.3	488.3
65°	392.2	404.2	418.9	424.3
67.5°	341.5	348.2	357.5	368.2
70°	288.2	292.2	301.5	316.2
72.5°	241.5	245.5	252.2	257.5
75°	192.1	196.1	201.5	206.8
77.5°	150.8	152.1	154.8	160.1
80°	109.4	113.4	116.1	117.4
82.5°	76.0	77.4	77.4	78.7
85°	48.0	45.4	45.4	46.7
87.5°	17.3	20.0	20.0	22.7
90°	7.3	5.3	3.2	1.2
92.5°	38.5	37.2	35.9	34.6
95°	76.6	76.1	75.5	75.0
97.5°	116.2	116.0	115.7	115.5
100°	161.6	161.6	161.6	161.6
102.5°	215.2	213.9	212.6	211.3
105°	267.1	265.8	264.5	263.2
107.5°	323.7	322.4	321.1	319.8
110°	382.6	381.3	380.0	378.7

TEST NUMBER: P1028463

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	440.2	439.7	439.2	438.7
115°	500.7	499.6	498.6	497.6
117.5°	558.4	558.2	557.9	557.7
120°	617.0	615.7	614.4	613.1
122.5°	673.9	673.6	673.4	673.1
125°	730.9	729.3	727.8	726.2
127.5°	787.4	786.7	785.9	785.1
130°	840.9	839.6	838.4	837.1
132.5°	895.9	893.6	891.3	889.0
135°	949.1	947.5	946.0	944.4
137.5°	1001.0	999.5	997.9	996.4
140°	1049.9	1048.6	1047.3	1046.0
142.5°	1098.8	1097.7	1096.7	1095.7
145°	1147.3	1146.2	1145.2	1144.2
147.5°	1191.5	1190.8	1190.0	1189.2
150°	1233.5	1233.7	1234.0	1234.2
152.5°	1272.7	1272.2	1271.7	1271.2
155°	1309.3	1309.3	1309.3	1309.3
157.5°	1342.4	1342.9	1343.4	1343.9
160°	1371.6	1372.4	1373.1	1373.9
162.5°	1399.0	1399.5	1400.0	1400.5
165°	1422.1	1422.6	1423.1	1423.6
167.5°	1441.3	1442.4	1443.4	1444.4
170°	1457.4	1458.5	1459.5	1460.5
172.5°	1469.0	1470.1	1471.1	1472.1
175°	1477.1	1478.1	1479.2	1480.2
177.5°	1482.8	1483.9	1484.9	1485.9
180°	1483.6	1483.6	1483.6	1483.6

(END OF REPORT)