

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028239

Luminaire Tested: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028239
REPORT IS A COMBINATION OF REPORTS P1002481 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D1270UB27-4F0-XX-W2A-A4
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7732.0 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	93	89	85	89	85	82	79	71	68	66	58	56	55	45	44	44
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	39	37
3	81	71	64	58	74	66	59	54	55	50	47	45	42	39	36	34	32
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24
6	62	50	43	37	57	47	40	34	39	34	30	33	29	25	26	23	21
7	58	46	38	32	53	42	35	30	36	30	26	30	26	22	24	21	19
8	53	41	34	28	49	38	31	27	33	27	23	27	23	20	22	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15
10	46	34	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7813	7813	7813	7813
5°	7819	8863	7826	6724
10°	7771	10102	7758	5772
15°	7714	10954	7666	5215
20°	7617	12003	7547	4761
25°	7530	13753	7393	4492
30°	7406	14510	7278	4249
35°	7209	11631	7058	4053
40°	6903	8039	6801	3846
45°	6515	5985	6442	3674
50°	6072	4927	5972	3537
55°	5593	4202	5549	3417
60°	5124	3597	5035	3324
65°	4617	3106	4543	3189
70°	4083	2579	4028	2955
75°	3516	1995	3469	2564
80°	2776	1349	2676	1885
85°	1778	676	1715	962

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 11933 cd/sqm

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	1.5
10°-20°	349.6	4.5
20°-30°	567.8	7.3
30°-40°	694.0	9.0
40°-50°	629.5	8.1
50°-60°	501.4	6.5
60°-70°	349.2	4.5
70°-80°	186.0	2.4
80°-90°	48.4	0.6
90°-100°	415.3	5.4
100°-110°	895.7	11.6
110°-120°	835.0	10.8
120°-130°	676.3	8.7
130°-140°	543.1	7.0
140°-150°	409.6	5.3
150°-160°	288.4	3.7
160°-170°	170.0	2.2
170°-180°	55.3	0.7
0°-30°	1034.8	13.4
0°-40°	1728.7	22.4
0°-60°	2859.6	37.0
0°-90°	3443.3	44.5
90°-120°	2146.0	27.8
90°-150°	3775.0	48.8
90°-180°	4289.0	55.5
0°-180°	7732.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1219	1219	1219	1219	1219	
5°	1218	1407	1219	1067	1218	116
15°	1171	1757	1164	836	1171	330
25°	1078	2161	1058	706	1078	496
35°	938	1735	918	604	938	586
45°	737	818	729	502	737	568
55°	519	504	514	410	519	464
65°	321	310	316	318	321	318
75°	155	152	153	196	155	165
85°	31	34	30	49	31	37
90°	1	26	1	26	1	5
95°	38	270	38	270	38	40
105°	130	1525	130	1525	130	137
115°	232	1699	232	1699	232	229
125°	322	1339	322	1339	322	286
135°	378	1112	378	1112	378	293
145°	440	877	440	877	440	276
155°	502	736	502	736	502	231
165°	548	645	548	645	548	154
175°	570	579	570	579	570	54
180°	571	571	571	571	571	

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4
2.5°	1221.5	1228.7	1237.0	1243.2	1253.6	1256.7	1261.9	1265.0	1268.1	1271.2	1273.2
5°	1218.4	1236.0	1251.5	1262.9	1282.6	1289.8	1299.1	1310.5	1324.0	1335.3	1342.6
7.5°	1210.1	1238.0	1258.7	1281.5	1308.4	1326.0	1335.3	1359.2	1380.9	1397.5	1419.2
10°	1199.7	1232.9	1265.0	1299.1	1337.4	1357.1	1375.7	1408.8	1438.9	1465.8	1487.5
12.5°	1188.4	1228.7	1267.0	1311.5	1363.3	1387.1	1399.5	1456.5	1493.7	1508.2	1550.7
15°	1170.8	1218.4	1273.2	1328.1	1371.6	1399.5	1433.7	1479.2	1516.5	1548.6	1582.7
17.5°	1154.2	1206.0	1261.9	1322.9	1386.1	1422.3	1448.2	1488.6	1528.9	1570.3	1602.4
20°	1127.3	1194.6	1251.5	1316.7	1391.2	1417.1	1444.0	1491.7	1535.1	1579.6	1620.0
22.5°	1105.5	1169.7	1247.4	1309.5	1372.6	1398.5	1431.6	1481.3	1533.1	1583.8	1642.8
25°	1077.6	1149.0	1216.3	1282.6	1347.8	1375.7	1405.7	1469.9	1523.7	1589.0	1654.2
27.5°	1047.6	1121.1	1188.4	1248.4	1309.5	1347.8	1379.9	1447.1	1518.6	1590.0	1674.9
30°	1015.5	1084.8	1149.0	1208.0	1275.3	1314.6	1346.7	1425.4	1505.1	1596.2	1697.7
32.5°	981.3	1046.5	1101.4	1161.4	1232.9	1269.1	1312.6	1398.5	1492.7	1601.4	1728.7
35°	937.8	1000.0	1048.6	1109.7	1181.1	1227.7	1273.2	1369.5	1479.2	1600.3	1746.3
37.5°	894.4	943.0	989.6	1054.8	1137.6	1180.1	1227.7	1333.3	1458.5	1597.2	1753.5
40°	842.6	890.2	930.6	996.9	1083.8	1132.5	1182.1	1292.9	1434.7	1585.9	1727.7
42.5°	790.9	831.2	875.7	945.1	1028.9	1080.7	1133.5	1256.7	1403.7	1552.7	1656.2
45°	737.0	768.1	816.7	879.9	968.9	1018.6	1078.6	1212.2	1360.2	1492.7	1544.4
47.5°	681.1	712.2	757.7	818.8	906.8	965.8	1022.7	1156.3	1305.3	1407.8	1407.8
50°	627.3	652.1	696.7	757.7	846.8	900.6	958.6	1100.4	1220.4	1296.0	1228.7
52.5°	569.3	597.3	634.5	698.7	786.7	835.4	898.5	1019.6	1133.5	1164.5	1061.0
55°	518.6	541.4	576.6	637.7	719.4	770.2	824.0	939.9	1036.2	1034.1	923.4
57.5°	465.8	484.5	521.7	577.6	653.2	698.7	752.6	853.0	931.6	903.7	799.1
60°	417.2	430.6	466.9	512.4	584.9	627.3	679.1	760.8	820.9	781.5	676.0
62.5°	366.4	382.0	411.0	455.5	519.6	553.8	592.1	674.9	713.2	678.0	570.4
65°	320.9	333.3	359.2	396.5	454.4	485.5	518.6	586.9	623.2	572.4	483.4
67.5°	275.4	289.8	308.5	341.6	387.1	416.1	445.1	504.1	520.7	475.1	400.6
70°	232.9	245.3	262.9	286.7	325.0	350.9	372.7	421.3	432.7	390.3	331.2
72.5°	191.5	199.8	214.3	233.9	269.1	283.6	306.4	339.5	354.0	315.7	273.3
75°	155.3	161.5	170.8	185.3	209.1	224.6	243.3	274.3	273.3	246.4	216.3
77.5°	120.1	121.1	131.5	144.9	159.4	172.9	182.2	203.9	206.0	189.4	164.6
80°	85.9	89.0	93.2	103.5	115.9	121.1	132.5	146.0	148.0	135.6	119.0
82.5°	54.9	56.9	60.0	66.2	74.5	80.7	87.0	92.1	97.3	90.1	76.6
85°	31.1	32.1	35.2	37.3	41.4	44.5	49.7	54.9	53.8	48.7	44.5
87.5°	15.5	15.5	15.5	17.6	19.7	19.7	21.7	22.8	23.8	21.7	19.7
90°	1.2	2.3	4.6	6.9	9.2	10.4	11.5	12.7	15.0	16.1	18.4
92.5°	17.3	20.7	32.2	49.5	73.7	94.4	115.1	193.4	324.6	467.4	459.3
95°	38.0	39.1	48.4	61.0	86.3	112.2	138.1	261.3	514.6	832.3	1020.0
97.5°	58.7	59.9	66.8	79.4	102.5	121.4	140.4	225.6	420.2	763.2	1101.7
100°	80.6	82.9	87.5	100.2	122.0	139.3	156.6	223.3	373.0	663.1	1039.5
102.5°	104.8	105.9	109.4	123.2	142.7	159.4	176.1	233.7	353.4	587.1	930.2
105°	130.1	130.1	135.8	147.4	165.8	181.9	198.0	248.7	351.1	543.4	834.6
107.5°	154.3	156.6	162.3	171.5	191.1	205.5	219.9	269.4	359.2	520.3	763.2
110°	180.7	183.0	187.6	198.0	215.3	230.2	245.2	292.4	371.8	511.1	716.0

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	207.2	209.5	213.0	223.3	240.6	255.0	269.4	314.3	388.0	511.1	688.4
115°	232.5	234.8	238.3	248.7	265.9	280.3	294.7	337.3	404.1	514.6	670.0
117.5°	255.6	259.0	262.5	272.8	292.4	306.2	320.0	360.3	422.5	520.3	659.6
120°	278.6	282.0	286.6	297.0	316.6	331.0	345.4	385.7	440.9	529.6	652.7
122.5°	302.8	305.1	308.5	318.9	340.8	355.2	369.5	409.8	461.6	537.6	647.0
125°	322.3	324.6	330.4	340.8	362.6	377.6	392.6	430.5	480.0	546.8	642.4
127.5°	338.5	341.9	348.8	361.5	384.5	399.4	414.4	451.3	497.3	557.2	640.1
130°	353.4	356.9	366.1	381.0	405.2	420.2	435.2	470.8	514.6	566.4	637.8
132.5°	364.9	369.5	381.0	398.3	423.6	438.6	453.6	489.3	529.6	576.8	637.8
135°	377.6	382.2	396.0	414.4	438.6	454.2	469.7	505.4	543.4	586.0	637.8
137.5°	393.7	397.2	409.8	428.2	452.4	468.6	484.7	516.9	553.7	595.2	638.9
140°	407.5	411.0	424.8	443.2	465.1	480.6	496.2	529.6	564.1	600.9	640.1
142.5°	423.6	425.9	438.6	457.0	477.7	492.1	506.5	537.6	569.8	604.4	641.2
145°	439.8	442.1	453.6	469.7	490.4	503.6	516.9	546.8	575.6	606.7	640.1
147.5°	457.0	458.2	468.5	483.5	501.9	514.0	526.1	552.6	579.1	607.8	637.8
150°	472.0	474.3	482.4	497.3	513.4	523.2	533.0	558.3	582.5	607.8	634.3
152.5°	488.1	489.3	496.2	508.8	523.8	532.4	541.1	564.1	584.8	606.7	629.7
155°	501.9	501.9	508.8	520.3	531.9	540.0	548.0	567.5	586.0	604.4	623.9
157.5°	514.6	514.6	520.3	530.7	541.1	547.4	553.7	571.0	587.1	602.1	618.2
160°	527.2	526.1	530.7	538.8	548.0	553.2	558.3	573.3	587.1	598.6	612.4
162.5°	537.6	536.5	541.1	548.0	554.9	558.9	562.9	575.6	586.0	595.2	605.5
165°	548.0	545.7	549.1	554.9	559.5	563.0	566.4	575.6	584.8	591.7	598.6
167.5°	554.9	553.7	556.0	559.5	562.9	565.2	567.5	575.6	582.5	586.0	591.7
170°	561.8	560.6	561.8	564.1	566.4	568.1	569.8	575.6	580.2	582.5	586.0
172.5°	566.4	564.1	565.2	567.5	568.7	569.2	569.8	574.4	577.9	577.9	579.1
175°	569.8	567.5	568.7	569.8	569.8	569.8	569.8	573.3	575.6	574.4	574.4
177.5°	572.1	569.8	569.8	571.0	569.8	569.8	569.8	572.1	573.3	571.0	571.0
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4
2.5°	1275.3	1282.6	1288.8	1293.9	1298.1	1304.3	1300.2	1301.2	1303.3	1307.4	1307.4
5°	1358.1	1369.5	1375.7	1396.4	1401.6	1400.6	1397.5	1414.0	1413.0	1406.8	1405.7
7.5°	1438.9	1458.5	1476.1	1492.7	1497.9	1511.3	1514.4	1521.7	1519.6	1530.0	1524.8
10°	1512.4	1543.4	1560.0	1584.8	1591.0	1597.2	1605.5	1609.7	1619.0	1617.9	1617.9
12.5°	1569.3	1606.6	1628.3	1634.5	1658.3	1665.6	1672.8	1686.3	1683.2	1684.2	1690.4
15°	1613.8	1650.0	1668.7	1697.7	1714.2	1722.5	1734.9	1749.4	1747.3	1756.7	1754.6
17.5°	1646.9	1681.1	1715.2	1758.7	1759.8	1781.5	1810.5	1816.7	1830.2	1820.8	1820.8
20°	1673.8	1719.4	1768.0	1823.9	1830.2	1843.6	1878.8	1902.6	1918.1	1913.0	1916.1
22.5°	1702.8	1768.0	1825.0	1880.9	1910.9	1934.7	1968.9	2006.1	2019.6	2027.9	2025.8
25°	1740.1	1808.4	1892.3	1969.9	2001.0	2046.5	2092.0	2128.3	2138.6	2161.4	2140.7
27.5°	1778.4	1874.7	1979.2	2070.3	2109.6	2146.9	2201.8	2228.7	2242.1	2252.5	2245.2
30°	1810.5	1943.0	2056.8	2140.7	2168.6	2190.4	2221.4	2227.6	2222.5	2230.8	2241.1
32.5°	1860.2	1989.6	2085.8	2126.2	2123.1	2122.1	2098.3	2065.1	2057.9	2038.2	2065.1
35°	1887.1	1990.6	2027.9	1974.0	1952.3	1913.0	1837.4	1787.7	1744.2	1734.9	1737.0
37.5°	1871.6	1911.9	1867.4	1725.6	1690.4	1630.4	1530.0	1459.6	1427.5	1402.6	1434.7
40°	1787.7	1743.2	1621.0	1448.2	1397.5	1340.5	1246.3	1208.0	1162.5	1153.2	1195.6
42.5°	1649.0	1513.4	1340.5	1207.0	1154.2	1122.1	1043.4	1007.2	975.1	960.6	984.4
45°	1460.6	1296.0	1122.1	1012.4	967.9	929.6	883.0	844.7	824.0	817.8	837.4
47.5°	1266.0	1092.1	953.4	871.6	825.0	796.0	752.6	730.8	714.3	716.3	719.4
50°	1079.7	921.3	814.7	732.9	710.1	687.3	658.4	639.7	631.4	634.5	632.5
52.5°	919.2	790.9	700.8	637.7	627.3	605.6	581.8	566.2	563.1	564.2	567.3
55°	778.4	678.0	606.6	561.1	549.7	534.1	519.6	509.3	501.0	504.1	503.1
57.5°	671.8	583.8	529.0	491.7	483.4	474.1	460.6	455.5	452.4	446.2	451.3
60°	577.6	506.2	458.6	435.8	428.6	422.3	407.9	401.6	399.6	396.5	404.7
62.5°	488.6	437.9	401.6	380.9	373.7	367.5	360.2	355.1	356.1	352.0	356.1
65°	418.2	376.8	350.9	332.3	323.0	318.8	317.8	309.5	308.5	309.5	310.5
67.5°	353.0	317.8	298.1	286.7	279.5	275.4	272.2	267.1	271.2	268.1	270.2
70°	294.0	270.2	249.5	238.1	235.0	236.0	230.8	228.8	229.8	227.7	229.8
72.5°	237.1	217.4	209.1	200.8	196.7	195.6	192.5	189.4	192.5	191.5	191.5
75°	189.4	174.9	165.6	160.4	160.4	158.4	153.2	153.2	153.2	152.2	153.2
77.5°	146.0	133.5	129.4	124.2	124.2	121.1	120.1	120.1	118.0	121.1	119.0
80°	108.7	99.4	93.2	90.1	90.1	89.0	87.0	85.9	87.0	85.9	85.9
82.5°	70.4	66.2	63.1	60.0	59.0	60.0	59.0	56.9	58.0	56.9	59.0
85°	40.4	36.2	36.2	34.2	35.2	33.1	34.2	32.1	31.1	34.2	32.1
87.5°	17.6	16.6	16.6	14.5	14.5	14.5	13.5	14.5	13.5	12.4	13.5
90°	19.6	20.7	21.9	23.0	24.2	25.3	25.3	25.3	26.5	26.5	26.5
92.5°	370.7	249.8	179.6	133.5	122.6	111.7	93.2	89.8	87.5	85.2	87.5
95°	998.1	827.7	652.7	511.1	462.8	414.4	332.7	298.2	289.0	270.5	289.0
97.5°	1246.7	1186.9	1047.6	904.8	835.8	766.7	697.6	637.8	606.7	592.9	606.7
100°	1327.3	1416.0	1359.6	1241.0	1181.2	1121.3	1041.8	958.9	916.4	897.9	916.4
102.5°	1279.0	1493.1	1550.7	1509.2	1473.5	1437.8	1351.5	1298.6	1251.4	1238.7	1251.4
105°	1165.0	1441.3	1599.0	1649.7	1643.4	1637.0	1600.2	1562.2	1539.2	1525.3	1539.2
107.5°	1056.8	1335.4	1543.8	1665.8	1691.1	1716.4	1726.8	1721.0	1709.5	1698.0	1709.5
110°	967.0	1215.7	1434.4	1596.7	1645.6	1694.6	1746.4	1768.2	1776.3	1776.3	1776.3

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	900.2	1121.3	1326.2	1490.8	1550.6	1610.5	1692.3	1733.7	1756.7	1767.1	1756.7
115°	855.3	1045.3	1223.7	1381.4	1444.2	1506.9	1596.7	1652.0	1684.2	1699.2	1684.2
117.5°	825.4	992.3	1150.0	1288.2	1347.5	1406.8	1497.7	1555.3	1587.5	1596.7	1587.5
120°	801.2	950.9	1089.0	1215.7	1266.4	1317.0	1402.2	1457.4	1488.5	1497.7	1488.5
122.5°	780.5	919.8	1045.3	1154.7	1201.3	1247.9	1321.6	1371.1	1402.2	1410.2	1402.2
125°	762.1	889.9	1007.3	1107.5	1148.9	1190.3	1254.8	1302.0	1327.3	1338.8	1327.3
127.5°	744.8	858.8	970.5	1064.9	1104.0	1143.1	1201.9	1244.4	1268.6	1273.2	1268.6
130°	727.6	830.0	931.3	1021.1	1058.5	1095.9	1153.5	1191.5	1214.5	1221.4	1214.5
132.5°	713.7	801.2	894.5	973.9	1009.6	1045.3	1102.8	1140.8	1161.6	1169.6	1161.6
135°	703.4	777.1	856.5	930.2	963.0	995.8	1046.4	1084.4	1105.2	1112.1	1105.2
137.5°	693.0	755.2	822.0	885.3	914.0	942.8	988.9	1024.6	1044.1	1052.2	1044.1
140°	686.1	737.9	792.0	845.0	869.2	893.3	935.9	965.9	983.1	988.9	983.1
142.5°	680.4	723.0	766.7	810.4	830.6	850.7	885.3	909.4	925.6	930.2	925.6
145°	674.6	710.3	746.0	781.7	797.2	812.7	840.4	859.9	872.6	877.2	872.6
147.5°	668.8	697.6	727.6	756.3	768.4	780.5	803.5	819.7	827.7	830.0	827.7
150°	661.9	687.3	712.6	734.5	744.8	755.2	772.5	786.3	790.9	792.0	790.9
152.5°	653.9	675.8	697.6	717.2	724.7	732.2	746.0	756.3	760.9	762.1	760.9
155°	644.7	664.2	682.7	698.8	705.1	711.4	723.0	731.0	734.5	735.6	734.5
157.5°	636.6	652.7	668.8	681.5	686.7	691.9	701.1	708.0	711.4	711.4	711.4
160°	626.3	641.2	652.7	664.2	668.2	672.3	680.4	686.1	688.4	687.3	688.4
162.5°	617.0	628.6	638.9	648.1	651.6	655.0	660.8	665.4	665.4	665.4	665.4
165°	607.8	617.0	625.1	632.0	634.9	637.8	642.4	644.7	644.7	644.7	644.7
167.5°	598.6	605.5	611.3	617.0	619.3	621.6	623.9	626.3	625.1	625.1	625.1
170°	590.6	596.3	599.8	603.2	604.4	605.5	607.8	609.0	609.0	607.8	609.0
172.5°	582.5	586.0	589.4	591.7	592.3	592.9	592.9	595.2	592.9	591.7	592.9
175°	575.6	579.1	579.1	581.4	581.4	581.4	581.4	582.5	580.2	579.1	580.2
177.5°	572.1	573.3	574.4	574.4	574.4	574.4	573.3	574.4	571.0	571.0	571.0
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4
2.5°	1305.3	1298.1	1300.2	1298.1	1292.9	1289.8	1281.5	1271.2	1267.0	1261.9	1258.7
5°	1409.9	1404.7	1403.7	1395.4	1393.3	1380.9	1360.2	1349.8	1337.4	1325.0	1312.6
7.5°	1523.7	1517.5	1496.8	1493.7	1495.8	1480.3	1453.4	1432.7	1406.8	1389.2	1365.4
10°	1617.9	1605.5	1587.9	1589.0	1581.7	1561.0	1534.1	1512.4	1475.1	1452.3	1418.2
12.5°	1674.9	1664.5	1662.5	1652.1	1645.9	1619.0	1586.9	1558.9	1531.0	1499.9	1474.1
15°	1744.2	1730.8	1721.5	1707.0	1702.8	1674.9	1639.7	1607.6	1575.5	1546.5	1491.7
17.5°	1820.8	1806.3	1771.1	1768.0	1743.2	1716.3	1682.1	1634.5	1600.3	1558.9	1518.6
20°	1907.8	1887.1	1841.5	1830.2	1810.5	1766.0	1719.4	1666.6	1611.7	1569.3	1521.7
22.5°	2005.1	1968.9	1935.7	1899.5	1885.0	1830.2	1766.0	1701.8	1635.5	1577.6	1520.6
25°	2131.4	2083.8	2037.2	2001.0	1976.1	1904.7	1818.8	1733.9	1657.3	1581.7	1507.2
27.5°	2230.8	2189.3	2138.6	2091.0	2058.9	1974.0	1875.7	1766.0	1670.7	1578.6	1498.9
30°	2238.0	2225.6	2194.5	2168.6	2133.5	2042.4	1933.7	1809.4	1691.4	1579.6	1482.3
32.5°	2102.4	2127.2	2140.7	2144.8	2137.6	2084.8	1985.4	1848.8	1710.1	1570.3	1467.8
35°	1810.5	1876.7	1958.5	1989.6	2019.6	2047.5	1995.8	1876.7	1716.3	1568.3	1445.1
37.5°	1490.6	1550.7	1686.3	1748.4	1783.6	1894.3	1936.8	1872.6	1728.7	1570.3	1423.3
40°	1202.8	1298.1	1395.4	1479.2	1534.1	1658.3	1789.8	1804.3	1711.1	1550.7	1395.4
42.5°	1012.4	1068.3	1141.8	1219.4	1268.1	1415.1	1593.1	1697.7	1656.2	1518.6	1361.2
45°	862.3	903.7	973.0	998.9	1061.0	1201.8	1390.2	1541.3	1562.0	1467.8	1321.9
47.5°	740.1	775.3	819.8	851.9	901.6	1007.2	1166.6	1333.3	1432.7	1398.5	1267.0
50°	652.1	681.1	718.4	737.0	769.1	864.4	984.4	1150.1	1283.6	1295.0	1195.6
52.5°	578.7	595.2	624.2	644.9	670.8	728.7	837.4	974.1	1124.2	1186.3	1107.6
55°	514.5	527.9	553.8	567.3	580.7	630.4	715.3	839.5	980.3	1062.1	1017.6
57.5°	456.5	467.9	489.6	502.0	509.3	556.9	622.1	719.4	845.7	945.1	920.3
60°	408.9	419.2	431.7	441.0	449.3	488.6	534.1	612.8	725.6	821.9	815.7
62.5°	358.2	367.5	380.9	390.3	397.5	422.3	460.6	520.7	617.0	706.0	723.6
65°	313.7	320.9	330.2	334.4	343.7	362.3	393.4	447.2	525.9	605.6	618.0
67.5°	273.3	275.4	281.6	290.9	292.9	309.5	337.5	377.8	438.9	504.1	523.8
70°	229.8	232.9	238.1	245.3	249.5	259.8	283.6	310.5	363.3	420.3	434.8
72.5°	191.5	195.6	197.7	201.9	203.9	220.5	230.8	257.8	294.0	341.6	357.1
75°	155.3	159.4	160.4	162.5	164.6	171.8	186.3	202.9	232.9	264.0	284.7
77.5°	123.2	122.1	124.2	127.3	126.3	132.5	141.8	156.3	176.0	201.9	215.3
80°	87.0	87.0	90.1	93.2	92.1	98.3	101.4	111.8	128.4	144.9	150.1
82.5°	58.0	58.0	61.1	61.1	63.1	64.2	68.3	73.5	87.0	95.2	98.3
85°	33.1	33.1	34.2	34.2	34.2	36.2	39.3	41.4	45.5	50.7	52.8
87.5°	13.5	14.5	14.5	14.5	14.5	16.6	16.6	18.6	19.7	21.7	21.7
90°	25.3	25.3	25.3	24.2	23.0	21.9	20.7	19.6	18.4	16.1	15.0
92.5°	89.8	93.2	111.7	122.6	133.5	179.6	249.8	370.7	459.3	467.4	324.6
95°	298.2	332.7	414.4	462.8	511.1	652.7	827.7	998.1	1020.0	832.3	514.6
97.5°	637.8	697.6	766.7	835.8	904.8	1047.6	1186.9	1246.7	1101.7	763.2	420.2
100°	958.9	1041.8	1121.3	1181.2	1241.0	1359.6	1416.0	1327.3	1039.5	663.1	373.0
102.5°	1298.6	1351.5	1437.8	1473.5	1509.2	1550.7	1493.1	1279.0	930.2	587.1	353.4
105°	1562.2	1600.2	1637.0	1643.4	1649.7	1599.0	1441.3	1165.0	834.6	543.4	351.1
107.5°	1721.0	1726.8	1716.4	1691.1	1665.8	1543.8	1335.4	1056.8	763.2	520.3	359.2
110°	1768.2	1746.4	1694.6	1645.6	1596.7	1434.4	1215.7	967.0	716.0	511.1	371.8

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1733.7	1692.3	1610.5	1550.6	1490.8	1326.2	1121.3	900.2	688.4	511.1	388.0
115°	1652.0	1596.7	1506.9	1444.2	1381.4	1223.7	1045.3	855.3	670.0	514.6	404.1
117.5°	1555.3	1497.7	1406.8	1347.5	1288.2	1150.0	992.3	825.4	659.6	520.3	422.5
120°	1457.4	1402.2	1317.0	1266.4	1215.7	1089.0	950.9	801.2	652.7	529.6	440.9
122.5°	1371.1	1321.6	1247.9	1201.3	1154.7	1045.3	919.8	780.5	647.0	537.6	461.6
125°	1302.0	1254.8	1190.3	1148.9	1107.5	1007.3	889.9	762.1	642.4	546.8	480.0
127.5°	1244.4	1201.9	1143.1	1104.0	1064.9	970.5	858.8	744.8	640.1	557.2	497.3
130°	1191.5	1153.5	1095.9	1058.5	1021.1	931.3	830.0	727.6	637.8	566.4	514.6
132.5°	1140.8	1102.8	1045.3	1009.6	973.9	894.5	801.2	713.7	637.8	576.8	529.6
135°	1084.4	1046.4	995.8	963.0	930.2	856.5	777.1	703.4	637.8	586.0	543.4
137.5°	1024.6	988.9	942.8	914.0	885.3	822.0	755.2	693.0	638.9	595.2	553.7
140°	965.9	935.9	893.3	869.2	845.0	792.0	737.9	686.1	640.1	600.9	564.1
142.5°	909.4	885.3	850.7	830.6	810.4	766.7	723.0	680.4	641.2	604.4	569.8
145°	859.9	840.4	812.7	797.2	781.7	746.0	710.3	674.6	640.1	606.7	575.6
147.5°	819.7	803.5	780.5	768.4	756.3	727.6	697.6	668.8	637.8	607.8	579.1
150°	786.3	772.5	755.2	744.8	734.5	712.6	687.3	661.9	634.3	607.8	582.5
152.5°	756.3	746.0	732.2	724.7	717.2	697.6	675.8	653.9	629.7	606.7	584.8
155°	731.0	723.0	711.4	705.1	698.8	682.7	664.2	644.7	623.9	604.4	586.0
157.5°	708.0	701.1	691.9	686.7	681.5	668.8	652.7	636.6	618.2	602.1	587.1
160°	686.1	680.4	672.3	668.2	664.2	652.7	641.2	626.3	612.4	598.6	587.1
162.5°	665.4	660.8	655.0	651.6	648.1	638.9	628.6	617.0	605.5	595.2	586.0
165°	644.7	642.4	637.8	634.9	632.0	625.1	617.0	607.8	598.6	591.7	584.8
167.5°	626.3	623.9	621.6	619.3	617.0	611.3	605.5	598.6	591.7	586.0	582.5
170°	609.0	607.8	605.5	604.4	603.2	599.8	596.3	590.6	586.0	582.5	580.2
172.5°	595.2	592.9	592.9	592.3	591.7	589.4	586.0	582.5	579.1	577.9	577.9
175°	582.5	581.4	581.4	581.4	581.4	579.1	579.1	575.6	574.4	574.4	575.6
177.5°	574.4	573.3	574.4	574.4	574.4	574.4	573.3	572.1	571.0	571.0	573.3
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4
2.5°	1254.6	1249.4	1243.2	1243.2	1236.0	1232.9	1226.7	1224.6	1219.4	1211.1	1204.9
5°	1299.1	1285.7	1277.4	1270.1	1254.6	1243.2	1231.8	1219.4	1207.0	1192.5	1175.9
7.5°	1342.6	1317.8	1306.4	1293.9	1271.2	1247.4	1224.6	1208.0	1191.5	1168.7	1148.0
10°	1388.1	1357.1	1336.4	1319.8	1284.6	1254.6	1221.5	1197.7	1171.8	1142.8	1115.9
12.5°	1426.4	1386.1	1368.5	1337.4	1297.0	1260.8	1219.4	1183.2	1149.0	1114.9	1081.7
15°	1458.5	1420.2	1376.8	1364.3	1308.4	1256.7	1210.1	1163.5	1121.1	1086.9	1048.6
17.5°	1468.9	1420.2	1398.5	1368.5	1302.2	1248.4	1189.4	1138.7	1098.3	1047.6	1017.6
20°	1472.0	1425.4	1395.4	1367.4	1308.4	1237.0	1179.0	1116.9	1068.3	1017.6	969.9
22.5°	1463.7	1408.8	1379.9	1352.9	1286.7	1225.6	1158.3	1090.0	1033.1	986.5	938.9
25°	1448.2	1384.0	1356.1	1327.1	1263.9	1196.6	1123.1	1057.9	1005.1	949.2	902.7
27.5°	1427.5	1354.0	1321.9	1291.9	1229.8	1166.6	1097.3	1030.0	971.0	912.0	868.5
30°	1401.6	1316.7	1287.7	1248.4	1188.4	1128.3	1065.2	997.9	931.6	875.7	828.1
32.5°	1368.5	1279.4	1241.1	1203.9	1138.7	1083.8	1023.8	960.6	896.4	841.6	791.9
35°	1338.5	1237.0	1194.6	1157.3	1084.8	1026.9	977.2	918.2	861.2	804.3	759.8
37.5°	1298.1	1194.6	1143.8	1105.5	1032.0	973.0	926.5	880.9	820.9	766.0	724.6
40°	1255.6	1141.8	1094.2	1055.9	979.3	915.1	870.6	830.2	781.5	730.8	687.3
42.5°	1217.3	1091.1	1040.3	993.7	916.1	859.2	813.6	782.6	738.1	692.5	653.2
45°	1168.7	1037.2	982.4	933.7	859.2	797.1	753.6	728.7	695.6	651.1	617.0
47.5°	1119.0	979.3	922.3	874.7	794.0	739.1	696.7	672.8	650.1	614.9	580.7
50°	1053.8	918.2	866.4	811.6	731.9	676.0	640.8	617.0	599.4	574.5	545.5
52.5°	982.4	855.0	799.1	751.5	672.8	622.1	581.8	568.3	550.7	532.1	507.2
55°	906.8	786.7	732.9	686.3	613.8	562.1	529.0	514.5	501.0	486.5	470.0
57.5°	831.2	715.3	664.6	623.2	555.9	506.2	479.3	459.6	450.3	442.0	428.6
60°	737.0	638.7	599.4	562.1	495.8	450.3	424.4	409.9	401.6	397.5	391.3
62.5°	654.2	573.5	530.0	493.8	441.0	400.6	375.8	364.4	357.1	355.1	347.8
65°	566.2	496.9	462.7	431.7	386.1	349.9	329.2	315.7	310.5	309.5	309.5
67.5°	483.4	427.5	393.4	371.6	332.3	300.2	280.5	275.4	272.2	268.1	267.1
70°	405.8	361.3	331.2	312.6	277.4	253.6	238.1	229.8	229.8	226.7	224.6
72.5°	337.5	292.9	273.3	257.8	228.8	208.1	196.7	194.6	187.4	186.3	186.3
75°	264.0	230.8	217.4	203.9	182.2	167.7	158.4	153.2	149.1	149.1	150.1
77.5°	198.7	176.0	163.6	153.2	137.7	128.4	121.1	119.0	114.9	114.9	114.9
80°	140.8	128.4	119.0	110.8	99.4	91.1	87.0	82.8	82.8	81.8	82.8
82.5°	91.1	80.7	75.6	74.5	64.2	61.1	55.9	56.9	53.8	52.8	54.9
85°	52.8	47.6	41.4	39.3	35.2	31.1	29.0	30.0	29.0	27.9	29.0
87.5°	20.7	17.6	16.6	16.6	13.5	12.4	11.4	12.4	10.4	10.4	11.4
90°	12.7	11.5	10.4	9.2	6.9	4.6	2.3	1.2	2.3	4.6	6.9
92.5°	193.4	115.1	94.4	73.7	49.5	32.2	20.7	17.3	20.7	32.2	49.5
95°	261.3	138.1	112.2	86.3	61.0	48.4	39.1	38.0	39.1	48.4	61.0
97.5°	225.6	140.4	121.4	102.5	79.4	66.8	59.9	58.7	59.9	66.8	79.4
100°	223.3	156.6	139.3	122.0	100.2	87.5	82.9	80.6	82.9	87.5	100.2
102.5°	233.7	176.1	159.4	142.7	123.2	109.4	105.9	104.8	105.9	109.4	123.2
105°	248.7	198.0	181.9	165.8	147.4	135.8	130.1	130.1	130.1	135.8	147.4
107.5°	269.4	219.9	205.5	191.1	171.5	162.3	156.6	154.3	156.6	162.3	171.5
110°	292.4	245.2	230.2	215.3	198.0	187.6	183.0	180.7	183.0	187.6	198.0

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	314.3	269.4	255.0	240.6	223.3	213.0	209.5	207.2	209.5	213.0	223.3
115°	337.3	294.7	280.3	265.9	248.7	238.3	234.8	232.5	234.8	238.3	248.7
117.5°	360.3	320.0	306.2	292.4	272.8	262.5	259.0	255.6	259.0	262.5	272.8
120°	385.7	345.4	331.0	316.6	297.0	286.6	282.0	278.6	282.0	286.6	297.0
122.5°	409.8	369.5	355.2	340.8	318.9	308.5	305.1	302.8	305.1	308.5	318.9
125°	430.5	392.6	377.6	362.6	340.8	330.4	324.6	322.3	324.6	330.4	340.8
127.5°	451.3	414.4	399.4	384.5	361.5	348.8	341.9	338.5	341.9	348.8	361.5
130°	470.8	435.2	420.2	405.2	381.0	366.1	356.9	353.4	356.9	366.1	381.0
132.5°	489.3	453.6	438.6	423.6	398.3	381.0	369.5	364.9	369.5	381.0	398.3
135°	505.4	469.7	454.2	438.6	414.4	396.0	382.2	377.6	382.2	396.0	414.4
137.5°	516.9	484.7	468.6	452.4	428.2	409.8	397.2	393.7	397.2	409.8	428.2
140°	529.6	496.2	480.6	465.1	443.2	424.8	411.0	407.5	411.0	424.8	443.2
142.5°	537.6	506.5	492.1	477.7	457.0	438.6	425.9	423.6	425.9	438.6	457.0
145°	546.8	516.9	503.6	490.4	469.7	453.6	442.1	439.8	442.1	453.6	469.7
147.5°	552.6	526.1	514.0	501.9	483.5	468.5	458.2	457.0	458.2	468.5	483.5
150°	558.3	533.0	523.2	513.4	497.3	482.4	474.3	472.0	474.3	482.4	497.3
152.5°	564.1	541.1	532.4	523.8	508.8	496.2	489.3	488.1	489.3	496.2	508.8
155°	567.5	548.0	540.0	531.9	520.3	508.8	501.9	501.9	501.9	508.8	520.3
157.5°	571.0	553.7	547.4	541.1	530.7	520.3	514.6	514.6	514.6	520.3	530.7
160°	573.3	558.3	553.2	548.0	538.8	530.7	526.1	527.2	526.1	530.7	538.8
162.5°	575.6	562.9	558.9	554.9	548.0	541.1	536.5	537.6	536.5	541.1	548.0
165°	575.6	566.4	563.0	559.5	554.9	549.1	545.7	548.0	545.7	549.1	554.9
167.5°	575.6	567.5	565.2	562.9	559.5	556.0	553.7	554.9	553.7	556.0	559.5
170°	575.6	569.8	568.1	566.4	564.1	561.8	560.6	561.8	560.6	561.8	564.1
172.5°	574.4	569.8	569.2	568.7	567.5	565.2	564.1	566.4	564.1	565.2	567.5
175°	573.3	569.8	569.8	569.8	569.8	568.7	567.5	569.8	567.5	568.7	569.8
177.5°	572.1	569.8	569.8	569.8	571.0	569.8	569.8	572.1	569.8	569.8	571.0
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4
2.5°	1202.8	1200.8	1195.6	1192.5	1182.1	1169.7	1165.6	1155.2	1159.4	1152.1	1152.1
5°	1170.8	1161.4	1155.2	1145.9	1126.2	1112.8	1098.3	1091.1	1086.9	1081.7	1077.6
7.5°	1129.4	1122.1	1115.9	1098.3	1076.6	1057.9	1040.3	1033.1	1019.6	1010.3	1006.2
10°	1093.1	1082.8	1068.3	1047.6	1024.8	1001.0	985.5	969.9	959.6	954.4	943.0
12.5°	1055.9	1043.4	1027.9	997.9	973.0	958.6	930.6	916.1	910.9	906.8	893.3
15°	1017.6	1004.1	985.5	957.5	935.8	901.6	885.1	873.7	861.2	860.2	849.9
17.5°	983.4	966.8	951.3	917.1	890.2	860.2	850.9	838.5	827.1	814.7	809.5
20°	939.9	924.4	913.0	875.7	845.7	827.1	811.6	801.2	794.0	781.5	779.5
22.5°	900.6	884.0	868.5	840.5	814.7	790.9	772.2	760.8	757.7	752.6	743.2
25°	862.3	845.7	827.1	801.2	774.3	757.7	741.2	733.9	727.7	719.4	712.2
27.5°	830.2	814.7	797.1	765.0	742.2	729.8	712.2	703.9	695.6	691.5	688.4
30°	791.9	774.3	760.8	736.0	711.2	694.6	682.2	674.9	667.7	663.5	661.5
32.5°	754.6	738.1	728.7	701.8	682.2	662.5	653.2	648.0	643.9	639.7	635.6
35°	724.6	708.0	693.6	668.7	649.0	635.6	628.3	620.1	617.0	612.8	612.8
37.5°	687.3	674.9	660.4	636.6	619.0	608.7	602.5	592.1	591.1	589.0	585.9
40°	655.3	642.8	629.4	608.7	593.1	580.7	572.4	567.3	564.2	562.1	560.0
42.5°	621.1	607.6	601.4	577.6	564.2	551.7	547.6	542.4	541.4	537.2	532.1
45°	588.0	576.6	564.2	546.6	535.2	524.8	518.6	514.5	509.3	508.3	505.2
47.5°	559.0	545.5	534.1	517.6	505.2	496.9	491.7	486.5	482.4	479.3	476.2
50°	521.7	511.4	502.0	484.5	474.1	465.8	458.6	454.4	450.3	450.3	450.3
52.5°	485.5	476.2	467.9	455.5	443.0	435.8	427.5	424.4	422.3	419.2	422.3
55°	450.3	441.0	432.7	423.4	408.9	402.7	394.4	391.3	392.3	392.3	395.4
57.5°	413.0	405.8	400.6	389.2	375.8	369.5	364.4	361.3	361.3	365.4	366.4
60°	376.8	369.5	360.2	349.9	341.6	334.4	331.2	332.3	332.3	334.4	339.5
62.5°	336.4	332.3	327.1	312.6	307.4	302.3	298.1	301.2	300.2	305.4	312.6
65°	299.2	295.0	287.8	280.5	274.3	269.1	268.1	269.1	271.2	276.4	284.7
67.5°	257.8	257.8	251.5	245.3	240.2	235.0	236.0	237.1	239.1	245.3	257.8
70°	223.6	219.5	213.2	209.1	205.0	202.9	200.8	205.0	211.2	215.3	224.6
72.5°	186.3	183.2	178.0	173.9	172.9	170.8	169.8	171.8	178.0	185.3	195.6
75°	147.0	148.0	144.9	141.8	141.8	138.7	140.8	140.8	147.0	154.2	162.5
77.5°	113.9	112.8	111.8	109.7	108.7	108.7	108.7	110.8	117.0	121.1	129.4
80°	80.7	81.8	78.7	79.7	78.7	79.7	79.7	83.8	87.0	92.1	98.3
82.5°	53.8	53.8	51.8	52.8	52.8	52.8	53.8	55.9	60.0	64.2	68.3
85°	30.0	31.1	29.0	31.1	31.1	31.1	32.1	33.1	36.2	37.3	41.4
87.5°	11.4	13.5	13.5	11.4	12.4	13.5	14.5	13.5	15.5	17.6	18.6
90°	9.2	10.4	11.5	12.7	15.0	16.1	18.4	19.6	20.7	21.9	23.0
92.5°	73.7	94.4	115.1	193.4	324.6	467.4	459.3	370.7	249.8	179.6	133.5
95°	86.3	112.2	138.1	261.3	514.6	832.3	1020.0	998.1	827.7	652.7	511.1
97.5°	102.5	121.4	140.4	225.6	420.2	763.2	1101.7	1246.7	1186.9	1047.6	904.8
100°	122.0	139.3	156.6	223.3	373.0	663.1	1039.5	1327.3	1416.0	1359.6	1241.0
102.5°	142.7	159.4	176.1	233.7	353.4	587.1	930.2	1279.0	1493.1	1550.7	1509.2
105°	165.8	181.9	198.0	248.7	351.1	543.4	834.6	1165.0	1441.3	1599.0	1649.7
107.5°	191.1	205.5	219.9	269.4	359.2	520.3	763.2	1056.8	1335.4	1543.8	1665.8
110°	215.3	230.2	245.2	292.4	371.8	511.1	716.0	967.0	1215.7	1434.4	1596.7

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	240.6	255.0	269.4	314.3	388.0	511.1	688.4	900.2	1121.3	1326.2	1490.8
115°	265.9	280.3	294.7	337.3	404.1	514.6	670.0	855.3	1045.3	1223.7	1381.4
117.5°	292.4	306.2	320.0	360.3	422.5	520.3	659.6	825.4	992.3	1150.0	1288.2
120°	316.6	331.0	345.4	385.7	440.9	529.6	652.7	801.2	950.9	1089.0	1215.7
122.5°	340.8	355.2	369.5	409.8	461.6	537.6	647.0	780.5	919.8	1045.3	1154.7
125°	362.6	377.6	392.6	430.5	480.0	546.8	642.4	762.1	889.9	1007.3	1107.5
127.5°	384.5	399.4	414.4	451.3	497.3	557.2	640.1	744.8	858.8	970.5	1064.9
130°	405.2	420.2	435.2	470.8	514.6	566.4	637.8	727.6	830.0	931.3	1021.1
132.5°	423.6	438.6	453.6	489.3	529.6	576.8	637.8	713.7	801.2	894.5	973.9
135°	438.6	454.2	469.7	505.4	543.4	586.0	637.8	703.4	777.1	856.5	930.2
137.5°	452.4	468.6	484.7	516.9	553.7	595.2	638.9	693.0	755.2	822.0	885.3
140°	465.1	480.6	496.2	529.6	564.1	600.9	640.1	686.1	737.9	792.0	845.0
142.5°	477.7	492.1	506.5	537.6	569.8	604.4	641.2	680.4	723.0	766.7	810.4
145°	490.4	503.6	516.9	546.8	575.6	606.7	640.1	674.6	710.3	746.0	781.7
147.5°	501.9	514.0	526.1	552.6	579.1	607.8	637.8	668.8	697.6	727.6	756.3
150°	513.4	523.2	533.0	558.3	582.5	607.8	634.3	661.9	687.3	712.6	734.5
152.5°	523.8	532.4	541.1	564.1	584.8	606.7	629.7	653.9	675.8	697.6	717.2
155°	531.9	540.0	548.0	567.5	586.0	604.4	623.9	644.7	664.2	682.7	698.8
157.5°	541.1	547.4	553.7	571.0	587.1	602.1	618.2	636.6	652.7	668.8	681.5
160°	548.0	553.2	558.3	573.3	587.1	598.6	612.4	626.3	641.2	652.7	664.2
162.5°	554.9	558.9	562.9	575.6	586.0	595.2	605.5	617.0	628.6	638.9	648.1
165°	559.5	563.0	566.4	575.6	584.8	591.7	598.6	607.8	617.0	625.1	632.0
167.5°	562.9	565.2	567.5	575.6	582.5	586.0	591.7	598.6	605.5	611.3	617.0
170°	566.4	568.1	569.8	575.6	580.2	582.5	586.0	590.6	596.3	599.8	603.2
172.5°	568.7	569.2	569.8	574.4	577.9	577.9	579.1	582.5	586.0	589.4	591.7
175°	569.8	569.8	569.8	573.3	575.6	574.4	574.4	575.6	579.1	579.1	581.4
177.5°	569.8	569.8	569.8	572.1	573.3	571.0	571.0	572.1	573.3	574.4	574.4
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4
2.5°	1156.3	1149.0	1148.0	1150.1	1145.9	1152.1	1150.1	1152.1	1146.9	1152.1	1149.0
5°	1076.6	1074.5	1070.3	1065.2	1066.2	1067.2	1072.4	1067.2	1071.4	1072.4	1077.6
7.5°	1002.0	997.9	1001.0	998.9	989.6	987.5	989.6	992.7	998.9	1003.1	1006.2
10°	942.0	939.9	935.8	932.7	927.5	924.4	928.5	924.4	932.7	939.9	939.9
12.5°	896.4	888.2	883.0	882.0	870.6	872.6	876.8	879.9	889.2	893.3	893.3
15°	848.8	842.6	840.5	836.4	832.3	836.4	834.3	837.4	841.6	845.7	847.8
17.5°	807.4	806.4	807.4	797.1	800.2	795.0	796.0	801.2	798.1	801.2	807.4
20°	770.2	772.2	769.1	765.0	765.0	758.8	766.0	763.9	765.0	771.2	780.5
22.5°	742.2	741.2	738.1	735.0	730.8	731.9	732.9	730.8	739.1	744.3	745.3
25°	712.2	710.1	709.1	706.0	701.8	706.0	704.9	706.0	708.0	716.3	710.1
27.5°	684.2	680.1	682.2	679.1	678.0	679.1	679.1	680.1	682.2	683.2	684.2
30°	660.4	656.3	655.3	653.2	652.1	653.2	655.3	653.2	661.5	660.4	660.4
32.5°	634.5	631.4	629.4	629.4	628.3	627.3	628.3	629.4	635.6	631.4	635.6
35°	609.7	607.6	607.6	605.6	604.5	604.5	604.5	608.7	606.6	609.7	609.7
37.5°	585.9	585.9	584.9	582.8	581.8	582.8	581.8	583.8	582.8	583.8	584.9
40°	561.1	559.0	557.9	557.9	554.8	551.7	554.8	554.8	555.9	559.0	560.0
42.5°	531.0	532.1	532.1	527.9	527.9	527.9	529.0	530.0	530.0	532.1	532.1
45°	505.2	503.1	503.1	503.1	501.0	502.0	504.1	504.1	504.1	504.1	502.0
47.5°	476.2	476.2	477.2	477.2	480.3	479.3	479.3	478.2	476.2	476.2	477.2
50°	449.3	452.4	453.4	453.4	454.4	455.5	455.5	453.4	452.4	449.3	449.3
52.5°	423.4	425.4	427.5	430.6	432.7	431.7	431.7	429.6	425.4	424.4	423.4
55°	395.4	398.5	402.7	405.8	408.9	409.9	409.9	405.8	401.6	396.5	396.5
57.5°	369.5	372.7	379.9	383.0	387.1	387.1	385.1	382.0	375.8	371.6	368.5
60°	343.7	348.8	354.0	360.2	365.4	366.4	363.3	359.2	352.0	346.8	342.6
62.5°	315.7	320.9	331.2	337.5	341.6	341.6	341.6	336.4	327.1	319.9	313.7
65°	288.8	294.0	303.3	311.6	314.7	317.8	314.7	309.5	302.3	294.0	287.8
67.5°	260.9	267.1	276.4	282.6	286.7	289.8	287.8	283.6	274.3	262.9	258.8
70°	229.8	232.9	246.4	252.6	258.8	260.9	258.8	252.6	243.3	230.8	226.7
72.5°	200.8	203.9	216.3	221.5	226.7	228.8	225.7	221.5	213.2	201.9	196.7
75°	167.7	172.9	179.1	187.4	193.6	195.6	192.5	189.4	179.1	171.8	167.7
77.5°	132.5	137.7	146.0	153.2	159.4	158.4	154.2	155.3	143.9	135.6	132.5
80°	100.4	104.6	110.8	117.0	120.1	120.1	119.0	114.9	110.8	104.6	99.4
82.5°	69.4	74.5	79.7	83.8	83.8	84.9	82.8	81.8	77.6	72.5	71.4
85°	41.4	42.4	46.6	46.6	50.7	48.7	47.6	50.7	46.6	43.5	42.4
87.5°	18.6	17.6	18.6	18.6	17.6	19.7	19.7	18.6	19.7	18.6	18.6
90°	24.2	25.3	25.3	25.3	26.5	26.5	26.5	25.3	25.3	25.3	24.2
92.5°	122.6	111.7	93.2	89.8	87.5	85.2	87.5	89.8	93.2	111.7	122.6
95°	462.8	414.4	332.7	298.2	289.0	270.5	289.0	298.2	332.7	414.4	462.8
97.5°	835.8	766.7	697.6	637.8	606.7	592.9	606.7	637.8	697.6	766.7	835.8
100°	1181.2	1121.3	1041.8	958.9	916.4	897.9	916.4	958.9	1041.8	1121.3	1181.2
102.5°	1473.5	1437.8	1351.5	1298.6	1251.4	1238.7	1251.4	1298.6	1351.5	1437.8	1473.5
105°	1643.4	1637.0	1600.2	1562.2	1539.2	1525.3	1539.2	1562.2	1600.2	1637.0	1643.4
107.5°	1691.1	1716.4	1726.8	1721.0	1709.5	1698.0	1709.5	1721.0	1726.8	1716.4	1691.1
110°	1645.6	1694.6	1746.4	1768.2	1776.3	1776.3	1776.3	1768.2	1746.4	1694.6	1645.6

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1550.6	1610.5	1692.3	1733.7	1756.7	1767.1	1756.7	1733.7	1692.3	1610.5	1550.6
115°	1444.2	1506.9	1596.7	1652.0	1684.2	1699.2	1684.2	1652.0	1596.7	1506.9	1444.2
117.5°	1347.5	1406.8	1497.7	1555.3	1587.5	1596.7	1587.5	1555.3	1497.7	1406.8	1347.5
120°	1266.4	1317.0	1402.2	1457.4	1488.5	1497.7	1488.5	1457.4	1402.2	1317.0	1266.4
122.5°	1201.3	1247.9	1321.6	1371.1	1402.2	1410.2	1402.2	1371.1	1321.6	1247.9	1201.3
125°	1148.9	1190.3	1254.8	1302.0	1327.3	1338.8	1327.3	1302.0	1254.8	1190.3	1148.9
127.5°	1104.0	1143.1	1201.9	1244.4	1268.6	1273.2	1268.6	1244.4	1201.9	1143.1	1104.0
130°	1058.5	1095.9	1153.5	1191.5	1214.5	1221.4	1214.5	1191.5	1153.5	1095.9	1058.5
132.5°	1009.6	1045.3	1102.8	1140.8	1161.6	1169.6	1161.6	1140.8	1102.8	1045.3	1009.6
135°	963.0	995.8	1046.4	1084.4	1105.2	1112.1	1105.2	1084.4	1046.4	995.8	963.0
137.5°	914.0	942.8	988.9	1024.6	1044.1	1052.2	1044.1	1024.6	988.9	942.8	914.0
140°	869.2	893.3	935.9	965.9	983.1	988.9	983.1	965.9	935.9	893.3	869.2
142.5°	830.6	850.7	885.3	909.4	925.6	930.2	925.6	909.4	885.3	850.7	830.6
145°	797.2	812.7	840.4	859.9	872.6	877.2	872.6	859.9	840.4	812.7	797.2
147.5°	768.4	780.5	803.5	819.7	827.7	830.0	827.7	819.7	803.5	780.5	768.4
150°	744.8	755.2	772.5	786.3	790.9	792.0	790.9	786.3	772.5	755.2	744.8
152.5°	724.7	732.2	746.0	756.3	760.9	762.1	760.9	756.3	746.0	732.2	724.7
155°	705.1	711.4	723.0	731.0	734.5	735.6	734.5	731.0	723.0	711.4	705.1
157.5°	686.7	691.9	701.1	708.0	711.4	711.4	711.4	708.0	701.1	691.9	686.7
160°	668.2	672.3	680.4	686.1	688.4	687.3	688.4	686.1	680.4	672.3	668.2
162.5°	651.6	655.0	660.8	665.4	665.4	665.4	665.4	665.4	660.8	655.0	651.6
165°	634.9	637.8	642.4	644.7	644.7	644.7	644.7	644.7	642.4	637.8	634.9
167.5°	619.3	621.6	623.9	626.3	625.1	625.1	625.1	626.3	623.9	621.6	619.3
170°	604.4	605.5	607.8	609.0	609.0	607.8	609.0	609.0	607.8	605.5	604.4
172.5°	592.3	592.9	592.9	595.2	592.9	591.7	592.9	595.2	592.9	592.9	592.3
175°	581.4	581.4	581.4	582.5	580.2	579.1	580.2	582.5	581.4	581.4	581.4
177.5°	574.4	574.4	573.3	574.4	571.0	571.0	571.0	574.4	573.3	574.4	574.4
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4
2.5°	1158.3	1152.1	1159.4	1150.1	1152.1	1163.5	1162.5	1172.8	1179.0	1178.0	1183.2
5°	1081.7	1081.7	1084.8	1083.8	1094.2	1103.5	1115.9	1126.2	1137.6	1143.8	1151.1
7.5°	1006.2	1016.5	1018.6	1023.8	1036.2	1051.7	1064.1	1079.7	1096.2	1107.6	1115.9
10°	944.1	952.3	960.6	964.8	978.2	998.9	1016.5	1041.4	1062.1	1074.5	1085.9
12.5°	889.2	898.5	902.7	921.3	930.6	944.1	968.9	995.8	1018.6	1032.0	1041.4
15°	849.9	855.0	864.4	875.7	885.1	901.6	922.3	952.3	974.1	985.5	1017.6
17.5°	816.7	822.9	828.1	833.3	847.8	865.4	885.1	910.9	938.9	958.6	975.1
20°	782.6	785.7	791.9	800.2	810.5	827.1	844.7	871.6	896.4	912.0	933.7
22.5°	742.2	751.5	757.7	763.9	775.3	794.0	810.5	830.2	861.2	878.8	901.6
25°	718.4	722.5	726.7	733.9	742.2	758.8	777.4	798.1	822.9	841.6	861.2
27.5°	687.3	693.6	698.7	708.0	713.2	726.7	744.3	765.0	795.0	810.5	827.1
30°	661.5	667.7	671.8	676.0	683.2	697.7	714.3	730.8	758.8	778.4	795.0
32.5°	635.6	641.8	647.0	650.1	657.3	666.6	680.1	700.8	724.6	738.1	759.8
35°	612.8	612.8	619.0	623.2	629.4	637.7	650.1	665.6	690.4	708.0	727.7
37.5°	586.9	588.0	593.1	596.2	602.5	610.7	623.2	637.7	658.4	671.8	691.5
40°	560.0	563.1	565.2	570.4	577.6	580.7	593.1	609.7	630.4	642.8	659.4
42.5°	533.1	535.2	540.3	544.5	550.7	555.9	564.2	579.7	595.2	613.8	627.3
45°	503.1	508.3	511.4	518.6	521.7	526.9	535.2	547.6	566.2	577.6	593.1
47.5°	477.2	479.3	481.3	490.7	496.9	500.0	508.3	515.5	535.2	545.5	560.0
50°	449.3	449.3	452.4	456.5	463.7	470.0	477.2	485.5	501.0	511.4	525.9
52.5°	423.4	420.3	422.3	424.4	431.7	437.9	445.1	456.5	471.0	477.2	489.6
55°	395.4	390.3	393.4	396.5	398.5	406.8	415.1	422.3	433.7	443.0	454.4
57.5°	365.4	364.4	362.3	363.3	368.5	373.7	379.9	389.2	402.7	409.9	416.1
60°	338.5	332.3	330.2	332.3	335.4	338.5	346.8	355.1	366.4	373.7	380.9
62.5°	310.5	304.3	300.2	297.1	300.2	307.4	312.6	318.8	328.1	336.4	342.6
65°	283.6	274.3	270.2	268.1	267.1	272.2	276.4	284.7	292.9	296.1	303.3
67.5°	253.6	245.3	240.2	237.1	237.1	237.1	241.2	249.5	257.8	258.8	266.0
70°	223.6	214.3	209.1	205.0	202.9	205.0	210.1	211.2	218.4	220.5	224.6
72.5°	191.5	183.2	177.0	171.8	172.9	174.9	174.9	177.0	181.2	186.3	186.3
75°	161.5	150.1	147.0	142.9	140.8	140.8	140.8	144.9	148.0	152.2	151.1
77.5°	127.3	121.1	114.9	112.8	109.7	108.7	110.8	110.8	112.8	115.9	117.0
80°	98.3	91.1	87.0	84.9	80.7	79.7	80.7	80.7	83.8	82.8	83.8
82.5°	68.3	63.1	60.0	56.9	54.9	55.9	54.9	54.9	55.9	54.9	54.9
85°	39.3	38.3	36.2	35.2	34.2	32.1	34.2	33.1	32.1	31.1	33.1
87.5°	18.6	17.6	17.6	15.5	15.5	14.5	15.5	15.5	14.5	14.5	14.5
90°	23.0	21.9	20.7	19.6	18.4	16.1	15.0	12.7	11.5	10.4	9.2
92.5°	133.5	179.6	249.8	370.7	459.3	467.4	324.6	193.4	115.1	94.4	73.7
95°	511.1	652.7	827.7	998.1	1020.0	832.3	514.6	261.3	138.1	112.2	86.3
97.5°	904.8	1047.6	1186.9	1246.7	1101.7	763.2	420.2	225.6	140.4	121.4	102.5
100°	1241.0	1359.6	1416.0	1327.3	1039.5	663.1	373.0	223.3	156.6	139.3	122.0
102.5°	1509.2	1550.7	1493.1	1279.0	930.2	587.1	353.4	233.7	176.1	159.4	142.7
105°	1649.7	1599.0	1441.3	1165.0	834.6	543.4	351.1	248.7	198.0	181.9	165.8
107.5°	1665.8	1543.8	1335.4	1056.8	763.2	520.3	359.2	269.4	219.9	205.5	191.1
110°	1596.7	1434.4	1215.7	967.0	716.0	511.1	371.8	292.4	245.2	230.2	215.3

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1490.8	1326.2	1121.3	900.2	688.4	511.1	388.0	314.3	269.4	255.0	240.6
115°	1381.4	1223.7	1045.3	855.3	670.0	514.6	404.1	337.3	294.7	280.3	265.9
117.5°	1288.2	1150.0	992.3	825.4	659.6	520.3	422.5	360.3	320.0	306.2	292.4
120°	1215.7	1089.0	950.9	801.2	652.7	529.6	440.9	385.7	345.4	331.0	316.6
122.5°	1154.7	1045.3	919.8	780.5	647.0	537.6	461.6	409.8	369.5	355.2	340.8
125°	1107.5	1007.3	889.9	762.1	642.4	546.8	480.0	430.5	392.6	377.6	362.6
127.5°	1064.9	970.5	858.8	744.8	640.1	557.2	497.3	451.3	414.4	399.4	384.5
130°	1021.1	931.3	830.0	727.6	637.8	566.4	514.6	470.8	435.2	420.2	405.2
132.5°	973.9	894.5	801.2	713.7	637.8	576.8	529.6	489.3	453.6	438.6	423.6
135°	930.2	856.5	777.1	703.4	637.8	586.0	543.4	505.4	469.7	454.2	438.6
137.5°	885.3	822.0	755.2	693.0	638.9	595.2	553.7	516.9	484.7	468.6	452.4
140°	845.0	792.0	737.9	686.1	640.1	600.9	564.1	529.6	496.2	480.6	465.1
142.5°	810.4	766.7	723.0	680.4	641.2	604.4	569.8	537.6	506.5	492.1	477.7
145°	781.7	746.0	710.3	674.6	640.1	606.7	575.6	546.8	516.9	503.6	490.4
147.5°	756.3	727.6	697.6	668.8	637.8	607.8	579.1	552.6	526.1	514.0	501.9
150°	734.5	712.6	687.3	661.9	634.3	607.8	582.5	558.3	533.0	523.2	513.4
152.5°	717.2	697.6	675.8	653.9	629.7	606.7	584.8	564.1	541.1	532.4	523.8
155°	698.8	682.7	664.2	644.7	623.9	604.4	586.0	567.5	548.0	540.0	531.9
157.5°	681.5	668.8	652.7	636.6	618.2	602.1	587.1	571.0	553.7	547.4	541.1
160°	664.2	652.7	641.2	626.3	612.4	598.6	587.1	573.3	558.3	553.2	548.0
162.5°	648.1	638.9	628.6	617.0	605.5	595.2	586.0	575.6	562.9	558.9	554.9
165°	632.0	625.1	617.0	607.8	598.6	591.7	584.8	575.6	566.4	563.0	559.5
167.5°	617.0	611.3	605.5	598.6	591.7	586.0	582.5	575.6	567.5	565.2	562.9
170°	603.2	599.8	596.3	590.6	586.0	582.5	580.2	575.6	569.8	568.1	566.4
172.5°	591.7	589.4	586.0	582.5	579.1	577.9	577.9	574.4	569.8	569.2	568.7
175°	581.4	579.1	579.1	575.6	574.4	574.4	575.6	573.3	569.8	569.8	569.8
177.5°	574.4	574.4	573.3	572.1	571.0	571.0	573.3	572.1	569.8	569.8	569.8
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1219.4	1219.4	1219.4	1219.4
2.5°	1190.4	1200.8	1208.0	1221.5
5°	1163.5	1182.1	1199.7	1218.4
7.5°	1136.6	1158.3	1186.3	1210.1
10°	1106.6	1134.5	1167.7	1199.7
12.5°	1076.6	1109.7	1145.9	1188.4
15°	1040.3	1082.8	1125.2	1170.8
17.5°	1008.2	1051.7	1097.3	1154.2
20°	972.0	1019.6	1069.3	1127.3
22.5°	939.9	992.7	1044.5	1105.5
25°	903.7	955.4	1012.4	1077.6
27.5°	873.7	921.3	977.2	1047.6
30°	837.4	889.2	945.1	1015.5
32.5°	803.3	853.0	912.0	981.3
35°	768.1	818.8	871.6	937.8
37.5°	735.0	778.4	831.2	894.4
40°	697.7	745.3	792.9	842.6
42.5°	663.5	707.0	751.5	790.9
45°	625.2	662.5	704.9	737.0
47.5°	590.0	623.2	656.3	681.1
50°	554.8	580.7	605.6	627.3
52.5°	513.4	542.4	555.9	569.3
55°	476.2	492.7	505.2	518.6
57.5°	439.9	447.2	453.4	465.8
60°	392.3	400.6	407.9	417.2
62.5°	350.9	355.1	357.1	366.4
65°	311.6	310.5	315.7	320.9
67.5°	269.1	268.1	273.3	275.4
70°	227.7	226.7	227.7	232.9
72.5°	188.4	188.4	189.4	191.5
75°	152.2	152.2	153.2	155.3
77.5°	114.9	117.0	115.9	120.1
80°	83.8	81.8	83.8	85.9
82.5°	54.9	56.9	56.9	54.9
85°	31.1	31.1	31.1	31.1
87.5°	13.5	13.5	14.5	15.5
90°	6.9	4.6	2.3	1.2
92.5°	49.5	32.2	20.7	17.3
95°	61.0	48.4	39.1	38.0
97.5°	79.4	66.8	59.9	58.7
100°	100.2	87.5	82.9	80.6
102.5°	123.2	109.4	105.9	104.8
105°	147.4	135.8	130.1	130.1
107.5°	171.5	162.3	156.6	154.3
110°	198.0	187.6	183.0	180.7

TEST NUMBER: P1028239

CATALOG NUMBER: S125DIP-B850D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	223.3	213.0	209.5	207.2
115°	248.7	238.3	234.8	232.5
117.5°	272.8	262.5	259.0	255.6
120°	297.0	286.6	282.0	278.6
122.5°	318.9	308.5	305.1	302.8
125°	340.8	330.4	324.6	322.3
127.5°	361.5	348.8	341.9	338.5
130°	381.0	366.1	356.9	353.4
132.5°	398.3	381.0	369.5	364.9
135°	414.4	396.0	382.2	377.6
137.5°	428.2	409.8	397.2	393.7
140°	443.2	424.8	411.0	407.5
142.5°	457.0	438.6	425.9	423.6
145°	469.7	453.6	442.1	439.8
147.5°	483.5	468.5	458.2	457.0
150°	497.3	482.4	474.3	472.0
152.5°	508.8	496.2	489.3	488.1
155°	520.3	508.8	501.9	501.9
157.5°	530.7	520.3	514.6	514.6
160°	538.8	530.7	526.1	527.2
162.5°	548.0	541.1	536.5	537.6
165°	554.9	549.1	545.7	548.0
167.5°	559.5	556.0	553.7	554.9
170°	564.1	561.8	560.6	561.8
172.5°	567.5	565.2	564.1	566.4
175°	569.8	568.7	567.5	569.8
177.5°	571.0	569.8	569.8	572.1
180°	571.0	571.0	571.0	571.0

(END OF REPORT)