

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028254

Luminaire Tested: S125DIP-B850D1270UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028254
REPORT IS A COMBINATION OF REPORTS P1002511 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D1270UB30-4F0-XX-W2A-F4
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7771.9 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028254

CATALOG NUMBER: S125DIP-B850D1270UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1028254

CATALOG NUMBER: S125DIP-B850D1270UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	38	36
3	80	71	63	58	73	65	59	53	54	49	46	44	41	38	35	33	31
4	73	62	55	49	67	57	51	45	48	43	39	39	36	32	31	29	26
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	37	32	52	42	34	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8456	8456	8456
5°	8456	8259	8275
10°	8386	8070	8045
15°	8276	7843	7774
20°	8127	7581	7462
25°	7968	7295	7128
30°	7774	6996	6777
35°	7569	6683	6384
40°	7356	6353	6034
45°	7126	6030	5662
50°	6872	5665	5229
55°	6621	5262	4831
60°	6322	4837	4367
65°	5964	4345	3888
70°	5601	3780	3334
75°	4988	3112	2696
80°	4253	2325	1983
85°	3282	1376	1092

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7126 cd/sqm

TEST NUMBER: P1028254

CATALOG NUMBER: S125DIP-B850D1270UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.5	1.6
10°-20°	351.8	4.5
20°-30°	519.3	6.7
30°-40°	605.9	7.8
40°-50°	608.5	7.8
50°-60°	534.2	6.9
60°-70°	397.9	5.1
70°-80°	227.2	2.9
80°-90°	67.9	0.9
90°-100°	433.7	5.6
100°-110°	900.8	11.6
110°-120°	841.4	10.8
120°-130°	680.8	8.8
130°-140°	547.0	7.0
140°-150°	412.9	5.3
150°-160°	290.7	3.7
160°-170°	171.4	2.2
170°-180°	55.7	0.7
0°-30°	995.6	12.8
0°-40°	1601.5	20.6
0°-60°	2744.3	35.3
0°-90°	3437.3	44.2
90°-120°	2175.9	28.0
90°-150°	3816.8	49.1
90°-180°	4335.0	55.8
0°-180°	7771.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1320	1320	1320	1320	1320	
5°	1318	1316	1305	1314	1314	125
15°	1256	1253	1241	1247	1247	354
25°	1140	1135	1121	1124	1120	525
35°	985	980	966	961	952	616
45°	806	802	789	777	774	621
55°	614	611	596	587	580	548
65°	414	412	401	392	387	411
75°	220	218	213	210	206	235
85°	57	58	58	57	55	63
90°	1	10	19	24	27	7
95°	38	113	1029	467	273	40
105°	131	183	842	1658	1538	138
115°	234	283	676	1457	1714	231
125°	325	381	648	1159	1350	289
135°	381	458	643	971	1122	296
145°	444	508	646	804	885	278
155°	506	545	629	711	742	233
165°	553	568	604	640	650	156
175°	575	575	579	586	584	55
180°	576	576	576	576	576	

TEST NUMBER: P1028254

CATALOG NUMBER: S125DIP-B850D1270UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.8	1319.8	1319.8	1319.8	1319.8
2.5°	1323.9	1320.8	1310.4	1320.8	1319.8
5°	1317.7	1315.6	1305.1	1314.5	1313.5
7.5°	1308.3	1306.2	1294.7	1304.1	1303.1
10°	1294.7	1292.6	1281.1	1289.5	1288.4
12.5°	1278.0	1273.8	1263.4	1269.6	1269.6
15°	1256.1	1252.9	1241.4	1246.7	1246.7
17.5°	1233.1	1227.9	1216.4	1222.7	1217.4
20°	1202.8	1200.7	1187.2	1194.5	1189.2
22.5°	1172.5	1168.4	1155.8	1160.0	1156.9
25°	1140.2	1134.9	1121.4	1123.5	1120.3
27.5°	1102.6	1099.4	1085.9	1086.9	1083.8
30°	1066.0	1062.9	1047.2	1045.2	1042.0
32.5°	1026.4	1021.1	1007.6	1003.4	997.1
35°	984.6	980.4	965.8	960.6	952.2
37.5°	941.8	936.6	923.0	915.7	910.5
40°	897.9	892.7	878.1	868.7	865.6
42.5°	851.0	846.8	832.2	823.8	818.6
45°	806.1	801.9	789.3	776.8	773.7
47.5°	757.0	758.0	742.4	729.8	722.5
50°	710.0	706.9	694.3	680.8	673.5
52.5°	662.0	659.9	646.3	634.8	626.5
55°	613.9	610.8	596.2	586.8	579.5
57.5°	562.8	561.7	549.2	536.7	533.5
60°	514.7	510.6	499.1	488.6	481.3
62.5°	464.6	461.5	452.1	440.6	435.4
65°	414.5	412.4	400.9	391.5	387.4
67.5°	365.4	361.3	352.9	344.6	342.5
70°	319.5	314.3	304.9	298.6	294.4
72.5°	269.4	266.2	261.0	253.7	249.5
75°	220.3	218.2	213.0	209.9	205.7
77.5°	174.4	173.3	170.2	168.1	165.0
80°	131.6	131.6	129.5	128.4	126.3
82.5°	94.0	91.9	91.9	89.8	89.8
85°	57.4	58.5	58.5	57.4	55.3
87.5°	28.2	28.2	27.1	27.1	25.1
90°	1.2	10.4	18.6	24.4	26.7
92.5°	17.4	95.2	463.3	123.6	85.9
95°	38.3	113.2	1028.8	466.8	272.9
97.5°	59.2	122.5	1111.2	843.0	598.0
100°	81.3	140.5	1048.5	1191.3	905.7
102.5°	105.7	160.8	938.2	1486.2	1249.4
105°	131.2	183.4	841.8	1657.5	1538.5
107.5°	155.6	207.2	769.8	1705.6	1712.7
110°	182.3	232.2	722.2	1659.8	1791.6

TEST NUMBER: P1028254

CATALOG NUMBER: S125DIP-B850D1270UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	209.0	257.2	694.4	1564.1	1782.3
115°	234.5	282.7	675.8	1456.6	1713.8
117.5°	257.8	308.8	665.3	1359.1	1610.5
120°	281.0	333.8	658.4	1277.2	1510.6
122.5°	305.4	358.2	652.6	1211.6	1422.4
125°	325.1	380.8	647.9	1158.8	1350.4
127.5°	341.4	402.9	645.6	1113.5	1284.2
130°	356.5	423.8	643.3	1067.6	1232.0
132.5°	368.1	442.4	643.3	1018.3	1179.7
135°	380.8	458.0	643.3	971.3	1121.6
137.5°	397.1	472.6	644.4	922.0	1061.3
140°	411.0	484.8	645.6	876.6	997.4
142.5°	427.3	496.4	646.7	837.8	938.2
145°	443.5	508.0	645.6	804.1	884.8
147.5°	461.0	518.4	643.3	775.0	837.2
150°	476.1	527.8	639.8	751.2	798.9
152.5°	492.3	537.0	635.1	731.0	768.7
155°	506.3	544.6	629.3	711.2	742.0
157.5°	519.0	552.1	623.5	692.6	717.6
160°	531.8	557.9	617.7	674.0	693.2
162.5°	542.2	563.8	610.8	657.2	671.1
165°	552.7	567.8	603.8	640.4	650.2
167.5°	559.7	570.1	596.8	624.7	630.5
170°	566.6	573.0	591.0	609.6	613.1
172.5°	571.3	574.2	584.0	597.4	596.8
175°	574.8	574.8	579.4	586.4	584.0
177.5°	577.1	574.8	575.9	579.4	575.9
180°	575.9	575.9	575.9	575.9	575.9

(END OF REPORT)