

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028262

Luminaire Tested: S125DIP-B850D1270UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028262
REPORT IS A COMBINATION OF REPORTS P1002519 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D1270UB35-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7635.0 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028262

CATALOG NUMBER: S125DIP-B850D1270UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028262

CATALOG NUMBER: S125DIP-B850D1270UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	45	44
2	88	81	74	69	80	74	69	64	62	58	55	51	48	45	40	38	37
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16
9	49	37	30	25	45	35	28	23	29	24	20	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8493	8493	8493
5°	8493	8295	8311
10°	8423	8105	8080
15°	8313	7878	7807
20°	8163	7614	7494
25°	8002	7327	7160
30°	7809	7027	6807
35°	7602	6713	6412
40°	7388	6380	6060
45°	7157	6057	5687
50°	6902	5690	5252
55°	6650	5285	4852
60°	6350	4858	4386
65°	5990	4364	3905
70°	5625	3796	3349
75°	5011	3125	2708
80°	4269	2334	1992
85°	3299	1380	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7157 cd/sqm

TEST NUMBER: P1028262

CATALOG NUMBER: S125DIP-B850D1270UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	1.6
10°-20°	353.3	4.6
20°-30°	521.6	6.8
30°-40°	608.6	8.0
40°-50°	611.2	8.0
50°-60°	536.5	7.0
60°-70°	399.6	5.2
70°-80°	228.2	3.0
80°-90°	68.2	0.9
90°-100°	99.7	1.3
100°-110°	296.1	3.9
110°-120°	502.1	6.6
120°-130°	661.0	8.7
130°-140°	740.7	9.7
140°-150°	726.0	9.5
150°-160°	609.8	8.0
160°-170°	405.4	5.3
170°-180°	141.9	1.9
0°-30°	1000.0	13.1
0°-40°	1608.5	21.1
0°-60°	2756.3	36.1
0°-90°	3452.4	45.2
90°-120°	897.8	11.8
90°-150°	3025.6	39.6
90°-180°	4183.0	54.8
0°-180°	7635.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1323	1321	1311	1320	1319	126
15°	1262	1258	1247	1252	1252	356
25°	1145	1140	1126	1128	1125	527
35°	989	985	970	965	956	619
45°	810	805	793	780	777	624
55°	617	614	599	589	582	550
65°	416	414	403	393	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	63
90°	1	10	19	24	28	9
95°	76	78	90	98	100	79
105°	266	272	279	286	289	284
115°	503	507	510	508	507	497
125°	734	741	742	739	738	657
135°	954	961	962	962	958	735
145°	1156	1160	1164	1164	1160	723
155°	1323	1323	1324	1328	1323	609
165°	1438	1436	1437	1442	1434	406
175°	1495	1490	1490	1498	1489	142
180°	1499	1499	1499	1499	1499	

TEST NUMBER: P1028262

CATALOG NUMBER: S125DIP-B850D1270UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1325.5	1325.5	1325.5	1325.5	1325.5
2.5°	1329.7	1326.6	1316.1	1326.6	1325.5
5°	1323.4	1321.3	1310.8	1320.3	1319.2
7.5°	1314.0	1311.9	1300.4	1309.8	1308.7
10°	1300.4	1298.3	1286.7	1295.1	1294.1
12.5°	1283.6	1279.4	1268.9	1275.2	1275.2
15°	1261.6	1258.4	1246.9	1252.1	1252.1
17.5°	1238.5	1233.2	1221.7	1228.0	1222.7
20°	1208.1	1206.0	1192.3	1199.7	1194.4
22.5°	1177.7	1173.5	1160.9	1165.1	1161.9
25°	1145.1	1139.9	1126.3	1128.4	1125.2
27.5°	1107.4	1104.2	1090.6	1091.7	1088.5
30°	1070.7	1067.5	1051.8	1049.7	1046.6
32.5°	1030.8	1025.6	1012.0	1007.8	1001.5
35°	988.9	984.7	970.0	964.8	956.4
37.5°	945.9	940.7	927.0	919.7	914.4
40°	901.9	896.6	881.9	872.5	869.3
42.5°	854.7	850.5	835.8	827.4	822.2
45°	809.6	805.4	792.8	780.2	777.1
47.5°	760.3	761.3	745.6	733.0	725.7
50°	713.1	709.9	697.4	683.7	676.4
52.5°	664.9	662.8	649.1	637.6	629.2
55°	616.6	613.5	598.8	589.4	582.0
57.5°	565.2	564.2	551.6	539.0	535.9
60°	517.0	512.8	501.3	490.8	483.4
62.5°	466.7	463.5	454.1	442.5	437.3
65°	416.3	414.2	402.7	393.3	389.1
67.5°	367.0	362.8	354.5	346.1	344.0
70°	320.9	315.6	306.2	299.9	295.7
72.5°	270.6	267.4	262.2	254.8	250.6
75°	221.3	219.2	213.9	210.8	206.6
77.5°	175.1	174.1	170.9	168.8	165.7
80°	132.1	132.1	130.0	129.0	126.9
82.5°	94.4	92.3	92.3	90.2	90.2
85°	57.7	58.7	58.7	57.7	55.6
87.5°	28.3	28.3	27.3	27.3	25.2
90°	1.2	10.5	18.7	24.5	28.0
92.5°	35.0	40.8	51.3	59.5	61.8
95°	75.8	78.1	89.8	98.0	100.3
97.5°	116.6	117.8	134.1	141.1	142.3
100°	163.3	163.3	178.4	188.9	191.3
102.5°	213.4	219.3	225.1	236.8	240.3
105°	265.9	271.7	278.7	285.7	289.2
107.5°	323.1	328.9	334.7	338.2	338.2
110°	382.5	388.4	391.9	395.4	394.2

TEST NUMBER: P1028262

CATALOG NUMBER: S125DIP-B850D1270UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.2	445.5	450.2	451.4	449.0
115°	502.7	507.3	509.7	508.5	507.3
117.5°	563.3	564.5	566.8	568.0	563.3
120°	619.3	625.1	626.3	626.3	621.6
122.5°	679.9	681.1	684.6	683.4	679.9
125°	733.6	740.6	741.8	739.4	738.3
127.5°	793.1	796.6	797.7	796.6	794.2
130°	845.6	851.4	853.7	852.6	850.2
132.5°	898.0	908.5	907.4	906.2	902.7
135°	954.0	961.0	962.2	962.2	957.5
137.5°	1006.5	1013.5	1015.8	1017.0	1011.2
140°	1056.6	1062.5	1066.0	1068.3	1062.5
142.5°	1106.8	1111.5	1116.1	1117.3	1111.5
145°	1155.8	1160.4	1163.9	1163.9	1160.4
147.5°	1201.3	1204.8	1207.1	1210.6	1201.3
150°	1246.8	1245.6	1250.3	1250.3	1247.9
152.5°	1284.1	1286.4	1287.6	1291.1	1286.4
155°	1322.6	1322.6	1323.7	1328.4	1322.6
157.5°	1357.6	1355.2	1356.4	1361.0	1352.9
160°	1387.9	1384.4	1385.5	1390.2	1384.4
162.5°	1414.7	1412.4	1412.4	1418.2	1411.2
165°	1438.0	1435.7	1436.9	1441.5	1434.5
167.5°	1459.0	1454.4	1454.4	1461.3	1454.4
170°	1475.3	1470.7	1470.7	1477.7	1469.5
172.5°	1487.0	1482.3	1482.3	1489.3	1482.3
175°	1495.2	1490.5	1490.5	1497.5	1489.3
177.5°	1501.0	1496.3	1495.2	1502.2	1494.0
180°	1498.7	1498.7	1498.7	1498.7	1498.7

(END OF REPORT)