

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028521

Luminaire Tested: S125RDIP-B1090D610UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028521
REPORT IS A COMBINATION OF REPORTS P1005066 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D610UB35-4F0-XX-W2A-F4
Description: Define 5 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6360.4 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028521

CATALOG NUMBER: S125RDIP-B1090D610UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1028521

CATALOG NUMBER: S125RDIP-B1090D610UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71
1	102	97	94	90	96	92	89	85	82	79	77	72	70	68	63	62	61
2	93	85	79	74	87	81	75	71	72	68	64	64	60	58	56	54	52
3	85	75	68	62	80	71	65	59	64	58	54	57	52	49	50	47	44
4	78	67	59	53	73	63	56	51	57	51	46	51	46	42	45	41	38
5	72	60	52	46	67	57	49	44	51	45	40	46	41	37	40	37	34
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	37	33	30
7	61	49	41	35	58	46	39	34	42	36	31	38	33	29	34	30	26
8	57	44	37	31	54	42	35	30	38	32	28	35	30	26	31	27	24
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22
10	50	38	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11433	11433	11433
5°	11434	11148	11166
10°	11323	10867	10771
15°	11162	10474	10253
20°	10964	10001	9708
25°	10737	9539	9125
30°	10458	9031	8512
35°	10174	8515	7861
40°	9903	7985	7225
45°	9579	7414	6560
50°	9250	6807	5881
55°	8867	6209	5179
60°	8476	5525	4451
65°	8009	4762	3665
70°	7466	3876	2884
75°	6714	2915	2102
80°	5662	1887	1418
85°	4237	1013	798

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9579 cd/sqm

TEST NUMBER: P1028521

CATALOG NUMBER: S125RDIP-B1090D610UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.9	2.6
10°-20°	469.3	7.4
20°-30°	680.5	10.7
30°-40°	775.3	12.2
40°-50°	755.7	11.9
50°-60°	636.0	10.0
60°-70°	445.7	7.0
70°-80°	228.5	3.6
80°-90°	58.1	0.9
90°-100°	214.4	3.4
100°-110°	445.4	7.0
110°-120°	416.0	6.5
120°-130°	336.7	5.3
130°-140°	270.5	4.3
140°-150°	204.2	3.2
150°-160°	143.7	2.3
160°-170°	84.7	1.3
170°-180°	27.5	0.4
0°-30°	1317.8	20.7
0°-40°	2093.2	32.9
0°-60°	3484.9	54.8
0°-90°	4217.1	66.3
90°-120°	1075.9	16.9
90°-150°	1887.2	29.7
90°-180°	2143.0	33.7
0°-180°	6360.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1784	1784	1784	1784	1784	
5°	1782	1776	1762	1775	1772	169
15°	1694	1686	1658	1656	1644	478
25°	1536	1516	1466	1449	1434	707
35°	1324	1291	1230	1191	1173	829
45°	1084	1044	970	916	896	836
55°	822	779	704	643	621	735
65°	557	511	439	386	365	551
75°	296	256	200	170	160	313
85°	74	50	43	42	40	81
90°	1	5	9	12	13	6
95°	19	56	509	231	135	20
105°	65	91	416	820	761	68
115°	116	140	334	720	847	114
125°	161	188	320	573	668	143
135°	188	226	318	480	555	146
145°	219	251	319	398	438	137
155°	250	269	311	352	367	115
165°	273	281	298	317	322	77
175°	284	284	286	290	289	27
180°	285	285	285	285	285	

TEST NUMBER: P1028521

CATALOG NUMBER: S125RDIP-B1090D610UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1784.4	1784.4	1784.4	1784.4	1784.4
2.5°	1788.5	1784.4	1771.0	1784.4	1783.1
5°	1781.7	1776.4	1761.5	1775.0	1772.3
7.5°	1768.3	1762.9	1745.4	1756.1	1753.4
10°	1748.1	1744.0	1725.1	1729.2	1725.1
12.5°	1725.1	1719.7	1692.8	1695.5	1688.8
15°	1694.1	1686.1	1657.8	1656.4	1644.3
17.5°	1661.8	1649.7	1616.0	1609.2	1599.8
20°	1622.7	1609.2	1566.1	1559.4	1547.2
22.5°	1579.6	1566.1	1520.3	1505.5	1496.0
25°	1536.5	1516.2	1466.4	1448.8	1434.0
27.5°	1487.9	1463.7	1411.1	1388.2	1373.4
30°	1434.0	1408.4	1351.8	1320.8	1308.7
32.5°	1381.5	1350.5	1292.5	1257.5	1241.3
35°	1323.5	1291.2	1230.5	1191.4	1172.6
37.5°	1268.2	1229.2	1167.2	1121.3	1102.5
40°	1208.9	1168.5	1103.8	1052.6	1036.4
42.5°	1146.9	1105.2	1037.8	989.3	963.7
45°	1083.6	1044.5	970.4	916.5	896.3
47.5°	1017.6	977.1	903.0	847.7	824.8
50°	955.6	911.1	834.3	777.7	757.4
52.5°	888.2	842.4	770.9	708.9	688.7
55°	822.1	779.0	703.5	642.9	621.3
57.5°	754.7	708.9	636.1	576.8	558.0
60°	690.1	642.9	570.1	510.8	490.6
62.5°	621.3	576.8	502.7	448.8	428.6
65°	556.6	510.8	439.4	385.5	365.2
67.5°	491.9	446.1	377.4	326.2	310.0
70°	425.9	380.1	312.7	270.9	254.7
72.5°	361.2	316.7	254.7	217.0	207.6
75°	296.5	256.1	199.5	169.8	160.4
77.5°	230.5	198.1	150.9	128.0	120.0
80°	175.2	142.9	105.1	93.0	90.3
82.5°	121.3	93.0	70.1	66.0	64.7
85°	74.1	49.9	43.1	41.8	40.4
87.5°	31.0	21.6	20.2	20.2	18.9
90°	0.6	5.2	9.2	12.0	13.2
92.5°	8.6	47.0	229.1	61.2	42.5
95°	18.9	56.0	508.7	230.8	134.9
97.5°	29.3	60.6	549.4	416.8	295.7
100°	40.2	69.5	518.4	589.0	447.8
102.5°	52.2	79.5	463.9	734.9	617.8
105°	64.9	90.7	416.2	819.6	760.7
107.5°	76.9	102.5	380.6	843.4	846.8
110°	90.1	114.8	357.1	820.7	885.9



TEST NUMBER: P1028521

CATALOG NUMBER: S125RDIP-B1090D610UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	103.3	127.2	343.3	773.4	881.3
115°	116.0	139.8	334.1	720.2	847.4
117.5°	127.5	152.7	329.0	672.0	796.3
120°	138.9	165.0	325.5	631.6	746.9
122.5°	151.0	177.1	322.7	599.1	703.3
125°	160.8	188.3	320.4	573.0	667.7
127.5°	168.8	199.2	319.2	550.6	635.0
130°	176.3	209.6	318.1	527.9	609.1
132.5°	182.0	218.8	318.1	503.5	583.3
135°	188.3	226.4	318.1	480.2	554.6
137.5°	196.4	233.6	318.6	455.8	524.7
140°	203.2	239.6	319.2	433.4	493.2
142.5°	211.3	245.4	319.8	414.2	463.9
145°	219.3	251.2	319.2	397.6	437.5
147.5°	227.9	256.4	318.1	383.2	413.9
150°	235.4	261.0	316.3	371.5	395.0
152.5°	243.4	265.5	314.0	361.4	380.1
155°	250.3	269.2	311.2	351.6	366.9
157.5°	256.6	273.0	308.3	342.4	354.8
160°	262.9	275.9	305.4	333.3	342.8
162.5°	268.1	278.7	302.0	325.0	331.8
165°	273.3	280.8	298.5	316.6	321.5
167.5°	276.7	281.8	295.1	308.8	311.7
170°	280.2	283.4	292.2	301.4	303.1
172.5°	282.5	283.9	288.8	295.4	295.1
175°	284.2	284.2	286.5	289.9	288.8
177.5°	285.3	284.2	284.8	286.5	284.8
180°	284.8	284.8	284.8	284.8	284.8

(END OF REPORT)