

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028280

Luminaire Tested: S125DIP-B850D1270UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028280
REPORT IS A COMBINATION OF REPORTS P1002537 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D1270UB50-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7310.0 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028280

CATALOG NUMBER: S125DIP-B850D1270UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028280

CATALOG NUMBER: S125DIP-B850D1270UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	45	44
2	88	81	74	69	80	74	69	64	62	58	55	51	48	45	40	38	37
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16
9	49	37	30	25	45	35	28	23	29	24	20	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8131	8131	8131
5°	8131	7942	7957
10°	8064	7760	7735
15°	7958	7542	7475
20°	7815	7289	7175
25°	7662	7014	6855
30°	7476	6727	6517
35°	7278	6427	6138
40°	7073	6109	5802
45°	6852	5799	5445
50°	6608	5448	5028
55°	6367	5060	4645
60°	6080	4651	4199
65°	5735	4178	3738
70°	5385	3635	3206
75°	4796	2992	2593
80°	4088	2235	1907
85°	3156	1321	1051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6852 cd/sqm

TEST NUMBER: P1028280

CATALOG NUMBER: S125DIP-B850D1270UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.7	1.6
10°-20°	338.2	4.6
20°-30°	499.4	6.8
30°-40°	582.6	8.0
40°-50°	585.2	8.0
50°-60°	513.6	7.0
60°-70°	382.6	5.2
70°-80°	218.5	3.0
80°-90°	65.3	0.9
90°-100°	95.4	1.3
100°-110°	283.5	3.9
110°-120°	480.8	6.6
120°-130°	632.9	8.7
130°-140°	709.2	9.7
140°-150°	695.1	9.5
150°-160°	583.9	8.0
160°-170°	388.1	5.3
170°-180°	135.8	1.9
0°-30°	957.4	13.1
0°-40°	1540.0	21.1
0°-60°	2638.8	36.1
0°-90°	3305.2	45.2
90°-120°	859.7	11.8
90°-150°	2896.9	39.6
90°-180°	4005.0	54.8
0°-180°	7310.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1267	1265	1255	1264	1263	120
15°	1208	1205	1194	1199	1199	341
25°	1096	1091	1078	1080	1077	504
35°	947	943	929	924	916	592
45°	775	771	759	747	744	597
55°	590	587	573	564	557	527
65°	399	397	386	376	372	395
75°	212	210	205	202	198	226
85°	55	56	56	55	53	60
90°	1	10	18	24	27	9
95°	73	75	86	94	96	76
105°	255	260	267	274	277	271
115°	481	486	488	487	486	476
125°	702	709	710	708	707	629
135°	913	920	921	921	917	704
145°	1107	1111	1114	1114	1111	692
155°	1266	1266	1267	1272	1266	583
165°	1377	1375	1376	1380	1374	388
175°	1432	1427	1427	1434	1426	136
180°	1435	1435	1435	1435	1435	

TEST NUMBER: P1028280

CATALOG NUMBER: S125DIP-B850D1270UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1269.0	1269.0	1269.0	1269.0	1269.0
2.5°	1273.1	1270.0	1260.0	1270.0	1269.0
5°	1267.0	1265.0	1255.0	1264.0	1263.0
7.5°	1258.0	1256.0	1244.9	1254.0	1253.0
10°	1244.9	1242.9	1231.9	1239.9	1238.9
12.5°	1228.9	1224.9	1214.8	1220.8	1220.8
15°	1207.8	1204.8	1193.7	1198.8	1198.8
17.5°	1185.7	1180.7	1169.6	1175.7	1170.6
20°	1156.6	1154.6	1141.5	1148.6	1143.5
22.5°	1127.5	1123.5	1111.4	1115.4	1112.4
25°	1096.4	1091.3	1078.3	1080.3	1077.3
27.5°	1060.2	1057.2	1044.1	1045.2	1042.1
30°	1025.1	1022.1	1007.0	1005.0	1002.0
32.5°	986.9	981.9	968.8	964.8	958.8
35°	946.8	942.7	928.7	923.7	915.6
37.5°	905.6	900.6	887.5	880.5	875.5
40°	863.4	858.4	844.4	835.3	832.3
42.5°	818.2	814.2	800.2	792.1	787.1
45°	775.1	771.1	759.0	747.0	744.0
47.5°	727.9	728.9	713.8	701.8	694.8
50°	682.7	679.7	667.7	654.6	647.6
52.5°	636.5	634.5	621.5	610.4	602.4
55°	590.3	587.3	573.3	564.2	557.2
57.5°	541.1	540.1	528.1	516.0	513.0
60°	495.0	490.9	479.9	469.9	462.8
62.5°	446.8	443.8	434.7	423.7	418.7
65°	398.6	396.6	385.5	376.5	372.5
67.5°	351.4	347.4	339.3	331.3	329.3
70°	307.2	302.2	293.2	287.1	283.1
72.5°	259.0	256.0	251.0	244.0	240.0
75°	211.8	209.8	204.8	201.8	197.8
77.5°	167.7	166.7	163.6	161.6	158.6
80°	126.5	126.5	124.5	123.5	121.5
82.5°	90.4	88.4	88.4	86.3	86.3
85°	55.2	56.2	56.2	55.2	53.2
87.5°	27.1	27.1	26.1	26.1	24.1
90°	1.1	10.1	17.9	23.5	26.8
92.5°	33.5	39.1	49.1	57.0	59.2
95°	72.6	74.8	86.0	93.8	96.0
97.5°	111.7	112.8	128.4	135.1	136.2
100°	156.3	156.3	170.9	180.9	183.1
102.5°	204.4	209.9	215.5	226.7	230.0
105°	254.6	260.2	266.9	273.6	276.9
107.5°	309.3	314.9	320.5	323.8	323.8
110°	366.3	371.9	375.2	378.6	377.4

TEST NUMBER: P1028280

CATALOG NUMBER: S125DIP-B850D1270UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	424.3	426.6	431.0	432.2	429.9
115°	481.3	485.8	488.0	486.9	485.8
117.5°	539.4	540.5	542.7	543.8	539.4
120°	593.0	598.5	599.7	599.7	595.2
122.5°	651.0	652.1	655.5	654.4	651.0
125°	702.4	709.1	710.2	708.0	706.9
127.5°	759.3	762.7	763.8	762.7	760.5
130°	809.6	815.2	817.4	816.3	814.1
132.5°	859.8	869.9	868.8	867.7	864.3
135°	913.4	920.1	921.3	921.3	916.8
137.5°	963.7	970.4	972.6	973.7	968.2
140°	1011.7	1017.3	1020.6	1022.9	1017.3
142.5°	1059.7	1064.2	1068.7	1069.8	1064.2
145°	1106.6	1111.1	1114.4	1114.4	1111.1
147.5°	1150.2	1153.5	1155.8	1159.1	1150.2
150°	1193.7	1192.6	1197.1	1197.1	1194.8
152.5°	1229.5	1231.7	1232.8	1236.2	1231.7
155°	1266.3	1266.3	1267.4	1271.9	1266.3
157.5°	1299.8	1297.6	1298.7	1303.2	1295.3
160°	1328.8	1325.5	1326.6	1331.1	1325.5
162.5°	1354.5	1352.3	1352.3	1357.9	1351.2
165°	1376.9	1374.6	1375.7	1380.2	1373.5
167.5°	1397.0	1392.5	1392.5	1399.2	1392.5
170°	1412.6	1408.1	1408.1	1414.8	1407.0
172.5°	1423.8	1419.3	1419.3	1426.0	1419.3
175°	1431.6	1427.1	1427.1	1433.8	1426.0
177.5°	1437.2	1432.7	1431.6	1438.3	1430.5
180°	1434.9	1434.9	1434.9	1434.9	1434.9

(END OF REPORT)