

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028538

Luminaire Tested: S125RDIP-B1090D850UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028538
REPORT IS A COMBINATION OF REPORTS P1005083 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D850UB27-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6879.0 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028538

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028538

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	59	57	56
2	92	84	78	73	85	79	74	69	69	65	62	60	57	54	52	50	48
3	84	74	67	61	78	70	63	58	61	56	52	53	50	46	46	43	41
4	77	66	58	52	72	62	55	49	55	49	45	48	43	40	41	38	35
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	34	31
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	27	24
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11287	11287	11287
5°	11288	11005	11023
10°	11178	10728	10633
15°	11019	10340	10121
20°	10824	9873	9584
25°	10599	9417	9008
30°	10325	8915	8403
35°	10044	8406	7760
40°	9777	7883	7133
45°	9456	7319	6475
50°	9130	6720	5806
55°	8753	6129	5113
60°	8367	5454	4394
65°	7907	4700	3619
70°	7369	3827	2848
75°	6627	2877	2075
80°	5591	1864	1399
85°	4185	1002	788

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9456 cd/sqm

TEST NUMBER: P1028538

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.8	2.4
10°-20°	463.3	6.7
20°-30°	671.8	9.8
30°-40°	765.4	11.1
40°-50°	746.0	10.8
50°-60°	627.8	9.1
60°-70°	440.0	6.4
70°-80°	225.6	3.3
80°-90°	57.8	0.8
90°-100°	64.7	0.9
100°-110°	192.2	2.8
110°-120°	326.0	4.7
120°-130°	429.1	6.2
130°-140°	480.9	7.0
140°-150°	471.4	6.9
150°-160°	395.9	5.8
160°-170°	263.2	3.8
170°-180°	92.1	1.3
0°-30°	1300.9	18.9
0°-40°	2066.3	30.0
0°-60°	3440.2	50.0
0°-90°	4163.5	60.5
90°-120°	582.9	8.5
90°-150°	1964.3	28.6
90°-180°	2715.0	39.5
0°-180°	6879.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1762	1762	1762	1762	1762	
5°	1759	1754	1739	1752	1750	167
15°	1672	1664	1636	1635	1623	472
25°	1517	1497	1448	1430	1416	698
35°	1307	1275	1215	1176	1158	818
45°	1070	1031	958	905	885	825
55°	812	769	694	635	613	726
65°	550	504	434	380	361	544
75°	293	253	197	168	158	309
85°	73	49	43	41	40	80
90°	1	7	12	16	18	8
95°	49	51	58	64	65	51
105°	173	176	181	186	188	184
115°	326	329	331	330	329	323
125°	476	481	482	480	479	427
135°	619	624	625	625	622	477
145°	750	753	756	756	753	469
155°	859	859	859	862	859	396
165°	934	932	933	936	931	263
175°	971	968	968	972	967	92
180°	973	973	973	973	973	

TEST NUMBER: P1028538

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1761.6	1761.6	1761.6	1761.6	1761.6
2.5°	1765.6	1761.6	1748.3	1761.6	1760.3
5°	1758.9	1753.6	1739.0	1752.3	1749.6
7.5°	1745.6	1740.3	1723.0	1733.6	1731.0
10°	1725.7	1721.7	1703.0	1707.0	1703.0
12.5°	1703.0	1697.7	1671.1	1673.8	1667.1
15°	1672.4	1664.5	1636.5	1635.2	1623.2
17.5°	1640.5	1628.5	1595.3	1588.6	1579.3
20°	1601.9	1588.6	1546.0	1539.4	1527.4
22.5°	1559.3	1546.0	1500.8	1486.2	1476.9
25°	1516.8	1496.8	1447.6	1430.3	1415.7
27.5°	1468.9	1444.9	1393.0	1370.4	1355.8
30°	1415.7	1390.4	1334.5	1303.9	1291.9
32.5°	1363.8	1333.2	1276.0	1241.4	1225.4
35°	1306.6	1274.6	1214.7	1176.2	1157.5
37.5°	1252.0	1213.4	1152.2	1107.0	1088.4
40°	1193.5	1153.5	1089.7	1039.1	1023.2
42.5°	1132.3	1091.0	1024.5	976.6	951.3
45°	1069.7	1031.1	958.0	904.7	884.8
47.5°	1004.5	964.6	891.4	836.9	814.3
50°	943.3	899.4	823.6	767.7	747.7
52.5°	876.8	831.6	761.0	699.8	679.9
55°	811.6	769.0	694.5	634.6	613.4
57.5°	745.1	699.8	628.0	569.5	550.8
60°	681.2	634.6	562.8	504.3	484.3
62.5°	613.4	569.5	496.3	443.1	423.1
65°	549.5	504.3	433.7	380.5	360.6
67.5°	485.6	440.4	372.5	322.0	306.0
70°	420.4	375.2	308.7	267.4	251.5
72.5°	356.6	312.7	251.5	214.2	204.9
75°	292.7	252.8	196.9	167.6	158.3
77.5°	227.5	195.6	149.0	126.4	118.4
80°	173.0	141.0	103.8	91.8	89.1
82.5°	119.7	91.8	69.2	65.2	63.9
85°	73.2	49.2	42.6	41.2	39.9
87.5°	30.6	21.3	20.0	20.0	18.6
90°	0.8	6.8	12.1	15.9	18.2
92.5°	22.7	26.5	33.3	38.6	40.1
95°	49.2	50.7	58.3	63.6	65.1
97.5°	75.7	76.5	87.1	91.6	92.4
100°	106.0	106.0	115.8	122.7	124.2
102.5°	138.6	142.3	146.1	153.7	156.0
105°	172.6	176.4	181.0	185.5	187.8
107.5°	209.7	213.5	217.3	219.6	219.6
110°	248.4	252.1	254.4	256.7	255.9

TEST NUMBER: P1028538

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	287.7	289.2	292.3	293.0	291.5
115°	326.3	329.4	330.9	330.1	329.4
117.5°	365.7	366.5	368.0	368.7	365.7
120°	402.1	405.8	406.6	406.6	403.6
122.5°	441.4	442.2	444.5	443.7	441.4
125°	476.3	480.8	481.6	480.0	479.3
127.5°	514.9	517.2	517.9	517.2	515.6
130°	549.0	552.7	554.3	553.5	552.0
132.5°	583.0	589.8	589.1	588.3	586.1
135°	619.4	623.9	624.7	624.7	621.6
137.5°	653.4	658.0	659.5	660.3	656.5
140°	686.0	689.8	692.1	693.6	689.8
142.5°	718.6	721.6	724.6	725.4	721.6
145°	750.4	753.4	755.7	755.7	753.4
147.5°	779.9	782.2	783.7	785.9	779.9
150°	809.4	808.7	811.7	811.7	810.2
152.5°	833.7	835.2	835.9	838.2	835.2
155°	858.6	858.6	859.4	862.4	858.6
157.5°	881.4	879.8	880.6	883.6	878.3
160°	901.0	898.8	899.5	902.6	898.8
162.5°	918.5	916.9	916.9	920.7	916.2
165°	933.6	932.1	932.8	935.9	931.3
167.5°	947.2	944.2	944.2	948.7	944.2
170°	957.8	954.8	954.8	959.3	954.0
172.5°	965.4	962.4	962.4	966.9	962.4
175°	970.7	967.7	967.7	972.2	966.9
177.5°	974.5	971.5	970.7	975.2	969.9
180°	973.0	973.0	973.0	973.0	973.0

(END OF REPORT)