

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028289

Luminaire Tested: S125DIP-B850D375UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028289
REPORT IS A COMBINATION OF REPORTS P1002546 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D375UB27-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4670.0 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028289

CATALOG NUMBER: S125DIP-B850D375UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028289

CATALOG NUMBER: S125DIP-B850D375UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	93	90	87	84	82	79	76	74	72	68	67	65
2	94	86	79	74	89	82	76	71	74	69	65	67	63	60	60	57	55
3	85	76	68	62	81	72	65	59	65	60	55	59	54	51	53	50	47
4	78	67	59	52	74	64	56	50	58	52	47	53	48	43	47	43	40
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	38	35
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31
7	61	49	40	35	58	47	39	33	43	36	31	39	33	29	35	31	27
8	57	44	36	31	54	42	35	30	39	33	28	36	30	26	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	22	28	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8382	8382	8382
5°	8383	8187	8203
10°	8313	7999	7975
15°	8204	7775	7706
20°	8056	7515	7397
25°	7898	7231	7066
30°	7707	6935	6718
35°	7503	6625	6328
40°	7292	6297	5981
45°	7063	5978	5613
50°	6812	5616	5184
55°	6564	5216	4788
60°	6268	4794	4329
65°	5912	4307	3854
70°	5551	3746	3306
75°	4945	3084	2673
80°	4214	2304	1965
85°	3253	1364	1084

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7063 cd/sqm

TEST NUMBER: P1028289

CATALOG NUMBER: S125DIP-B850D375UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.4	2.6
10°-20°	348.7	7.5
20°-30°	514.8	11.0
30°-40°	600.6	12.9
40°-50°	603.2	12.9
50°-60°	529.5	11.3
60°-70°	394.4	8.4
70°-80°	225.2	4.8
80°-90°	65.7	1.4
90°-100°	30.1	0.6
100°-110°	89.5	1.9
110°-120°	151.8	3.3
120°-130°	199.8	4.3
130°-140°	223.9	4.8
140°-150°	219.5	4.7
150°-160°	184.3	3.9
160°-170°	122.5	2.6
170°-180°	42.9	0.9
0°-30°	986.9	21.1
0°-40°	1587.5	34.0
0°-60°	2720.3	58.3
0°-90°	3405.7	72.9
90°-120°	271.4	5.8
90°-150°	914.6	19.6
90°-180°	1264.0	27.1
0°-180°	4670.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1308	1308	1308	1308	1308	
5°	1306	1304	1294	1303	1302	124
15°	1245	1242	1231	1236	1236	351
25°	1130	1125	1112	1114	1110	520
35°	976	972	957	952	944	611
45°	799	795	782	770	767	616
55°	609	606	591	582	574	543
65°	411	409	397	388	384	408
75°	218	216	211	208	204	232
85°	57	58	58	57	55	62
90°	0	3	6	7	8	5
95°	23	24	27	30	30	24
105°	80	82	84	86	87	86
115°	152	153	154	154	153	150
125°	222	224	224	224	223	199
135°	288	290	291	291	289	222
145°	349	351	352	352	351	218
155°	400	400	400	402	400	184
165°	435	434	434	436	434	123
175°	452	450	450	453	450	43
180°	453	453	453	453	453	

TEST NUMBER: P1028289

CATALOG NUMBER: S125DIP-B850D375UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1308.2	1308.2	1308.2	1308.2	1308.2
2.5°	1312.4	1309.3	1298.9	1309.3	1308.2
5°	1306.2	1304.1	1293.7	1303.1	1302.0
7.5°	1296.8	1294.8	1283.4	1292.7	1291.7
10°	1283.4	1281.3	1269.9	1278.2	1277.2
12.5°	1266.8	1262.7	1252.3	1258.6	1258.6
15°	1245.1	1242.0	1230.6	1235.8	1235.8
17.5°	1222.3	1217.2	1205.8	1212.0	1206.8
20°	1192.3	1190.2	1176.8	1184.0	1178.9
22.5°	1162.3	1158.2	1145.7	1149.9	1146.8
25°	1130.2	1125.0	1111.6	1113.7	1110.5
27.5°	1093.0	1089.8	1076.4	1077.4	1074.3
30°	1056.7	1053.6	1038.1	1036.0	1032.9
32.5°	1017.4	1012.2	998.8	994.6	988.4
35°	976.0	971.9	957.4	952.2	943.9
37.5°	933.6	928.4	914.9	907.7	902.5
40°	890.1	884.9	870.4	861.1	858.0
42.5°	843.5	839.4	824.9	816.6	811.4
45°	799.0	794.9	782.5	770.0	766.9
47.5°	750.4	751.4	735.9	723.5	716.2
50°	703.8	700.7	688.3	674.8	667.6
52.5°	656.2	654.1	640.7	629.3	621.0
55°	608.6	605.5	591.0	581.7	574.4
57.5°	557.9	556.8	544.4	532.0	528.9
60°	510.3	506.1	494.7	484.4	477.1
62.5°	460.6	457.5	448.2	436.8	431.6
65°	410.9	408.8	397.4	388.1	384.0
67.5°	362.2	358.1	349.8	341.5	339.5
70°	316.7	311.5	302.2	296.0	291.9
72.5°	267.0	263.9	258.7	251.5	247.4
75°	218.4	216.3	211.1	208.0	203.9
77.5°	172.8	171.8	168.7	166.6	163.5
80°	130.4	130.4	128.3	127.3	125.2
82.5°	93.1	91.1	91.1	89.0	89.0
85°	56.9	58.0	58.0	56.9	54.9
87.5°	27.9	27.9	26.9	26.9	24.8
90°	0.4	3.2	5.6	7.4	8.5
92.5°	10.6	12.3	15.5	18.0	18.7
95°	22.9	23.6	27.1	29.6	30.3
97.5°	35.3	35.6	40.5	42.7	43.0
100°	49.4	49.4	53.9	57.1	57.8
102.5°	64.5	66.3	68.0	71.6	72.6
105°	80.4	82.1	84.3	86.4	87.4
107.5°	97.7	99.4	101.2	102.2	102.2
110°	115.6	117.4	118.5	119.5	119.2

TEST NUMBER: P1028289

CATALOG NUMBER: S125DIP-B850D375UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	134.0	134.7	136.1	136.4	135.7
115°	151.9	153.4	154.1	153.7	153.4
117.5°	170.3	170.6	171.3	171.7	170.3
120°	187.2	189.0	189.3	189.3	187.9
122.5°	205.5	205.9	206.9	206.6	205.5
125°	221.7	223.9	224.2	223.5	223.2
127.5°	239.7	240.8	241.1	240.8	240.1
130°	255.6	257.3	258.1	257.7	257.0
132.5°	271.4	274.6	274.3	273.9	272.9
135°	288.4	290.5	290.8	290.8	289.4
137.5°	304.2	306.3	307.1	307.4	305.6
140°	319.4	321.2	322.2	322.9	321.2
142.5°	334.6	336.0	337.4	337.7	336.0
145°	349.4	350.8	351.8	351.8	350.8
147.5°	363.1	364.2	364.9	365.9	363.1
150°	376.9	376.5	377.9	377.9	377.2
152.5°	388.1	388.8	389.2	390.3	388.8
155°	399.8	399.8	400.1	401.5	399.8
157.5°	410.3	409.6	410.0	411.4	408.9
160°	419.5	418.5	418.8	420.2	418.5
162.5°	427.6	426.9	426.9	428.7	426.6
165°	434.7	434.0	434.3	435.7	433.6
167.5°	441.0	439.6	439.6	441.7	439.6
170°	446.0	444.5	444.5	446.7	444.2
172.5°	449.5	448.1	448.1	450.2	448.1
175°	451.9	450.5	450.5	452.7	450.2
177.5°	453.7	452.3	451.9	454.1	451.6
180°	453.0	453.0	453.0	453.0	453.0

(END OF REPORT)