

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028293

Luminaire Tested: S125DIP-B850D375UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028293
REPORT IS A COMBINATION OF REPORTS P1002565 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D375UB30-4F0-XX-W2A-A4
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4796.0 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	99	95	91	98	94	90	87	85	82	80	76	74	72	68	67	66
2	94	87	80	75	89	82	77	72	75	70	66	67	64	61	61	58	56
3	86	76	69	63	81	73	66	61	66	61	56	60	55	52	54	51	48
4	79	68	60	54	75	65	57	52	59	53	48	53	49	45	48	44	41
5	73	61	52	46	69	58	50	45	53	47	42	48	43	39	44	39	36
6	67	55	46	40	63	52	45	39	48	41	37	44	38	34	40	35	32
7	62	50	41	36	59	47	40	35	43	37	32	40	34	30	36	32	28
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	29	25
9	54	41	34	28	51	40	32	28	36	30	26	34	28	24	31	26	23
10	50	38	31	26	48	36	30	25	34	28	24	31	26	22	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7881	7881	7881	7881
5°	7887	8940	7894	6782
10°	7839	10191	7825	5822
15°	7782	11049	7733	5261
20°	7683	12107	7613	4803
25°	7596	13873	7458	4531
30°	7470	14636	7341	4286
35°	7272	11732	7120	4088
40°	6963	8109	6860	3879
45°	6573	6037	6498	3706
50°	6125	4970	6023	3567
55°	5642	4239	5598	3447
60°	5168	3628	5079	3353
65°	4658	3133	4583	3218
70°	4118	2601	4063	2980
75°	3546	2012	3498	2586
80°	2802	1361	2698	1901
85°	1790	682	1732	970

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 12038 cd/sqm

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.4	2.5
10°-20°	352.6	7.4
20°-30°	572.8	11.9
30°-40°	700.0	14.6
40°-50°	635.0	13.2
50°-60°	505.8	10.5
60°-70°	352.3	7.3
70°-80°	187.7	3.9
80°-90°	47.2	1.0
90°-100°	128.3	2.7
100°-110°	276.6	5.8
110°-120°	257.8	5.4
120°-130°	208.8	4.4
130°-140°	167.7	3.5
140°-150°	126.5	2.6
150°-160°	89.1	1.9
160°-170°	52.5	1.1
170°-180°	17.1	0.4
0°-30°	1043.8	21.8
0°-40°	1743.8	36.4
0°-60°	2884.6	60.1
0°-90°	3471.7	72.4
90°-120°	662.7	13.8
90°-150°	1165.7	24.3
90°-180°	1324.0	27.6
0°-180°	4796.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1230	1230	1230	1230	1230	
5°	1229	1419	1230	1076	1229	117
15°	1181	1772	1174	844	1181	333
25°	1087	2180	1067	712	1087	501
35°	946	1750	926	610	946	591
45°	744	825	735	506	744	573
55°	523	508	519	414	523	468
65°	324	312	318	321	324	321
75°	157	154	154	197	157	167
85°	31	34	30	49	31	37
90°	0	8	0	8	0	3
95°	12	84	12	84	12	12
105°	40	471	40	471	40	42
115°	72	525	72	525	72	71
125°	100	413	100	413	100	88
135°	117	343	117	343	117	90
145°	136	271	136	271	136	85
155°	155	227	155	227	155	71
165°	169	199	169	199	169	48
175°	176	179	176	179	176	17
180°	176	176	176	176	176	

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0
2.5°	1232.1	1239.4	1247.8	1254.1	1264.5	1267.6	1272.9	1276.0	1279.1	1282.3	1284.3
5°	1229.0	1246.7	1262.4	1273.9	1293.7	1301.0	1310.4	1321.9	1335.5	1347.0	1354.3
7.5°	1220.6	1248.8	1269.7	1292.7	1319.8	1337.6	1347.0	1371.0	1392.9	1409.6	1431.6
10°	1210.2	1243.6	1276.0	1310.4	1349.1	1368.9	1387.7	1421.1	1451.4	1478.6	1500.5
12.5°	1198.7	1239.4	1278.1	1323.0	1375.2	1399.2	1411.7	1469.2	1506.7	1521.4	1564.2
15°	1181.0	1229.0	1284.3	1339.7	1383.5	1411.7	1446.2	1492.1	1529.7	1562.1	1596.5
17.5°	1164.3	1216.5	1272.9	1334.5	1398.2	1434.7	1460.8	1501.5	1542.3	1584.0	1616.4
20°	1137.1	1205.0	1262.4	1328.2	1403.4	1429.5	1456.6	1504.7	1548.5	1593.4	1634.1
22.5°	1115.2	1179.9	1258.2	1320.9	1384.6	1410.7	1444.1	1494.2	1546.4	1597.6	1657.1
25°	1087.0	1159.0	1226.9	1293.7	1359.5	1387.7	1418.0	1482.7	1537.0	1602.8	1668.6
27.5°	1056.7	1130.8	1198.7	1259.3	1320.9	1359.5	1391.9	1459.8	1531.8	1603.9	1689.5
30°	1024.3	1094.3	1159.0	1218.6	1286.4	1326.1	1358.5	1437.8	1518.2	1610.1	1712.5
32.5°	989.9	1055.7	1111.0	1171.6	1243.6	1280.2	1324.0	1410.7	1505.7	1615.3	1743.8
35°	946.0	1008.7	1057.8	1119.4	1191.4	1238.4	1284.3	1381.4	1492.1	1614.3	1761.5
37.5°	902.2	951.2	998.2	1064.0	1147.6	1190.4	1238.4	1344.9	1471.2	1611.2	1768.8
40°	850.0	898.0	938.7	1005.5	1093.3	1142.3	1192.5	1304.2	1447.2	1599.7	1742.7
42.5°	797.8	838.5	883.4	953.3	1037.9	1090.1	1143.4	1267.6	1415.9	1566.3	1670.7
45°	743.5	774.8	823.9	887.6	977.4	1027.5	1088.0	1222.7	1372.1	1505.7	1557.9
47.5°	687.1	718.4	764.3	825.9	914.7	974.2	1031.6	1166.3	1316.7	1420.1	1420.1
50°	632.8	657.8	702.7	764.3	854.1	908.4	966.9	1110.0	1231.1	1307.3	1239.4
52.5°	574.3	602.5	640.1	704.8	793.6	842.7	906.3	1028.5	1143.4	1174.7	1070.3
55°	523.1	546.1	581.6	643.2	725.7	776.9	831.2	948.1	1045.2	1043.1	931.4
57.5°	469.9	488.7	526.3	582.7	658.9	704.8	759.1	860.4	939.8	911.6	806.1
60°	420.8	434.4	470.9	516.9	590.0	632.8	685.0	767.5	828.0	788.4	681.8
62.5°	369.6	385.3	414.5	459.4	524.2	558.6	597.3	680.8	719.4	683.9	575.3
65°	323.7	336.2	362.3	399.9	458.4	489.7	523.1	592.0	628.6	577.4	487.6
67.5°	277.8	292.4	311.2	344.6	390.5	419.8	449.0	508.5	525.2	479.3	404.1
70°	234.9	247.5	265.2	289.2	327.9	354.0	375.9	425.0	436.5	393.7	334.1
72.5°	193.2	201.5	216.1	236.0	271.5	286.1	309.1	342.5	357.1	318.5	275.7
75°	156.6	162.9	172.3	186.9	210.9	226.6	245.4	276.7	275.7	248.5	218.2
77.5°	121.1	122.2	132.6	146.2	160.8	174.4	183.8	205.7	207.8	191.1	166.0
80°	86.7	89.8	94.0	104.4	116.9	122.2	133.7	147.2	149.3	136.8	120.1
82.5°	55.3	57.4	60.6	66.8	75.2	81.4	87.7	92.9	98.2	90.8	77.3
85°	31.3	32.4	35.5	37.6	41.8	44.9	50.1	55.3	54.3	49.1	44.9
87.5°	15.7	15.7	15.7	17.8	19.8	19.8	21.9	23.0	24.0	21.9	19.8
90°	0.4	0.7	1.4	2.1	2.8	3.2	3.6	3.9	4.6	5.0	5.7
92.5°	5.3	6.4	10.0	15.3	22.8	29.2	35.5	59.7	100.2	144.3	141.8
95°	11.7	12.1	14.9	18.8	26.7	34.7	42.7	80.7	158.9	257.0	314.9
97.5°	18.1	18.5	20.6	24.5	31.6	37.5	43.4	69.7	129.7	235.7	340.2
100°	24.9	25.6	27.0	30.9	37.7	43.0	48.3	69.0	115.2	204.8	321.0
102.5°	32.3	32.7	33.8	38.0	44.1	49.2	54.4	72.2	109.1	181.3	287.2
105°	40.2	40.2	41.9	45.5	51.2	56.2	61.1	76.8	108.4	167.8	257.7
107.5°	47.6	48.3	50.1	53.0	59.0	63.4	67.9	83.2	110.9	160.7	235.7
110°	55.8	56.5	57.9	61.1	66.5	71.1	75.7	90.3	114.8	157.8	221.1

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	64.0	64.7	65.8	69.0	74.3	78.8	83.2	97.0	119.8	157.8	212.6
115°	71.8	72.5	73.6	76.8	82.1	86.6	91.0	104.2	124.8	158.9	206.9
117.5°	78.9	80.0	81.0	84.2	90.3	94.6	98.8	111.3	130.5	160.7	203.7
120°	86.0	87.1	88.5	91.7	97.8	102.2	106.6	119.1	136.1	163.5	201.6
122.5°	93.5	94.2	95.3	98.5	105.2	109.6	114.1	126.5	142.5	166.0	199.8
125°	99.5	100.2	102.0	105.2	112.0	116.6	121.2	132.9	148.2	168.9	198.4
127.5°	104.5	105.6	107.7	111.6	118.7	123.4	128.0	139.3	153.6	172.0	197.6
130°	109.1	110.2	113.0	117.7	125.1	129.8	134.4	145.4	158.9	174.9	196.9
132.5°	112.7	114.1	117.7	123.0	130.8	135.4	140.1	151.1	163.5	178.1	196.9
135°	116.6	118.0	122.3	128.0	135.4	140.2	145.0	156.1	167.8	180.9	196.9
137.5°	121.6	122.6	126.5	132.2	139.7	144.7	149.7	159.6	171.0	183.8	197.3
140°	125.8	126.9	131.2	136.9	143.6	148.4	153.2	163.5	174.2	185.6	197.6
142.5°	130.8	131.5	135.4	141.1	147.5	152.0	156.4	166.0	176.0	186.6	198.0
145°	135.8	136.5	140.1	145.0	151.4	155.5	159.6	168.9	177.7	187.3	197.6
147.5°	141.1	141.5	144.7	149.3	155.0	158.8	162.5	170.6	178.8	187.7	196.9
150°	145.7	146.5	148.9	153.6	158.5	161.6	164.6	172.4	179.9	187.7	195.9
152.5°	150.7	151.1	153.2	157.1	161.7	164.4	167.1	174.2	180.6	187.3	194.4
155°	155.0	155.0	157.1	160.7	164.2	166.7	169.2	175.2	180.9	186.6	192.7
157.5°	158.9	158.9	160.7	163.9	167.1	169.0	171.0	176.3	181.3	185.9	190.9
160°	162.8	162.5	163.9	166.4	169.2	170.8	172.4	177.0	181.3	184.8	189.1
162.5°	166.0	165.7	167.1	169.2	171.3	172.6	173.8	177.7	180.9	183.8	187.0
165°	169.2	168.5	169.6	171.3	172.8	173.9	174.9	177.7	180.6	182.7	184.8
167.5°	171.3	171.0	171.7	172.8	173.8	174.5	175.2	177.7	179.9	180.9	182.7
170°	173.5	173.1	173.5	174.2	174.9	175.4	176.0	177.7	179.2	179.9	180.9
172.5°	174.9	174.2	174.5	175.2	175.6	175.8	176.0	177.4	178.4	178.4	178.8
175°	176.0	175.2	175.6	176.0	176.0	176.0	176.0	177.0	177.7	177.4	177.4
177.5°	176.7	176.0	176.0	176.3	176.0	176.0	176.0	176.7	177.0	176.3	176.3
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0
2.5°	1286.4	1293.7	1300.0	1305.2	1309.4	1315.7	1311.5	1312.5	1314.6	1318.8	1318.8
5°	1370.0	1381.4	1387.7	1408.6	1413.8	1412.8	1409.6	1426.3	1425.3	1419.0	1418.0
7.5°	1451.4	1471.2	1489.0	1505.7	1510.9	1524.5	1527.6	1534.9	1532.9	1543.3	1538.1
10°	1525.5	1556.9	1573.6	1598.6	1604.9	1611.2	1619.5	1623.7	1633.1	1632.1	1632.1
12.5°	1583.0	1620.6	1642.5	1648.8	1672.8	1680.1	1687.4	1701.0	1697.8	1698.9	1705.1
15°	1627.9	1664.4	1683.2	1712.5	1729.2	1737.5	1750.0	1764.7	1762.6	1772.0	1769.9
17.5°	1661.3	1695.7	1730.2	1774.1	1775.1	1797.0	1826.3	1832.5	1846.1	1836.7	1836.7
20°	1688.4	1734.4	1783.5	1839.8	1846.1	1859.7	1895.2	1919.2	1934.9	1929.6	1932.8
22.5°	1717.7	1783.5	1840.9	1897.3	1927.6	1951.6	1986.0	2023.6	2037.2	2045.5	2043.5
25°	1755.3	1824.2	1908.8	1987.1	2018.4	2064.3	2110.3	2146.8	2157.3	2180.2	2159.4
27.5°	1793.9	1891.0	1996.5	2088.4	2128.0	2165.6	2221.0	2248.1	2261.7	2272.1	2264.8
30°	1826.3	1959.9	2074.8	2159.4	2187.6	2209.5	2240.8	2247.1	2241.9	2250.2	2260.6
32.5°	1876.4	2006.9	2104.0	2144.7	2141.6	2140.6	2116.5	2083.1	2075.8	2056.0	2083.1
35°	1903.5	2008.0	2045.5	1991.2	1969.3	1929.6	1853.4	1803.3	1759.4	1750.0	1752.1
37.5°	1887.9	1928.6	1883.7	1740.6	1705.1	1644.6	1543.3	1472.3	1439.9	1414.9	1447.2
40°	1803.3	1758.4	1635.2	1460.8	1409.6	1352.2	1257.2	1218.6	1172.6	1163.2	1206.0
42.5°	1663.4	1526.6	1352.2	1217.5	1164.3	1131.9	1052.5	1016.0	983.6	969.0	993.0
45°	1473.3	1307.3	1131.9	1021.2	976.3	937.7	890.7	852.0	831.2	824.9	844.7
47.5°	1277.0	1101.6	961.7	879.2	832.2	803.0	759.1	737.2	720.5	722.6	725.7
50°	1089.1	929.3	821.8	739.3	716.3	693.3	664.1	645.3	636.9	640.1	638.0
52.5°	927.2	797.8	706.9	643.2	632.8	610.8	586.8	571.2	568.0	569.1	572.2
55°	785.2	683.9	611.9	565.9	554.5	538.8	524.2	513.7	505.4	508.5	507.5
57.5°	677.7	588.9	533.6	496.0	487.6	478.2	464.7	459.4	456.3	450.0	455.3
60°	582.7	510.6	462.6	439.6	432.3	426.0	411.4	405.1	403.1	399.9	408.3
62.5°	492.9	441.7	405.1	384.3	376.9	370.7	363.4	358.2	359.2	355.0	359.2
65°	421.8	380.1	354.0	335.2	325.8	321.6	320.6	312.2	311.2	312.2	313.3
67.5°	356.1	320.6	300.7	289.2	281.9	277.8	274.6	269.4	273.6	270.4	272.5
70°	296.5	272.5	251.6	240.2	237.0	238.1	232.9	230.8	231.8	229.7	231.8
72.5°	239.1	219.3	210.9	202.6	198.4	197.3	194.2	191.1	194.2	193.2	193.2
75°	191.1	176.5	167.1	161.8	161.8	159.8	154.5	154.5	154.5	153.5	154.5
77.5°	147.2	134.7	130.5	125.3	125.3	122.2	121.1	121.1	119.0	122.2	120.1
80°	109.6	100.2	94.0	90.8	90.8	89.8	87.7	86.7	87.7	86.7	86.7
82.5°	71.0	66.8	63.7	60.6	59.5	60.6	59.5	57.4	58.5	57.4	59.5
85°	40.7	36.5	36.5	34.5	35.5	33.4	34.5	32.4	31.3	34.5	32.4
87.5°	17.8	16.7	16.7	14.6	14.6	14.6	13.6	14.6	13.6	12.5	13.6
90°	6.0	6.4	6.8	7.1	7.4	7.8	7.8	7.8	8.2	8.2	8.2
92.5°	114.5	77.1	55.5	41.2	37.8	34.5	28.8	27.7	27.0	26.3	27.0
95°	308.2	255.6	201.6	157.8	142.9	128.0	102.7	92.1	89.2	83.5	89.2
97.5°	385.0	366.5	323.5	279.4	258.0	236.7	215.4	196.9	187.3	183.1	187.3
100°	409.9	437.2	419.8	383.2	364.7	346.2	321.7	296.1	283.0	277.3	283.0
102.5°	394.9	461.0	478.8	466.0	455.0	444.0	417.3	401.0	386.4	382.5	386.4
105°	359.7	445.1	493.8	509.4	507.4	505.5	494.1	482.4	475.3	471.0	475.3
107.5°	326.3	412.3	476.7	514.4	522.2	530.0	533.2	531.4	527.9	524.3	527.9
110°	298.6	375.4	442.9	493.0	508.2	523.3	539.3	546.0	548.5	548.5	548.5

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	278.0	346.2	409.5	460.3	478.8	497.3	522.5	535.3	542.5	545.7	542.5
115°	264.1	322.8	377.9	426.6	446.0	465.3	493.0	510.1	520.1	524.7	520.1
117.5°	254.9	306.4	355.1	397.8	416.1	434.4	462.5	480.2	490.2	493.0	490.2
120°	247.4	293.6	336.3	375.4	391.0	406.7	433.0	450.0	459.6	462.5	459.6
122.5°	241.0	284.0	322.8	356.5	370.9	385.3	408.1	423.4	433.0	435.5	433.0
125°	235.3	274.8	311.0	342.0	354.8	367.6	387.5	402.0	409.9	413.4	409.9
127.5°	230.0	265.2	299.7	328.8	340.9	353.0	371.1	384.3	391.7	393.2	391.7
130°	224.7	256.3	287.6	315.3	326.8	338.4	356.2	367.9	375.0	377.2	375.0
132.5°	220.4	247.4	276.2	300.7	311.8	322.8	340.5	352.3	358.7	361.2	358.7
135°	217.2	239.9	264.5	287.2	297.4	307.5	323.1	334.9	341.3	343.4	341.3
137.5°	214.0	233.2	253.8	273.4	282.2	291.1	305.4	316.4	322.4	324.9	322.4
140°	211.9	227.9	244.6	260.9	268.4	275.8	289.0	298.2	303.6	305.4	303.6
142.5°	210.1	223.2	236.7	250.3	256.5	262.7	273.4	280.8	285.8	287.2	285.8
145°	208.3	219.3	230.3	241.4	246.2	251.0	259.5	265.5	269.4	270.9	269.4
147.5°	206.5	215.4	224.7	233.5	237.2	241.0	248.1	253.1	255.6	256.3	255.6
150°	204.4	212.2	220.0	226.8	230.0	233.2	238.5	242.8	244.2	244.6	244.2
152.5°	201.9	208.7	215.4	221.5	223.8	226.1	230.3	233.5	235.0	235.3	235.0
155°	199.1	205.1	210.8	215.8	217.8	219.7	223.2	225.7	226.8	227.1	226.8
157.5°	196.6	201.6	206.5	210.4	212.0	213.6	216.5	218.6	219.7	219.7	219.7
160°	193.4	198.0	201.6	205.1	206.4	207.6	210.1	211.9	212.6	212.2	212.6
162.5°	190.5	194.1	197.3	200.1	201.2	202.3	204.0	205.5	205.5	205.5	205.5
165°	187.7	190.5	193.0	195.2	196.0	196.9	198.4	199.1	199.1	199.1	199.1
167.5°	184.8	187.0	188.8	190.5	191.2	192.0	192.7	193.4	193.0	193.0	193.0
170°	182.4	184.1	185.2	186.3	186.6	187.0	187.7	188.0	188.0	187.7	188.0
172.5°	179.9	180.9	182.0	182.7	182.9	183.1	183.1	183.8	183.1	182.7	183.1
175°	177.7	178.8	178.8	179.5	179.5	179.5	179.5	179.9	179.2	178.8	179.2
177.5°	176.7	177.0	177.4	177.4	177.4	177.4	177.0	177.4	176.3	176.3	176.3
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0
2.5°	1316.7	1309.4	1311.5	1309.4	1304.2	1301.0	1292.7	1282.3	1278.1	1272.9	1269.7
5°	1422.2	1416.9	1415.9	1407.6	1405.5	1392.9	1372.1	1361.6	1349.1	1336.5	1324.0
7.5°	1537.0	1530.8	1509.9	1506.7	1508.8	1493.2	1466.0	1445.1	1419.0	1401.3	1377.3
10°	1632.1	1619.5	1601.8	1602.8	1595.5	1574.6	1547.5	1525.5	1488.0	1465.0	1430.5
12.5°	1689.5	1679.0	1677.0	1666.5	1660.2	1633.1	1600.7	1572.5	1544.3	1513.0	1486.9
15°	1759.4	1745.9	1736.5	1721.8	1717.7	1689.5	1654.0	1621.6	1589.2	1560.0	1504.7
17.5°	1836.7	1822.1	1786.6	1783.5	1758.4	1731.2	1696.8	1648.8	1614.3	1572.5	1531.8
20°	1924.4	1903.5	1857.6	1846.1	1826.3	1781.4	1734.4	1681.1	1625.8	1583.0	1534.9
22.5°	2022.6	1986.0	1952.6	1916.1	1901.4	1846.1	1781.4	1716.6	1649.8	1591.3	1533.9
25°	2150.0	2101.9	2054.9	2018.4	1993.3	1921.3	1834.6	1749.0	1671.7	1595.5	1520.3
27.5°	2250.2	2208.4	2157.3	2109.2	2076.9	1991.2	1892.1	1781.4	1685.3	1592.4	1512.0
30°	2257.5	2245.0	2213.7	2187.6	2152.1	2060.2	1950.5	1825.2	1706.2	1593.4	1495.3
32.5°	2120.7	2145.8	2159.4	2163.5	2156.2	2103.0	2002.7	1864.9	1725.0	1584.0	1480.6
35°	1826.3	1893.1	1975.6	2006.9	2037.2	2065.4	2013.2	1893.1	1731.2	1581.9	1457.7
37.5°	1503.6	1564.2	1701.0	1763.6	1799.1	1910.8	1953.7	1888.9	1743.8	1584.0	1435.7
40°	1213.3	1309.4	1407.6	1492.1	1547.5	1672.8	1805.4	1820.0	1726.0	1564.2	1407.6
42.5°	1021.2	1077.6	1151.7	1230.0	1279.1	1427.4	1607.0	1712.5	1670.7	1531.8	1373.1
45°	869.8	911.6	981.5	1007.6	1070.3	1212.3	1402.3	1554.8	1575.7	1480.6	1333.4
47.5°	746.6	782.1	827.0	859.4	909.5	1016.0	1176.8	1344.9	1445.1	1410.7	1278.1
50°	657.8	687.1	724.7	743.5	775.8	871.9	993.0	1160.1	1294.8	1306.3	1206.0
52.5°	583.7	600.4	629.6	650.5	676.6	735.1	844.7	982.6	1134.0	1196.6	1117.3
55°	519.0	532.5	558.6	572.2	585.8	635.9	721.5	846.8	988.8	1071.3	1026.4
57.5°	460.5	472.0	493.9	506.4	513.7	561.8	627.6	725.7	853.1	953.3	928.3
60°	412.5	422.9	435.4	444.8	453.2	492.9	538.8	618.2	732.0	829.1	822.8
62.5°	361.3	370.7	384.3	393.7	401.0	426.0	464.7	525.2	622.3	712.1	729.9
65°	316.4	323.7	333.1	337.3	346.7	365.5	396.8	451.1	530.4	610.8	623.4
67.5°	275.7	277.8	284.0	293.4	295.5	312.2	340.4	381.1	442.7	508.5	528.4
70°	231.8	234.9	240.2	247.5	251.6	262.1	286.1	313.3	366.5	423.9	438.6
72.5°	193.2	197.3	199.4	203.6	205.7	222.4	232.9	260.0	296.5	344.6	360.2
75°	156.6	160.8	161.8	163.9	166.0	173.3	188.0	204.7	234.9	266.3	287.1
77.5°	124.3	123.2	125.3	128.4	127.4	133.7	143.1	157.7	177.5	203.6	217.2
80°	87.7	87.7	90.8	94.0	92.9	99.2	102.3	112.8	129.5	146.2	151.4
82.5°	58.5	58.5	61.6	61.6	63.7	64.7	68.9	74.1	87.7	96.1	99.2
85°	33.4	33.4	34.5	34.5	34.5	36.5	39.7	41.8	45.9	51.2	53.3
87.5°	13.6	14.6	14.6	14.6	14.6	16.7	16.7	18.8	19.8	21.9	21.9
90°	7.8	7.8	7.8	7.4	7.1	6.8	6.4	6.0	5.7	5.0	4.6
92.5°	27.7	28.8	34.5	37.8	41.2	55.5	77.1	114.5	141.8	144.3	100.2
95°	92.1	102.7	128.0	142.9	157.8	201.6	255.6	308.2	314.9	257.0	158.9
97.5°	196.9	215.4	236.7	258.0	279.4	323.5	366.5	385.0	340.2	235.7	129.7
100°	296.1	321.7	346.2	364.7	383.2	419.8	437.2	409.9	321.0	204.8	115.2
102.5°	401.0	417.3	444.0	455.0	466.0	478.8	461.0	394.9	287.2	181.3	109.1
105°	482.4	494.1	505.5	507.4	509.4	493.8	445.1	359.7	257.7	167.8	108.4
107.5°	531.4	533.2	530.0	522.2	514.4	476.7	412.3	326.3	235.7	160.7	110.9
110°	546.0	539.3	523.3	508.2	493.0	442.9	375.4	298.6	221.1	157.8	114.8

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	535.3	522.5	497.3	478.8	460.3	409.5	346.2	278.0	212.6	157.8	119.8
115°	510.1	493.0	465.3	446.0	426.6	377.9	322.8	264.1	206.9	158.9	124.8
117.5°	480.2	462.5	434.4	416.1	397.8	355.1	306.4	254.9	203.7	160.7	130.5
120°	450.0	433.0	406.7	391.0	375.4	336.3	293.6	247.4	201.6	163.5	136.1
122.5°	423.4	408.1	385.3	370.9	356.5	322.8	284.0	241.0	199.8	166.0	142.5
125°	402.0	387.5	367.6	354.8	342.0	311.0	274.8	235.3	198.4	168.9	148.2
127.5°	384.3	371.1	353.0	340.9	328.8	299.7	265.2	230.0	197.6	172.0	153.6
130°	367.9	356.2	338.4	326.8	315.3	287.6	256.3	224.7	196.9	174.9	158.9
132.5°	352.3	340.5	322.8	311.8	300.7	276.2	247.4	220.4	196.9	178.1	163.5
135°	334.9	323.1	307.5	297.4	287.2	264.5	239.9	217.2	196.9	180.9	167.8
137.5°	316.4	305.4	291.1	282.2	273.4	253.8	233.2	214.0	197.3	183.8	171.0
140°	298.2	289.0	275.8	268.4	260.9	244.6	227.9	211.9	197.6	185.6	174.2
142.5°	280.8	273.4	262.7	256.5	250.3	236.7	223.2	210.1	198.0	186.6	176.0
145°	265.5	259.5	251.0	246.2	241.4	230.3	219.3	208.3	197.6	187.3	177.7
147.5°	253.1	248.1	241.0	237.2	233.5	224.7	215.4	206.5	196.9	187.7	178.8
150°	242.8	238.5	233.2	230.0	226.8	220.0	212.2	204.4	195.9	187.7	179.9
152.5°	233.5	230.3	226.1	223.8	221.5	215.4	208.7	201.9	194.4	187.3	180.6
155°	225.7	223.2	219.7	217.8	215.8	210.8	205.1	199.1	192.7	186.6	180.9
157.5°	218.6	216.5	213.6	212.0	210.4	206.5	201.6	196.6	190.9	185.9	181.3
160°	211.9	210.1	207.6	206.4	205.1	201.6	198.0	193.4	189.1	184.8	181.3
162.5°	205.5	204.0	202.3	201.2	200.1	197.3	194.1	190.5	187.0	183.8	180.9
165°	199.1	198.4	196.9	196.0	195.2	193.0	190.5	187.7	184.8	182.7	180.6
167.5°	193.4	192.7	192.0	191.2	190.5	188.8	187.0	184.8	182.7	180.9	179.9
170°	188.0	187.7	187.0	186.6	186.3	185.2	184.1	182.4	180.9	179.9	179.2
172.5°	183.8	183.1	183.1	182.9	182.7	182.0	180.9	179.9	178.8	178.4	178.4
175°	179.9	179.5	179.5	179.5	179.5	178.8	178.8	177.7	177.4	177.4	177.7
177.5°	177.4	177.0	177.4	177.4	177.4	177.4	177.0	176.7	176.3	176.3	177.0
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0
2.5°	1265.5	1260.3	1254.1	1254.1	1246.7	1243.6	1237.4	1235.3	1230.0	1221.7	1215.4
5°	1310.4	1296.9	1288.5	1281.2	1265.5	1254.1	1242.6	1230.0	1217.5	1202.9	1186.2
7.5°	1354.3	1329.2	1317.8	1305.2	1282.3	1258.2	1235.3	1218.6	1201.8	1178.9	1158.0
10°	1400.2	1368.9	1348.0	1331.3	1295.8	1265.5	1232.1	1208.1	1182.0	1152.8	1125.6
12.5°	1438.9	1398.2	1380.4	1349.1	1308.4	1271.8	1230.0	1193.5	1159.0	1124.6	1091.2
15°	1471.2	1432.6	1388.8	1376.2	1319.8	1267.6	1220.6	1173.7	1130.8	1096.4	1057.8
17.5°	1481.7	1432.6	1410.7	1380.4	1313.6	1259.3	1199.8	1148.6	1107.9	1056.7	1026.4
20°	1484.8	1437.8	1407.6	1379.4	1319.8	1247.8	1189.3	1126.7	1077.6	1026.4	978.4
22.5°	1476.5	1421.1	1391.9	1364.7	1297.9	1236.3	1168.4	1099.5	1042.1	995.1	947.1
25°	1460.8	1396.1	1367.9	1338.6	1274.9	1207.1	1132.9	1067.2	1013.9	957.5	910.5
27.5°	1439.9	1365.8	1333.4	1303.1	1240.5	1176.8	1106.8	1039.0	979.4	919.9	876.1
30°	1413.8	1328.2	1299.0	1259.3	1198.7	1138.2	1074.5	1006.6	939.8	883.4	835.3
32.5°	1380.4	1290.6	1252.0	1214.4	1148.6	1093.3	1032.7	969.0	904.3	848.9	798.8
35°	1350.1	1247.8	1205.0	1167.4	1094.3	1035.8	985.7	926.2	868.8	811.3	766.4
37.5°	1309.4	1205.0	1153.8	1115.2	1041.0	981.5	934.5	888.6	828.0	772.7	730.9
40°	1266.6	1151.7	1103.7	1065.1	987.8	923.1	878.2	837.4	788.4	737.2	693.3
42.5°	1228.0	1100.6	1049.4	1002.4	924.1	866.7	820.7	789.4	744.5	698.6	658.9
45°	1178.9	1046.3	990.9	941.8	866.7	804.0	760.2	735.1	701.7	656.8	622.3
47.5°	1128.8	987.8	930.4	882.3	800.9	745.5	702.7	678.7	655.7	620.2	585.8
50°	1063.0	926.2	874.0	818.6	738.2	681.8	646.3	622.3	604.6	579.5	550.3
52.5°	990.9	862.5	806.1	758.1	678.7	627.6	586.8	573.3	555.5	536.7	511.6
55°	914.7	793.6	739.3	692.3	619.2	567.0	533.6	519.0	505.4	490.8	474.1
57.5°	838.5	721.5	670.4	628.6	560.7	510.6	483.5	463.6	454.2	445.9	432.3
60°	743.5	644.3	604.6	567.0	500.2	454.2	428.1	413.5	405.1	401.0	394.7
62.5°	659.9	578.5	534.6	498.1	444.8	404.1	379.0	367.6	360.2	358.2	350.8
65°	571.2	501.2	466.7	435.4	389.5	352.9	332.0	318.5	313.3	312.2	312.2
67.5°	487.6	431.2	396.8	374.9	335.2	302.8	283.0	277.8	274.6	270.4	269.4
70°	409.3	364.4	334.1	315.3	279.8	255.8	240.2	231.8	231.8	228.7	226.6
72.5°	340.4	295.5	275.7	260.0	230.8	209.9	198.4	196.3	189.0	188.0	188.0
75°	266.3	232.9	219.3	205.7	183.8	169.2	159.8	154.5	150.4	150.4	151.4
77.5°	200.5	177.5	165.0	154.5	138.9	129.5	122.2	120.1	115.9	115.9	115.9
80°	142.0	129.5	120.1	111.7	100.2	91.9	87.7	83.5	83.5	82.5	83.5
82.5°	91.9	81.4	76.2	75.2	64.7	61.6	56.4	57.4	54.3	53.3	55.3
85°	53.3	48.0	41.8	39.7	35.5	31.3	29.2	30.3	29.2	28.2	29.2
87.5°	20.9	17.8	16.7	16.7	13.6	12.5	11.5	12.5	10.4	10.4	11.5
90°	3.9	3.6	3.2	2.8	2.1	1.4	0.7	0.4	0.7	1.4	2.1
92.5°	59.7	35.5	29.2	22.8	15.3	10.0	6.4	5.3	6.4	10.0	15.3
95°	80.7	42.7	34.7	26.7	18.8	14.9	12.1	11.7	12.1	14.9	18.8
97.5°	69.7	43.4	37.5	31.6	24.5	20.6	18.5	18.1	18.5	20.6	24.5
100°	69.0	48.3	43.0	37.7	30.9	27.0	25.6	24.9	25.6	27.0	30.9
102.5°	72.2	54.4	49.2	44.1	38.0	33.8	32.7	32.3	32.7	33.8	38.0
105°	76.8	61.1	56.2	51.2	45.5	41.9	40.2	40.2	40.2	41.9	45.5
107.5°	83.2	67.9	63.4	59.0	53.0	50.1	48.3	47.6	48.3	50.1	53.0
110°	90.3	75.7	71.1	66.5	61.1	57.9	56.5	55.8	56.5	57.9	61.1

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	97.0	83.2	78.8	74.3	69.0	65.8	64.7	64.0	64.7	65.8	69.0
115°	104.2	91.0	86.6	82.1	76.8	73.6	72.5	71.8	72.5	73.6	76.8
117.5°	111.3	98.8	94.6	90.3	84.2	81.0	80.0	78.9	80.0	81.0	84.2
120°	119.1	106.6	102.2	97.8	91.7	88.5	87.1	86.0	87.1	88.5	91.7
122.5°	126.5	114.1	109.6	105.2	98.5	95.3	94.2	93.5	94.2	95.3	98.5
125°	132.9	121.2	116.6	112.0	105.2	102.0	100.2	99.5	100.2	102.0	105.2
127.5°	139.3	128.0	123.4	118.7	111.6	107.7	105.6	104.5	105.6	107.7	111.6
130°	145.4	134.4	129.8	125.1	117.7	113.0	110.2	109.1	110.2	113.0	117.7
132.5°	151.1	140.1	135.4	130.8	123.0	117.7	114.1	112.7	114.1	117.7	123.0
135°	156.1	145.0	140.2	135.4	128.0	122.3	118.0	116.6	118.0	122.3	128.0
137.5°	159.6	149.7	144.7	139.7	132.2	126.5	122.6	121.6	122.6	126.5	132.2
140°	163.5	153.2	148.4	143.6	136.9	131.2	126.9	125.8	126.9	131.2	136.9
142.5°	166.0	156.4	152.0	147.5	141.1	135.4	131.5	130.8	131.5	135.4	141.1
145°	168.9	159.6	155.5	151.4	145.0	140.1	136.5	135.8	136.5	140.1	145.0
147.5°	170.6	162.5	158.8	155.0	149.3	144.7	141.5	141.1	141.5	144.7	149.3
150°	172.4	164.6	161.6	158.5	153.6	148.9	146.5	145.7	146.5	148.9	153.6
152.5°	174.2	167.1	164.4	161.7	157.1	153.2	151.1	150.7	151.1	153.2	157.1
155°	175.2	169.2	166.7	164.2	160.7	157.1	155.0	155.0	155.0	157.1	160.7
157.5°	176.3	171.0	169.0	167.1	163.9	160.7	158.9	158.9	158.9	160.7	163.9
160°	177.0	172.4	170.8	169.2	166.4	163.9	162.5	162.8	162.5	163.9	166.4
162.5°	177.7	173.8	172.6	171.3	169.2	167.1	165.7	166.0	165.7	167.1	169.2
165°	177.7	174.9	173.9	172.8	171.3	169.6	168.5	169.2	168.5	169.6	171.3
167.5°	177.7	175.2	174.5	173.8	172.8	171.7	171.0	171.3	171.0	171.7	172.8
170°	177.7	176.0	175.4	174.9	174.2	173.5	173.1	173.5	173.1	173.5	174.2
172.5°	177.4	176.0	175.8	175.6	175.2	174.5	174.2	174.9	174.2	174.5	175.2
175°	177.0	176.0	176.0	176.0	176.0	175.6	175.2	176.0	175.2	175.6	176.0
177.5°	176.7	176.0	176.0	176.0	176.3	176.0	176.0	176.7	176.0	176.0	176.3
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0
2.5°	1213.3	1211.2	1206.0	1202.9	1192.5	1179.9	1175.7	1165.3	1169.5	1162.2	1162.2
5°	1181.0	1171.6	1165.3	1155.9	1136.1	1122.5	1107.9	1100.6	1096.4	1091.2	1087.0
7.5°	1139.2	1131.9	1125.6	1107.9	1085.9	1067.2	1049.4	1042.1	1028.5	1019.1	1014.9
10°	1102.7	1092.2	1077.6	1056.7	1033.7	1009.7	994.1	978.4	968.0	962.7	951.2
12.5°	1065.1	1052.5	1036.9	1006.6	981.5	966.9	938.7	924.1	918.9	914.7	901.1
15°	1026.4	1012.9	994.1	965.9	943.9	909.5	892.8	881.3	868.8	867.7	857.3
17.5°	992.0	975.3	959.6	925.1	898.0	867.7	858.3	845.8	834.3	821.8	816.5
20°	948.1	932.5	921.0	883.4	853.1	834.3	818.6	808.2	800.9	788.4	786.3
22.5°	908.4	891.7	876.1	847.9	821.8	797.8	779.0	767.5	764.3	759.1	749.7
25°	869.8	853.1	834.3	808.2	781.0	764.3	747.6	740.3	734.1	725.7	718.4
27.5°	837.4	821.8	804.0	771.6	748.7	736.1	718.4	710.0	701.7	697.5	694.4
30°	798.8	781.0	767.5	742.4	717.4	700.6	688.1	680.8	673.5	669.3	667.2
32.5°	761.2	744.5	735.1	708.0	688.1	668.3	658.9	653.7	649.5	645.3	641.1
35°	730.9	714.2	699.6	674.5	654.7	641.1	633.8	625.5	622.3	618.2	618.2
37.5°	693.3	680.8	666.2	642.2	624.4	614.0	607.7	597.3	596.2	594.1	591.0
40°	661.0	648.4	634.9	614.0	598.3	585.8	577.4	572.2	569.1	567.0	564.9
42.5°	626.5	612.9	606.7	582.7	569.1	556.5	552.4	547.1	546.1	541.9	536.7
45°	593.1	581.6	569.1	551.3	539.8	529.4	523.1	519.0	513.7	512.7	509.6
47.5°	563.9	550.3	538.8	522.1	509.6	501.2	496.0	490.8	486.6	483.5	480.3
50°	526.3	515.8	506.4	488.7	478.2	469.9	462.6	458.4	454.2	454.2	454.2
52.5°	489.7	480.3	472.0	459.4	446.9	439.6	431.2	428.1	426.0	422.9	426.0
55°	454.2	444.8	436.5	427.1	412.5	406.2	397.8	394.7	395.7	395.7	398.9
57.5°	416.6	409.3	404.1	392.6	379.0	372.8	367.6	364.4	364.4	368.6	369.6
60°	380.1	372.8	363.4	352.9	344.6	337.3	334.1	335.2	335.2	337.3	342.5
62.5°	339.4	335.2	330.0	315.3	310.1	304.9	300.7	303.9	302.8	308.0	315.3
65°	301.8	297.6	290.3	283.0	276.7	271.5	270.4	271.5	273.6	278.8	287.1
67.5°	260.0	260.0	253.7	247.5	242.2	237.0	238.1	239.1	241.2	247.5	260.0
70°	225.5	221.4	215.1	210.9	206.7	204.7	202.6	206.7	213.0	217.2	226.6
72.5°	188.0	184.8	179.6	175.4	174.4	172.3	171.2	173.3	179.6	186.9	197.3
75°	148.3	149.3	146.2	143.1	143.1	139.9	142.0	142.0	148.3	155.6	163.9
77.5°	114.9	113.8	112.8	110.7	109.6	109.6	109.6	111.7	118.0	122.2	130.5
80°	81.4	82.5	79.4	80.4	79.4	80.4	80.4	84.6	87.7	92.9	99.2
82.5°	54.3	54.3	52.2	53.3	53.3	53.3	54.3	56.4	60.6	64.7	68.9
85°	30.3	31.3	29.2	31.3	31.3	31.3	32.4	33.4	36.5	37.6	41.8
87.5°	11.5	13.6	13.6	11.5	12.5	13.6	14.6	13.6	15.7	17.8	18.8
90°	2.8	3.2	3.6	3.9	4.6	5.0	5.7	6.0	6.4	6.8	7.1
92.5°	22.8	29.2	35.5	59.7	100.2	144.3	141.8	114.5	77.1	55.5	41.2
95°	26.7	34.7	42.7	80.7	158.9	257.0	314.9	308.2	255.6	201.6	157.8
97.5°	31.6	37.5	43.4	69.7	129.7	235.7	340.2	385.0	366.5	323.5	279.4
100°	37.7	43.0	48.3	69.0	115.2	204.8	321.0	409.9	437.2	419.8	383.2
102.5°	44.1	49.2	54.4	72.2	109.1	181.3	287.2	394.9	461.0	478.8	466.0
105°	51.2	56.2	61.1	76.8	108.4	167.8	257.7	359.7	445.1	493.8	509.4
107.5°	59.0	63.4	67.9	83.2	110.9	160.7	235.7	326.3	412.3	476.7	514.4
110°	66.5	71.1	75.7	90.3	114.8	157.8	221.1	298.6	375.4	442.9	493.0

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	74.3	78.8	83.2	97.0	119.8	157.8	212.6	278.0	346.2	409.5	460.3
115°	82.1	86.6	91.0	104.2	124.8	158.9	206.9	264.1	322.8	377.9	426.6
117.5°	90.3	94.6	98.8	111.3	130.5	160.7	203.7	254.9	306.4	355.1	397.8
120°	97.8	102.2	106.6	119.1	136.1	163.5	201.6	247.4	293.6	336.3	375.4
122.5°	105.2	109.6	114.1	126.5	142.5	166.0	199.8	241.0	284.0	322.8	356.5
125°	112.0	116.6	121.2	132.9	148.2	168.9	198.4	235.3	274.8	311.0	342.0
127.5°	118.7	123.4	128.0	139.3	153.6	172.0	197.6	230.0	265.2	299.7	328.8
130°	125.1	129.8	134.4	145.4	158.9	174.9	196.9	224.7	256.3	287.6	315.3
132.5°	130.8	135.4	140.1	151.1	163.5	178.1	196.9	220.4	247.4	276.2	300.7
135°	135.4	140.2	145.0	156.1	167.8	180.9	196.9	217.2	239.9	264.5	287.2
137.5°	139.7	144.7	149.7	159.6	171.0	183.8	197.3	214.0	233.2	253.8	273.4
140°	143.6	148.4	153.2	163.5	174.2	185.6	197.6	211.9	227.9	244.6	260.9
142.5°	147.5	152.0	156.4	166.0	176.0	186.6	198.0	210.1	223.2	236.7	250.3
145°	151.4	155.5	159.6	168.9	177.7	187.3	197.6	208.3	219.3	230.3	241.4
147.5°	155.0	158.8	162.5	170.6	178.8	187.7	196.9	206.5	215.4	224.7	233.5
150°	158.5	161.6	164.6	172.4	179.9	187.7	195.9	204.4	212.2	220.0	226.8
152.5°	161.7	164.4	167.1	174.2	180.6	187.3	194.4	201.9	208.7	215.4	221.5
155°	164.2	166.7	169.2	175.2	180.9	186.6	192.7	199.1	205.1	210.8	215.8
157.5°	167.1	169.0	171.0	176.3	181.3	185.9	190.9	196.6	201.6	206.5	210.4
160°	169.2	170.8	172.4	177.0	181.3	184.8	189.1	193.4	198.0	201.6	205.1
162.5°	171.3	172.6	173.8	177.7	180.9	183.8	187.0	190.5	194.1	197.3	200.1
165°	172.8	173.9	174.9	177.7	180.6	182.7	184.8	187.7	190.5	193.0	195.2
167.5°	173.8	174.5	175.2	177.7	179.9	180.9	182.7	184.8	187.0	188.8	190.5
170°	174.9	175.4	176.0	177.7	179.2	179.9	180.9	182.4	184.1	185.2	186.3
172.5°	175.6	175.8	176.0	177.4	178.4	178.4	178.8	179.9	180.9	182.0	182.7
175°	176.0	176.0	176.0	177.0	177.7	177.4	177.4	177.7	178.8	178.8	179.5
177.5°	176.0	176.0	176.0	176.7	177.0	176.3	176.3	176.7	177.0	177.4	177.4
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0
2.5°	1166.3	1159.0	1158.0	1160.1	1155.9	1162.2	1160.1	1162.2	1156.9	1162.2	1159.0
5°	1085.9	1083.9	1079.7	1074.5	1075.5	1076.5	1081.8	1076.5	1080.7	1081.8	1087.0
7.5°	1010.8	1006.6	1009.7	1007.6	998.2	996.1	998.2	1001.4	1007.6	1011.8	1014.9
10°	950.2	948.1	943.9	940.8	935.6	932.5	936.6	932.5	940.8	948.1	948.1
12.5°	904.3	895.9	890.7	889.6	878.2	880.2	884.4	887.6	896.9	901.1	901.1
15°	856.2	850.0	847.9	843.7	839.5	843.7	841.6	844.7	848.9	853.1	855.2
17.5°	814.5	813.4	814.5	804.0	807.1	801.9	803.0	808.2	805.1	808.2	814.5
20°	776.9	779.0	775.8	771.6	771.6	765.4	772.7	770.6	771.6	777.9	787.3
22.5°	748.7	747.6	744.5	741.4	737.2	738.2	739.3	737.2	745.5	750.8	751.8
25°	718.4	716.3	715.3	712.1	708.0	712.1	711.1	712.1	714.2	722.6	716.3
27.5°	690.2	686.0	688.1	685.0	683.9	685.0	685.0	686.0	688.1	689.2	690.2
30°	666.2	662.0	661.0	658.9	657.8	658.9	661.0	658.9	667.2	666.2	666.2
32.5°	640.1	636.9	634.9	634.9	633.8	632.8	633.8	634.9	641.1	636.9	641.1
35°	615.0	612.9	612.9	610.8	609.8	609.8	609.8	614.0	611.9	615.0	615.0
37.5°	591.0	591.0	590.0	587.9	586.8	587.9	586.8	588.9	587.9	588.9	590.0
40°	565.9	563.9	562.8	562.8	559.7	556.5	559.7	559.7	560.7	563.9	564.9
42.5°	535.7	536.7	536.7	532.5	532.5	532.5	533.6	534.6	534.6	536.7	536.7
45°	509.6	507.5	507.5	507.5	505.4	506.4	508.5	508.5	508.5	508.5	506.4
47.5°	480.3	480.3	481.4	481.4	484.5	483.5	483.5	482.4	480.3	480.3	481.4
50°	453.2	456.3	457.4	457.4	458.4	459.4	459.4	457.4	456.3	453.2	453.2
52.5°	427.1	429.2	431.2	434.4	436.5	435.4	435.4	433.3	429.2	428.1	427.1
55°	398.9	402.0	406.2	409.3	412.5	413.5	413.5	409.3	405.1	399.9	399.9
57.5°	372.8	375.9	383.2	386.3	390.5	390.5	388.4	385.3	379.0	374.9	371.7
60°	346.7	351.9	357.1	363.4	368.6	369.6	366.5	362.3	355.0	349.8	345.6
62.5°	318.5	323.7	334.1	340.4	344.6	344.6	344.6	339.4	330.0	322.7	316.4
65°	291.3	296.5	305.9	314.3	317.4	320.6	317.4	312.2	304.9	296.5	290.3
67.5°	263.1	269.4	278.8	285.1	289.2	292.4	290.3	286.1	276.7	265.2	261.0
70°	231.8	234.9	248.5	254.8	261.0	263.1	261.0	254.8	245.4	232.9	228.7
72.5°	202.6	205.7	218.2	223.5	228.7	230.8	227.6	223.5	215.1	203.6	198.4
75°	169.2	174.4	180.6	189.0	195.3	197.3	194.2	191.1	180.6	173.3	169.2
77.5°	133.7	138.9	147.2	154.5	160.8	159.8	155.6	156.6	145.1	136.8	133.7
80°	101.3	105.5	111.7	118.0	121.1	121.1	120.1	115.9	111.7	105.5	100.2
82.5°	70.0	75.2	80.4	84.6	84.6	85.6	83.5	82.5	78.3	73.1	72.0
85°	41.8	42.8	47.0	47.0	51.2	49.1	48.0	51.2	47.0	43.9	42.8
87.5°	18.8	17.8	18.8	18.8	17.8	19.8	19.8	18.8	19.8	18.8	18.8
90°	7.4	7.8	7.8	7.8	8.2	8.2	8.2	7.8	7.8	7.8	7.4
92.5°	37.8	34.5	28.8	27.7	27.0	26.3	27.0	27.7	28.8	34.5	37.8
95°	142.9	128.0	102.7	92.1	89.2	83.5	89.2	92.1	102.7	128.0	142.9
97.5°	258.0	236.7	215.4	196.9	187.3	183.1	187.3	196.9	215.4	236.7	258.0
100°	364.7	346.2	321.7	296.1	283.0	277.3	283.0	296.1	321.7	346.2	364.7
102.5°	455.0	444.0	417.3	401.0	386.4	382.5	386.4	401.0	417.3	444.0	455.0
105°	507.4	505.5	494.1	482.4	475.3	471.0	475.3	482.4	494.1	505.5	507.4
107.5°	522.2	530.0	533.2	531.4	527.9	524.3	527.9	531.4	533.2	530.0	522.2
110°	508.2	523.3	539.3	546.0	548.5	548.5	548.5	546.0	539.3	523.3	508.2

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	478.8	497.3	522.5	535.3	542.5	545.7	542.5	535.3	522.5	497.3	478.8
115°	446.0	465.3	493.0	510.1	520.1	524.7	520.1	510.1	493.0	465.3	446.0
117.5°	416.1	434.4	462.5	480.2	490.2	493.0	490.2	480.2	462.5	434.4	416.1
120°	391.0	406.7	433.0	450.0	459.6	462.5	459.6	450.0	433.0	406.7	391.0
122.5°	370.9	385.3	408.1	423.4	433.0	435.5	433.0	423.4	408.1	385.3	370.9
125°	354.8	367.6	387.5	402.0	409.9	413.4	409.9	402.0	387.5	367.6	354.8
127.5°	340.9	353.0	371.1	384.3	391.7	393.2	391.7	384.3	371.1	353.0	340.9
130°	326.8	338.4	356.2	367.9	375.0	377.2	375.0	367.9	356.2	338.4	326.8
132.5°	311.8	322.8	340.5	352.3	358.7	361.2	358.7	352.3	340.5	322.8	311.8
135°	297.4	307.5	323.1	334.9	341.3	343.4	341.3	334.9	323.1	307.5	297.4
137.5°	282.2	291.1	305.4	316.4	322.4	324.9	322.4	316.4	305.4	291.1	282.2
140°	268.4	275.8	289.0	298.2	303.6	305.4	303.6	298.2	289.0	275.8	268.4
142.5°	256.5	262.7	273.4	280.8	285.8	287.2	285.8	280.8	273.4	262.7	256.5
145°	246.2	251.0	259.5	265.5	269.4	270.9	269.4	265.5	259.5	251.0	246.2
147.5°	237.2	241.0	248.1	253.1	255.6	256.3	255.6	253.1	248.1	241.0	237.2
150°	230.0	233.2	238.5	242.8	244.2	244.6	244.2	242.8	238.5	233.2	230.0
152.5°	223.8	226.1	230.3	233.5	235.0	235.3	235.0	233.5	230.3	226.1	223.8
155°	217.8	219.7	223.2	225.7	226.8	227.1	226.8	225.7	223.2	219.7	217.8
157.5°	212.0	213.6	216.5	218.6	219.7	219.7	219.7	218.6	216.5	213.6	212.0
160°	206.4	207.6	210.1	211.9	212.6	212.2	212.6	211.9	210.1	207.6	206.4
162.5°	201.2	202.3	204.0	205.5	205.5	205.5	205.5	205.5	204.0	202.3	201.2
165°	196.0	196.9	198.4	199.1	199.1	199.1	199.1	199.1	198.4	196.9	196.0
167.5°	191.2	192.0	192.7	193.4	193.0	193.0	193.0	193.4	192.7	192.0	191.2
170°	186.6	187.0	187.7	188.0	188.0	187.7	188.0	188.0	187.7	187.0	186.6
172.5°	182.9	183.1	183.1	183.8	183.1	182.7	183.1	183.8	183.1	183.1	182.9
175°	179.5	179.5	179.5	179.9	179.2	178.8	179.2	179.9	179.5	179.5	179.5
177.5°	177.4	177.4	177.0	177.4	176.3	176.3	176.3	177.4	177.0	177.4	177.4
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0
2.5°	1168.4	1162.2	1169.5	1160.1	1162.2	1173.7	1172.6	1183.1	1189.3	1188.3	1193.5
5°	1091.2	1091.2	1094.3	1093.3	1103.7	1113.1	1125.6	1136.1	1147.6	1153.8	1161.1
7.5°	1014.9	1025.4	1027.5	1032.7	1045.2	1060.9	1073.4	1089.1	1105.8	1117.3	1125.6
10°	952.3	960.6	969.0	973.2	986.7	1007.6	1025.4	1050.4	1071.3	1083.9	1095.3
12.5°	896.9	906.3	910.5	929.3	938.7	952.3	977.4	1004.5	1027.5	1041.0	1050.4
15°	857.3	862.5	871.9	883.4	892.8	909.5	930.4	960.6	982.6	994.1	1026.4
17.5°	823.9	830.1	835.3	840.6	855.2	872.9	892.8	918.9	947.1	966.9	983.6
20°	789.4	792.5	798.8	807.1	817.6	834.3	852.0	879.2	904.3	919.9	941.8
22.5°	748.7	758.1	764.3	770.6	782.1	800.9	817.6	837.4	868.8	886.5	909.5
25°	724.7	728.8	733.0	740.3	748.7	765.4	784.2	805.1	830.1	848.9	868.8
27.5°	693.3	699.6	704.8	714.2	719.4	733.0	750.8	771.6	801.9	817.6	834.3
30°	667.2	673.5	677.7	681.8	689.2	703.8	720.5	737.2	765.4	785.2	801.9
32.5°	641.1	647.4	652.6	655.7	663.1	672.5	686.0	706.9	730.9	744.5	766.4
35°	618.2	618.2	624.4	628.6	634.9	643.2	655.7	671.4	696.5	714.2	734.1
37.5°	592.0	593.1	598.3	601.4	607.7	616.1	628.6	643.2	664.1	677.7	697.5
40°	564.9	568.0	570.1	575.3	582.7	585.8	598.3	615.0	635.9	648.4	665.1
42.5°	537.8	539.8	545.1	549.2	555.5	560.7	569.1	584.7	600.4	619.2	632.8
45°	507.5	512.7	515.8	523.1	526.3	531.5	539.8	552.4	571.2	582.7	598.3
47.5°	481.4	483.5	485.5	494.9	501.2	504.3	512.7	520.0	539.8	550.3	564.9
50°	453.2	453.2	456.3	460.5	467.8	474.1	481.4	489.7	505.4	515.8	530.4
52.5°	427.1	423.9	426.0	428.1	435.4	441.7	449.0	460.5	475.1	481.4	493.9
55°	398.9	393.7	396.8	399.9	402.0	410.4	418.7	426.0	437.5	446.9	458.4
57.5°	368.6	367.6	365.5	366.5	371.7	376.9	383.2	392.6	406.2	413.5	419.8
60°	341.4	335.2	333.1	335.2	338.3	341.4	349.8	358.2	369.6	376.9	384.3
62.5°	313.3	307.0	302.8	299.7	302.8	310.1	315.3	321.6	331.0	339.4	345.6
65°	286.1	276.7	272.5	270.4	269.4	274.6	278.8	287.1	295.5	298.6	305.9
67.5°	255.8	247.5	242.2	239.1	239.1	239.1	243.3	251.6	260.0	261.0	268.4
70°	225.5	216.1	210.9	206.7	204.7	206.7	212.0	213.0	220.3	222.4	226.6
72.5°	193.2	184.8	178.6	173.3	174.4	176.5	176.5	178.6	182.7	188.0	188.0
75°	162.9	151.4	148.3	144.1	142.0	142.0	142.0	146.2	149.3	153.5	152.5
77.5°	128.4	122.2	115.9	113.8	110.7	109.6	111.7	111.7	113.8	116.9	118.0
80°	99.2	91.9	87.7	85.6	81.4	80.4	81.4	81.4	84.6	83.5	84.6
82.5°	68.9	63.7	60.6	57.4	55.3	56.4	55.3	55.3	56.4	55.3	55.3
85°	39.7	38.6	36.5	35.5	34.5	32.4	34.5	33.4	32.4	31.3	33.4
87.5°	18.8	17.8	17.8	15.7	15.7	14.6	15.7	15.7	14.6	14.6	14.6
90°	7.1	6.8	6.4	6.0	5.7	5.0	4.6	3.9	3.6	3.2	2.8
92.5°	41.2	55.5	77.1	114.5	141.8	144.3	100.2	59.7	35.5	29.2	22.8
95°	157.8	201.6	255.6	308.2	314.9	257.0	158.9	80.7	42.7	34.7	26.7
97.5°	279.4	323.5	366.5	385.0	340.2	235.7	129.7	69.7	43.4	37.5	31.6
100°	383.2	419.8	437.2	409.9	321.0	204.8	115.2	69.0	48.3	43.0	37.7
102.5°	466.0	478.8	461.0	394.9	287.2	181.3	109.1	72.2	54.4	49.2	44.1
105°	509.4	493.8	445.1	359.7	257.7	167.8	108.4	76.8	61.1	56.2	51.2
107.5°	514.4	476.7	412.3	326.3	235.7	160.7	110.9	83.2	67.9	63.4	59.0
110°	493.0	442.9	375.4	298.6	221.1	157.8	114.8	90.3	75.7	71.1	66.5

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	460.3	409.5	346.2	278.0	212.6	157.8	119.8	97.0	83.2	78.8	74.3
115°	426.6	377.9	322.8	264.1	206.9	158.9	124.8	104.2	91.0	86.6	82.1
117.5°	397.8	355.1	306.4	254.9	203.7	160.7	130.5	111.3	98.8	94.6	90.3
120°	375.4	336.3	293.6	247.4	201.6	163.5	136.1	119.1	106.6	102.2	97.8
122.5°	356.5	322.8	284.0	241.0	199.8	166.0	142.5	126.5	114.1	109.6	105.2
125°	342.0	311.0	274.8	235.3	198.4	168.9	148.2	132.9	121.2	116.6	112.0
127.5°	328.8	299.7	265.2	230.0	197.6	172.0	153.6	139.3	128.0	123.4	118.7
130°	315.3	287.6	256.3	224.7	196.9	174.9	158.9	145.4	134.4	129.8	125.1
132.5°	300.7	276.2	247.4	220.4	196.9	178.1	163.5	151.1	140.1	135.4	130.8
135°	287.2	264.5	239.9	217.2	196.9	180.9	167.8	156.1	145.0	140.2	135.4
137.5°	273.4	253.8	233.2	214.0	197.3	183.8	171.0	159.6	149.7	144.7	139.7
140°	260.9	244.6	227.9	211.9	197.6	185.6	174.2	163.5	153.2	148.4	143.6
142.5°	250.3	236.7	223.2	210.1	198.0	186.6	176.0	166.0	156.4	152.0	147.5
145°	241.4	230.3	219.3	208.3	197.6	187.3	177.7	168.9	159.6	155.5	151.4
147.5°	233.5	224.7	215.4	206.5	196.9	187.7	178.8	170.6	162.5	158.8	155.0
150°	226.8	220.0	212.2	204.4	195.9	187.7	179.9	172.4	164.6	161.6	158.5
152.5°	221.5	215.4	208.7	201.9	194.4	187.3	180.6	174.2	167.1	164.4	161.7
155°	215.8	210.8	205.1	199.1	192.7	186.6	180.9	175.2	169.2	166.7	164.2
157.5°	210.4	206.5	201.6	196.6	190.9	185.9	181.3	176.3	171.0	169.0	167.1
160°	205.1	201.6	198.0	193.4	189.1	184.8	181.3	177.0	172.4	170.8	169.2
162.5°	200.1	197.3	194.1	190.5	187.0	183.8	180.9	177.7	173.8	172.6	171.3
165°	195.2	193.0	190.5	187.7	184.8	182.7	180.6	177.7	174.9	173.9	172.8
167.5°	190.5	188.8	187.0	184.8	182.7	180.9	179.9	177.7	175.2	174.5	173.8
170°	186.3	185.2	184.1	182.4	180.9	179.9	179.2	177.7	176.0	175.4	174.9
172.5°	182.7	182.0	180.9	179.9	178.8	178.4	178.4	177.4	176.0	175.8	175.6
175°	179.5	178.8	178.8	177.7	177.4	177.4	177.7	177.0	176.0	176.0	176.0
177.5°	177.4	177.4	177.0	176.7	176.3	176.3	177.0	176.7	176.0	176.0	176.0
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1230.0	1230.0	1230.0	1230.0
2.5°	1200.8	1211.2	1218.6	1232.1
5°	1173.7	1192.5	1210.2	1229.0
7.5°	1146.5	1168.4	1196.6	1220.6
10°	1116.2	1144.4	1177.8	1210.2
12.5°	1085.9	1119.4	1155.9	1198.7
15°	1049.4	1092.2	1135.0	1181.0
17.5°	1017.0	1060.9	1106.8	1164.3
20°	980.5	1028.5	1078.6	1137.1
22.5°	948.1	1001.4	1053.6	1115.2
25°	911.6	963.8	1021.2	1087.0
27.5°	881.3	929.3	985.7	1056.7
30°	844.7	896.9	953.3	1024.3
32.5°	810.3	860.4	919.9	989.9
35°	774.8	825.9	879.2	946.0
37.5°	741.4	785.2	838.5	902.2
40°	703.8	751.8	799.8	850.0
42.5°	669.3	713.2	758.1	797.8
45°	630.7	668.3	711.1	743.5
47.5°	595.2	628.6	662.0	687.1
50°	559.7	585.8	610.8	632.8
52.5°	517.9	547.1	560.7	574.3
55°	480.3	497.0	509.6	523.1
57.5°	443.8	451.1	457.4	469.9
60°	395.7	404.1	411.4	420.8
62.5°	354.0	358.2	360.2	369.6
65°	314.3	313.3	318.5	323.7
67.5°	271.5	270.4	275.7	277.8
70°	229.7	228.7	229.7	234.9
72.5°	190.0	190.0	191.1	193.2
75°	153.5	153.5	154.5	156.6
77.5°	115.9	118.0	116.9	121.1
80°	84.6	82.5	84.6	86.7
82.5°	55.3	57.4	57.4	55.3
85°	31.3	31.3	31.3	31.3
87.5°	13.6	13.6	14.6	15.7
90°	2.1	1.4	0.7	0.4
92.5°	15.3	10.0	6.4	5.3
95°	18.8	14.9	12.1	11.7
97.5°	24.5	20.6	18.5	18.1
100°	30.9	27.0	25.6	24.9
102.5°	38.0	33.8	32.7	32.3
105°	45.5	41.9	40.2	40.2
107.5°	53.0	50.1	48.3	47.6
110°	61.1	57.9	56.5	55.8

TEST NUMBER: P1028293

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	69.0	65.8	64.7	64.0
115°	76.8	73.6	72.5	71.8
117.5°	84.2	81.0	80.0	78.9
120°	91.7	88.5	87.1	86.0
122.5°	98.5	95.3	94.2	93.5
125°	105.2	102.0	100.2	99.5
127.5°	111.6	107.7	105.6	104.5
130°	117.7	113.0	110.2	109.1
132.5°	123.0	117.7	114.1	112.7
135°	128.0	122.3	118.0	116.6
137.5°	132.2	126.5	122.6	121.6
140°	136.9	131.2	126.9	125.8
142.5°	141.1	135.4	131.5	130.8
145°	145.0	140.1	136.5	135.8
147.5°	149.3	144.7	141.5	141.1
150°	153.6	148.9	146.5	145.7
152.5°	157.1	153.2	151.1	150.7
155°	160.7	157.1	155.0	155.0
157.5°	163.9	160.7	158.9	158.9
160°	166.4	163.9	162.5	162.8
162.5°	169.2	167.1	165.7	166.0
165°	171.3	169.6	168.5	169.2
167.5°	172.8	171.7	171.0	171.3
170°	174.2	173.5	173.1	173.5
172.5°	175.2	174.5	174.2	174.9
175°	176.0	175.6	175.2	176.0
177.5°	176.3	176.0	176.0	176.7
180°	176.3	176.3	176.3	176.3

(END OF REPORT)