

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028298

Luminaire Tested: S125DIP-B850D375UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028298
REPORT IS A COMBINATION OF REPORTS P1002570 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D375UB30-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4711.0 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028298

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028298

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	93	90	87	84	82	79	76	74	72	68	67	65
2	94	86	79	74	89	82	76	71	74	69	65	67	63	60	60	57	55
3	85	76	68	62	81	72	65	59	65	60	55	59	54	51	53	50	47
4	78	67	59	52	74	64	56	50	58	52	47	53	48	43	47	43	40
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	38	35
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31
7	61	49	40	35	58	47	39	33	43	36	31	39	33	29	35	31	27
8	57	44	36	31	54	42	35	30	39	33	28	36	30	26	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	22	28	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8456	8456	8456
5°	8456	8259	8275
10°	8386	8070	8045
15°	8276	7843	7774
20°	8127	7581	7462
25°	7968	7295	7128
30°	7774	6996	6777
35°	7569	6683	6384
40°	7356	6353	6034
45°	7126	6030	5662
50°	6872	5665	5229
55°	6621	5262	4831
60°	6322	4837	4367
65°	5964	4345	3888
70°	5601	3780	3334
75°	4988	3112	2696
80°	4253	2325	1983
85°	3282	1376	1092

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7126 cd/sqm

TEST NUMBER: P1028298

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.5	2.6
10°-20°	351.8	7.5
20°-30°	519.3	11.0
30°-40°	605.9	12.9
40°-50°	608.5	12.9
50°-60°	534.2	11.3
60°-70°	397.9	8.4
70°-80°	227.2	4.8
80°-90°	66.3	1.4
90°-100°	30.4	0.6
100°-110°	90.3	1.9
110°-120°	153.1	3.2
120°-130°	201.5	4.3
130°-140°	225.8	4.8
140°-150°	221.4	4.7
150°-160°	185.9	3.9
160°-170°	123.6	2.6
170°-180°	43.3	0.9
0°-30°	995.6	21.1
0°-40°	1601.5	34.0
0°-60°	2744.3	58.3
0°-90°	3435.7	72.9
90°-120°	273.8	5.8
90°-150°	922.5	19.6
90°-180°	1275.0	27.1
0°-180°	4711.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1320	1320	1320	1320	1320	
5°	1318	1316	1305	1314	1314	125
15°	1256	1253	1241	1247	1247	354
25°	1140	1135	1121	1124	1120	525
35°	985	980	966	961	952	616
45°	806	802	789	777	774	621
55°	614	611	596	587	580	548
65°	414	412	401	392	387	411
75°	220	218	213	210	206	235
85°	57	58	58	57	55	63
90°	0	3	6	8	8	5
95°	23	24	27	30	31	24
105°	81	83	85	87	88	86
115°	153	155	155	155	155	152
125°	224	226	226	225	225	200
135°	291	293	293	293	292	224
145°	352	354	355	355	354	220
155°	403	403	404	405	403	186
165°	438	438	438	440	437	124
175°	456	454	454	457	454	43
180°	457	457	457	457	457	

TEST NUMBER: P1028298

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.8	1319.8	1319.8	1319.8	1319.8
2.5°	1323.9	1320.8	1310.4	1320.8	1319.8
5°	1317.7	1315.6	1305.1	1314.5	1313.5
7.5°	1308.3	1306.2	1294.7	1304.1	1303.1
10°	1294.7	1292.6	1281.1	1289.5	1288.4
12.5°	1278.0	1273.8	1263.4	1269.6	1269.6
15°	1256.1	1252.9	1241.4	1246.7	1246.7
17.5°	1233.1	1227.9	1216.4	1222.7	1217.4
20°	1202.8	1200.7	1187.2	1194.5	1189.2
22.5°	1172.5	1168.4	1155.8	1160.0	1156.9
25°	1140.2	1134.9	1121.4	1123.5	1120.3
27.5°	1102.6	1099.4	1085.9	1086.9	1083.8
30°	1066.0	1062.9	1047.2	1045.2	1042.0
32.5°	1026.4	1021.1	1007.6	1003.4	997.1
35°	984.6	980.4	965.8	960.6	952.2
37.5°	941.8	936.6	923.0	915.7	910.5
40°	897.9	892.7	878.1	868.7	865.6
42.5°	851.0	846.8	832.2	823.8	818.6
45°	806.1	801.9	789.3	776.8	773.7
47.5°	757.0	758.0	742.4	729.8	722.5
50°	710.0	706.9	694.3	680.8	673.5
52.5°	662.0	659.9	646.3	634.8	626.5
55°	613.9	610.8	596.2	586.8	579.5
57.5°	562.8	561.7	549.2	536.7	533.5
60°	514.7	510.6	499.1	488.6	481.3
62.5°	464.6	461.5	452.1	440.6	435.4
65°	414.5	412.4	400.9	391.5	387.4
67.5°	365.4	361.3	352.9	344.6	342.5
70°	319.5	314.3	304.9	298.6	294.4
72.5°	269.4	266.2	261.0	253.7	249.5
75°	220.3	218.2	213.0	209.9	205.7
77.5°	174.4	173.3	170.2	168.1	165.0
80°	131.6	131.6	129.5	128.4	126.3
82.5°	94.0	91.9	91.9	89.8	89.8
85°	57.4	58.5	58.5	57.4	55.3
87.5°	28.2	28.2	27.1	27.1	25.1
90°	0.4	3.2	5.7	7.5	8.5
92.5°	10.7	12.4	15.6	18.1	18.8
95°	23.1	23.8	27.4	29.9	30.6
97.5°	35.6	35.9	40.9	43.0	43.4
100°	49.8	49.8	54.4	57.6	58.3
102.5°	65.1	66.9	68.6	72.2	73.3
105°	81.1	82.9	85.0	87.1	88.2
107.5°	98.5	100.3	102.1	103.1	103.1
110°	116.6	118.4	119.5	120.5	120.2

TEST NUMBER: P1028298

CATALOG NUMBER: S125DIP-B850D375UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.1	135.8	137.3	137.6	136.9
115°	153.3	154.7	155.4	155.0	154.7
117.5°	171.8	172.1	172.8	173.2	171.8
120°	188.8	190.6	191.0	191.0	189.5
122.5°	207.3	207.7	208.7	208.4	207.3
125°	223.7	225.8	226.2	225.4	225.1
127.5°	241.8	242.9	243.2	242.9	242.2
130°	257.8	259.6	260.3	259.9	259.2
132.5°	273.8	277.0	276.7	276.3	275.2
135°	290.9	293.0	293.4	293.4	291.9
137.5°	306.9	309.0	309.7	310.1	308.3
140°	322.2	323.9	325.0	325.7	323.9
142.5°	337.5	338.9	340.3	340.7	338.9
145°	352.4	353.8	354.9	354.9	353.8
147.5°	366.3	367.3	368.0	369.1	366.3
150°	380.1	379.8	381.2	381.2	380.5
152.5°	391.5	392.2	392.6	393.6	392.2
155°	403.2	403.2	403.6	405.0	403.2
157.5°	413.9	413.2	413.6	415.0	412.5
160°	423.2	422.1	422.4	423.9	422.1
162.5°	431.3	430.6	430.6	432.4	430.3
165°	438.5	437.7	438.1	439.5	437.4
167.5°	444.9	443.4	443.4	445.6	443.4
170°	449.8	448.4	448.4	450.5	448.1
172.5°	453.4	452.0	452.0	454.1	452.0
175°	455.9	454.5	454.5	456.6	454.1
177.5°	457.7	456.2	455.9	458.0	455.5
180°	456.9	456.9	456.9	456.9	456.9

(END OF REPORT)