

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028316

Luminaire Tested: S125DIP-B850D375UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028316
REPORT IS A COMBINATION OF REPORTS P1002588 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D375UB40-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4684.0 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028316

CATALOG NUMBER: S125DIP-B850D375UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028316

CATALOG NUMBER: S125DIP-B850D375UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	93	90	87	84	82	79	76	74	72	68	67	65
2	94	86	79	74	89	82	76	71	74	69	65	67	63	60	60	57	55
3	85	76	68	62	81	72	65	59	65	60	55	59	54	51	53	50	47
4	78	67	59	52	74	64	56	50	58	52	47	53	48	43	47	43	40
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	38	35
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31
7	61	49	40	35	58	47	39	33	43	36	31	39	33	29	35	31	27
8	57	44	36	31	54	42	35	30	39	33	28	36	30	26	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	22	28	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8407	8407	8407
5°	8407	8211	8227
10°	8338	8023	7998
15°	8228	7798	7728
20°	8080	7537	7418
25°	7921	7252	7087
30°	7729	6955	6738
35°	7525	6645	6347
40°	7313	6316	5999
45°	7084	5996	5629
50°	6833	5632	5198
55°	6583	5231	4802
60°	6285	4809	4341
65°	5930	4320	3865
70°	5567	3757	3315
75°	4959	3095	2681
80°	4227	2311	1972
85°	3265	1366	1086

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7084 cd/sqm

TEST NUMBER: P1028316

CATALOG NUMBER: S125DIP-B850D375UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.8	2.6
10°-20°	349.7	7.5
20°-30°	516.3	11.0
30°-40°	602.4	12.9
40°-50°	605.0	12.9
50°-60°	531.1	11.3
60°-70°	395.6	8.4
70°-80°	225.9	4.8
80°-90°	65.9	1.4
90°-100°	30.2	0.6
100°-110°	89.8	1.9
110°-120°	152.3	3.3
120°-130°	200.4	4.3
130°-140°	224.6	4.8
140°-150°	220.1	4.7
150°-160°	184.9	3.9
160°-170°	122.9	2.6
170°-180°	43.0	0.9
0°-30°	989.8	21.1
0°-40°	1592.2	34.0
0°-60°	2728.3	58.2
0°-90°	3415.7	72.9
90°-120°	272.3	5.8
90°-150°	917.4	19.6
90°-180°	1268.0	27.1
0°-180°	4684.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1312	1312	1312	1312	1312	
5°	1310	1308	1298	1307	1306	124
15°	1249	1246	1234	1239	1239	352
25°	1134	1128	1115	1117	1114	522
35°	979	975	960	955	947	612
45°	801	797	785	772	769	617
55°	610	607	593	583	576	545
65°	412	410	399	389	385	409
75°	219	217	212	209	204	233
85°	57	58	58	57	55	63
90°	0	3	6	7	8	5
95°	23	24	27	30	30	24
105°	81	82	84	87	88	86
115°	152	154	154	154	154	151
125°	222	225	225	224	224	199
135°	289	291	292	292	290	223
145°	350	352	353	353	352	219
155°	401	401	401	403	401	185
165°	436	435	436	437	435	123
175°	453	452	452	454	452	43
180°	454	454	454	454	454	

TEST NUMBER: P1028316

CATALOG NUMBER: S125DIP-B850D375UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1312.1	1312.1	1312.1	1312.1	1312.1
2.5°	1316.2	1313.1	1302.7	1313.1	1312.1
5°	1310.0	1307.9	1297.5	1306.9	1305.8
7.5°	1300.7	1298.6	1287.2	1296.5	1295.5
10°	1287.2	1285.1	1273.7	1282.0	1280.9
12.5°	1270.6	1266.4	1256.0	1262.2	1262.2
15°	1248.8	1245.6	1234.2	1239.4	1239.4
17.5°	1225.9	1220.7	1209.3	1215.5	1210.3
20°	1195.8	1193.7	1180.2	1187.5	1182.3
22.5°	1165.7	1161.6	1149.1	1153.3	1150.1
25°	1133.5	1128.3	1114.8	1116.9	1113.8
27.5°	1096.2	1093.0	1079.6	1080.6	1077.5
30°	1059.8	1056.7	1041.1	1039.1	1036.0
32.5°	1020.4	1015.2	1001.7	997.5	991.3
35°	978.9	974.7	960.2	955.0	946.7
37.5°	936.3	931.1	917.6	910.4	905.2
40°	892.7	887.5	873.0	863.6	860.5
42.5°	846.0	841.8	827.3	819.0	813.8
45°	801.4	797.2	784.8	772.3	769.2
47.5°	752.6	753.6	738.0	725.6	718.3
50°	705.9	702.7	690.3	676.8	669.5
52.5°	658.1	656.0	642.5	631.1	622.8
55°	610.4	607.2	592.7	583.4	576.1
57.5°	559.5	558.5	546.0	533.5	530.4
60°	511.7	507.6	496.2	485.8	478.5
62.5°	461.9	458.8	449.5	438.0	432.9
65°	412.1	410.0	398.6	389.3	385.1
67.5°	363.3	359.2	350.9	342.6	340.5
70°	317.6	312.4	303.1	296.9	292.7
72.5°	267.8	264.7	259.5	252.2	248.1
75°	219.0	216.9	211.8	208.6	204.5
77.5°	173.4	172.3	169.2	167.1	164.0
80°	130.8	130.8	128.7	127.7	125.6
82.5°	93.4	91.3	91.3	89.3	89.3
85°	57.1	58.1	58.1	57.1	55.0
87.5°	28.0	28.0	27.0	27.0	24.9
90°	0.4	3.2	5.7	7.4	8.5
92.5°	10.6	12.4	15.6	18.0	18.7
95°	23.0	23.7	27.2	29.7	30.4
97.5°	35.4	35.7	40.7	42.8	43.1
100°	49.5	49.5	54.1	57.3	58.0
102.5°	64.7	66.5	68.3	71.8	72.9
105°	80.6	82.4	84.5	86.6	87.7
107.5°	98.0	99.7	101.5	102.6	102.6
110°	116.0	117.8	118.8	119.9	119.5



TEST NUMBER: P1028316

CATALOG NUMBER: S125DIP-B850D375UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	134.4	135.1	136.5	136.9	136.2
115°	152.4	153.8	154.5	154.2	153.8
117.5°	170.8	171.2	171.9	172.2	170.8
120°	187.8	189.6	189.9	189.9	188.5
122.5°	206.2	206.5	207.6	207.2	206.2
125°	222.4	224.6	224.9	224.2	223.9
127.5°	240.5	241.5	241.9	241.5	240.8
130°	256.4	258.2	258.9	258.5	257.8
132.5°	272.3	275.5	275.1	274.8	273.7
135°	289.3	291.4	291.8	291.8	290.3
137.5°	305.2	307.3	308.0	308.4	306.6
140°	320.4	322.2	323.2	323.9	322.2
142.5°	335.6	337.0	338.4	338.8	337.0
145°	350.5	351.9	352.9	352.9	351.9
147.5°	364.3	365.3	366.0	367.1	364.3
150°	378.0	377.7	379.1	379.1	378.4
152.5°	389.4	390.1	390.4	391.5	390.1
155°	401.0	401.0	401.4	402.8	401.0
157.5°	411.6	410.9	411.3	412.7	410.2
160°	420.8	419.8	420.1	421.5	419.8
162.5°	429.0	428.3	428.3	430.0	427.9
165°	436.0	435.3	435.7	437.1	435.0
167.5°	442.4	441.0	441.0	443.1	441.0
170°	447.4	445.9	445.9	448.1	445.6
172.5°	450.9	449.5	449.5	451.6	449.5
175°	453.4	452.0	452.0	454.1	451.6
177.5°	455.1	453.7	453.4	455.5	453.0
180°	454.4	454.4	454.4	454.4	454.4

(END OF REPORT)