

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028567

Luminaire Tested: S125RDIP-B1270D1090UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028567
REPORT IS A COMBINATION OF REPORTS P1005124 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D1090UB27-4F0-XX-W2A-F4
Description: Define 5 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8505.5 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028567

CATALOG NUMBER: S125RDIP-B1270D1090UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1028567

CATALOG NUMBER: S125RDIP-B1270D1090UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63
1	100	95	92	88	93	89	86	83	77	74	72	66	64	63	56	55	53
2	91	84	77	72	84	78	73	68	68	64	60	58	55	53	49	47	45
3	83	74	66	61	77	69	62	57	60	55	51	52	48	45	44	41	39
4	76	65	57	51	71	61	54	49	53	48	44	46	42	39	39	36	34
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	32	29
6	65	52	44	39	60	49	42	37	43	37	33	38	33	30	32	29	26
7	60	47	40	34	56	45	37	32	39	33	29	34	30	26	30	26	23
8	56	43	35	30	52	41	34	29	36	30	26	31	27	23	27	24	21
9	52	40	32	27	48	37	30	26	33	27	23	29	24	21	25	22	19
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13142	13142	13142
5°	13143	12814	12834
10°	13015	12491	12381
15°	12831	12039	11785
20°	12603	11495	11159
25°	12341	10964	10488
30°	12021	10380	9784
35°	11694	9788	9036
40°	11384	9179	8305
45°	11010	8521	7540
50°	10632	7823	6760
55°	10192	7137	5954
60°	9742	6351	5116
65°	9206	5473	4213
70°	8580	4455	3316
75°	7717	3350	2417
80°	6508	2169	1630
85°	4871	1166	919

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11010 cd/sqm

TEST NUMBER: P1028567

CATALOG NUMBER: S125RDIP-B1270D1090UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.0	2.3
10°-20°	539.5	6.3
20°-30°	782.2	9.2
30°-40°	891.2	10.5
40°-50°	868.6	10.2
50°-60°	731.0	8.6
60°-70°	512.3	6.0
70°-80°	262.6	3.1
80°-90°	67.4	0.8
90°-100°	366.0	4.3
100°-110°	760.1	8.9
110°-120°	710.0	8.3
120°-130°	574.5	6.8
130°-140°	461.6	5.4
140°-150°	348.4	4.1
150°-160°	245.3	2.9
160°-170°	144.6	1.7
170°-180°	47.0	0.6
0°-30°	1514.8	17.8
0°-40°	2405.9	28.3
0°-60°	4005.6	47.1
0°-90°	4848.0	57.0
90°-120°	1836.1	21.6
90°-150°	3220.6	37.9
90°-180°	3658.0	43.0
0°-180°	8505.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2051	2051	2051	2051	2051	
5°	2048	2042	2025	2040	2037	194
15°	1947	1938	1906	1904	1890	549
25°	1766	1743	1686	1665	1648	813
35°	1521	1484	1414	1370	1348	953
45°	1246	1201	1115	1053	1030	961
55°	945	895	809	739	714	845
65°	640	587	505	443	420	634
75°	341	294	229	195	184	360
85°	85	57	50	48	46	93
90°	1	9	16	21	22	7
95°	32	96	868	394	230	34
105°	111	155	710	1399	1298	117
115°	198	239	570	1229	1446	195
125°	274	321	547	978	1140	244
135°	321	386	543	820	946	249
145°	374	429	545	678	747	235
155°	427	460	531	600	626	197
165°	466	479	510	540	549	131
175°	485	485	489	495	493	46
180°	486	486	486	486	486	

TEST NUMBER: P1028567

CATALOG NUMBER: S125RDIP-B1270D1090UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2051.1	2051.1	2051.1	2051.1	2051.1
2.5°	2055.7	2051.1	2035.6	2051.1	2049.5
5°	2048.0	2041.8	2024.8	2040.2	2037.1
7.5°	2032.5	2026.3	2006.2	2018.6	2015.5
10°	2009.3	2004.6	1982.9	1987.6	1982.9
12.5°	1982.9	1976.7	1945.7	1948.8	1941.1
15°	1947.3	1938.0	1905.5	1903.9	1890.0
17.5°	1910.1	1896.2	1857.4	1849.7	1838.9
20°	1865.2	1849.7	1800.1	1792.4	1778.4
22.5°	1815.6	1800.1	1747.5	1730.4	1719.6
25°	1766.0	1742.8	1685.5	1665.4	1648.3
27.5°	1710.3	1682.4	1622.0	1595.6	1578.6
30°	1648.3	1618.9	1553.8	1518.2	1504.2
32.5°	1587.9	1552.3	1485.6	1445.4	1426.8
35°	1521.3	1484.1	1414.4	1369.5	1347.8
37.5°	1457.8	1412.8	1341.6	1288.9	1267.2
40°	1389.6	1343.1	1268.8	1209.9	1191.3
42.5°	1318.3	1270.3	1192.9	1137.1	1107.7
45°	1245.5	1200.6	1115.4	1053.4	1030.2
47.5°	1169.6	1123.1	1037.9	974.4	948.1
50°	1098.4	1047.2	958.9	893.9	870.6
52.5°	1020.9	968.2	886.1	814.9	791.6
55°	945.0	895.4	808.7	739.0	714.2
57.5°	867.5	814.9	731.2	663.0	641.4
60°	793.2	739.0	655.3	587.1	563.9
62.5°	714.2	663.0	577.8	515.9	492.6
65°	639.8	587.1	505.0	443.1	419.8
67.5°	565.4	512.8	433.8	374.9	356.3
70°	489.5	436.9	359.4	311.4	292.8
72.5°	415.2	364.1	292.8	249.4	238.6
75°	340.8	294.3	229.3	195.2	184.4
77.5°	264.9	227.7	173.5	147.2	137.9
80°	201.4	164.2	120.8	106.9	103.8
82.5°	139.4	106.9	80.6	75.9	74.4
85°	85.2	57.3	49.6	48.0	46.5
87.5°	35.6	24.8	23.2	23.2	21.7
90°	1.0	8.8	15.7	20.6	22.5
92.5°	14.7	80.4	390.9	104.4	72.5
95°	32.3	95.6	868.1	393.8	230.2
97.5°	50.0	103.4	937.6	711.3	504.6
100°	68.6	118.6	884.7	1005.2	764.2
102.5°	89.2	135.7	791.7	1254.1	1054.2
105°	110.7	154.8	710.3	1398.6	1298.2
107.5°	131.3	174.8	649.6	1439.2	1445.2
110°	153.8	196.0	609.4	1400.6	1511.8

TEST NUMBER: P1028567

CATALOG NUMBER: S125RDIP-B1270D1090UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	176.4	217.0	585.9	1319.8	1503.9
115°	197.9	238.6	570.2	1229.1	1446.1
117.5°	217.5	260.6	561.4	1146.8	1358.9
120°	237.1	281.6	555.5	1077.8	1274.7
122.5°	257.7	302.2	550.6	1022.4	1200.2
125°	274.3	321.4	546.7	977.8	1139.5
127.5°	288.1	340.0	544.8	939.6	1083.6
130°	300.8	357.6	542.8	900.9	1039.5
132.5°	310.6	373.3	542.8	859.2	995.4
135°	321.4	386.5	542.8	819.6	946.5
137.5°	335.1	398.8	543.8	777.9	895.5
140°	346.8	409.0	544.8	739.7	841.6
142.5°	360.6	418.8	545.7	706.9	791.7
145°	374.3	428.6	544.8	678.5	746.6
147.5°	389.0	437.5	542.8	654.0	706.4
150°	401.7	445.3	539.9	633.9	674.1
152.5°	415.4	453.2	535.9	616.8	648.6
155°	427.2	459.6	531.0	600.1	626.1
157.5°	438.0	465.9	526.1	584.4	605.5
160°	448.7	470.8	521.2	568.8	584.9
162.5°	457.6	475.6	515.4	554.6	566.3
165°	466.4	479.1	509.5	540.3	548.7
167.5°	472.2	481.0	503.6	527.2	532.0
170°	478.1	483.5	498.7	514.4	517.3
172.5°	482.0	484.5	492.8	504.1	503.6
175°	485.0	485.0	488.9	494.8	492.8
177.5°	486.9	485.0	486.0	488.9	486.0
180°	486.0	486.0	486.0	486.0	486.0

(END OF REPORT)