

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028602

Luminaire Tested: S125RDIP-B1270D1270UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028602
REPORT IS A COMBINATION OF REPORTS P1005179 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D1270UB30-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9055.0 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028602

CATALOG NUMBER: S125RDIP-B1270D1270UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028602

CATALOG NUMBER: S125RDIP-B1270D1270UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	87	92	88	85	82	75	73	71	64	62	61	53	52	51
2	90	83	77	72	83	77	72	67	66	62	59	56	54	51	47	45	43
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	31	28
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	28	25
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	30	25	30	26	23	26	23	20
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	21	18
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13256	13256	13256
5°	13257	12925	12946
10°	13128	12599	12488
15°	12942	12144	11887
20°	12712	11595	11256
25°	12448	11059	10579
30°	12125	10471	9869
35°	11796	9872	9114
40°	11482	9259	8377
45°	11106	8595	7605
50°	10724	7891	6819
55°	10281	7199	6005
60°	9826	6406	5161
65°	9285	5520	4250
70°	8656	4494	3344
75°	7785	3379	2437
80°	6563	2189	1644
85°	4911	1176	926

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11106 cd/sqm

TEST NUMBER: P1028602

CATALOG NUMBER: S125RDIP-B1270D1270UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.7	2.2
10°-20°	544.2	6.0
20°-30°	789.0	8.7
30°-40°	898.9	9.9
40°-50°	876.2	9.7
50°-60°	737.4	8.1
60°-70°	516.7	5.7
70°-80°	264.9	2.9
80°-90°	68.4	0.8
90°-100°	99.2	1.1
100°-110°	294.8	3.3
110°-120°	499.9	5.5
120°-130°	658.2	7.3
130°-140°	737.5	8.1
140°-150°	722.9	8.0
150°-160°	607.2	6.7
160°-170°	403.6	4.5
170°-180°	141.3	1.6
0°-30°	1527.9	16.9
0°-40°	2426.8	26.8
0°-60°	4040.3	44.6
0°-90°	4890.3	54.0
90°-120°	894.0	9.9
90°-150°	3012.5	33.3
90°-180°	4165.0	46.0
0°-180°	9055.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2069	2069	2069	2069	2069	
5°	2066	2060	2042	2058	2055	196
15°	1964	1955	1922	1920	1906	554
25°	1781	1758	1700	1680	1663	820
35°	1534	1497	1427	1381	1360	961
45°	1256	1211	1125	1063	1039	969
55°	953	903	816	745	720	852
65°	645	592	509	447	424	639
75°	344	297	231	197	186	363
85°	86	58	50	48	47	94
90°	1	10	19	24	28	10
95°	76	78	89	98	100	79
105°	265	271	278	284	288	282
115°	500	505	508	506	505	495
125°	730	737	739	736	735	654
135°	950	957	958	958	953	732
145°	1151	1156	1159	1159	1156	719
155°	1317	1317	1318	1323	1317	607
165°	1432	1430	1431	1435	1428	404
175°	1489	1484	1484	1491	1483	141
180°	1492	1492	1492	1492	1492	

TEST NUMBER: P1028602

CATALOG NUMBER: S125RDIP-B1270D1270UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2068.9	2068.9	2068.9	2068.9	2068.9
2.5°	2073.6	2068.9	2053.2	2068.9	2067.3
5°	2065.7	2059.5	2042.3	2057.9	2054.8
7.5°	2050.1	2043.9	2023.6	2036.1	2032.9
10°	2026.7	2022.0	2000.1	2004.8	2000.1
12.5°	2000.1	1993.9	1962.6	1965.7	1957.9
15°	1964.2	1954.8	1922.0	1920.4	1906.4
17.5°	1926.7	1912.6	1873.5	1865.7	1854.8
20°	1881.4	1865.7	1815.7	1807.9	1793.9
22.5°	1831.4	1815.7	1762.6	1745.4	1734.5
25°	1781.4	1757.9	1700.1	1679.8	1662.6
27.5°	1725.1	1697.0	1636.0	1609.5	1592.3
30°	1662.6	1632.9	1567.3	1531.3	1517.3
32.5°	1601.7	1565.7	1498.5	1457.9	1439.1
35°	1534.5	1497.0	1426.6	1381.3	1359.5
37.5°	1470.4	1425.1	1353.2	1300.1	1278.2
40°	1401.6	1354.8	1279.8	1220.4	1201.6
42.5°	1329.8	1281.3	1203.2	1146.9	1117.3
45°	1256.3	1211.0	1125.1	1062.6	1039.1
47.5°	1179.8	1132.9	1046.9	982.9	956.3
50°	1107.9	1056.3	967.2	901.6	878.2
52.5°	1029.7	976.6	893.8	821.9	798.5
55°	953.2	903.2	815.7	745.4	720.4
57.5°	875.1	821.9	737.5	668.8	646.9
60°	800.0	745.4	661.0	592.2	568.8
62.5°	720.4	668.8	582.8	520.3	496.9
65°	645.3	592.2	509.4	446.9	423.5
67.5°	570.3	517.2	437.5	378.1	359.4
70°	493.8	440.7	362.5	314.1	295.3
72.5°	418.8	367.2	295.3	251.6	240.6
75°	343.8	296.9	231.3	196.9	185.9
77.5°	267.2	229.7	175.0	148.4	139.1
80°	203.1	165.6	121.9	107.8	104.7
82.5°	140.6	107.8	81.3	76.6	75.0
85°	85.9	57.8	50.0	48.4	46.9
87.5°	35.9	25.0	23.4	23.4	21.9
90°	1.2	10.5	18.6	24.4	27.9
92.5°	34.8	40.6	51.1	59.2	61.5
95°	75.5	77.8	89.4	97.5	99.9
97.5°	116.1	117.3	133.5	140.5	141.7
100°	162.6	162.6	177.7	188.1	190.4
102.5°	212.5	218.3	224.1	235.7	239.2
105°	264.8	270.6	277.5	284.5	288.0
107.5°	321.7	327.5	333.3	336.8	336.8
110°	380.9	386.7	390.2	393.7	392.5



TEST NUMBER: P1028602

CATALOG NUMBER: S125RDIP-B1270D1270UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	441.3	443.6	448.2	449.4	447.1
115°	500.5	505.1	507.5	506.3	505.1
117.5°	560.9	562.1	564.4	565.5	560.9
120°	616.6	622.4	623.6	623.6	619.0
122.5°	677.0	678.2	681.7	680.5	677.0
125°	730.4	737.4	738.6	736.2	735.1
127.5°	789.7	793.1	794.3	793.1	790.8
130°	841.9	847.7	850.0	848.9	846.6
132.5°	894.2	904.6	903.5	902.3	898.8
135°	949.9	956.9	958.0	958.0	953.4
137.5°	1002.2	1009.1	1011.5	1012.6	1006.8
140°	1052.1	1057.9	1061.4	1063.7	1057.9
142.5°	1102.0	1106.7	1111.3	1112.5	1106.7
145°	1150.8	1155.5	1158.9	1158.9	1155.5
147.5°	1196.1	1199.6	1201.9	1205.4	1196.1
150°	1241.4	1240.2	1244.9	1244.9	1242.6
152.5°	1278.6	1280.9	1282.0	1285.5	1280.9
155°	1316.9	1316.9	1318.0	1322.7	1316.9
157.5°	1351.7	1349.4	1350.5	1355.2	1347.1
160°	1381.9	1378.4	1379.6	1384.2	1378.4
162.5°	1408.6	1406.3	1406.3	1412.1	1405.1
165°	1431.8	1429.5	1430.7	1435.3	1428.4
167.5°	1452.7	1448.1	1448.1	1455.1	1448.1
170°	1469.0	1464.4	1464.4	1471.3	1463.2
172.5°	1480.6	1476.0	1476.0	1482.9	1476.0
175°	1488.7	1484.1	1484.1	1491.1	1482.9
177.5°	1494.5	1489.9	1488.7	1495.7	1487.6
180°	1492.2	1492.2	1492.2	1492.2	1492.2

(END OF REPORT)