

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028608

Luminaire Tested: S125RDIP-B1270D1270UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028608
REPORT IS A COMBINATION OF REPORTS P1005185 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D1270UB35-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9094.0 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028608

CATALOG NUMBER: S125RDIP-B1270D1270UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028608

CATALOG NUMBER: S125RDIP-B1270D1270UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	87	92	88	85	82	75	73	71	64	62	61	53	52	51
2	90	83	77	72	83	77	72	67	66	62	59	56	54	51	47	45	43
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	31	28
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	28	25
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	30	25	30	26	23	26	23	20
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	21	18
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13313	13313	13313
5°	13314	12981	13001
10°	13184	12653	12542
15°	12997	12195	11938
20°	12766	11645	11304
25°	12501	11107	10624
30°	12177	10515	9911
35°	11847	9915	9153
40°	11532	9299	8413
45°	11153	8632	7638
50°	10769	7925	6848
55°	10325	7230	6030
60°	9869	6433	5182
65°	9326	5544	4268
70°	8693	4514	3359
75°	7816	3394	2447
80°	6592	2198	1650
85°	4934	1180	930

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11153 cd/sqm

TEST NUMBER: P1028608

CATALOG NUMBER: S125RDIP-B1270D1270UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.6	2.2
10°-20°	546.5	6.0
20°-30°	792.4	8.7
30°-40°	902.8	9.9
40°-50°	879.9	9.7
50°-60°	740.5	8.1
60°-70°	518.9	5.7
70°-80°	266.0	2.9
80°-90°	68.7	0.8
90°-100°	99.7	1.1
100°-110°	296.1	3.3
110°-120°	502.1	5.5
120°-130°	661.0	7.3
130°-140°	740.7	8.1
140°-150°	726.0	8.0
150°-160°	609.8	6.7
160°-170°	405.4	4.5
170°-180°	141.9	1.6
0°-30°	1534.4	16.9
0°-40°	2437.2	26.8
0°-60°	4057.7	44.6
0°-90°	4911.3	54.0
90°-120°	897.8	9.9
90°-150°	3025.6	33.3
90°-180°	4183.0	46.0
0°-180°	9094.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2078	2078	2078	2078	2078	
5°	2075	2068	2051	2067	2064	197
15°	1973	1963	1930	1929	1914	556
25°	1789	1766	1707	1687	1670	823
35°	1541	1503	1433	1387	1365	965
45°	1262	1216	1130	1067	1044	973
55°	957	907	819	749	723	856
65°	648	595	512	449	425	642
75°	345	298	232	198	187	365
85°	86	58	50	49	47	95
90°	1	10	19	24	28	10
95°	76	78	90	98	100	79
105°	266	272	279	286	289	284
115°	503	507	510	508	507	497
125°	734	741	742	739	738	657
135°	954	961	962	962	958	735
145°	1156	1160	1164	1164	1160	723
155°	1323	1323	1324	1328	1323	609
165°	1438	1436	1437	1442	1434	406
175°	1495	1490	1490	1498	1489	142
180°	1499	1499	1499	1499	1499	

TEST NUMBER: P1028608

CATALOG NUMBER: S125RDIP-B1270D1270UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2077.8	2077.8	2077.8	2077.8	2077.8
2.5°	2082.5	2077.8	2062.1	2077.8	2076.2
5°	2074.6	2068.3	2051.1	2066.8	2063.6
7.5°	2058.9	2052.6	2032.2	2044.8	2041.7
10°	2035.4	2030.7	2008.7	2013.4	2008.7
12.5°	2008.7	2002.4	1971.0	1974.2	1966.3
15°	1972.6	1963.2	1930.2	1928.7	1914.5
17.5°	1935.0	1920.8	1881.6	1873.7	1862.8
20°	1889.4	1873.7	1823.5	1815.7	1801.6
22.5°	1839.2	1823.5	1770.2	1752.9	1741.9
25°	1789.0	1765.5	1707.4	1687.0	1669.7
27.5°	1732.5	1704.3	1643.1	1616.4	1599.1
30°	1669.7	1639.9	1574.0	1537.9	1523.8
32.5°	1608.5	1572.4	1505.0	1464.2	1445.3
35°	1541.1	1503.4	1432.8	1387.3	1365.3
37.5°	1476.7	1431.2	1359.0	1305.7	1283.7
40°	1407.7	1360.6	1285.3	1225.6	1206.8
42.5°	1335.5	1286.8	1208.4	1151.9	1122.1
45°	1261.7	1216.2	1129.9	1067.1	1043.6
47.5°	1184.8	1137.7	1051.4	987.1	960.4
50°	1112.6	1060.8	971.4	905.5	881.9
52.5°	1034.2	980.8	897.6	825.5	801.9
55°	957.3	907.1	819.2	748.6	723.4
57.5°	878.8	825.5	740.7	671.7	649.7
60°	803.5	748.6	663.8	594.8	571.2
62.5°	723.4	671.7	585.3	522.6	499.0
65°	648.1	594.8	511.6	448.8	425.3
67.5°	572.8	519.4	439.4	379.8	360.9
70°	495.9	442.5	364.1	315.4	296.6
72.5°	420.6	368.8	296.6	252.7	241.7
75°	345.2	298.2	232.3	197.7	186.7
77.5°	268.4	230.7	175.8	149.1	139.7
80°	204.0	166.3	122.4	108.3	105.1
82.5°	141.2	108.3	81.6	76.9	75.3
85°	86.3	58.1	50.2	48.6	47.1
87.5°	36.1	25.1	23.5	23.5	22.0
90°	1.2	10.5	18.7	24.5	28.0
92.5°	35.0	40.8	51.3	59.5	61.8
95°	75.8	78.1	89.8	98.0	100.3
97.5°	116.6	117.8	134.1	141.1	142.3
100°	163.3	163.3	178.4	188.9	191.3
102.5°	213.4	219.3	225.1	236.8	240.3
105°	265.9	271.7	278.7	285.7	289.2
107.5°	323.1	328.9	334.7	338.2	338.2
110°	382.5	388.4	391.9	395.4	394.2

TEST NUMBER: P1028608

CATALOG NUMBER: S125RDIP-B1270D1270UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.2	445.5	450.2	451.4	449.0
115°	502.7	507.3	509.7	508.5	507.3
117.5°	563.3	564.5	566.8	568.0	563.3
120°	619.3	625.1	626.3	626.3	621.6
122.5°	679.9	681.1	684.6	683.4	679.9
125°	733.6	740.6	741.8	739.4	738.3
127.5°	793.1	796.6	797.7	796.6	794.2
130°	845.6	851.4	853.7	852.6	850.2
132.5°	898.0	908.5	907.4	906.2	902.7
135°	954.0	961.0	962.2	962.2	957.5
137.5°	1006.5	1013.5	1015.8	1017.0	1011.2
140°	1056.6	1062.5	1066.0	1068.3	1062.5
142.5°	1106.8	1111.5	1116.1	1117.3	1111.5
145°	1155.8	1160.4	1163.9	1163.9	1160.4
147.5°	1201.3	1204.8	1207.1	1210.6	1201.3
150°	1246.8	1245.6	1250.3	1250.3	1247.9
152.5°	1284.1	1286.4	1287.6	1291.1	1286.4
155°	1322.6	1322.6	1323.7	1328.4	1322.6
157.5°	1357.6	1355.2	1356.4	1361.0	1352.9
160°	1387.9	1384.4	1385.5	1390.2	1384.4
162.5°	1414.7	1412.4	1412.4	1418.2	1411.2
165°	1438.0	1435.7	1436.9	1441.5	1434.5
167.5°	1459.0	1454.4	1454.4	1461.3	1454.4
170°	1475.3	1470.7	1470.7	1477.7	1469.5
172.5°	1487.0	1482.3	1482.3	1489.3	1482.3
175°	1495.2	1490.5	1490.5	1497.5	1489.3
177.5°	1501.0	1496.3	1495.2	1502.2	1494.0
180°	1498.7	1498.7	1498.7	1498.7	1498.7

(END OF REPORT)