

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028621

Luminaire Tested: S125RDIP-B1270D1270UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028621
REPORT IS A COMBINATION OF REPORTS P1005198 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D1270UB50-4F0-XX-W2A-F4
Description: Define 5 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8870.5 lumens
Efficiency: N/A
Efficacy: 92.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028621

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1028621

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	99	94	91	87	91	88	84	81	75	73	70	63	62	60	52	51	50
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	43
3	82	73	66	60	76	68	61	56	58	53	50	49	46	43	41	39	37
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	33	30	28
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	24	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20
9	51	39	32	26	47	37	30	25	32	27	23	28	23	20	24	20	18
10	48	36	29	24	44	34	27	23	30	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12746	12746	12746
5°	12747	12428	12448
10°	12622	12115	12008
15°	12444	11677	11429
20°	12223	11149	10823
25°	11969	10634	10172
30°	11659	10068	9489
35°	11341	9493	8763
40°	11040	8902	8054
45°	10679	8265	7313
50°	10311	7588	6556
55°	9885	6922	5773
60°	9449	6160	4962
65°	8928	5308	4087
70°	8323	4322	3216
75°	7483	3249	2344
80°	6311	2104	1581
85°	4723	1131	891

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10679 cd/sqm

TEST NUMBER: P1028621

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	2.1
10°-20°	523.2	5.9
20°-30°	758.7	8.6
30°-40°	864.3	9.7
40°-50°	842.5	9.5
50°-60°	709.0	8.0
60°-70°	496.8	5.6
70°-80°	254.7	2.9
80°-90°	65.7	0.7
90°-100°	417.0	4.7
100°-110°	866.3	9.8
110°-120°	809.1	9.1
120°-130°	654.7	7.4
130°-140°	526.1	5.9
140°-150°	397.1	4.5
150°-160°	279.6	3.2
160°-170°	164.8	1.9
170°-180°	53.6	0.6
0°-30°	1469.1	16.6
0°-40°	2333.5	26.3
0°-60°	3884.9	43.8
0°-90°	4702.2	53.0
90°-120°	2092.5	23.6
90°-150°	3670.4	41.4
90°-180°	4168.0	47.0
0°-180°	8870.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1989	1989	1989	1989	1989	
5°	1986	1980	1964	1979	1976	188
15°	1889	1880	1848	1847	1833	533
25°	1713	1690	1635	1615	1599	788
35°	1475	1439	1372	1328	1307	924
45°	1208	1164	1082	1022	999	932
55°	916	868	784	717	693	820
65°	620	569	490	430	407	614
75°	330	286	222	189	179	349
85°	83	56	48	47	45	90
90°	1	10	18	24	26	7
95°	37	109	989	449	262	38
105°	126	176	810	1594	1480	133
115°	226	272	650	1401	1648	222
125°	313	366	623	1114	1299	278
135°	366	440	619	934	1079	284
145°	426	488	621	773	851	267
155°	487	524	605	684	714	224
165°	532	546	581	616	625	150
175°	553	553	557	564	562	53
180°	554	554	554	554	554	

TEST NUMBER: P1028621

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1989.3	1989.3	1989.3	1989.3	1989.3
2.5°	1993.8	1989.3	1974.3	1989.3	1987.8
5°	1986.3	1980.3	1963.8	1978.8	1975.8
7.5°	1971.3	1965.3	1945.7	1957.7	1954.7
10°	1948.7	1944.2	1923.2	1927.7	1923.2
12.5°	1923.2	1917.2	1887.1	1890.1	1882.6
15°	1888.6	1879.6	1848.1	1846.6	1833.0
17.5°	1852.6	1839.0	1801.5	1794.0	1783.5
20°	1809.0	1794.0	1745.9	1738.4	1724.9
22.5°	1760.9	1745.9	1694.8	1678.3	1667.8
25°	1712.8	1690.3	1634.7	1615.2	1598.6
27.5°	1658.7	1631.7	1573.1	1547.6	1531.0
30°	1598.6	1570.1	1507.0	1472.4	1458.9
32.5°	1540.1	1505.5	1440.9	1401.8	1383.8
35°	1475.4	1439.4	1371.8	1328.2	1307.2
37.5°	1413.8	1370.3	1301.2	1250.1	1229.0
40°	1347.7	1302.7	1230.5	1173.4	1155.4
42.5°	1278.6	1232.0	1156.9	1102.8	1074.3
45°	1208.0	1164.4	1081.8	1021.7	999.2
47.5°	1134.4	1089.3	1006.7	945.1	919.5
50°	1065.3	1015.7	930.0	866.9	844.4
52.5°	990.1	939.1	859.4	790.3	767.8
55°	916.5	868.4	784.3	716.7	692.6
57.5°	841.4	790.3	709.2	643.1	622.0
60°	769.3	716.7	635.6	569.4	546.9
62.5°	692.6	643.1	560.4	500.3	477.8
65°	620.5	569.4	489.8	429.7	407.2
67.5°	548.4	497.3	420.7	363.6	345.6
70°	474.8	423.7	348.6	302.0	284.0
72.5°	402.7	353.1	284.0	241.9	231.4
75°	330.5	285.5	222.4	189.3	178.8
77.5°	256.9	220.9	168.3	142.7	133.7
80°	195.3	159.3	117.2	103.7	100.7
82.5°	135.2	103.7	78.1	73.6	72.1
85°	82.6	55.6	48.1	46.6	45.1
87.5°	34.6	24.0	22.5	22.5	21.0
90°	1.1	10.0	17.9	23.5	25.7
92.5°	16.7	91.6	445.5	118.9	82.6
95°	36.8	108.8	989.3	448.9	262.4
97.5°	56.9	117.8	1068.6	810.6	575.0
100°	78.2	135.2	1008.3	1145.6	870.9
102.5°	101.6	154.6	902.2	1429.2	1201.5
105°	126.2	176.4	809.5	1593.9	1479.5
107.5°	149.6	199.4	740.3	1640.2	1647.0
110°	175.3	223.3	694.5	1596.2	1722.9

TEST NUMBER: P1028621

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	201.0	247.4	667.7	1504.0	1714.0
115°	225.6	271.8	649.9	1400.8	1648.1
117.5°	247.9	297.0	639.8	1307.0	1548.7
120°	270.2	321.0	633.1	1228.2	1452.7
122.5°	293.7	344.4	627.5	1165.2	1367.8
125°	312.6	366.2	623.1	1114.4	1298.6
127.5°	328.3	387.4	620.8	1070.8	1234.9
130°	342.8	407.6	618.6	1026.7	1184.7
132.5°	354.0	425.4	618.6	979.2	1134.5
135°	366.2	440.5	618.6	934.0	1078.6
137.5°	381.9	454.4	619.7	886.6	1020.6
140°	395.3	466.2	620.8	843.0	959.2
142.5°	410.9	477.4	621.9	805.7	902.2
145°	426.5	488.5	620.8	773.2	850.8
147.5°	443.3	498.6	618.6	745.3	805.1
150°	457.8	507.5	615.2	722.4	768.2
152.5°	473.4	516.4	610.8	702.9	739.2
155°	486.8	523.7	605.2	684.0	713.5
157.5°	499.1	531.0	599.6	666.0	690.1
160°	511.4	536.5	594.0	648.2	666.6
162.5°	521.4	542.1	587.3	632.0	645.4
165°	531.5	546.0	580.6	615.8	625.3
167.5°	538.2	548.2	573.9	600.8	606.3
170°	544.9	551.0	568.3	586.2	589.6
172.5°	549.4	552.2	561.6	574.4	573.9
175°	552.7	552.7	557.2	563.9	561.6
177.5°	554.9	552.7	553.8	557.2	553.8
180°	553.8	553.8	553.8	553.8	553.8

(END OF REPORT)