

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028630

Luminaire Tested: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028630
REPORT IS A COMBINATION OF REPORTS P1005217 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4
Description: Define 5 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6256.0 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83
1	105	101	97	94	100	96	93	90	88	86	83	81	79	77	74	73	71
2	96	89	83	77	92	85	80	75	78	74	70	72	68	65	66	63	61
3	88	79	71	65	84	75	69	63	70	64	60	64	60	56	59	56	53
4	81	70	62	56	77	67	60	54	62	56	51	57	53	49	53	49	46
5	75	63	55	48	71	60	53	47	56	50	45	52	47	42	48	44	40
6	69	57	48	42	66	55	47	41	51	44	39	47	42	37	44	39	36
7	64	51	43	38	61	50	42	37	46	40	35	43	37	33	40	35	32
8	60	47	39	33	57	45	38	33	42	36	31	39	34	30	37	32	29
9	56	43	35	30	53	42	34	29	39	33	28	36	31	27	34	29	26
10	52	40	32	27	50	38	31	27	36	30	26	34	28	25	32	27	24

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12195	12195	12195	12195
5°	12184	13744	12184	10564
10°	12116	15445	12075	9132
15°	11985	16340	11902	7951
20°	11825	17639	11720	7187
25°	11618	19966	11488	6523
30°	11408	21222	11236	6048
35°	11135	17452	10979	5605
40°	10650	11852	10561	5207
45°	10015	8520	10001	4815
50°	9363	6552	9408	4453
55°	8629	5327	8612	4103
60°	7945	4367	7907	3644
65°	7150	3638	7195	2933
70°	6491	2920	6465	2442
75°	5484	2213	5484	2007
80°	4443	1349	4392	1349
85°	3127	709	3036	802

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 17358 cd/sqm

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.5	2.9
10°-20°	535.1	8.6
20°-30°	848.4	13.6
30°-40°	1025.2	16.4
40°-50°	912.8	14.6
50°-60°	699.9	11.2
60°-70°	454.6	7.3
70°-80°	220.6	3.5
80°-90°	52.6	0.8
90°-100°	128.3	2.1
100°-110°	276.6	4.4
110°-120°	257.8	4.1
120°-130°	208.8	3.3
130°-140°	167.7	2.7
140°-150°	126.5	2.0
150°-160°	89.1	1.4
160°-170°	52.5	0.8
170°-180°	17.1	0.3
0°-30°	1566.0	25.0
0°-40°	2591.2	41.4
0°-60°	4203.9	67.2
0°-90°	4931.7	78.8
90°-120°	662.7	10.6
90°-150°	1165.7	18.6
90°-180°	1324.0	21.2
0°-180°	6256.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1903	1903	1903	1903	1903	
5°	1899	2181	1899	1677	1899	180
15°	1819	2620	1806	1275	1819	513
25°	1663	3138	1644	1025	1663	766
35°	1449	2603	1428	836	1449	902
45°	1133	1164	1131	658	1133	874
55°	800	639	798	492	800	717
65°	497	362	500	292	497	497
75°	242	169	242	153	242	260
85°	55	36	53	41	55	62
90°	0	8	0	8	0	4
95°	12	84	12	84	12	12
105°	40	471	40	471	40	42
115°	72	525	72	525	72	71
125°	100	413	100	413	100	88
135°	117	343	117	343	117	90
145°	136	271	136	271	136	85
155°	155	227	155	227	155	71
165°	169	199	169	199	169	48
175°	176	179	176	179	176	17
180°	176	176	176	176	176	

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1904.8	1920.5	1925.2	1937.7	1951.7	1954.8	1962.7	1973.6	1979.8	1978.3	1978.3
5°	1898.6	1925.2	1943.9	1965.8	1992.3	2003.3	2012.7	2036.1	2054.9	2065.8	2084.5
7.5°	1887.7	1926.7	1958.0	1990.8	2031.4	2050.2	2070.5	2103.3	2137.7	2159.5	2179.9
10°	1870.5	1920.5	1964.2	2012.7	2067.4	2095.5	2120.5	2170.5	2212.7	2240.8	2287.7
12.5°	1845.5	1908.0	1968.9	2033.0	2101.7	2131.4	2165.8	2220.5	2279.9	2320.5	2359.6
15°	1818.9	1893.9	1959.5	2036.1	2118.9	2164.2	2208.0	2265.8	2318.9	2364.3	2409.6
17.5°	1787.6	1867.3	1948.6	2036.1	2129.9	2175.2	2212.7	2281.4	2337.7	2383.0	2423.6
20°	1750.1	1839.2	1931.4	2028.3	2123.6	2165.8	2201.7	2276.7	2326.7	2375.2	2433.0
22.5°	1709.5	1806.4	1904.8	2000.2	2093.9	2139.2	2181.4	2247.1	2301.7	2367.4	2442.4
25°	1662.6	1768.9	1868.9	1964.2	2053.3	2095.5	2133.0	2204.9	2281.4	2364.3	2448.6
27.5°	1615.8	1718.9	1815.8	1903.3	2000.2	2039.2	2076.7	2167.4	2258.0	2345.5	2461.1
30°	1564.2	1668.9	1753.3	1834.5	1928.3	1968.9	2015.8	2118.9	2222.1	2340.8	2481.4
32.5°	1506.4	1601.7	1679.8	1764.2	1848.6	1898.6	1958.0	2070.5	2189.2	2331.4	2511.1
35°	1448.6	1525.1	1597.0	1676.7	1778.3	1831.4	1889.2	2008.0	2156.4	2326.7	2536.1
37.5°	1375.1	1448.6	1504.8	1586.1	1690.8	1753.3	1811.1	1948.6	2117.4	2315.8	2534.6
40°	1300.1	1362.6	1415.7	1500.1	1614.2	1672.0	1734.5	1884.5	2076.7	2284.6	2497.1
42.5°	1218.8	1272.0	1329.8	1411.1	1522.0	1578.3	1650.1	1825.1	2020.5	2240.8	2400.2
45°	1132.9	1184.5	1232.9	1317.3	1428.2	1489.2	1567.3	1747.0	1951.7	2148.6	2243.9
47.5°	1048.5	1093.8	1145.4	1218.8	1331.4	1398.5	1478.2	1670.4	1859.5	2025.2	2033.0
50°	967.3	1003.2	1047.0	1122.0	1239.2	1303.2	1386.0	1565.8	1750.1	1864.2	1787.6
52.5°	882.9	915.7	961.0	1026.6	1136.0	1211.0	1282.9	1462.6	1617.3	1693.9	1553.2
55°	800.1	828.2	875.1	948.5	1043.8	1101.7	1175.1	1342.3	1478.2	1479.8	1326.7
57.5°	718.8	743.8	782.9	848.5	937.6	1004.8	1072.0	1217.3	1309.5	1282.9	1112.6
60°	646.9	662.6	698.5	762.6	845.4	893.8	965.7	1087.6	1148.5	1100.1	917.3
62.5°	571.9	587.5	615.7	667.2	745.4	796.9	842.3	942.3	984.5	911.0	761.0
65°	496.9	515.7	536.0	576.6	650.1	684.4	725.1	798.5	839.1	753.2	623.5
67.5°	431.3	440.7	461.0	503.2	554.7	586.0	614.1	664.1	671.9	603.2	496.9
70°	370.3	373.5	392.2	417.2	456.3	475.0	498.5	528.2	528.2	471.9	387.5
72.5°	301.6	306.3	320.3	346.9	370.3	379.7	387.5	406.3	403.2	351.6	293.8
75°	242.2	245.3	256.3	268.8	278.1	295.3	301.6	298.5	296.9	253.1	220.3
77.5°	187.5	189.1	196.9	207.8	209.4	215.6	211.0	211.0	196.9	171.9	154.7
80°	137.5	139.1	142.2	145.3	145.3	145.3	145.3	137.5	128.1	112.5	107.8
82.5°	92.2	92.2	93.8	96.9	95.3	92.2	89.1	81.3	75.0	70.3	67.2
85°	54.7	54.7	56.3	54.7	48.4	46.9	43.8	42.2	40.6	39.1	39.1
87.5°	26.6	25.0	21.9	18.8	18.8	18.8	18.8	18.8	18.8	17.2	17.2
90°	0.4	0.7	1.4	2.1	2.8	3.2	3.6	3.9	4.6	5.0	5.7
92.5°	5.3	6.4	10.0	15.3	22.8	29.2	35.5	59.7	100.2	144.3	141.8
95°	11.7	12.1	14.9	18.8	26.7	34.7	42.7	80.7	158.9	257.0	314.9
97.5°	18.1	18.5	20.6	24.5	31.6	37.5	43.4	69.7	129.7	235.7	340.2
100°	24.9	25.6	27.0	30.9	37.7	43.0	48.3	69.0	115.2	204.8	321.0
102.5°	32.3	32.7	33.8	38.0	44.1	49.2	54.4	72.2	109.1	181.3	287.2
105°	40.2	40.2	41.9	45.5	51.2	56.2	61.1	76.8	108.4	167.8	257.7
107.5°	47.6	48.3	50.1	53.0	59.0	63.4	67.9	83.2	110.9	160.7	235.7
110°	55.8	56.5	57.9	61.1	66.5	71.1	75.7	90.3	114.8	157.8	221.1

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	64.0	64.7	65.8	69.0	74.3	78.8	83.2	97.0	119.8	157.8	212.6
115°	71.8	72.5	73.6	76.8	82.1	86.6	91.0	104.2	124.8	158.9	206.9
117.5°	78.9	80.0	81.0	84.2	90.3	94.6	98.8	111.3	130.5	160.7	203.7
120°	86.0	87.1	88.5	91.7	97.8	102.2	106.6	119.1	136.1	163.5	201.6
122.5°	93.5	94.2	95.3	98.5	105.2	109.6	114.1	126.5	142.5	166.0	199.8
125°	99.5	100.2	102.0	105.2	112.0	116.6	121.2	132.9	148.2	168.9	198.4
127.5°	104.5	105.6	107.7	111.6	118.7	123.4	128.0	139.3	153.6	172.0	197.6
130°	109.1	110.2	113.0	117.7	125.1	129.8	134.4	145.4	158.9	174.9	196.9
132.5°	112.7	114.1	117.7	123.0	130.8	135.4	140.1	151.1	163.5	178.1	196.9
135°	116.6	118.0	122.3	128.0	135.4	140.2	145.0	156.1	167.8	180.9	196.9
137.5°	121.6	122.6	126.5	132.2	139.7	144.7	149.7	159.6	171.0	183.8	197.3
140°	125.8	126.9	131.2	136.9	143.6	148.4	153.2	163.5	174.2	185.6	197.6
142.5°	130.8	131.5	135.4	141.1	147.5	152.0	156.4	166.0	176.0	186.6	198.0
145°	135.8	136.5	140.1	145.0	151.4	155.5	159.6	168.9	177.7	187.3	197.6
147.5°	141.1	141.5	144.7	149.3	155.0	158.8	162.5	170.6	178.8	187.7	196.9
150°	145.7	146.5	148.9	153.6	158.5	161.6	164.6	172.4	179.9	187.7	195.9
152.5°	150.7	151.1	153.2	157.1	161.7	164.4	167.1	174.2	180.6	187.3	194.4
155°	155.0	155.0	157.1	160.7	164.2	166.7	169.2	175.2	180.9	186.6	192.7
157.5°	158.9	158.9	160.7	163.9	167.1	169.0	171.0	176.3	181.3	185.9	190.9
160°	162.8	162.5	163.9	166.4	169.2	170.8	172.4	177.0	181.3	184.8	189.1
162.5°	166.0	165.7	167.1	169.2	171.3	172.6	173.8	177.7	180.9	183.8	187.0
165°	169.2	168.5	169.6	171.3	172.8	173.9	174.9	177.7	180.6	182.7	184.8
167.5°	171.3	171.0	171.7	172.8	173.8	174.5	175.2	177.7	179.9	180.9	182.7
170°	173.5	173.1	173.5	174.2	174.9	175.4	176.0	177.7	179.2	179.9	180.9
172.5°	174.9	174.2	174.5	175.2	175.6	175.8	176.0	177.4	178.4	178.4	178.8
175°	176.0	175.2	175.6	176.0	176.0	176.0	176.0	177.0	177.7	177.4	177.4
177.5°	176.7	176.0	176.0	176.3	176.0	176.0	176.0	176.7	177.0	176.3	176.3
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1986.1	1997.0	2006.4	2001.7	2020.5	2018.9	2022.0	2028.3	2029.9	2026.7	2020.5
5°	2093.9	2109.5	2136.1	2150.2	2147.0	2159.5	2165.8	2175.2	2184.5	2181.4	2181.4
7.5°	2214.2	2236.1	2262.7	2298.6	2303.3	2314.2	2333.0	2333.0	2343.9	2339.2	2337.7
10°	2318.9	2345.5	2387.7	2415.8	2428.3	2434.6	2453.3	2459.6	2472.1	2473.6	2473.6
12.5°	2404.9	2451.8	2479.9	2508.0	2514.3	2523.6	2537.7	2547.1	2551.8	2551.8	2547.1
15°	2450.2	2487.7	2520.5	2550.2	2567.4	2575.2	2589.3	2600.2	2606.5	2620.5	2623.6
17.5°	2468.9	2514.3	2567.4	2609.6	2639.3	2647.1	2675.2	2684.6	2697.1	2703.3	2711.2
20°	2495.5	2561.1	2625.2	2676.8	2704.9	2725.2	2754.9	2798.7	2811.2	2811.2	2806.5
22.5°	2519.0	2603.3	2690.8	2773.7	2797.1	2837.7	2892.4	2939.3	2958.0	2965.9	2959.6
25°	2547.1	2662.7	2776.8	2879.9	2944.0	2973.7	3047.1	3103.4	3125.3	3137.8	3140.9
27.5°	2595.5	2740.8	2886.2	3017.4	3083.1	3117.4	3194.0	3242.4	3269.0	3280.0	3272.1
30°	2650.2	2828.4	2997.1	3114.3	3158.1	3200.3	3250.3	3269.0	3262.8	3262.8	3286.2
32.5°	2706.5	2890.9	3040.9	3117.4	3133.1	3126.8	3106.5	3050.2	3017.4	3017.4	3037.7
35°	2737.7	2897.1	2973.7	2948.7	2887.7	2851.8	2740.8	2678.3	2608.0	2603.3	2626.8
37.5°	2720.5	2789.3	2758.0	2594.0	2511.1	2442.4	2268.9	2200.2	2148.6	2076.7	2187.7
40°	2600.2	2576.8	2414.3	2178.3	2086.1	1989.2	1851.7	1783.0	1711.1	1700.1	1726.7
42.5°	2397.1	2258.0	2020.5	1792.3	1698.6	1629.8	1525.1	1457.9	1412.6	1393.9	1425.1
45°	2143.9	1925.2	1687.6	1506.4	1403.2	1367.3	1272.0	1212.6	1178.2	1164.2	1186.0
47.5°	1834.5	1614.2	1389.2	1236.0	1175.1	1139.2	1075.1	1023.5	993.8	984.5	993.8
50°	1557.9	1331.4	1142.3	1043.8	989.1	959.5	906.3	873.5	850.1	843.8	859.4
52.5°	1318.9	1112.6	968.8	881.3	845.4	820.4	782.9	754.7	740.7	734.4	745.4
55°	1104.8	937.6	821.9	746.9	720.4	704.7	671.9	656.3	640.7	639.1	650.1
57.5°	915.7	800.1	693.8	640.7	632.9	609.4	581.3	567.2	559.4	557.9	562.5
60°	762.6	659.4	595.4	548.5	537.5	518.8	503.2	493.8	484.4	481.3	484.4
62.5°	634.4	553.2	501.6	470.4	454.7	450.0	432.8	421.9	420.3	420.3	423.5
65°	523.5	454.7	421.9	396.9	386.0	381.3	368.8	361.0	362.5	362.5	364.1
67.5°	426.6	376.6	346.9	334.4	325.0	323.5	311.0	307.8	304.7	304.7	307.8
70°	339.1	307.8	286.0	279.7	278.1	267.2	262.5	261.0	256.3	257.8	257.8
72.5°	265.6	245.3	232.8	223.5	225.0	218.8	212.5	212.5	209.4	214.1	214.1
75°	196.9	187.5	178.1	175.0	178.1	175.0	170.3	168.8	170.3	168.8	168.8
77.5°	145.3	140.6	137.5	135.9	135.9	129.7	126.6	129.7	123.4	126.6	126.6
80°	101.6	95.3	93.8	90.6	92.2	87.5	89.1	85.9	85.9	85.9	85.9
82.5°	64.1	62.5	62.5	62.5	60.9	60.9	60.9	60.9	60.9	60.9	59.4
85°	39.1	37.5	37.5	37.5	35.9	35.9	35.9	35.9	35.9	35.9	35.9
87.5°	15.6	17.2	17.2	18.8	17.2	15.6	15.6	15.6	17.2	17.2	15.6
90°	6.0	6.4	6.8	7.1	7.4	7.8	7.8	7.8	8.2	8.2	8.2
92.5°	114.5	77.1	55.5	41.2	37.8	34.5	28.8	27.7	27.0	26.3	27.0
95°	308.2	255.6	201.6	157.8	142.9	128.0	102.7	92.1	89.2	83.5	89.2
97.5°	385.0	366.5	323.5	279.4	258.0	236.7	215.4	196.9	187.3	183.1	187.3
100°	409.9	437.2	419.8	383.2	364.7	346.2	321.7	296.1	283.0	277.3	283.0
102.5°	394.9	461.0	478.8	466.0	455.0	444.0	417.3	401.0	386.4	382.5	386.4
105°	359.7	445.1	493.8	509.4	507.4	505.5	494.1	482.4	475.3	471.0	475.3
107.5°	326.3	412.3	476.7	514.4	522.2	530.0	533.2	531.4	527.9	524.3	527.9
110°	298.6	375.4	442.9	493.0	508.2	523.3	539.3	546.0	548.5	548.5	548.5

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	278.0	346.2	409.5	460.3	478.8	497.3	522.5	535.3	542.5	545.7	542.5
115°	264.1	322.8	377.9	426.6	446.0	465.3	493.0	510.1	520.1	524.7	520.1
117.5°	254.9	306.4	355.1	397.8	416.1	434.4	462.5	480.2	490.2	493.0	490.2
120°	247.4	293.6	336.3	375.4	391.0	406.7	433.0	450.0	459.6	462.5	459.6
122.5°	241.0	284.0	322.8	356.5	370.9	385.3	408.1	423.4	433.0	435.5	433.0
125°	235.3	274.8	311.0	342.0	354.8	367.6	387.5	402.0	409.9	413.4	409.9
127.5°	230.0	265.2	299.7	328.8	340.9	353.0	371.1	384.3	391.7	393.2	391.7
130°	224.7	256.3	287.6	315.3	326.8	338.4	356.2	367.9	375.0	377.2	375.0
132.5°	220.4	247.4	276.2	300.7	311.8	322.8	340.5	352.3	358.7	361.2	358.7
135°	217.2	239.9	264.5	287.2	297.4	307.5	323.1	334.9	341.3	343.4	341.3
137.5°	214.0	233.2	253.8	273.4	282.2	291.1	305.4	316.4	322.4	324.9	322.4
140°	211.9	227.9	244.6	260.9	268.4	275.8	289.0	298.2	303.6	305.4	303.6
142.5°	210.1	223.2	236.7	250.3	256.5	262.7	273.4	280.8	285.8	287.2	285.8
145°	208.3	219.3	230.3	241.4	246.2	251.0	259.5	265.5	269.4	270.9	269.4
147.5°	206.5	215.4	224.7	233.5	237.2	241.0	248.1	253.1	255.6	256.3	255.6
150°	204.4	212.2	220.0	226.8	230.0	233.2	238.5	242.8	244.2	244.6	244.2
152.5°	201.9	208.7	215.4	221.5	223.8	226.1	230.3	233.5	235.0	235.3	235.0
155°	199.1	205.1	210.8	215.8	217.8	219.7	223.2	225.7	226.8	227.1	226.8
157.5°	196.6	201.6	206.5	210.4	212.0	213.6	216.5	218.6	219.7	219.7	219.7
160°	193.4	198.0	201.6	205.1	206.4	207.6	210.1	211.9	212.6	212.2	212.6
162.5°	190.5	194.1	197.3	200.1	201.2	202.3	204.0	205.5	205.5	205.5	205.5
165°	187.7	190.5	193.0	195.2	196.0	196.9	198.4	199.1	199.1	199.1	199.1
167.5°	184.8	187.0	188.8	190.5	191.2	192.0	192.7	193.4	193.0	193.0	193.0
170°	182.4	184.1	185.2	186.3	186.6	187.0	187.7	188.0	188.0	187.7	188.0
172.5°	179.9	180.9	182.0	182.7	182.9	183.1	183.1	183.8	183.1	182.7	183.1
175°	177.7	178.8	178.8	179.5	179.5	179.5	179.5	179.9	179.2	178.8	179.2
177.5°	176.7	177.0	177.4	177.4	177.4	177.4	177.0	177.4	176.3	176.3	176.3
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	2028.3	2017.3	2022.0	2017.3	2012.7	2008.0	1997.0	1981.4	1968.9	1959.5	1958.0
5°	2184.5	2170.5	2161.1	2156.4	2147.0	2134.5	2114.2	2090.8	2062.7	2051.7	2029.9
7.5°	2328.3	2323.6	2301.7	2298.6	2292.4	2268.9	2234.6	2203.3	2167.4	2137.7	2109.5
10°	2464.3	2453.3	2437.7	2415.8	2412.7	2383.0	2350.2	2306.4	2259.6	2231.4	2181.4
12.5°	2548.6	2536.1	2519.0	2504.9	2497.1	2478.3	2433.0	2389.3	2347.1	2295.5	2251.7
15°	2609.6	2594.0	2562.7	2551.8	2542.4	2517.4	2484.6	2439.3	2383.0	2347.1	2284.6
17.5°	2692.4	2673.7	2642.4	2622.1	2604.9	2565.8	2519.0	2458.0	2404.9	2364.3	2308.0
20°	2787.7	2759.6	2719.0	2692.4	2667.4	2622.1	2556.5	2484.6	2408.0	2358.0	2300.2
22.5°	2945.5	2892.4	2828.4	2790.8	2756.5	2678.3	2600.2	2511.1	2425.2	2350.2	2279.9
25°	3098.7	3045.6	2965.9	2914.3	2861.2	2770.5	2667.4	2544.0	2434.6	2347.1	2254.9
27.5°	3240.9	3186.2	3112.7	3050.2	2998.7	2862.7	2726.8	2587.7	2448.6	2328.3	2234.6
30°	3273.7	3250.3	3194.0	3139.3	3092.4	2967.4	2809.6	2633.0	2465.8	2311.1	2206.4
32.5°	3075.2	3133.1	3147.1	3139.3	3109.6	3020.6	2875.2	2689.3	2490.8	2303.3	2159.5
35°	2662.7	2767.4	2875.2	2933.0	2961.2	2973.7	2887.7	2717.4	2508.0	2290.8	2128.3
37.5°	2208.0	2309.6	2479.9	2565.8	2661.2	2786.2	2820.5	2711.2	2500.2	2281.4	2078.3
40°	1814.2	1943.9	2084.5	2162.7	2245.5	2470.5	2640.8	2628.3	2475.2	2247.1	2039.2
42.5°	1476.7	1557.9	1681.4	1767.3	1868.9	2120.5	2348.6	2461.1	2400.2	2204.9	1989.2
45°	1231.3	1293.9	1381.4	1468.9	1531.4	1759.5	2029.9	2214.2	2272.1	2129.9	1912.7
47.5°	1037.6	1084.5	1161.0	1215.7	1282.9	1462.6	1697.0	1956.4	2078.3	2023.6	1831.4
50°	889.1	926.6	987.6	1022.0	1081.3	1236.0	1414.2	1686.1	1870.5	1876.7	1723.6
52.5°	759.4	796.9	848.5	878.2	914.1	1018.8	1198.5	1428.2	1640.8	1718.9	1600.1
55°	661.0	682.9	725.1	748.5	781.3	882.9	997.0	1192.3	1414.2	1542.3	1467.3
57.5°	570.4	593.8	620.4	639.1	662.6	743.8	846.9	993.8	1214.2	1353.2	1328.2
60°	496.9	511.0	536.0	550.0	571.9	625.1	696.9	843.8	1018.8	1150.1	1164.2
62.5°	428.2	440.7	457.8	470.4	484.4	526.6	579.7	684.4	837.6	979.8	998.5
65°	368.8	379.7	389.1	400.0	411.0	437.5	482.9	564.1	682.9	815.7	856.3
67.5°	315.7	318.8	332.8	334.4	340.7	361.0	393.8	459.4	545.4	651.6	704.7
70°	264.1	270.3	273.5	278.1	284.4	298.5	325.0	359.4	423.5	509.4	559.4
72.5°	214.1	215.6	220.3	223.5	229.7	240.6	253.1	279.7	320.3	382.8	428.2
75°	170.3	171.9	175.0	176.6	181.3	184.4	190.6	209.4	237.5	275.0	307.8
77.5°	128.1	131.3	134.4	134.4	135.9	139.1	142.2	148.4	162.5	187.5	215.6
80°	87.5	89.1	89.1	90.6	89.1	93.8	98.4	106.3	112.5	120.3	134.4
82.5°	60.9	60.9	60.9	62.5	62.5	64.1	64.1	65.6	67.2	71.9	78.1
85°	37.5	37.5	39.1	35.9	37.5	39.1	39.1	37.5	39.1	40.6	42.2
87.5°	15.6	15.6	17.2	17.2	17.2	17.2	15.6	17.2	15.6	17.2	17.2
90°	7.8	7.8	7.8	7.4	7.1	6.8	6.4	6.0	5.7	5.0	4.6
92.5°	27.7	28.8	34.5	37.8	41.2	55.5	77.1	114.5	141.8	144.3	100.2
95°	92.1	102.7	128.0	142.9	157.8	201.6	255.6	308.2	314.9	257.0	158.9
97.5°	196.9	215.4	236.7	258.0	279.4	323.5	366.5	385.0	340.2	235.7	129.7
100°	296.1	321.7	346.2	364.7	383.2	419.8	437.2	409.9	321.0	204.8	115.2
102.5°	401.0	417.3	444.0	455.0	466.0	478.8	461.0	394.9	287.2	181.3	109.1
105°	482.4	494.1	505.5	507.4	509.4	493.8	445.1	359.7	257.7	167.8	108.4
107.5°	531.4	533.2	530.0	522.2	514.4	476.7	412.3	326.3	235.7	160.7	110.9
110°	546.0	539.3	523.3	508.2	493.0	442.9	375.4	298.6	221.1	157.8	114.8

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	535.3	522.5	497.3	478.8	460.3	409.5	346.2	278.0	212.6	157.8	119.8
115°	510.1	493.0	465.3	446.0	426.6	377.9	322.8	264.1	206.9	158.9	124.8
117.5°	480.2	462.5	434.4	416.1	397.8	355.1	306.4	254.9	203.7	160.7	130.5
120°	450.0	433.0	406.7	391.0	375.4	336.3	293.6	247.4	201.6	163.5	136.1
122.5°	423.4	408.1	385.3	370.9	356.5	322.8	284.0	241.0	199.8	166.0	142.5
125°	402.0	387.5	367.6	354.8	342.0	311.0	274.8	235.3	198.4	168.9	148.2
127.5°	384.3	371.1	353.0	340.9	328.8	299.7	265.2	230.0	197.6	172.0	153.6
130°	367.9	356.2	338.4	326.8	315.3	287.6	256.3	224.7	196.9	174.9	158.9
132.5°	352.3	340.5	322.8	311.8	300.7	276.2	247.4	220.4	196.9	178.1	163.5
135°	334.9	323.1	307.5	297.4	287.2	264.5	239.9	217.2	196.9	180.9	167.8
137.5°	316.4	305.4	291.1	282.2	273.4	253.8	233.2	214.0	197.3	183.8	171.0
140°	298.2	289.0	275.8	268.4	260.9	244.6	227.9	211.9	197.6	185.6	174.2
142.5°	280.8	273.4	262.7	256.5	250.3	236.7	223.2	210.1	198.0	186.6	176.0
145°	265.5	259.5	251.0	246.2	241.4	230.3	219.3	208.3	197.6	187.3	177.7
147.5°	253.1	248.1	241.0	237.2	233.5	224.7	215.4	206.5	196.9	187.7	178.8
150°	242.8	238.5	233.2	230.0	226.8	220.0	212.2	204.4	195.9	187.7	179.9
152.5°	233.5	230.3	226.1	223.8	221.5	215.4	208.7	201.9	194.4	187.3	180.6
155°	225.7	223.2	219.7	217.8	215.8	210.8	205.1	199.1	192.7	186.6	180.9
157.5°	218.6	216.5	213.6	212.0	210.4	206.5	201.6	196.6	190.9	185.9	181.3
160°	211.9	210.1	207.6	206.4	205.1	201.6	198.0	193.4	189.1	184.8	181.3
162.5°	205.5	204.0	202.3	201.2	200.1	197.3	194.1	190.5	187.0	183.8	180.9
165°	199.1	198.4	196.9	196.0	195.2	193.0	190.5	187.7	184.8	182.7	180.6
167.5°	193.4	192.7	192.0	191.2	190.5	188.8	187.0	184.8	182.7	180.9	179.9
170°	188.0	187.7	187.0	186.6	186.3	185.2	184.1	182.4	180.9	179.9	179.2
172.5°	183.8	183.1	183.1	182.9	182.7	182.0	180.9	179.9	178.8	178.4	178.4
175°	179.9	179.5	179.5	179.5	179.5	178.8	178.8	177.7	177.4	177.4	177.7
177.5°	177.4	177.0	177.4	177.4	177.4	177.4	177.0	176.7	176.3	176.3	177.0
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1953.3	1943.9	1937.7	1936.1	1926.7	1918.9	1909.5	1908.0	1903.3	1890.8	1883.0
5°	2014.2	1992.3	1987.7	1973.6	1950.2	1933.0	1911.1	1898.6	1884.5	1861.1	1842.3
7.5°	2076.7	2047.0	2025.2	2004.8	1972.0	1940.8	1909.5	1884.5	1859.5	1825.1	1797.0
10°	2137.7	2092.4	2065.8	2036.1	1990.8	1943.9	1900.2	1864.2	1823.6	1783.0	1742.3
12.5°	2193.9	2136.1	2097.0	2054.9	1998.6	1940.8	1884.5	1834.5	1792.3	1737.6	1692.3
15°	2228.3	2164.2	2125.2	2084.5	2000.2	1936.1	1870.5	1806.4	1750.1	1692.3	1650.1
17.5°	2248.6	2176.7	2133.0	2095.5	2009.5	1922.0	1837.6	1768.9	1707.9	1639.2	1582.9
20°	2239.2	2168.9	2128.3	2092.4	1992.3	1904.8	1814.2	1734.5	1657.9	1587.6	1528.2
22.5°	2218.9	2145.5	2100.2	2067.4	1978.3	1875.2	1775.1	1689.2	1609.5	1539.2	1472.0
25°	2175.2	2103.3	2064.2	2023.6	1936.1	1837.6	1736.1	1643.9	1559.5	1484.5	1409.5
27.5°	2136.1	2048.6	2008.0	1972.0	1879.8	1792.3	1692.3	1590.8	1504.8	1426.7	1351.7
30°	2090.8	1992.3	1948.6	1900.2	1817.3	1734.5	1634.5	1540.7	1451.7	1368.9	1297.0
32.5°	2042.4	1928.3	1878.3	1823.6	1739.2	1661.1	1576.7	1484.5	1395.4	1314.2	1239.2
35°	1979.8	1858.0	1800.1	1748.6	1661.1	1582.9	1504.8	1428.2	1339.2	1253.2	1181.3
37.5°	1920.5	1786.1	1725.1	1665.8	1573.6	1498.6	1434.5	1362.6	1276.7	1193.8	1125.1
40°	1853.3	1698.6	1636.1	1581.4	1486.1	1403.2	1345.4	1289.2	1214.2	1134.5	1059.5
42.5°	1792.3	1617.3	1551.7	1495.4	1395.4	1317.3	1262.6	1215.7	1150.1	1076.6	1000.1
45°	1707.9	1529.8	1462.6	1403.2	1301.7	1228.2	1172.0	1131.3	1079.8	1011.0	942.3
47.5°	1629.8	1445.4	1372.0	1300.1	1207.9	1132.9	1081.3	1050.1	1015.7	954.8	884.4
50°	1534.5	1348.5	1273.5	1214.2	1109.5	1045.4	993.8	972.0	940.7	882.9	826.6
52.5°	1431.4	1254.8	1184.5	1112.6	1015.7	953.2	907.9	882.9	857.9	815.7	762.6
55°	1311.0	1150.1	1084.5	1020.4	923.5	865.7	825.1	798.5	784.4	745.4	706.3
57.5°	1195.4	1043.8	982.9	923.5	839.1	773.5	746.9	723.5	703.2	675.1	642.2
60°	1078.2	940.7	875.1	821.9	748.5	689.1	667.2	643.8	628.2	606.3	582.9
62.5°	943.8	826.6	776.6	726.6	664.1	617.2	592.2	573.5	553.2	539.1	518.8
65°	801.6	718.8	670.4	632.9	573.5	531.3	512.5	500.0	482.9	468.8	453.2
67.5°	668.8	603.2	582.9	542.2	496.9	459.4	445.3	429.7	415.7	407.8	393.8
70°	540.7	493.8	473.5	462.5	412.5	387.5	375.0	368.8	351.6	343.8	334.4
72.5°	418.8	401.6	387.5	373.5	340.7	325.0	311.0	304.7	292.2	286.0	282.8
75°	309.4	298.5	290.6	289.1	275.0	259.4	245.3	242.2	232.8	226.6	223.5
77.5°	217.2	214.1	212.5	214.1	204.7	195.3	192.2	189.1	178.1	176.6	176.6
80°	142.2	150.0	150.0	148.4	145.3	143.8	139.1	135.9	129.7	128.1	129.7
82.5°	87.5	92.2	93.8	96.9	95.3	93.8	90.6	89.1	90.6	87.5	89.1
85°	43.8	46.9	53.1	53.1	54.7	54.7	54.7	53.1	50.0	51.6	50.0
87.5°	17.2	18.8	18.8	18.8	17.2	21.9	23.4	23.4	23.4	20.3	20.3
90°	3.9	3.6	3.2	2.8	2.1	1.4	0.7	0.4	0.7	1.4	2.1
92.5°	59.7	35.5	29.2	22.8	15.3	10.0	6.4	5.3	6.4	10.0	15.3
95°	80.7	42.7	34.7	26.7	18.8	14.9	12.1	11.7	12.1	14.9	18.8
97.5°	69.7	43.4	37.5	31.6	24.5	20.6	18.5	18.1	18.5	20.6	24.5
100°	69.0	48.3	43.0	37.7	30.9	27.0	25.6	24.9	25.6	27.0	30.9
102.5°	72.2	54.4	49.2	44.1	38.0	33.8	32.7	32.3	32.7	33.8	38.0
105°	76.8	61.1	56.2	51.2	45.5	41.9	40.2	40.2	40.2	41.9	45.5
107.5°	83.2	67.9	63.4	59.0	53.0	50.1	48.3	47.6	48.3	50.1	53.0
110°	90.3	75.7	71.1	66.5	61.1	57.9	56.5	55.8	56.5	57.9	61.1

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	97.0	83.2	78.8	74.3	69.0	65.8	64.7	64.0	64.7	65.8	69.0
115°	104.2	91.0	86.6	82.1	76.8	73.6	72.5	71.8	72.5	73.6	76.8
117.5°	111.3	98.8	94.6	90.3	84.2	81.0	80.0	78.9	80.0	81.0	84.2
120°	119.1	106.6	102.2	97.8	91.7	88.5	87.1	86.0	87.1	88.5	91.7
122.5°	126.5	114.1	109.6	105.2	98.5	95.3	94.2	93.5	94.2	95.3	98.5
125°	132.9	121.2	116.6	112.0	105.2	102.0	100.2	99.5	100.2	102.0	105.2
127.5°	139.3	128.0	123.4	118.7	111.6	107.7	105.6	104.5	105.6	107.7	111.6
130°	145.4	134.4	129.8	125.1	117.7	113.0	110.2	109.1	110.2	113.0	117.7
132.5°	151.1	140.1	135.4	130.8	123.0	117.7	114.1	112.7	114.1	117.7	123.0
135°	156.1	145.0	140.2	135.4	128.0	122.3	118.0	116.6	118.0	122.3	128.0
137.5°	159.6	149.7	144.7	139.7	132.2	126.5	122.6	121.6	122.6	126.5	132.2
140°	163.5	153.2	148.4	143.6	136.9	131.2	126.9	125.8	126.9	131.2	136.9
142.5°	166.0	156.4	152.0	147.5	141.1	135.4	131.5	130.8	131.5	135.4	141.1
145°	168.9	159.6	155.5	151.4	145.0	140.1	136.5	135.8	136.5	140.1	145.0
147.5°	170.6	162.5	158.8	155.0	149.3	144.7	141.5	141.1	141.5	144.7	149.3
150°	172.4	164.6	161.6	158.5	153.6	148.9	146.5	145.7	146.5	148.9	153.6
152.5°	174.2	167.1	164.4	161.7	157.1	153.2	151.1	150.7	151.1	153.2	157.1
155°	175.2	169.2	166.7	164.2	160.7	157.1	155.0	155.0	155.0	157.1	160.7
157.5°	176.3	171.0	169.0	167.1	163.9	160.7	158.9	158.9	158.9	160.7	163.9
160°	177.0	172.4	170.8	169.2	166.4	163.9	162.5	162.8	162.5	163.9	166.4
162.5°	177.7	173.8	172.6	171.3	169.2	167.1	165.7	166.0	165.7	167.1	169.2
165°	177.7	174.9	173.9	172.8	171.3	169.6	168.5	169.2	168.5	169.6	171.3
167.5°	177.7	175.2	174.5	173.8	172.8	171.7	171.0	171.3	171.0	171.7	172.8
170°	177.7	176.0	175.4	174.9	174.2	173.5	173.1	173.5	173.1	173.5	174.2
172.5°	177.4	176.0	175.8	175.6	175.2	174.5	174.2	174.9	174.2	174.5	175.2
175°	177.0	176.0	176.0	176.0	176.0	175.6	175.2	176.0	175.2	175.6	176.0
177.5°	176.7	176.0	176.0	176.0	176.3	176.0	176.0	176.7	176.0	176.0	176.3
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1878.3	1872.0	1867.3	1862.6	1842.3	1820.5	1817.3	1812.6	1803.3	1814.2	1809.5
5°	1829.8	1815.8	1808.0	1787.6	1762.6	1743.9	1728.3	1709.5	1701.7	1695.4	1693.9
7.5°	1770.5	1758.0	1743.9	1723.6	1692.3	1661.1	1637.6	1618.9	1603.3	1595.4	1595.4
10°	1712.6	1697.0	1678.3	1643.9	1614.2	1575.1	1550.1	1531.4	1509.5	1497.0	1486.1
12.5°	1653.3	1636.1	1618.9	1575.1	1540.7	1500.1	1464.2	1440.7	1429.8	1415.7	1397.0
15°	1593.9	1567.3	1550.1	1506.4	1462.6	1422.0	1398.5	1373.5	1348.5	1334.5	1328.2
17.5°	1531.4	1512.6	1484.5	1437.6	1389.2	1353.2	1318.9	1295.4	1265.7	1251.7	1237.6
20°	1475.1	1447.0	1418.9	1372.0	1325.1	1276.7	1242.3	1214.2	1195.4	1184.5	1172.0
22.5°	1407.9	1381.4	1357.9	1307.9	1256.4	1211.0	1173.5	1156.3	1137.6	1120.4	1107.9
25°	1350.1	1323.5	1300.1	1245.4	1189.2	1147.0	1118.8	1097.0	1076.6	1068.8	1056.3
27.5°	1289.2	1264.2	1232.9	1178.2	1128.2	1092.3	1062.6	1042.3	1026.6	1011.0	1001.6
30°	1231.3	1203.2	1175.1	1115.7	1075.1	1039.1	1011.0	986.0	973.5	965.7	950.1
32.5°	1175.1	1139.2	1115.7	1061.0	1022.0	987.6	964.1	942.3	926.6	912.6	900.1
35°	1114.2	1075.1	1051.6	1006.3	965.7	931.3	911.0	895.4	876.6	864.1	857.9
37.5°	1056.3	1023.5	1000.1	953.2	912.6	884.4	862.6	842.3	834.4	817.3	814.1
40°	993.8	965.7	943.8	898.5	861.0	839.1	815.7	796.9	782.9	775.1	764.1
42.5°	937.6	914.1	890.7	848.5	812.6	786.0	768.8	751.6	739.1	726.6	718.8
45°	886.0	861.0	839.1	798.5	762.6	739.1	721.9	701.6	698.5	681.3	673.5
47.5°	831.3	809.4	790.7	748.5	715.7	692.2	671.9	657.9	643.8	637.6	626.6
50°	778.2	756.3	734.4	696.9	667.2	643.8	623.5	607.9	600.0	590.7	581.3
52.5°	720.4	703.2	686.0	646.9	617.2	596.9	579.7	559.4	551.6	543.8	537.5
55°	671.9	646.9	628.2	595.4	568.8	546.9	528.2	512.5	504.7	498.5	490.7
57.5°	606.3	590.7	575.0	545.4	520.4	498.5	479.7	467.2	457.8	453.2	454.7
60°	550.0	532.9	523.5	492.2	467.2	450.0	432.8	420.3	411.0	406.3	404.7
62.5°	490.7	478.2	461.0	439.1	414.1	398.5	386.0	376.6	361.0	359.4	354.7
65°	432.8	423.5	407.8	387.5	367.2	353.2	339.1	326.6	320.3	312.5	307.8
67.5°	376.6	367.2	353.2	336.0	321.9	307.8	295.3	282.8	271.9	265.6	262.5
70°	321.9	314.1	304.7	284.4	267.2	256.3	246.9	239.1	228.1	225.0	223.5
72.5°	268.8	261.0	256.3	239.1	223.5	214.1	204.7	196.9	192.2	190.6	186.0
75°	220.3	212.5	206.3	190.6	181.3	175.0	165.6	162.5	157.8	156.3	154.7
77.5°	171.9	164.1	162.5	151.6	140.6	137.5	134.4	128.1	128.1	128.1	125.0
80°	123.4	121.9	120.3	109.4	104.7	101.6	100.0	95.3	92.2	89.1	87.5
82.5°	82.8	81.3	79.7	75.0	70.3	68.8	67.2	64.1	64.1	65.6	62.5
85°	50.0	46.9	45.3	43.8	40.6	40.6	42.2	40.6	40.6	40.6	39.1
87.5°	18.8	18.8	18.8	18.8	20.3	17.2	18.8	18.8	17.2	17.2	15.6
90°	2.8	3.2	3.6	3.9	4.6	5.0	5.7	6.0	6.4	6.8	7.1
92.5°	22.8	29.2	35.5	59.7	100.2	144.3	141.8	114.5	77.1	55.5	41.2
95°	26.7	34.7	42.7	80.7	158.9	257.0	314.9	308.2	255.6	201.6	157.8
97.5°	31.6	37.5	43.4	69.7	129.7	235.7	340.2	385.0	366.5	323.5	279.4
100°	37.7	43.0	48.3	69.0	115.2	204.8	321.0	409.9	437.2	419.8	383.2
102.5°	44.1	49.2	54.4	72.2	109.1	181.3	287.2	394.9	461.0	478.8	466.0
105°	51.2	56.2	61.1	76.8	108.4	167.8	257.7	359.7	445.1	493.8	509.4
107.5°	59.0	63.4	67.9	83.2	110.9	160.7	235.7	326.3	412.3	476.7	514.4
110°	66.5	71.1	75.7	90.3	114.8	157.8	221.1	298.6	375.4	442.9	493.0

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	74.3	78.8	83.2	97.0	119.8	157.8	212.6	278.0	346.2	409.5	460.3
115°	82.1	86.6	91.0	104.2	124.8	158.9	206.9	264.1	322.8	377.9	426.6
117.5°	90.3	94.6	98.8	111.3	130.5	160.7	203.7	254.9	306.4	355.1	397.8
120°	97.8	102.2	106.6	119.1	136.1	163.5	201.6	247.4	293.6	336.3	375.4
122.5°	105.2	109.6	114.1	126.5	142.5	166.0	199.8	241.0	284.0	322.8	356.5
125°	112.0	116.6	121.2	132.9	148.2	168.9	198.4	235.3	274.8	311.0	342.0
127.5°	118.7	123.4	128.0	139.3	153.6	172.0	197.6	230.0	265.2	299.7	328.8
130°	125.1	129.8	134.4	145.4	158.9	174.9	196.9	224.7	256.3	287.6	315.3
132.5°	130.8	135.4	140.1	151.1	163.5	178.1	196.9	220.4	247.4	276.2	300.7
135°	135.4	140.2	145.0	156.1	167.8	180.9	196.9	217.2	239.9	264.5	287.2
137.5°	139.7	144.7	149.7	159.6	171.0	183.8	197.3	214.0	233.2	253.8	273.4
140°	143.6	148.4	153.2	163.5	174.2	185.6	197.6	211.9	227.9	244.6	260.9
142.5°	147.5	152.0	156.4	166.0	176.0	186.6	198.0	210.1	223.2	236.7	250.3
145°	151.4	155.5	159.6	168.9	177.7	187.3	197.6	208.3	219.3	230.3	241.4
147.5°	155.0	158.8	162.5	170.6	178.8	187.7	196.9	206.5	215.4	224.7	233.5
150°	158.5	161.6	164.6	172.4	179.9	187.7	195.9	204.4	212.2	220.0	226.8
152.5°	161.7	164.4	167.1	174.2	180.6	187.3	194.4	201.9	208.7	215.4	221.5
155°	164.2	166.7	169.2	175.2	180.9	186.6	192.7	199.1	205.1	210.8	215.8
157.5°	167.1	169.0	171.0	176.3	181.3	185.9	190.9	196.6	201.6	206.5	210.4
160°	169.2	170.8	172.4	177.0	181.3	184.8	189.1	193.4	198.0	201.6	205.1
162.5°	171.3	172.6	173.8	177.7	180.9	183.8	187.0	190.5	194.1	197.3	200.1
165°	172.8	173.9	174.9	177.7	180.6	182.7	184.8	187.7	190.5	193.0	195.2
167.5°	173.8	174.5	175.2	177.7	179.9	180.9	182.7	184.8	187.0	188.8	190.5
170°	174.9	175.4	176.0	177.7	179.2	179.9	180.9	182.4	184.1	185.2	186.3
172.5°	175.6	175.8	176.0	177.4	178.4	178.4	178.8	179.9	180.9	182.0	182.7
175°	176.0	176.0	176.0	177.0	177.7	177.4	177.4	177.7	178.8	178.8	179.5
177.5°	176.0	176.0	176.0	176.7	177.0	176.3	176.3	176.7	177.0	177.4	177.4
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1801.7	1804.8	1797.0	1793.9	1787.6	1795.5	1797.0	1795.5	1809.5	1803.3	1806.4
5°	1697.0	1690.8	1686.1	1675.1	1675.1	1676.7	1681.4	1673.6	1678.3	1689.2	1687.6
7.5°	1581.4	1578.3	1579.8	1567.3	1557.9	1561.1	1557.9	1572.0	1579.8	1576.7	1582.9
10°	1476.7	1482.9	1468.9	1462.6	1456.4	1462.6	1461.1	1464.2	1473.6	1479.8	1490.7
12.5°	1392.3	1390.7	1382.9	1376.7	1365.7	1368.9	1378.2	1375.1	1376.7	1390.7	1389.2
15°	1312.6	1303.2	1297.0	1282.9	1286.0	1275.1	1284.5	1295.4	1300.1	1312.6	1320.4
17.5°	1232.9	1231.3	1223.5	1222.0	1204.8	1200.1	1209.5	1212.6	1217.3	1223.5	1234.5
20°	1165.7	1164.2	1153.2	1150.1	1136.0	1145.4	1142.3	1148.5	1151.7	1164.2	1168.8
22.5°	1104.8	1097.0	1093.8	1089.1	1084.5	1082.9	1089.1	1087.6	1098.5	1103.2	1104.8
25°	1048.5	1042.3	1040.7	1032.9	1029.8	1025.1	1029.8	1034.5	1047.0	1051.6	1057.9
27.5°	997.0	992.3	989.1	982.9	978.2	978.2	981.3	987.6	992.3	995.4	998.5
30°	950.1	947.0	937.6	934.4	929.8	929.8	929.8	932.9	940.7	950.1	954.8
32.5°	901.6	895.4	889.1	889.1	884.4	884.4	886.0	889.1	896.9	898.5	906.3
35°	854.8	848.5	843.8	840.7	842.3	836.0	839.1	843.8	853.2	856.3	861.0
37.5°	809.4	807.9	798.5	793.8	796.9	796.9	795.4	798.5	804.8	811.0	814.1
40°	759.4	756.3	756.3	751.6	753.2	746.9	751.6	754.7	757.9	764.1	768.8
42.5°	715.7	712.6	706.3	707.9	703.2	703.2	706.3	707.9	712.6	720.4	723.5
45°	668.8	668.8	665.7	661.0	662.6	657.9	661.0	662.6	668.8	676.6	673.5
47.5°	623.5	621.9	621.9	615.7	618.8	614.1	618.8	620.4	623.5	628.2	626.6
50°	579.7	575.0	576.6	575.0	573.5	573.5	576.6	576.6	579.7	579.7	584.4
52.5°	534.4	534.4	531.3	532.9	536.0	532.9	537.5	532.9	536.0	537.5	540.7
55°	493.8	490.7	492.2	490.7	496.9	492.2	496.9	493.8	496.9	495.4	498.5
57.5°	450.0	445.3	446.9	445.3	450.0	448.5	453.2	448.5	450.0	451.6	456.3
60°	400.0	400.0	400.0	396.9	401.6	401.6	400.0	400.0	406.3	409.4	407.8
62.5°	353.2	351.6	346.9	345.3	346.9	343.8	350.0	348.5	351.6	354.7	357.8
65°	301.6	298.5	296.9	293.8	293.8	292.2	293.8	300.0	301.6	303.1	311.0
67.5°	259.4	257.8	256.3	251.6	251.6	254.7	254.7	254.7	264.1	259.4	265.6
70°	221.9	218.8	215.6	214.1	214.1	215.6	217.2	218.8	217.2	223.5	225.0
72.5°	186.0	187.5	184.4	184.4	184.4	182.8	182.8	186.0	187.5	186.0	187.5
75°	154.7	154.7	153.1	154.7	154.7	153.1	153.1	156.3	156.3	154.7	159.4
77.5°	125.0	123.4	120.3	117.2	118.8	117.2	118.8	117.2	121.9	126.6	123.4
80°	87.5	85.9	85.9	85.9	87.5	85.9	89.1	85.9	87.5	87.5	89.1
82.5°	62.5	64.1	64.1	62.5	64.1	62.5	64.1	64.1	64.1	62.5	64.1
85°	40.6	40.6	40.6	40.6	39.1	40.6	40.6	40.6	42.2	40.6	42.2
87.5°	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2	18.8	17.2	18.8
90°	7.4	7.8	7.8	7.8	8.2	8.2	8.2	7.8	7.8	7.8	7.4
92.5°	37.8	34.5	28.8	27.7	27.0	26.3	27.0	27.7	28.8	34.5	37.8
95°	142.9	128.0	102.7	92.1	89.2	83.5	89.2	92.1	102.7	128.0	142.9
97.5°	258.0	236.7	215.4	196.9	187.3	183.1	187.3	196.9	215.4	236.7	258.0
100°	364.7	346.2	321.7	296.1	283.0	277.3	283.0	296.1	321.7	346.2	364.7
102.5°	455.0	444.0	417.3	401.0	386.4	382.5	386.4	401.0	417.3	444.0	455.0
105°	507.4	505.5	494.1	482.4	475.3	471.0	475.3	482.4	494.1	505.5	507.4
107.5°	522.2	530.0	533.2	531.4	527.9	524.3	527.9	531.4	533.2	530.0	522.2
110°	508.2	523.3	539.3	546.0	548.5	548.5	548.5	546.0	539.3	523.3	508.2

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	478.8	497.3	522.5	535.3	542.5	545.7	542.5	535.3	522.5	497.3	478.8
115°	446.0	465.3	493.0	510.1	520.1	524.7	520.1	510.1	493.0	465.3	446.0
117.5°	416.1	434.4	462.5	480.2	490.2	493.0	490.2	480.2	462.5	434.4	416.1
120°	391.0	406.7	433.0	450.0	459.6	462.5	459.6	450.0	433.0	406.7	391.0
122.5°	370.9	385.3	408.1	423.4	433.0	435.5	433.0	423.4	408.1	385.3	370.9
125°	354.8	367.6	387.5	402.0	409.9	413.4	409.9	402.0	387.5	367.6	354.8
127.5°	340.9	353.0	371.1	384.3	391.7	393.2	391.7	384.3	371.1	353.0	340.9
130°	326.8	338.4	356.2	367.9	375.0	377.2	375.0	367.9	356.2	338.4	326.8
132.5°	311.8	322.8	340.5	352.3	358.7	361.2	358.7	352.3	340.5	322.8	311.8
135°	297.4	307.5	323.1	334.9	341.3	343.4	341.3	334.9	323.1	307.5	297.4
137.5°	282.2	291.1	305.4	316.4	322.4	324.9	322.4	316.4	305.4	291.1	282.2
140°	268.4	275.8	289.0	298.2	303.6	305.4	303.6	298.2	289.0	275.8	268.4
142.5°	256.5	262.7	273.4	280.8	285.8	287.2	285.8	280.8	273.4	262.7	256.5
145°	246.2	251.0	259.5	265.5	269.4	270.9	269.4	265.5	259.5	251.0	246.2
147.5°	237.2	241.0	248.1	253.1	255.6	256.3	255.6	253.1	248.1	241.0	237.2
150°	230.0	233.2	238.5	242.8	244.2	244.6	244.2	242.8	238.5	233.2	230.0
152.5°	223.8	226.1	230.3	233.5	235.0	235.3	235.0	233.5	230.3	226.1	223.8
155°	217.8	219.7	223.2	225.7	226.8	227.1	226.8	225.7	223.2	219.7	217.8
157.5°	212.0	213.6	216.5	218.6	219.7	219.7	219.7	218.6	216.5	213.6	212.0
160°	206.4	207.6	210.1	211.9	212.6	212.2	212.6	211.9	210.1	207.6	206.4
162.5°	201.2	202.3	204.0	205.5	205.5	205.5	205.5	205.5	204.0	202.3	201.2
165°	196.0	196.9	198.4	199.1	199.1	199.1	199.1	199.1	198.4	196.9	196.0
167.5°	191.2	192.0	192.7	193.4	193.0	193.0	193.0	193.4	192.7	192.0	191.2
170°	186.6	187.0	187.7	188.0	188.0	187.7	188.0	188.0	187.7	187.0	186.6
172.5°	182.9	183.1	183.1	183.8	183.1	182.7	183.1	183.8	183.1	183.1	182.9
175°	179.5	179.5	179.5	179.9	179.2	178.8	179.2	179.9	179.5	179.5	179.5
177.5°	177.4	177.4	177.0	177.4	176.3	176.3	176.3	177.4	177.0	177.4	177.4
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1800.1	1808.0	1801.7	1797.0	1809.5	1815.8	1815.8	1826.7	1837.6	1847.0	1848.6
5°	1689.2	1701.7	1704.8	1703.3	1722.0	1731.4	1751.7	1762.6	1778.3	1789.2	1801.7
7.5°	1587.6	1604.8	1606.4	1609.5	1637.6	1653.3	1670.4	1698.6	1720.5	1736.1	1750.1
10°	1486.1	1497.0	1507.9	1522.0	1550.1	1576.7	1601.7	1631.4	1659.5	1675.1	1695.4
12.5°	1409.5	1417.3	1429.8	1439.2	1468.9	1492.3	1525.1	1565.8	1606.4	1618.9	1643.9
15°	1329.8	1334.5	1359.5	1368.9	1393.9	1432.9	1453.2	1492.3	1536.1	1559.5	1587.6
17.5°	1237.6	1265.7	1281.4	1292.3	1323.5	1354.8	1387.6	1428.2	1484.5	1506.4	1526.7
20°	1172.0	1192.3	1209.5	1223.5	1251.7	1298.5	1328.2	1361.0	1414.2	1439.2	1468.9
22.5°	1114.2	1131.3	1147.0	1162.6	1181.3	1223.5	1257.9	1303.2	1356.4	1379.8	1414.2
25°	1059.5	1076.6	1086.0	1104.8	1129.8	1159.5	1200.1	1240.7	1293.9	1320.4	1353.2
27.5°	1006.3	1023.5	1040.7	1056.3	1073.5	1101.7	1129.8	1181.3	1236.0	1267.3	1295.4
30°	961.0	968.8	984.5	1001.6	1018.8	1045.4	1078.2	1114.2	1176.7	1204.8	1239.2
32.5°	911.0	925.1	936.0	948.5	970.4	992.3	1022.0	1067.3	1117.3	1143.8	1181.3
35°	864.1	876.6	884.4	906.3	920.4	943.8	973.5	1014.1	1056.3	1086.0	1118.8
37.5°	818.8	831.3	840.7	853.2	871.9	892.3	923.5	953.2	1003.2	1028.2	1065.7
40°	771.9	782.9	793.8	807.9	825.1	850.1	868.8	906.3	947.0	975.1	1003.2
42.5°	726.6	732.9	745.4	761.0	778.2	800.1	826.6	856.3	896.9	921.9	947.0
45°	678.2	689.1	703.2	714.1	729.7	751.6	775.1	801.6	842.3	867.3	893.8
47.5°	632.9	640.7	650.1	667.2	687.6	703.2	728.2	753.2	790.7	814.1	839.1
50°	586.0	593.8	607.9	618.8	634.4	654.7	678.2	704.7	740.7	756.3	781.3
52.5°	542.2	545.4	559.4	570.4	586.0	609.4	628.2	651.6	686.0	703.2	728.2
55°	498.5	501.6	509.4	520.4	537.5	556.3	576.6	603.2	632.9	648.5	671.9
57.5°	453.2	456.3	464.1	471.9	489.1	506.3	529.7	551.6	581.3	595.4	617.2
60°	407.8	407.8	415.7	426.6	439.1	454.7	475.0	501.6	523.5	540.7	556.3
62.5°	359.4	364.1	368.8	376.6	390.7	409.4	426.6	445.3	471.9	484.4	498.5
65°	311.0	315.7	325.0	332.8	343.8	356.3	378.2	393.8	414.1	428.2	440.7
67.5°	268.8	273.5	279.7	289.1	296.9	311.0	326.6	342.2	364.1	373.5	382.8
70°	225.0	229.7	234.4	246.9	254.7	265.6	276.6	292.2	311.0	317.2	325.0
72.5°	190.6	192.2	198.5	201.6	212.5	221.9	234.4	243.8	257.8	265.6	271.9
75°	161.0	161.0	162.5	165.6	171.9	178.1	187.5	196.9	209.4	214.1	221.9
77.5°	126.6	131.3	129.7	132.8	135.9	139.1	146.9	153.1	165.6	168.8	171.9
80°	90.6	92.2	96.9	101.6	101.6	106.3	110.9	112.5	120.3	125.0	125.0
82.5°	65.6	67.2	65.6	67.2	68.8	70.3	75.0	81.3	81.3	82.8	85.9
85°	40.6	40.6	42.2	43.8	43.8	42.2	45.3	43.8	45.3	48.4	48.4
87.5°	20.3	18.8	18.8	18.8	18.8	18.8	20.3	18.8	20.3	20.3	20.3
90°	7.1	6.8	6.4	6.0	5.7	5.0	4.6	3.9	3.6	3.2	2.8
92.5°	41.2	55.5	77.1	114.5	141.8	144.3	100.2	59.7	35.5	29.2	22.8
95°	157.8	201.6	255.6	308.2	314.9	257.0	158.9	80.7	42.7	34.7	26.7
97.5°	279.4	323.5	366.5	385.0	340.2	235.7	129.7	69.7	43.4	37.5	31.6
100°	383.2	419.8	437.2	409.9	321.0	204.8	115.2	69.0	48.3	43.0	37.7
102.5°	466.0	478.8	461.0	394.9	287.2	181.3	109.1	72.2	54.4	49.2	44.1
105°	509.4	493.8	445.1	359.7	257.7	167.8	108.4	76.8	61.1	56.2	51.2
107.5°	514.4	476.7	412.3	326.3	235.7	160.7	110.9	83.2	67.9	63.4	59.0
110°	493.0	442.9	375.4	298.6	221.1	157.8	114.8	90.3	75.7	71.1	66.5

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	460.3	409.5	346.2	278.0	212.6	157.8	119.8	97.0	83.2	78.8	74.3
115°	426.6	377.9	322.8	264.1	206.9	158.9	124.8	104.2	91.0	86.6	82.1
117.5°	397.8	355.1	306.4	254.9	203.7	160.7	130.5	111.3	98.8	94.6	90.3
120°	375.4	336.3	293.6	247.4	201.6	163.5	136.1	119.1	106.6	102.2	97.8
122.5°	356.5	322.8	284.0	241.0	199.8	166.0	142.5	126.5	114.1	109.6	105.2
125°	342.0	311.0	274.8	235.3	198.4	168.9	148.2	132.9	121.2	116.6	112.0
127.5°	328.8	299.7	265.2	230.0	197.6	172.0	153.6	139.3	128.0	123.4	118.7
130°	315.3	287.6	256.3	224.7	196.9	174.9	158.9	145.4	134.4	129.8	125.1
132.5°	300.7	276.2	247.4	220.4	196.9	178.1	163.5	151.1	140.1	135.4	130.8
135°	287.2	264.5	239.9	217.2	196.9	180.9	167.8	156.1	145.0	140.2	135.4
137.5°	273.4	253.8	233.2	214.0	197.3	183.8	171.0	159.6	149.7	144.7	139.7
140°	260.9	244.6	227.9	211.9	197.6	185.6	174.2	163.5	153.2	148.4	143.6
142.5°	250.3	236.7	223.2	210.1	198.0	186.6	176.0	166.0	156.4	152.0	147.5
145°	241.4	230.3	219.3	208.3	197.6	187.3	177.7	168.9	159.6	155.5	151.4
147.5°	233.5	224.7	215.4	206.5	196.9	187.7	178.8	170.6	162.5	158.8	155.0
150°	226.8	220.0	212.2	204.4	195.9	187.7	179.9	172.4	164.6	161.6	158.5
152.5°	221.5	215.4	208.7	201.9	194.4	187.3	180.6	174.2	167.1	164.4	161.7
155°	215.8	210.8	205.1	199.1	192.7	186.6	180.9	175.2	169.2	166.7	164.2
157.5°	210.4	206.5	201.6	196.6	190.9	185.9	181.3	176.3	171.0	169.0	167.1
160°	205.1	201.6	198.0	193.4	189.1	184.8	181.3	177.0	172.4	170.8	169.2
162.5°	200.1	197.3	194.1	190.5	187.0	183.8	180.9	177.7	173.8	172.6	171.3
165°	195.2	193.0	190.5	187.7	184.8	182.7	180.6	177.7	174.9	173.9	172.8
167.5°	190.5	188.8	187.0	184.8	182.7	180.9	179.9	177.7	175.2	174.5	173.8
170°	186.3	185.2	184.1	182.4	180.9	179.9	179.2	177.7	176.0	175.4	174.9
172.5°	182.7	182.0	180.9	179.9	178.8	178.4	178.4	177.4	176.0	175.8	175.6
175°	179.5	178.8	178.8	177.7	177.4	177.4	177.7	177.0	176.0	176.0	176.0
177.5°	177.4	177.4	177.0	176.7	176.3	176.3	177.0	176.7	176.0	176.0	176.0
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1903.3	1903.3	1903.3	1903.3
2.5°	1859.5	1873.6	1887.7	1904.8
5°	1822.0	1847.0	1873.6	1898.6
7.5°	1781.4	1817.3	1851.7	1887.7
10°	1736.1	1781.4	1820.5	1870.5
12.5°	1686.1	1734.5	1789.2	1845.5
15°	1636.1	1697.0	1754.8	1818.9
17.5°	1589.2	1647.0	1711.1	1787.6
20°	1532.9	1597.0	1668.9	1750.1
22.5°	1473.6	1543.9	1622.0	1709.5
25°	1423.6	1495.4	1570.4	1662.6
27.5°	1368.9	1443.9	1517.3	1615.8
30°	1306.4	1387.6	1462.6	1564.2
32.5°	1247.0	1328.2	1411.1	1506.4
35°	1189.2	1268.9	1351.7	1448.6
37.5°	1134.5	1206.3	1287.6	1375.1
40°	1082.9	1148.5	1220.4	1300.1
42.5°	1017.3	1093.8	1161.0	1218.8
45°	961.0	1023.5	1086.0	1132.9
47.5°	895.4	957.9	1011.0	1048.5
50°	840.7	890.7	934.4	967.3
52.5°	775.1	821.9	857.9	882.9
55°	711.0	751.6	782.9	800.1
57.5°	653.2	679.7	703.2	718.8
60°	589.1	609.4	629.7	646.9
62.5°	520.4	542.2	553.2	571.9
65°	459.4	473.5	490.7	496.9
67.5°	400.0	407.8	418.8	431.3
70°	337.5	342.2	353.2	370.3
72.5°	282.8	287.5	295.3	301.6
75°	225.0	229.7	236.0	242.2
77.5°	176.6	178.1	181.3	187.5
80°	128.1	132.8	135.9	137.5
82.5°	89.1	90.6	90.6	92.2
85°	56.3	53.1	53.1	54.7
87.5°	20.3	23.4	23.4	26.6
90°	2.1	1.4	0.7	0.4
92.5°	15.3	10.0	6.4	5.3
95°	18.8	14.9	12.1	11.7
97.5°	24.5	20.6	18.5	18.1
100°	30.9	27.0	25.6	24.9
102.5°	38.0	33.8	32.7	32.3
105°	45.5	41.9	40.2	40.2
107.5°	53.0	50.1	48.3	47.6
110°	61.1	57.9	56.5	55.8

TEST NUMBER: P1028630

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	69.0	65.8	64.7	64.0
115°	76.8	73.6	72.5	71.8
117.5°	84.2	81.0	80.0	78.9
120°	91.7	88.5	87.1	86.0
122.5°	98.5	95.3	94.2	93.5
125°	105.2	102.0	100.2	99.5
127.5°	111.6	107.7	105.6	104.5
130°	117.7	113.0	110.2	109.1
132.5°	123.0	117.7	114.1	112.7
135°	128.0	122.3	118.0	116.6
137.5°	132.2	126.5	122.6	121.6
140°	136.9	131.2	126.9	125.8
142.5°	141.1	135.4	131.5	130.8
145°	145.0	140.1	136.5	135.8
147.5°	149.3	144.7	141.5	141.1
150°	153.6	148.9	146.5	145.7
152.5°	157.1	153.2	151.1	150.7
155°	160.7	157.1	155.0	155.0
157.5°	163.9	160.7	158.9	158.9
160°	166.4	163.9	162.5	162.8
162.5°	169.2	167.1	165.7	166.0
165°	171.3	169.6	168.5	169.2
167.5°	172.8	171.7	171.0	171.3
170°	174.2	173.5	173.1	173.5
172.5°	175.2	174.5	174.2	174.9
175°	176.0	175.6	175.2	176.0
177.5°	176.3	176.0	176.0	176.7
180°	176.3	176.3	176.3	176.3

(END OF REPORT)