

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007772

Luminaire Tested: S125IP-B1090UB2750-4F0-XX-W2A-1_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007772
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B1090UB2750-4F0-XX-W2A-1_2700K
Description: Define 5 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3516.0 lumens
Efficiency: N/A
Efficacy: 123.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007772

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A-1_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007772

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A-1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007772

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A-1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.1
90°-100°	83.7	2.4
100°-110°	248.7	7.1
110°-120°	421.8	12.0
120°-130°	555.3	15.8
130°-140°	622.3	17.7
140°-150°	610.0	17.3
150°-160°	512.4	14.6
160°-170°	340.6	9.7
170°-180°	119.2	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.1
90°-120°	754.3	21.5
90°-150°	2541.9	72.3
90°-180°	3514.0	99.9
0°-180°	3516.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	9	16	21	24	4
95°	64	66	75	82	84	67
105°	223	228	234	240	243	238
115°	422	426	428	427	426	418
125°	616	622	623	621	620	552
135°	802	807	808	808	804	618
145°	971	975	978	978	975	607
155°	1111	1111	1112	1116	1111	512
165°	1208	1206	1207	1211	1205	341
175°	1256	1252	1252	1258	1251	119
180°	1259	1259	1259	1259	1259	

TEST NUMBER: P1007772

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	8.8	15.7	20.6	23.5
92.5°	29.4	34.3	43.1	50.0	51.9
95°	63.7	65.6	75.4	82.3	84.3
97.5°	98.0	99.0	112.7	118.6	119.5
100°	137.2	137.2	149.9	158.7	160.7
102.5°	179.3	184.2	189.1	198.9	201.8
105°	223.4	228.3	234.2	240.1	243.0
107.5°	271.4	276.3	281.2	284.2	284.2
110°	321.4	326.3	329.2	332.2	331.2

TEST NUMBER: P1007772

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.3	374.3	378.2	379.2	377.2
115°	422.3	426.2	428.2	427.2	426.2
117.5°	473.3	474.2	476.2	477.2	473.3
120°	520.3	525.2	526.2	526.2	522.3
122.5°	571.2	572.2	575.2	574.2	571.2
125°	616.3	622.2	623.2	621.2	620.2
127.5°	666.3	669.2	670.2	669.2	667.3
130°	710.4	715.3	717.2	716.3	714.3
132.5°	754.5	763.3	762.3	761.3	758.4
135°	801.5	807.4	808.4	808.4	804.5
137.5°	845.6	851.5	853.4	854.4	849.5
140°	887.7	892.6	895.6	897.5	892.6
142.5°	929.9	933.8	937.7	938.7	933.8
145°	971.0	974.9	977.9	977.9	974.9
147.5°	1009.2	1012.2	1014.1	1017.1	1009.2
150°	1047.5	1046.5	1050.4	1050.4	1048.4
152.5°	1078.8	1080.8	1081.7	1084.7	1080.8
155°	1111.1	1111.1	1112.1	1116.0	1111.1
157.5°	1140.5	1138.6	1139.6	1143.5	1136.6
160°	1166.0	1163.1	1164.1	1168.0	1163.1
162.5°	1188.5	1186.6	1186.6	1191.5	1185.6
165°	1208.1	1206.2	1207.2	1211.1	1205.2
167.5°	1225.8	1221.9	1221.9	1227.7	1221.9
170°	1239.5	1235.6	1235.6	1241.5	1234.6
172.5°	1249.3	1245.4	1245.4	1251.3	1245.4
175°	1256.2	1252.2	1252.2	1258.1	1251.3
177.5°	1261.1	1257.1	1256.2	1262.0	1255.2
180°	1259.1	1259.1	1259.1	1259.1	1259.1

(END OF REPORT)