

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007773

Luminaire Tested: S125IP-B1090UB2750-4F0-XX-W2A-1_3000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007773
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B1090UB2750-4F0-XX-W2A-1_3000K
Description: Define 5 Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3547.0 lumens
Efficiency: N/A
Efficacy: 124.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007773

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A-1_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007773

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A-1_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007773

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A-1_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.1
90°-100°	84.5	2.4
100°-110°	250.9	7.1
110°-120°	425.6	12.0
120°-130°	560.2	15.8
130°-140°	627.8	17.7
140°-150°	615.3	17.3
150°-160°	516.9	14.6
160°-170°	343.6	9.7
170°-180°	120.2	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.1
90°-120°	761.0	21.5
90°-150°	2564.3	72.3
90°-180°	3545.0	99.9
0°-180°	3547.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	9	16	21	24	4
95°	64	66	76	83	85	67
105°	225	230	236	242	245	240
115°	426	430	432	431	430	421
125°	622	628	629	627	626	557
135°	809	814	816	816	812	623
145°	980	984	986	986	984	612
155°	1121	1121	1122	1126	1121	516
165°	1219	1217	1218	1222	1216	344
175°	1267	1263	1263	1269	1262	120
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1007773

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	8.9	15.8	20.8	23.7
92.5°	29.7	34.6	43.5	50.4	52.4
95°	64.3	66.2	76.1	83.0	85.0
97.5°	98.8	99.8	113.7	119.6	120.6
100°	138.4	138.4	151.2	160.1	162.1
102.5°	180.9	185.8	190.8	200.7	203.6
105°	225.4	230.3	236.2	242.2	245.1
107.5°	273.8	278.8	283.7	286.7	286.7
110°	324.2	329.2	332.1	335.1	334.1

TEST NUMBER: P1007773

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.6	377.6	381.6	382.5	380.6
115°	426.0	430.0	432.0	431.0	430.0
117.5°	477.4	478.4	480.4	481.4	477.4
120°	524.9	529.8	530.8	530.8	526.9
122.5°	576.3	577.3	580.2	579.3	576.3
125°	621.8	627.7	628.7	626.7	625.7
127.5°	672.2	675.1	676.1	675.1	673.2
130°	716.6	721.6	723.6	722.6	720.6
132.5°	761.1	770.0	769.0	768.1	765.1
135°	808.6	814.5	815.5	815.5	811.5
137.5°	853.1	859.0	861.0	862.0	857.0
140°	895.6	900.5	903.5	905.4	900.5
142.5°	938.1	942.0	946.0	947.0	942.0
145°	979.6	983.5	986.5	986.5	983.5
147.5°	1018.1	1021.1	1023.1	1026.0	1018.1
150°	1056.7	1055.7	1059.7	1059.7	1057.7
152.5°	1088.3	1090.3	1091.3	1094.2	1090.3
155°	1120.9	1120.9	1121.9	1125.9	1120.9
157.5°	1150.6	1148.6	1149.6	1153.6	1146.6
160°	1176.3	1173.3	1174.3	1178.3	1173.3
162.5°	1199.0	1197.1	1197.1	1202.0	1196.1
165°	1218.8	1216.8	1217.8	1221.8	1215.8
167.5°	1236.6	1232.6	1232.6	1238.6	1232.6
170°	1250.4	1246.5	1246.5	1252.4	1245.5
172.5°	1260.3	1256.4	1256.4	1262.3	1256.4
175°	1267.2	1263.3	1263.3	1269.2	1262.3
177.5°	1272.2	1268.2	1267.2	1273.2	1266.2
180°	1270.2	1270.2	1270.2	1270.2	1270.2

(END OF REPORT)