

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028379

Luminaire Tested: S125DIP-B850D850UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028379
REPORT IS A COMBINATION OF REPORTS P1002666 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D850UB27-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6122.0 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028379

CATALOG NUMBER: S125DIP-B850D850UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028379

CATALOG NUMBER: S125DIP-B850D850UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	52
2	90	83	76	71	83	77	71	67	66	62	59	57	54	51	48	45	43
3	82	73	65	59	76	68	61	56	59	53	49	50	46	43	42	39	37
4	75	64	56	50	70	60	53	47	52	46	42	45	40	37	38	34	32
5	69	57	49	43	64	54	46	41	47	41	36	40	35	32	34	30	28
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	24
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8382	8382	8382
5°	8383	8187	8203
10°	8313	7999	7975
15°	8204	7775	7706
20°	8056	7515	7397
25°	7898	7231	7066
30°	7707	6935	6718
35°	7503	6625	6328
40°	7292	6297	5981
45°	7063	5978	5613
50°	6812	5616	5184
55°	6564	5216	4788
60°	6268	4794	4329
65°	5912	4307	3854
70°	5551	3746	3306
75°	4945	3084	2673
80°	4214	2304	1965
85°	3253	1364	1084

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7063 cd/sqm

TEST NUMBER: P1028379

CATALOG NUMBER: S125DIP-B850D850UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.4	2.0
10°-20°	348.7	5.7
20°-30°	514.8	8.4
30°-40°	600.6	9.8
40°-50°	603.2	9.9
50°-60°	529.5	8.6
60°-70°	394.4	6.4
70°-80°	225.2	3.7
80°-90°	66.5	1.1
90°-100°	64.7	1.1
100°-110°	192.2	3.1
110°-120°	326.0	5.3
120°-130°	429.1	7.0
130°-140°	480.9	7.9
140°-150°	471.4	7.7
150°-160°	395.9	6.5
160°-170°	263.2	4.3
170°-180°	92.1	1.5
0°-30°	986.9	16.1
0°-40°	1587.5	25.9
0°-60°	2720.3	44.4
0°-90°	3406.5	55.6
90°-120°	582.9	9.5
90°-150°	1964.3	32.1
90°-180°	2715.0	44.3
0°-180°	6122.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1308	1308	1308	1308	1308	
5°	1306	1304	1294	1303	1302	124
15°	1245	1242	1231	1236	1236	351
25°	1130	1125	1112	1114	1110	520
35°	976	972	957	952	944	611
45°	799	795	782	770	767	616
55°	609	606	591	582	574	543
65°	411	409	397	388	384	408
75°	218	216	211	208	204	232
85°	57	58	58	57	55	62
90°	1	7	12	16	18	7
95°	49	51	58	64	65	51
105°	173	176	181	186	188	184
115°	326	329	331	330	329	323
125°	476	481	482	480	479	427
135°	619	624	625	625	622	477
145°	750	753	756	756	753	469
155°	859	859	859	862	859	396
165°	934	932	933	936	931	263
175°	971	968	968	972	967	92
180°	973	973	973	973	973	

TEST NUMBER: P1028379

CATALOG NUMBER: S125DIP-B850D850UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1308.2	1308.2	1308.2	1308.2	1308.2
2.5°	1312.4	1309.3	1298.9	1309.3	1308.2
5°	1306.2	1304.1	1293.7	1303.1	1302.0
7.5°	1296.8	1294.8	1283.4	1292.7	1291.7
10°	1283.4	1281.3	1269.9	1278.2	1277.2
12.5°	1266.8	1262.7	1252.3	1258.6	1258.6
15°	1245.1	1242.0	1230.6	1235.8	1235.8
17.5°	1222.3	1217.2	1205.8	1212.0	1206.8
20°	1192.3	1190.2	1176.8	1184.0	1178.9
22.5°	1162.3	1158.2	1145.7	1149.9	1146.8
25°	1130.2	1125.0	1111.6	1113.7	1110.5
27.5°	1093.0	1089.8	1076.4	1077.4	1074.3
30°	1056.7	1053.6	1038.1	1036.0	1032.9
32.5°	1017.4	1012.2	998.8	994.6	988.4
35°	976.0	971.9	957.4	952.2	943.9
37.5°	933.6	928.4	914.9	907.7	902.5
40°	890.1	884.9	870.4	861.1	858.0
42.5°	843.5	839.4	824.9	816.6	811.4
45°	799.0	794.9	782.5	770.0	766.9
47.5°	750.4	751.4	735.9	723.5	716.2
50°	703.8	700.7	688.3	674.8	667.6
52.5°	656.2	654.1	640.7	629.3	621.0
55°	608.6	605.5	591.0	581.7	574.4
57.5°	557.9	556.8	544.4	532.0	528.9
60°	510.3	506.1	494.7	484.4	477.1
62.5°	460.6	457.5	448.2	436.8	431.6
65°	410.9	408.8	397.4	388.1	384.0
67.5°	362.2	358.1	349.8	341.5	339.5
70°	316.7	311.5	302.2	296.0	291.9
72.5°	267.0	263.9	258.7	251.5	247.4
75°	218.4	216.3	211.1	208.0	203.9
77.5°	172.8	171.8	168.7	166.6	163.5
80°	130.4	130.4	128.3	127.3	125.2
82.5°	93.1	91.1	91.1	89.0	89.0
85°	56.9	58.0	58.0	56.9	54.9
87.5°	27.9	27.9	26.9	26.9	24.8
90°	0.8	6.8	12.1	15.9	18.2
92.5°	22.7	26.5	33.3	38.6	40.1
95°	49.2	50.7	58.3	63.6	65.1
97.5°	75.7	76.5	87.1	91.6	92.4
100°	106.0	106.0	115.8	122.7	124.2
102.5°	138.6	142.3	146.1	153.7	156.0
105°	172.6	176.4	181.0	185.5	187.8
107.5°	209.7	213.5	217.3	219.6	219.6
110°	248.4	252.1	254.4	256.7	255.9



TEST NUMBER: P1028379

CATALOG NUMBER: S125DIP-B850D850UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	287.7	289.2	292.3	293.0	291.5
115°	326.3	329.4	330.9	330.1	329.4
117.5°	365.7	366.5	368.0	368.7	365.7
120°	402.1	405.8	406.6	406.6	403.6
122.5°	441.4	442.2	444.5	443.7	441.4
125°	476.3	480.8	481.6	480.0	479.3
127.5°	514.9	517.2	517.9	517.2	515.6
130°	549.0	552.7	554.3	553.5	552.0
132.5°	583.0	589.8	589.1	588.3	586.1
135°	619.4	623.9	624.7	624.7	621.6
137.5°	653.4	658.0	659.5	660.3	656.5
140°	686.0	689.8	692.1	693.6	689.8
142.5°	718.6	721.6	724.6	725.4	721.6
145°	750.4	753.4	755.7	755.7	753.4
147.5°	779.9	782.2	783.7	785.9	779.9
150°	809.4	808.7	811.7	811.7	810.2
152.5°	833.7	835.2	835.9	838.2	835.2
155°	858.6	858.6	859.4	862.4	858.6
157.5°	881.4	879.8	880.6	883.6	878.3
160°	901.0	898.8	899.5	902.6	898.8
162.5°	918.5	916.9	916.9	920.7	916.2
165°	933.6	932.1	932.8	935.9	931.3
167.5°	947.2	944.2	944.2	948.7	944.2
170°	957.8	954.8	954.8	959.3	954.0
172.5°	965.4	962.4	962.4	966.9	962.4
175°	970.7	967.7	967.7	972.2	966.9
177.5°	974.5	971.5	970.7	975.2	969.9
180°	973.0	973.0	973.0	973.0	973.0

(END OF REPORT)