

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007784

Luminaire Tested: S125IP-B1090UB2750-4F0-XX-W2A_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007784
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B1090UB2750-4F0-XX-W2A_3500K
Description: Define 5 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4116.0 lumens
Efficiency: N/A
Efficacy: 144.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007784

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007784

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007784

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.0
90°-100°	45.4	1.1
100°-110°	302.3	7.3
110°-120°	544.3	13.2
120°-130°	698.7	17.0
130°-140°	751.4	18.3
140°-150°	705.3	17.1
150°-160°	570.5	13.9
160°-170°	368.9	9.0
170°-180°	127.2	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.0
90°-120°	892.0	21.7
90°-150°	3047.4	74.0
90°-180°	4114.0	100.0
0°-180°	4116.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	9	16	21	24	3
95°	57	54	16	21	21	69
105°	292	296	296	296	295	309
115°	548	553	554	550	544	543
125°	779	786	786	782	779	696
135°	972	978	976	974	968	749
145°	1127	1129	1129	1130	1124	705
155°	1241	1235	1237	1240	1232	572
165°	1310	1304	1304	1310	1303	370
175°	1339	1333	1334	1342	1333	128
180°	1339	1339	1339	1339	1339	

TEST NUMBER: P1007784

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	8.9	15.9	20.8	23.8
92.5°	18.9	9.9	15.9	20.8	21.8
95°	56.6	53.6	15.9	20.8	20.8
97.5°	106.2	112.2	17.9	19.9	20.8
100°	165.8	168.8	172.7	24.8	20.8
102.5°	226.4	230.3	232.3	234.3	150.9
105°	291.9	295.9	295.9	295.9	294.9
107.5°	359.4	359.4	361.4	362.4	358.4
110°	424.9	424.9	426.9	423.9	424.9

TEST NUMBER: P1007784

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	486.5	489.5	490.4	486.5	484.5
115°	548.0	553.0	554.0	550.0	544.1
117.5°	612.6	612.6	616.5	610.6	608.6
120°	672.1	671.1	674.1	672.1	667.2
122.5°	724.7	729.7	730.7	728.7	722.8
125°	779.3	786.3	786.3	782.3	779.3
127.5°	832.0	836.9	835.9	834.0	826.0
130°	879.6	884.6	885.6	882.6	877.6
132.5°	927.3	933.2	930.3	930.3	925.3
135°	972.0	977.9	975.9	973.9	968.0
137.5°	1013.7	1019.6	1017.6	1017.6	1012.7
140°	1054.4	1056.3	1055.3	1057.3	1051.4
142.5°	1091.1	1092.1	1094.1	1094.1	1088.1
145°	1126.8	1128.8	1128.8	1129.8	1123.9
147.5°	1158.6	1158.6	1159.6	1160.6	1153.6
150°	1188.4	1186.4	1188.4	1190.4	1182.4
152.5°	1217.2	1212.2	1214.2	1216.2	1209.2
155°	1241.0	1235.0	1237.0	1240.0	1232.1
157.5°	1259.9	1256.9	1256.9	1259.9	1251.9
160°	1279.7	1273.8	1274.8	1278.7	1270.8
162.5°	1295.6	1289.6	1290.6	1296.6	1287.7
165°	1309.5	1303.5	1304.5	1310.5	1302.6
167.5°	1320.4	1314.5	1315.5	1322.4	1313.5
170°	1329.4	1322.4	1323.4	1331.3	1322.4
172.5°	1335.3	1328.4	1330.4	1337.3	1328.4
175°	1339.3	1333.3	1334.3	1342.3	1333.3
177.5°	1342.3	1336.3	1337.3	1344.3	1336.3
180°	1339.3	1339.3	1339.3	1339.3	1339.3

(END OF REPORT)