

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007804

Luminaire Tested: S125IP-B1270UB2750-4F0-XX-W2A-1_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007804
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B1270UB2750-4F0-XX-W2A-1_3500K
Description: Define 5 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4185.0 lumens
Efficiency: N/A
Efficacy: 119.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007804

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007804

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007804

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.3	0.1
90°-100°	99.7	2.4
100°-110°	296.1	7.1
110°-120°	502.1	12.0
120°-130°	661.0	15.8
130°-140°	740.7	17.7
140°-150°	726.0	17.3
150°-160°	609.8	14.6
160°-170°	405.4	9.7
170°-180°	141.9	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.3	0.1
90°-120°	897.8	21.5
90°-150°	3025.6	72.3
90°-180°	4183.0	100.0
0°-180°	4185.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	10	19	24	28	5
95°	76	78	90	98	100	79
105°	266	272	279	286	289	284
115°	503	507	510	508	507	497
125°	734	741	742	739	738	657
135°	954	961	962	962	958	735
145°	1156	1160	1164	1164	1160	723
155°	1323	1323	1324	1328	1323	609
165°	1438	1436	1437	1442	1434	406
175°	1495	1490	1490	1498	1489	142
180°	1499	1499	1499	1499	1499	

TEST NUMBER: P1007804

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.2	10.5	18.7	24.5	28.0
92.5°	35.0	40.8	51.3	59.5	61.8
95°	75.8	78.1	89.8	98.0	100.3
97.5°	116.6	117.8	134.1	141.1	142.3
100°	163.3	163.3	178.4	188.9	191.3
102.5°	213.4	219.3	225.1	236.8	240.3
105°	265.9	271.7	278.7	285.7	289.2
107.5°	323.1	328.9	334.7	338.2	338.2
110°	382.5	388.4	391.9	395.4	394.2

TEST NUMBER: P1007804

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.2	445.5	450.2	451.4	449.0
115°	502.7	507.3	509.7	508.5	507.3
117.5°	563.3	564.5	566.8	568.0	563.3
120°	619.3	625.1	626.3	626.3	621.6
122.5°	679.9	681.1	684.6	683.4	679.9
125°	733.6	740.6	741.8	739.4	738.3
127.5°	793.1	796.6	797.7	796.6	794.2
130°	845.6	851.4	853.7	852.6	850.2
132.5°	898.0	908.5	907.4	906.2	902.7
135°	954.0	961.0	962.2	962.2	957.5
137.5°	1006.5	1013.5	1015.8	1017.0	1011.2
140°	1056.6	1062.5	1066.0	1068.3	1062.5
142.5°	1106.8	1111.5	1116.1	1117.3	1111.5
145°	1155.8	1160.4	1163.9	1163.9	1160.4
147.5°	1201.3	1204.8	1207.1	1210.6	1201.3
150°	1246.8	1245.6	1250.3	1250.3	1247.9
152.5°	1284.1	1286.4	1287.6	1291.1	1286.4
155°	1322.6	1322.6	1323.7	1328.4	1322.6
157.5°	1357.6	1355.2	1356.4	1361.0	1352.9
160°	1387.9	1384.4	1385.5	1390.2	1384.4
162.5°	1414.7	1412.4	1412.4	1418.2	1411.2
165°	1438.0	1435.7	1436.9	1441.5	1434.5
167.5°	1459.0	1454.4	1454.4	1461.3	1454.4
170°	1475.3	1470.7	1470.7	1477.7	1469.5
172.5°	1487.0	1482.3	1482.3	1489.3	1482.3
175°	1495.2	1490.5	1490.5	1497.5	1489.3
177.5°	1501.0	1496.3	1495.2	1502.2	1494.0
180°	1498.7	1498.7	1498.7	1498.7	1498.7

(END OF REPORT)