

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007805

Luminaire Tested: S125IP-B1270UB2750-4F0-XX-W2A-1_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007805
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B1270UB2750-4F0-XX-W2A-1_4000K
Description: Define 5 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4143.0 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007805

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007805

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007805

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.3	0.1
90°-100°	98.7	2.4
100°-110°	293.1	7.1
110°-120°	497.1	12.0
120°-130°	654.4	15.8
130°-140°	733.3	17.7
140°-150°	718.7	17.3
150°-160°	603.7	14.6
160°-170°	401.3	9.7
170°-180°	140.4	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.3	0.1
90°-120°	888.8	21.5
90°-150°	2995.2	72.3
90°-180°	4141.0	100.0
0°-180°	4143.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	10	18	24	28	5
95°	75	77	89	97	99	78
105°	263	269	276	283	286	281
115°	498	502	504	503	502	492
125°	726	733	734	732	731	651
135°	944	951	952	952	948	728
145°	1144	1149	1152	1152	1149	715
155°	1309	1309	1310	1315	1309	603
165°	1424	1421	1422	1427	1420	402
175°	1480	1476	1476	1482	1474	141
180°	1484	1484	1484	1484	1484	

TEST NUMBER: P1007805

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.2	10.4	18.5	24.2	27.7
92.5°	34.6	40.4	50.8	58.9	61.2
95°	75.0	77.4	88.9	97.0	99.3
97.5°	115.5	116.6	132.8	139.7	140.9
100°	161.6	161.6	176.7	187.0	189.4
102.5°	211.3	217.1	222.8	234.4	237.8
105°	263.2	269.0	275.9	282.9	286.3
107.5°	319.8	325.6	331.4	334.8	334.8
110°	378.7	384.5	387.9	391.4	390.2

TEST NUMBER: P1007805

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	438.7	441.0	445.7	446.8	444.5
115°	497.6	502.2	504.5	503.4	502.2
117.5°	557.7	558.8	561.1	562.3	557.7
120°	613.1	618.9	620.0	620.0	615.4
122.5°	673.1	674.3	677.7	676.6	673.1
125°	726.2	733.2	734.3	732.0	730.8
127.5°	785.1	788.6	789.7	788.6	786.3
130°	837.1	842.8	845.1	844.0	841.7
132.5°	889.0	899.4	898.3	897.1	893.6
135°	944.4	951.4	952.5	952.5	947.9
137.5°	996.4	1003.3	1005.6	1006.8	1001.0
140°	1046.0	1051.8	1055.3	1057.6	1051.8
142.5°	1095.7	1100.3	1104.9	1106.1	1100.3
145°	1144.2	1148.8	1152.3	1152.3	1148.8
147.5°	1189.2	1192.7	1195.0	1198.4	1189.2
150°	1234.2	1233.1	1237.7	1237.7	1235.4
152.5°	1271.2	1273.5	1274.7	1278.1	1273.5
155°	1309.3	1309.3	1310.4	1315.1	1309.3
157.5°	1343.9	1341.6	1342.8	1347.4	1339.3
160°	1373.9	1370.5	1371.6	1376.3	1370.5
162.5°	1400.5	1398.2	1398.2	1404.0	1397.0
165°	1423.6	1421.3	1422.4	1427.1	1420.1
167.5°	1444.4	1439.8	1439.8	1446.7	1439.8
170°	1460.5	1455.9	1455.9	1462.8	1454.8
172.5°	1472.1	1467.5	1467.5	1474.4	1467.5
175°	1480.2	1475.5	1475.5	1482.5	1474.4
177.5°	1485.9	1481.3	1480.2	1487.1	1479.0
180°	1483.6	1483.6	1483.6	1483.6	1483.6

(END OF REPORT)