

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007806

Luminaire Tested: S125IP-B1270UB2750-4F0-XX-W2A-1_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B1270UB2750-4F0-XX-W2A-1_5000K
Description: Define 5 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4007.0 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007806

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007806

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007806

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.2	0.1
90°-100°	95.4	2.4
100°-110°	283.5	7.1
110°-120°	480.8	12.0
120°-130°	632.9	15.8
130°-140°	709.2	17.7
140°-150°	695.1	17.3
150°-160°	583.9	14.6
160°-170°	388.1	9.7
170°-180°	135.8	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.2	0.1
90°-120°	859.7	21.5
90°-150°	2896.9	72.3
90°-180°	4005.0	99.9
0°-180°	4007.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	10	18	24	27	5
95°	73	75	86	94	96	76
105°	255	260	267	274	277	271
115°	481	486	488	487	486	476
125°	702	709	710	708	707	629
135°	913	920	921	921	917	704
145°	1107	1111	1114	1114	1111	692
155°	1266	1266	1267	1272	1266	583
165°	1377	1375	1376	1380	1374	388
175°	1432	1427	1427	1434	1426	136
180°	1435	1435	1435	1435	1435	

TEST NUMBER: P1007806

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.1	10.1	17.9	23.5	26.8
92.5°	33.5	39.1	49.1	57.0	59.2
95°	72.6	74.8	86.0	93.8	96.0
97.5°	111.7	112.8	128.4	135.1	136.2
100°	156.3	156.3	170.9	180.9	183.1
102.5°	204.4	209.9	215.5	226.7	230.0
105°	254.6	260.2	266.9	273.6	276.9
107.5°	309.3	314.9	320.5	323.8	323.8
110°	366.3	371.9	375.2	378.6	377.4

TEST NUMBER: P1007806

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	424.3	426.6	431.0	432.2	429.9
115°	481.3	485.8	488.0	486.9	485.8
117.5°	539.4	540.5	542.7	543.8	539.4
120°	593.0	598.5	599.7	599.7	595.2
122.5°	651.0	652.1	655.5	654.4	651.0
125°	702.4	709.1	710.2	708.0	706.9
127.5°	759.3	762.7	763.8	762.7	760.5
130°	809.6	815.2	817.4	816.3	814.1
132.5°	859.8	869.9	868.8	867.7	864.3
135°	913.4	920.1	921.3	921.3	916.8
137.5°	963.7	970.4	972.6	973.7	968.2
140°	1011.7	1017.3	1020.6	1022.9	1017.3
142.5°	1059.7	1064.2	1068.7	1069.8	1064.2
145°	1106.6	1111.1	1114.4	1114.4	1111.1
147.5°	1150.2	1153.5	1155.8	1159.1	1150.2
150°	1193.7	1192.6	1197.1	1197.1	1194.8
152.5°	1229.5	1231.7	1232.8	1236.2	1231.7
155°	1266.3	1266.3	1267.4	1271.9	1266.3
157.5°	1299.8	1297.6	1298.7	1303.2	1295.3
160°	1328.8	1325.5	1326.6	1331.1	1325.5
162.5°	1354.5	1352.3	1352.3	1357.9	1351.2
165°	1376.9	1374.6	1375.7	1380.2	1373.5
167.5°	1397.0	1392.5	1392.5	1399.2	1392.5
170°	1412.6	1408.1	1408.1	1414.8	1407.0
172.5°	1423.8	1419.3	1419.3	1426.0	1419.3
175°	1431.6	1427.1	1427.1	1433.8	1426.0
177.5°	1437.2	1432.7	1431.6	1438.3	1430.5
180°	1434.9	1434.9	1434.9	1434.9	1434.9

(END OF REPORT)