

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007815

Luminaire Tested: S125IP-B1270UB2750-4F0-XX-W2A_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007815
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B1270UB2750-4F0-XX-W2A_4000K
Description: Define 5 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4788.0 lumens
Efficiency: N/A
Efficacy: 136.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007815

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007815

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007815

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.3	0.0
90°-100°	52.9	1.1
100°-110°	351.6	7.3
110°-120°	633.2	13.2
120°-130°	812.7	17.0
130°-140°	874.1	18.3
140°-150°	820.4	17.1
150°-160°	663.6	13.9
160°-170°	429.2	9.0
170°-180°	148.0	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.3	0.0
90°-120°	1037.7	21.7
90°-150°	3544.9	74.0
90°-180°	4786.0	100.0
0°-180°	4788.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	10	18	24	28	3
95°	66	62	18	24	24	81
105°	340	344	344	344	343	360
115°	638	643	644	640	633	632
125°	907	915	915	910	907	810
135°	1131	1138	1135	1133	1126	872
145°	1311	1313	1313	1314	1307	820
155°	1444	1437	1439	1442	1433	665
165°	1523	1516	1518	1524	1515	430
175°	1558	1551	1552	1561	1551	148
180°	1558	1558	1558	1558	1558	

TEST NUMBER: P1007815

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.2	10.4	18.5	24.3	27.7
92.5°	21.9	11.5	18.5	24.3	25.4
95°	65.8	62.4	18.5	24.3	24.3
97.5°	123.6	130.5	20.8	23.1	24.3
100°	192.9	196.3	201.0	28.9	24.3
102.5°	263.3	267.9	270.2	272.6	175.5
105°	339.5	344.2	344.2	344.2	343.0
107.5°	418.1	418.1	420.4	421.5	416.9
110°	494.3	494.3	496.6	493.1	494.3

TEST NUMBER: P1007815

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	565.9	569.4	570.5	565.9	563.6
115°	637.5	643.3	644.4	639.8	632.9
117.5°	712.6	712.6	717.2	710.3	707.9
120°	781.9	780.7	784.2	781.9	776.1
122.5°	843.1	848.8	850.0	847.7	840.8
125°	906.6	914.7	914.7	910.1	906.6
127.5°	967.8	973.6	972.4	970.1	960.9
130°	1023.2	1029.0	1030.2	1026.7	1020.9
132.5°	1078.7	1085.6	1082.1	1082.1	1076.4
135°	1130.6	1137.6	1135.3	1132.9	1126.0
137.5°	1179.1	1186.1	1183.8	1183.8	1178.0
140°	1226.5	1228.8	1227.6	1230.0	1223.0
142.5°	1269.2	1270.4	1272.7	1272.7	1265.8
145°	1310.8	1313.1	1313.1	1314.3	1307.3
147.5°	1347.8	1347.8	1348.9	1350.1	1342.0
150°	1382.4	1380.1	1382.4	1384.7	1375.5
152.5°	1415.9	1410.1	1412.4	1414.7	1406.7
155°	1443.6	1436.7	1439.0	1442.5	1433.2
157.5°	1465.6	1462.1	1462.1	1465.6	1456.3
160°	1488.7	1481.7	1482.9	1487.5	1478.3
162.5°	1507.1	1500.2	1501.4	1508.3	1497.9
165°	1523.3	1516.4	1517.5	1524.5	1515.2
167.5°	1536.0	1529.1	1530.2	1538.3	1527.9
170°	1546.4	1538.3	1539.5	1548.7	1538.3
172.5°	1553.3	1545.2	1547.6	1555.6	1545.2
175°	1557.9	1551.0	1552.2	1561.4	1551.0
177.5°	1561.4	1554.5	1555.6	1563.7	1554.5
180°	1557.9	1557.9	1557.9	1557.9	1557.9

(END OF REPORT)