

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007816

Luminaire Tested: S125IP-B1270UB2750-4F0-XX-W2A_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007816
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B1270UB2750-4F0-XX-W2A_5000K
Description: Define 5 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4630.0 lumens
Efficiency: N/A
Efficacy: 132.3 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007816

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007816

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007816

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.2	0.0
90°-100°	51.2	1.1
100°-110°	340.0	7.3
110°-120°	612.3	13.2
120°-130°	785.9	17.0
130°-140°	845.3	18.3
140°-150°	793.3	17.1
150°-160°	641.7	13.9
160°-170°	415.0	9.0
170°-180°	143.1	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.2	0.0
90°-120°	1003.5	21.7
90°-150°	3428.0	74.0
90°-180°	4628.0	100.0
0°-180°	4630.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	10	18	24	27	3
95°	64	60	18	24	24	78
105°	328	333	333	333	332	348
115°	616	622	623	619	612	611
125°	877	884	884	880	877	783
135°	1093	1100	1098	1096	1089	843
145°	1268	1270	1270	1271	1264	793
155°	1396	1389	1392	1395	1386	643
165°	1473	1466	1468	1474	1465	416
175°	1506	1500	1501	1510	1500	143
180°	1506	1506	1506	1506	1506	

TEST NUMBER: P1007816

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.1	10.1	17.9	23.5	26.8
92.5°	21.2	11.2	17.9	23.5	24.6
95°	63.7	60.3	17.9	23.5	23.5
97.5°	119.5	126.2	20.1	22.3	23.5
100°	186.5	189.9	194.3	27.9	23.5
102.5°	254.6	259.1	261.3	263.6	169.8
105°	328.3	332.8	332.8	332.8	331.7
107.5°	404.3	404.3	406.5	407.6	403.2
110°	478.0	478.0	480.2	476.9	478.0

TEST NUMBER: P1007816

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	547.2	550.6	551.7	547.2	545.0
115°	616.5	622.0	623.2	618.7	612.0
117.5°	689.1	689.1	693.5	686.8	684.6
120°	756.1	754.9	758.3	756.1	750.5
122.5°	815.3	820.8	822.0	819.7	813.0
125°	876.7	884.5	884.5	880.0	876.7
127.5°	935.9	941.4	940.3	938.1	929.2
130°	989.5	995.1	996.2	992.8	987.2
132.5°	1043.1	1049.8	1046.4	1046.4	1040.8
135°	1093.3	1100.0	1097.8	1095.6	1088.9
137.5°	1140.2	1146.9	1144.7	1144.7	1139.1
140°	1186.0	1188.3	1187.1	1189.4	1182.7
142.5°	1227.3	1228.5	1230.7	1230.7	1224.0
145°	1267.5	1269.8	1269.8	1270.9	1264.2
147.5°	1303.3	1303.3	1304.4	1305.5	1297.7
150°	1336.8	1334.6	1336.8	1339.0	1330.1
152.5°	1369.2	1363.6	1365.8	1368.1	1360.2
155°	1396.0	1389.3	1391.5	1394.9	1385.9
157.5°	1417.2	1413.8	1413.8	1417.2	1408.3
160°	1439.5	1432.8	1433.9	1438.4	1429.5
162.5°	1457.4	1450.7	1451.8	1458.5	1448.5
165°	1473.0	1466.3	1467.5	1474.2	1465.2
167.5°	1485.3	1478.6	1479.7	1487.6	1477.5
170°	1495.4	1487.6	1488.7	1497.6	1487.6
172.5°	1502.1	1494.3	1496.5	1504.3	1494.3
175°	1506.5	1499.8	1501.0	1509.9	1499.8
177.5°	1509.9	1503.2	1504.3	1512.1	1503.2
180°	1506.5	1506.5	1506.5	1506.5	1506.5

(END OF REPORT)