

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007832

Luminaire Tested: S125IP-B375UB2750-4F0-XX-W2A-1_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007832
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B375UB2750-4F0-XX-W2A-1_2700K
Description: Define 5 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1265.0 lumens
Efficiency: N/A
Efficacy: 136.0 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 9.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007832

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A-1_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007832

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A-1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007832

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A-1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.7	0.1
90°-100°	30.1	2.4
100°-110°	89.5	7.1
110°-120°	151.8	12.0
120°-130°	199.8	15.8
130°-140°	223.9	17.7
140°-150°	219.5	17.3
150°-160°	184.3	14.6
160°-170°	122.5	9.7
170°-180°	42.9	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.7	0.1
90°-120°	271.4	21.5
90°-150°	914.6	72.3
90°-180°	1264.0	99.9
0°-180°	1265.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	3	6	7	8	2
95°	23	24	27	30	30	24
105°	80	82	84	86	87	86
115°	152	153	154	154	153	150
125°	222	224	224	224	223	199
135°	288	290	291	291	289	222
145°	349	351	352	352	351	218
155°	400	400	400	402	400	184
165°	435	434	434	436	434	123
175°	452	450	450	453	450	43
180°	453	453	453	453	453	

TEST NUMBER: P1007832

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.4	3.2	5.6	7.4	8.5
92.5°	10.6	12.3	15.5	18.0	18.7
95°	22.9	23.6	27.1	29.6	30.3
97.5°	35.3	35.6	40.5	42.7	43.0
100°	49.4	49.4	53.9	57.1	57.8
102.5°	64.5	66.3	68.0	71.6	72.6
105°	80.4	82.1	84.3	86.4	87.4
107.5°	97.7	99.4	101.2	102.2	102.2
110°	115.6	117.4	118.5	119.5	119.2

TEST NUMBER: P1007832

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	134.0	134.7	136.1	136.4	135.7
115°	151.9	153.4	154.1	153.7	153.4
117.5°	170.3	170.6	171.3	171.7	170.3
120°	187.2	189.0	189.3	189.3	187.9
122.5°	205.5	205.9	206.9	206.6	205.5
125°	221.7	223.9	224.2	223.5	223.2
127.5°	239.7	240.8	241.1	240.8	240.1
130°	255.6	257.3	258.1	257.7	257.0
132.5°	271.4	274.6	274.3	273.9	272.9
135°	288.4	290.5	290.8	290.8	289.4
137.5°	304.2	306.3	307.1	307.4	305.6
140°	319.4	321.2	322.2	322.9	321.2
142.5°	334.6	336.0	337.4	337.7	336.0
145°	349.4	350.8	351.8	351.8	350.8
147.5°	363.1	364.2	364.9	365.9	363.1
150°	376.9	376.5	377.9	377.9	377.2
152.5°	388.1	388.8	389.2	390.3	388.8
155°	399.8	399.8	400.1	401.5	399.8
157.5°	410.3	409.6	410.0	411.4	408.9
160°	419.5	418.5	418.8	420.2	418.5
162.5°	427.6	426.9	426.9	428.7	426.6
165°	434.7	434.0	434.3	435.7	433.6
167.5°	441.0	439.6	439.6	441.7	439.6
170°	446.0	444.5	444.5	446.7	444.2
172.5°	449.5	448.1	448.1	450.2	448.1
175°	451.9	450.5	450.5	452.7	450.2
177.5°	453.7	452.3	451.9	454.1	451.6
180°	453.0	453.0	453.0	453.0	453.0

(END OF REPORT)