

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007833

Luminaire Tested: S125IP-B375UB2750-4F0-XX-W2A-1_3000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007833
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B375UB2750-4F0-XX-W2A-1_3000K
Description: Define 5 Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1276.0 lumens
Efficiency: N/A
Efficacy: 137.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 9.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007833

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A-1_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007833

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A-1_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007833

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A-1_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.7	0.1
90°-100°	30.4	2.4
100°-110°	90.3	7.1
110°-120°	153.1	12.0
120°-130°	201.5	15.8
130°-140°	225.8	17.7
140°-150°	221.4	17.3
150°-160°	185.9	14.6
160°-170°	123.6	9.7
170°-180°	43.3	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.7	0.1
90°-120°	273.8	21.5
90°-150°	922.5	72.3
90°-180°	1275.0	99.9
0°-180°	1276.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	3	6	8	8	2
95°	23	24	27	30	31	24
105°	81	83	85	87	88	86
115°	153	155	155	155	155	152
125°	224	226	226	225	225	200
135°	291	293	293	293	292	224
145°	352	354	355	355	354	220
155°	403	403	404	405	403	186
165°	438	438	438	440	437	124
175°	456	454	454	457	454	43
180°	457	457	457	457	457	

TEST NUMBER: P1007833

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.4	3.2	5.7	7.5	8.5
92.5°	10.7	12.4	15.6	18.1	18.8
95°	23.1	23.8	27.4	29.9	30.6
97.5°	35.6	35.9	40.9	43.0	43.4
100°	49.8	49.8	54.4	57.6	58.3
102.5°	65.1	66.9	68.6	72.2	73.3
105°	81.1	82.9	85.0	87.1	88.2
107.5°	98.5	100.3	102.1	103.1	103.1
110°	116.6	118.4	119.5	120.5	120.2

TEST NUMBER: P1007833

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.1	135.8	137.3	137.6	136.9
115°	153.3	154.7	155.4	155.0	154.7
117.5°	171.8	172.1	172.8	173.2	171.8
120°	188.8	190.6	191.0	191.0	189.5
122.5°	207.3	207.7	208.7	208.4	207.3
125°	223.7	225.8	226.2	225.4	225.1
127.5°	241.8	242.9	243.2	242.9	242.2
130°	257.8	259.6	260.3	259.9	259.2
132.5°	273.8	277.0	276.7	276.3	275.2
135°	290.9	293.0	293.4	293.4	291.9
137.5°	306.9	309.0	309.7	310.1	308.3
140°	322.2	323.9	325.0	325.7	323.9
142.5°	337.5	338.9	340.3	340.7	338.9
145°	352.4	353.8	354.9	354.9	353.8
147.5°	366.3	367.3	368.0	369.1	366.3
150°	380.1	379.8	381.2	381.2	380.5
152.5°	391.5	392.2	392.6	393.6	392.2
155°	403.2	403.2	403.6	405.0	403.2
157.5°	413.9	413.2	413.6	415.0	412.5
160°	423.2	422.1	422.4	423.9	422.1
162.5°	431.3	430.6	430.6	432.4	430.3
165°	438.5	437.7	438.1	439.5	437.4
167.5°	444.9	443.4	443.4	445.6	443.4
170°	449.8	448.4	448.4	450.5	448.1
172.5°	453.4	452.0	452.0	454.1	452.0
175°	455.9	454.5	454.5	456.6	454.1
177.5°	457.7	456.2	455.9	458.0	455.5
180°	456.9	456.9	456.9	456.9	456.9

(END OF REPORT)